

**THM WO 33.5/93.1 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

|            |                                                                       |
|------------|-----------------------------------------------------------------------|
| Version    | THM, Conductor and cable markers, 8 - 21.7 mm, 33.5 x 93.1 mm, yellow |
| Order No.  | <a href="#">1774410000</a>                                            |
| Type       | THM WO 33.5/93.1 GE                                                   |
| GTIN (EAN) | 4032248148592                                                         |
| Qty.       | 1 pc(s).                                                              |

## THM WO 33.5/93.1 GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 0.025 mm | Depth (inches)  | 0.001 inch |
| Height     | 33.5 mm  | Height (inches) | 1.319 inch |
| Width      | 93.1 mm  | Width (inches)  | 3.665 inch |
| Net weight | 281 g    |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

## General data

|                                              |                                            |            |
|----------------------------------------------|--------------------------------------------|------------|
| Adhesive                                     | Polyacrylate adhesive                      |            |
| Colour                                       | yellow                                     |            |
| Halogen                                      | No                                         |            |
| Material                                     | Polyester film                             |            |
| Material colour according to resistance code | 4                                          |            |
| Number of markers per combination            | 1 Label reel = Conductor and cable markers |            |
| Number of markers per packaging unit         | Form of supply                             | Label reel |
| Number per roll                              | 500                                        |            |
| Operating temperature range                  | -40... 150 °C                              |            |
| Operating temperature range, max.            | 150 °C                                     |            |
| Operating temperature range, min.            | -40 °C                                     |            |
| Size of labelling field                      | 33.5 x 25 mm                               |            |
| Type of printing                             | neutral                                    |            |
| UL 94 flammability rating                    | V-0                                        |            |
| Version                                      | Self-adhesive                              |            |
| Width                                        | 93.1 mm                                    |            |

## Conductor and cable markers

|                               |                      |                                  |                            |
|-------------------------------|----------------------|----------------------------------|----------------------------|
| Conductor O.D.                | 8 - 21.7 mm          | Conductor O.D., max.             | 21.7 mm                    |
| Conductor O.D., min.          | 8 mm                 | Conductor cross-section, max.    | 400 mm <sup>2</sup>        |
| Conductor cross-section, min. | 0.75 mm <sup>2</sup> | Cross-section for connected wire | 0.75 - 400 mm <sup>2</sup> |
| Halogen                       | No                   | Text field height                | 25 mm                      |
| Text field width              | 33.5 mm              |                                  |                            |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |
| ECLASS 13.0 | 27-28-11-02 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## THM WO 33.5/93.1 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads


|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

### THM WO 33.5/93.1 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



**THM WO 33.5/93.1 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |            |
|------------|----------------------------|------------|
| Type       | RIBBON MM 110/360 SW       | Version    |
| Order No.  | <a href="#">2005070000</a> | Ink ribbon |
| GTIN (EAN) | 4050118390049              |            |
| Qty.       | 1 pc(s).                   |            |