

VPCB PV I+II R M 1000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

'Abbildung ähnlich'

Versatile accessories round off the surge protection range. E.g. the all-purpose measuring device V-TEST, which is used to check the function of pluggable arresters such as VSPC.

General ordering data

Order No.	2665770000
Type	VPCB PV I+II R M 1000
GTIN (EAN)	4050118686265
Qty.	20 pc(s).

VPCB PV I+II R M 1000

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	52.2 mm	Depth (inches)	2.055 inch
Height	61.6 mm	Height (inches)	2.425 inch
Width	17.9 mm	Width (inches)	0.705 inch
Net weight	20 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 - 95% rel. humidity		

General data

Number of poles	1	Protection degree	IP20
Colour	grey		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Photovoltaic technical data

Conditions and requirements	EN 50539-11	Discharge current I_n (8/20 μ s)	20 kA
Lightning test current I_{imp} (10/350 μ s)	6.25 kA	Operating height in the grounded PV system	≤ 4000 m
PV system voltage, max. U_{cpv}	1,500 V	Requirements class	Type I/II
Short-circuit current I_{scpv}	11 kA		

Rated data IEC / EN

Discharge current I_{max} (8/20 μ s) wire-PE	40 kA	Integrated back-up fuse	No
Lightning test current I_{imp} (10/350 μ s)	6.25 kA	Number of poles	1
Signalling contact	250 V / 0.5 A, 48 V CC / 0.5 A	Voltage type	DC

Connection data

Type of connection	Solder connection, when screwed in
--------------------	------------------------------------

Electrical data

Voltage type	DC
--------------	----

Guarantee

Time interval	5 years
---------------	---------

VPCB PV I+II R M 1000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ETIM 10.0	EC000941	ECLASS 9.0	27-13-08-05
ECLASS 9.1	27-13-08-05	ECLASS 10.0	27-13-08-05
ECLASS 11.0	27-13-08-05	ECLASS 12.0	27-17-90-90
ECLASS 13.0	27-17-90-90	ECLASS 14.0	27-17-90-90
ECLASS 15.0	27-17-90-90		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/
ROHS	Conform

Downloads

Engineering Data	CAD data – STEP
User Documentation	Assembly instructions VPCB PV
Catalogues	Catalogues in PDF-format


VPCB PV I+II R M 1000

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Similar to illustration




Dimensioned drawing




Example of use



Electric symbol



Schematic circuit diagram



Application with arrestor

Bestellnummer / Order number / Numéro de commande / Número de pedido / 订货号	Bezeichnung / Designation / Désignation / Designazione / 规格	Bestellnummer / Order number / Numéro de commande / Número de pedido / 订货号	Bezeichnung / Designation / Désignation / Designazione / 规格
25430000	VPCB PV I+II R M 1000	25060000	VPCB PV I+II R M 1000
25430000	VPCB PV I+II R M 1000	25060000	VPCB PV I+II R M 1000
25430000	VPCB PV I+II R M 1000	25060000	VPCB PV I+II R M 1000
25430000	VPCB PV I+II R M 1000	25060000	VPCB PV I+II R M 1000
25430000	VPCB PV I+II R M 1000	25060000	VPCB PV I+II R M 1000

1) R = Fernmeldeanlage / Remote signaling contacts / Contactos de teleseñalización / Contatti di segnalazione remota / Contactos de señalización a distancia / 远端信号触点

Selection