

DURA ECO LA-BAT 24V 17AH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The 5 battery modules with capacities from 1,2 Ah to 17Ah can supply up to 40 A for 30 minutes or 1 A for 30 hours and are fully compatible with the DC UPS control units CP DC UPS 24V 20A/10A & CP DC UPS 24V 40A. And for sure, the DURAeco series is a flexible & ease of use solution in a cost-effective design.

General ordering data

Version	Battery
Order No.	2789930000
Type	DURA ECO LA-BAT 24V 17AH
GTIN (EAN)	4064675068686
Qty.	1 pc(s).

DURA ECO LA-BAT 24V 17AH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	189 mm	Depth (inches)	7.441 inch
Height	178 mm	Height (inches)	7.008 inch
Width	242 mm	Width (inches)	9.528 inch
Net weight	13,639 g		

Temperatures

Storage temperature	-15 °C...50 °C	Humidity	5...95 % RH
---------------------	----------------	----------	-------------

Operating interfaces and control inputs

Temperature probe	NTC 100 kΩ
-------------------	------------

Input

Charging current, max.	2 A	Nominal capacity	17 Ah
Rated input voltage	24 V DC		

Output

Buffer time depending on current	Current	42 A
	Buffer time	10 min
	Current	21 A
	Buffer time	30 min
	Current	12 A
	Buffer time	60 min

Output current, max.	50 A
Overload and short circuit protection	2x25 A fuse
Parallel connection option	Yes
Temperature probe	NTC 100 kΩ

General data

Ambient temperature	-15 °C...+50 °C	Humidity	5...95 % RH
Life expectancy	5.65 a	Protection degree	IP20
Shock wall acc. to IEC 68227	30 g		

Insulation coordination

Protection class	III, with no ground connection, for SELV
------------------	--

Connection data (input)

Conductor cross-section, AWG/kcmil , max.	6 AWG	Conductor cross-section, AWG/kcmil , min.	24 AWG
Conductor cross-section, flexible , min.	0.5 mm ²	Conductor cross-section, rigid , max.	16 mm ²
Conductor cross-section, rigid , min.	0.5 mm ²	Number of terminals	2 (+,-)
Tightening torque, max.	2.4 Nm	Tightening torque, min.	1.2 Nm
Wire connection cross section, flexible (input), max.	10 mm ²		

DURA ECO LA-BAT 24V 17AH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Connection data (signal)

Number of terminals	2	Wire connection cross-section, flexible (signal), max.	1.5 mm ²
Wire connection cross-section, flexible (signal), min.	0.2 mm ²	Wire connection method	Pluggable screw connection
Wire cross-section, AWG/kcmil, max.	16	Wire cross-section, AWG/kcmil, min.	24 mm ²
Wire cross-section, solid, max.	1.5 mm ²	Wire cross-section, solid, min.	0.2 mm ²

Classifications


ETIM 6.0	EC002850	ETIM 7.0	EC002850
ETIM 8.0	EC002850	ETIM 9.0	EC002850
ETIM 10.0	EC002850	ECLASS 9.0	27-04-06-92
ECLASS 9.1	27-04-92-01	ECLASS 10.0	27-04-06-92
ECLASS 11.0	27-04-06-92	ECLASS 12.0	27-04-06-92
ECLASS 13.0	27-04-06-92	ECLASS 14.0	27-04-06-92
ECLASS 15.0	27-04-06-92		

Environmental Product Compliance

RoHS Compliance Status	Not affected
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	30bf869c-8adc-4ed2-ad02-c1fec963e943

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319212/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319215/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319228/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319234/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319258/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/
UL File Number Search	UL Website
Certificate no. (cULus)	E258476

DURA ECO LA-BAT 24V 17AH

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads


Approval/Certificate/Document of Conformity	DNV Certificate.pdf
	UL 61010-1 Certificate.pdf
	DURA ECO LA BAT ABS Cert.pdf
	BV Certificate
	Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Instruction sheets
	Safety Data Sheet
Catalogues	Catalogues in PDF-format

DURA ECO LA-BAT 24V 17AH

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Buffer Time