

MCB 1077 2P B 10A ACDC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	Miniature circuit breaker, Characteristic curve: B, Number of poles: 2, 10 A, white
Order No.	2479630000
Type	MCB 1077 2P B 10A ACDC
GTIN (EAN)	4050118490367
Qty.	1 pc(s).

MCB 1077 2P B 10A ACDC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	60.2 mm	Depth (inches)	2.37 inch
Height	82 mm	Height (inches)	3.228 inch
Width	35.3 mm	Width (inches)	1.39 inch
Net weight	216 g		

Temperatures

Ambient temperature	-35 °C...70 °C	Humidity	40 °C / 95 % rel. humidity, no condensation
---------------------	----------------	----------	--

Electrical data

Voltage type	AC/DC	Rated AC voltage	480,277 V
Rated DC voltage	125 V	Rated current	10 A
Interrupting capacity	10,000 A		

General data

Characteristic curve	B	Number of poles	2
Version circuit breaker	Thermomagnetic	Typical lifetime in cycles mechanical	20,000
Typical lifetime in cycles electrical	6,000	Type of mounting	DIN rail
Type of fixing	Rail mounting	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Colour	white

Classifications

ETIM 6.0	EC000042	ETIM 7.0	EC000042
ETIM 8.0	EC000042	ETIM 9.0	EC000042
ETIM 10.0	EC000042	ECLASS 9.0	27-14-19-01
ECLASS 9.1	27-14-19-01	ECLASS 10.0	27-14-19-01
ECLASS 11.0	27-14-19-01	ECLASS 12.0	27-14-19-01
ECLASS 13.0	27-14-19-01	ECLASS 14.0	27-14-19-01
ECLASS 15.0	27-14-19-01		

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format