

SAIBGC-M-5L-5.8/13.5-M12-CF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Version	Field attachable connector, M12 socket
Order No.	2525620000
Type	SAIBGC-M-5L-5.8/13.5-M12-CF
GTIN (EAN)	4050118536935
Qty.	1 pc(s).

SAIBGC-M-5L-5.8/13.5-M12-CF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	39 g
------------	------

Technical data customisable plug-in connectors

Cable diameter, max.	13.5 mm	Cable diameter, min.	5.8 mm
Coding	L-coded	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	0.5 mm ²	Connection cross-section, max.	1.5 mm ²
Connection cross-section, min.	0.75 mm ²	Contact material	Cu
Contact surface	Gold-plated	Housing main material	Zinc diecast
Number of poles	5	Plugging cycles	500
Pollution severity	3	Protection degree	IP67, when screwed in
Rated current	16 A	Rated current	16 A
Rated voltage	63 V	Shield connection	Yes
Temperature range of housing	-40 ... +85 °C	Threaded ring material	Diecast zinc
Type of connection	Crimp connection		

General Info

Number of poles	5	Connection 1	M12
Connection 2	Crimp	Housing main material	Zinc diecast
Connection thread	M12 socket	Contact material	Cu
Contact surface	Gold-plated	Protection degree	IP67, when screwed in
Plugging cycles	500		

Standards

Connector standard	IEC 61076-2-111
--------------------	-----------------

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 9.0	27-44-01-02
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-02
ECLASS 11.0	27-44-01-02	ECLASS 12.0	27-44-01-16
ECLASS 13.0	27-44-01-02	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Important note

Product information	Enclosures, inserts and crimp contacts need to be ordered separately. 4 x Crimp contact, Socket / 1 x Crimp contact, Pin (FE) for FE-Function.
---------------------	---

SAIBGC-M-5L-5.8/13.5-M12-CF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/
-----------------	---

ROHS	Conform
------	---------

UL File Number Search	UL Website
-----------------------	------------

Certificate No. (cURus)	E307231
-------------------------	---------

Downloads

Engineering Data	CAD data – STEP
------------------	---------------------------------

Product Change Notification	Technische Änderung für freikonfektionierbare M8 und M12 Steckverbinder Technical change to field attachable M8 and M12 connectors
-----------------------------	---

Catalogues	Catalogues in PDF-format
------------	--


SAIBGC-M-5L-5.8/13.5-M12-CF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Pole scheme

