

**CH 5.00/14/180F 3.9SN GN BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

|              |                                       |
|--------------|---------------------------------------|
|              |                                       |
| Order No.    | <a href="#">2645530000</a>            |
| Type         | CH 5.00/14/180F 3.9SN GN BX           |
| GTIN (EAN)   | 4050118641448                         |
| Qty.         | 75 pc(s).                             |
| Product data | IEC: 630 V / 15 A<br>UL: 300 V / 15 A |
| Packaging    | Box                                   |

**CH 5.00/14/180F 3.9SN GN BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |        |
|------------|--------|
| Net weight | 5.84 g |
|------------|--------|

**System specifications**

|                                 |                                     |                                |                  |
|---------------------------------|-------------------------------------|--------------------------------|------------------|
| Product family                  | OMNIMATE Signal - series BL/SL 5.08 | Type of connection             | Board connection |
| Mounting onto the PCB           | THT solder connection               | Pitch in mm (P)                | 5 mm             |
| Pitch in inches (P)             | 0.197 "                             | Outgoing elbow                 | 180°             |
| Number of poles                 | 14                                  | Number of solder pins per pole | 1                |
| Solder pin length (l)           | 3.9 mm                              | Solder pin dimensions          | 1.0 x 1.0 mm     |
| Solder eyelet hole diameter (D) | 1.6 mm                              | L1 in mm                       | 65 mm            |
| L1 in inches                    | 2.561 "                             | Number of rows                 | 1                |
| Pin series quantity             | 1                                   |                                |                  |

**Material data**

|                             |          |                             |            |
|-----------------------------|----------|-----------------------------|------------|
| Insulating material         | PA GF    | Colour                      | Pale green |
| Colour chart (similar)      | RAL 6021 | Insulating material group   | I          |
| UL 94 flammability rating   | V-0      | Contact base material       | Cu-alloy   |
| Contact material            | Cu-alloy | Contact surface             | tinned     |
| Tinning type                | matt     | Storage temperature, min.   | -40 °C     |
| Storage temperature, max.   | 70 °C    | Operating temperature, min. | -40 °C     |
| Operating temperature, max. | 105 °C   |                             |            |

**Rated data acc. to IEC**

|                                                                           |       |                                                                       |       |
|---------------------------------------------------------------------------|-------|-----------------------------------------------------------------------|-------|
| Rated current, min. number of poles (Tu=20°C)                             | 15 A  | Rated voltage for surge voltage class / pollution degree II/2         | 630 V |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V | Rated voltage for surge voltage class / pollution degree III/3        | 250 V |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV  | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV  |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV  |                                                                       |       |

**Rated data acc. to CSA**

|                                   |       |                                   |       |
|-----------------------------------|-------|-----------------------------------|-------|
| Rated voltage (Use group B / CSA) | 300 V | Rated voltage (Use group D / CSA) | 300 V |
| Rated current (Use group B / CSA) | 15 A  | Rated current (Use group D / CSA) | 10 A  |

**Rated data acc. to UL 1059**

|                                       |                                                                                     |                                       |        |
|---------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------|--------|
| Institute (cURus)                     |  | Certificate No. (cURus)               | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V                                                                               | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 15 A                                                                                | Rated current (Use group D / UL 1059) | 10 A   |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate.              |                                       |        |

**CH 5.00/14/180F 3.9SN GN BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Packing**

|           |      |            |      |
|-----------|------|------------|------|
| Packaging | Box  | VPE length | 0 mm |
| VPE width | 0 mm | VPE height | 0 mm |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002637    | ETIM 7.0    | EC002637    |
| ETIM 8.0    | EC002637    | ETIM 9.0    | EC002637    |
| ETIM 10.0   | EC002637    | ECLASS 9.0  | 27-44-04-02 |
| ECLASS 9.1  | 27-44-04-02 | ECLASS 10.0 | 27-44-04-02 |
| ECLASS 11.0 | 27-46-02-01 | ECLASS 12.0 | 27-46-02-01 |
| ECLASS 13.0 | 27-46-02-01 | ECLASS 14.0 | 27-46-02-01 |
| ECLASS 15.0 | 27-46-02-01 |             |             |

**Approvals**

Approvals



|                         |                                                                                                                                                                             |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approvals MAMID         | <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/</a> |
| ROHS                    | Conform                                                                                                                                                                     |
| UL File Number Search   | UL Website                                                                                                                                                                  |
| Certificate No. (cURus) | E60693                                                                                                                                                                      |

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 2f5e7231-4ad1-4dcb-8e0f-b14defbd9d78 |

**Important note**

Notes

- Only compatible with OMNIMATE basic products
- P on drawing = pitch
- Rated current related to rated cross-section & min. No. of poles.
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

**Downloads**


|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|

## CH 5.00/14/180F 3.9SN GN BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



## Recommended wave soldering profiles

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

### Single Wave:



### Double Wave:



### Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260°C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.