

# SBS<sup>®</sup> Mini Connectors Up to 52 amps



### SBS® MINI ORDERING INFORMATION

#### **SBS® Mini Housing**

The smallest SBS® connector has 2 finger proof positions in a polycarbonate housing with an ergonomic grip. The housing securely holds crimp and poke contacts from the popular Powerpole® 15/45 series connectors.

Description	Part Numbers
Minimum Quantity Red	100 B02265G1
Black	B02265G1 B02265G2
Blue	B02265G3
Grav	B02265G4









#### SBS® Mini Cable Clamp Assembly Kit

Insert Cable Clamp into middle position of housing, securing with pins and using a wire tie to secure wires. Kit includes clamp and 2 pins only. Wire ties sold separately.

Description	Part Numbers	in.	mm
Minimum Quantity Gray Clamp Kit, ( ray	1,000 B02597G4	1.15 x 0.34	29.1 x 8.60
Cable Wire Tie	H1835P11	4 x 0.10	100 x 2.50

SBS® Mini Connector series is our smallest DC power connector in the SBS® group. The SBS® Mini securely holds two crimp and poke contacts with sacrificial tips to enable hot swap capabilities on DC circuits. The low resistance contacts accept 20 to 10 AWG (0.52 to 5.3 mm²) wires allowing up to 52 amps of UL rated performance per position.


## • Touch Safe Housing Minimizes potential contact with live circuits

willimizes potential contact with live circuits

## • Color-Coded Mechanical Key Prevents accidental mating of connectors operating at different voltage levels

- Compact & Ergonomic Housing
  Is "user friendly" during connection and disconnection
  of the system
- UL Hot Plug Rated to 45 Amps @ 72 Volts Good for applications where the ability to interrupt circuits is required








Mated Side View



#### **PP15/45 Tin Plated Power Contacts**

Offer cost effective performance up to 200 mating cycles. See specifications and temperature charts for amperage ratings by wire size.

Barrel	AWG	mm²	Loose Piece Part Num	Reeled bers	Dimer - A inches	-
Open Open	m Quantity 20 to 16 16 to 12	0.52 to 1.3 1.3 to 3.3	200 262G1-LPBK 261G1-LPBK	5,000 262G1 261G1	0.16 0.18	4.06 4.57
Open <i>K</i> * - <i>Fo</i>	14 to 10 K * or 10 AWG clas	2.1 to 5.3 s <i>K stranded</i> v	261G2-LPBK wire or smaller.	261G2	0.20	5.08




#### **PP15/45 Silver Plated Power Contacts**

Maximize performance by offering up to 1,500 mating cycles. Recommended for circuit interrupt or hot plug applications. See specifications and temperature charts for amperage ratings by wire size. Only closed barrel contacts are suitable for soldering.


			Loos	e Piece	Reeled	- A	Dimens	sions - B	-
Barrel	AWG	mm²	Part N	Numbers	Part Numbers	inches	mm	inches	mm
	n Quantity 20 to 16 16 to 12 20 to 16 14 to 10 K *	0.52 to 1.3 1.3 to 3.3 0.52 to 1.3 2.1 to 5.3	5,000 1332-BK 1331-BK -	200 1332 1331 262G2-LPBK 261G3-LPBK	5,000 - - 262G2 261G3	0.12 0.15 0.16 0.20	3.05 3.81 4.06 5.08	0.07 0.10 -	1.78 2.54 -

K \* - For 10 AWG class K stranded wire or smaller.

#### Open Barrel Contact



#### **Closed Barrel Contact**



## SBS® Mini - Tooling Information

Wire	Wire Size Loose Piece Part Numbers				Reeled Part Numbers		Reeled Contact Crimp Tools			
AWG	mm²	Open Closed Barrel	Tin Plating	Silver Plating	Hand Tool	OR	Tin Plating	Silver Plating	Anderson Power™ Applicator	Anderson Power™ Press
20 to 16	0.52 to 1.3	Closed	N/A	1332 / 1332-BK	1309G2		N1 /A	N1 /A	N1 /A	NI/A
16 to 12	1.3 to 3.3	Closed	N/A	1331 / 1331-BK	0r		N/A	N/A	N/A	N/A
20 to 16	0.52 to 1.3	Open	262G1-LPBK	262G2-LPBK	1309G8		262G1	262G2		
16 to 12	1.3 to 3.3	Open	261G1-LPBK	N/A	1309G3		261G1	N/A	TD0101	115V = TE0101 230V = TE0102
14 to 10 K*	2.1 to 5.3	Open	261G2-LPBK	261G3-LPBK	or 1309G8		261G2	261G3		2300 - 120102

**Insertion / Extraction Tool** 

Insertion / Extraction Tool 111038G2

K\* - For 10 AWG class K stranded wire or smaller.




#### **Need More Than 2 Positions?**


See the stackable Powerpole® 15 to 45 connectors. These single position connectors use the same contact system as SBS® Mini and can be stacked together to create custom multiple position configurations.

## SBS® Mini CONNECTOR TEMPERATURE CHARTS - Temperature rise charts are based

on a 25°C ambient temperature.

Current - Temperature Derating per IEC 60512-5-2 Test 5B





## SBS® MINI SPECIFICATIONS

ELECTRICAL		
Current Rating Amperes <sup>1</sup>	UL 1977	CSA
10 AWG	52	35
12 AWG	41	28
14 AWG	31	23
16 AWG	24	16
18 AWG	20	15
Voltage Rating AC/DC		
UL 1977	600	
Dielectric Withstanding Voltage		
Volts AC	2,200	
Avg. Mated Contact Resistance Milliohms <sup>2</sup>		
Wire Contact with 5/8" of 16 AWG	0.875	
Wire Contact with 5/8" of 12 AWG	0.600	
Wire Contact with 5/8" of 10 AWG	0.525	
UL Hot Plug Current Rating Amperes <sup>3</sup>		
250 Cycles at 72V DC	45A	

MATERIALS	
Housing	
Plastic Resin	Polycarbonate
Contact Retention Spring	Stainless Steel
Housing Flammability Rating	
UL94	V-0
Glow Wire	960°C (GWFI) / 800°C (GWIT)
Contact	
Base	Copper Alloy
Plating	Tin or Silver
<b>Contact Termination Methods</b>	
Crimp <sup>3</sup>	Wire Contacts
Hand Solder	1331 & 1332

## SBS® MINI specifications continued

MECHANICAL		
Wire Size Range	AWG	mm²
	20 to 10	0.52 to 5.3
Max. Wire Insulation Diameter	in.	mm
	0.183	4.65
Operating Temperature	°F	°C
	-4° to 221°	-20° to 105°
Mating Cycles No Load by Plating	Silver (Ag)	Tin (Sn)
10 to 12 AWG	1,500	200
14 to 18 AWG	8,000	200
Avg. Mating / Unmating Force 4	Lbf.	N
10 AWG	10 to 11	45 to 49
12 to 18 AWG	4 to 7	17 to 31
Min. Contact / Spring Retention Force	Lbf.	N
	20	90

#### IFC INFORMATION

Connector Series	Configurations	Creepage / Clearance per IEC 60950-1	Material Group
CDC® Mi:	Unmated	1.47 mm	IIIa
SBS® Mini	Mated	2.40 mm	IIIa

PROTECTION					
Touch Safety					
UL 1977 Sec. 10.2	Pass				
IEC 60950	Pass				
IEC 60529	IP20				









Inquire with Customer Service for IEC / EN Approvals

NOTE 1: See IEC 60664-1 for working voltage.

- 1 Based on: 105°C rated or better cable of the largest size. Properly calibrated Anderson Power™ recommended tooling, and a 25°C ambient temperature. UL rating not to exceed the maximum operating temperature. CSA rating below a 30°C temperature rise.
- 2 Use Anderson Power™ recommended tooling only. Alternate tools may adversely affect the performance of our connectors along with UL and CSA recognition.
- 3 Based on 261G3 with 10 AWG wire.
- 4 Contact customer service for contacts with a higher disconnect force.

All Data Subject to Change Without Notice 2024-0103 DS-SBSMINI REV 8 Your Best Connection™

2768 2118 F: +(86) 755 2768 2218 • www.ideal-Industries.in • www.andersonpower.com

Anderson™ will use reasonable efforts to include accurate and up-to-date content in the data sheet. All product information contained in the data sheet including ordering information, illustrations, specifications, and dimensions, are believed to be reliable as of the date of publishing, but is subject to change without notice. Anderson™ makes no warranty or representation as to its accuracy. Content in the data sheet may contain technical inaccuracies, typographical errors and may be changed or updated without notice. Anderson™ may also make improvements and/or changes to the products and/or to the programs described in the content at any time without notice. Current sales drawings and specifications are available upon request.

©2024 Anderson Power Products, Inc. All rights reserved. A®, Anderson Power Products®, SBS®, are registered trademarks of Anderson Power Products, Inc. Anderson™, Anderson Power™, Anderson Power™ logo and Your Best Connection™ are trademarks of Anderson Power Products, Inc.



HEADQUARTERS: Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T: +1 978-422-3800 F: +1 978-422-0128 • EUROPE: Anderson Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 520203 • GERMANY: IDEAL® Industries Germany GmbH, Esslinger Strasse 7, D – 70771 Leinfelden-Echterdingen, T: +49 (0) 711 – 997606666 • ASIA / PACIFIC: IDEAL® Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T: +(852) 2636 0836 F: +(852) 2635 9036 • INDIA: IDEAL® INDUSTRIES India Private Limited, 229-230, SPAZEDGE, Tower B, Sector 47, Sohna Road, Gurgaon – 122018, Haryana, India T: +(91) 956-0075905 T: +(91) 124-4495101 • CHINA: IDEAL® Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, PR. China 518105 T: +(86) 755