


FLORENTINA-2X2-W

~40° wide beam

SPECIFICATION:

Dimensions	89.6 x 89.6
Height	22.2 mm
Fastening	pin, screw
ROHS compliant	yes 




MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
ROSE-C-C-W-V4	Single lens	PC	clear		
FLORENTINA-2X2-HLD	Holder	PC	black		

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
FCP14969_FLORENTINA-2X2-W » Box size: 476 x 273 x 292 mm	88	24	8	4.0




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):




LED EASY-T FLUX 2x2 FLR XG xxx G7
FWHM / FWTM 42.0° / 72.0°
Efficiency 77 %
Peak intensity 1.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED EASY-T FLUX 2x2 FLR XT xxx G5
FWHM / FWTM 40.0° / 70.0°
Efficiency 77 %
Peak intensity 1.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files





LED XHP35 HD
FWHM / FWTM 49.0° / 77.0°
Efficiency 70 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C15196_FLORENTINA-2X2-SHD-OPEN

OPTICAL RESULTS (MEASURED):





LED XHP35 HD
 FWHM / FWTM 49.0° / 77.0°
 Efficiency 70 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C14734_FLORENTINA-2X2-SHD



Light distribution files




LED XP-G2
 FWHM / FWTM 44.0° / 72.0°
 Efficiency 78 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C14960_FLORENTINA-2X2-SHD-WHT



Light distribution files



LED XP-G2
 FWHM / FWTM 44.0° / 72.0°
 Efficiency 76 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C14734_FLORENTINA-2X2-SHD





Light distribution files

OPTICAL RESULTS (MEASURED):





LED XP-G2
FWHM / FWTM 44.0° / 73.0°
Efficiency 79 %
Peak intensity 1.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED XP-G2
FWHM / FWTM 46.0° / 74.0°
Efficiency 77 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C15196_FLORENTINA-2X2-SHD-OPEN



Light distribution files




LED XP-L HD
FWHM / FWTM 49.0° / 77.0°
Efficiency 70 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C14960_FLORENTINA-2X2-SHD-WHT

OPTICAL RESULTS (MEASURED):




LED XP-L HD
 FWHM / FWTM 49.0° / 77.0°
 Efficiency 70 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C15196_FLORENTINA-2X2-SHD-OPEN



Light distribution files



LED LUXEON MZ
 FWHM / FWTM 37.0° / 63.0°
 Efficiency 69 %
 Peak intensity 1.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C14960_FLORENTINA-2X2-SHD-WHT




Light distribution files

OPTICAL RESULTS (MEASURED):




LED LUXEON MZ
FWHM / FWTM 36.0° / 63.0°
Efficiency 66 %
Peak intensity 1.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C15196_FLORENTINA-2X2-SHD-OPEN



Light distribution files



LED LUXEON MZ
FWHM / FWTM 36.0° / 63.0°
Efficiency 66 %
Peak intensity 1.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C14734_FLORENTINA-2X2-SHD



Light distribution files





LED LUXEON TX
FWHM / FWTM 41.0° / 67.0°
Efficiency 76 %
Peak intensity 1.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C15196_FLORENTINA-2X2-SHD-OPEN

OPTICAL RESULTS (MEASURED):





LED LUXEON TX
 FWHM / FWTM 41.0° / 67.0°
 Efficiency 76 %
 Peak intensity 1.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C14734_FLORENTINA-2X2-SHD



Light distribution files



LED NVSxx19B/NVSxx19C
 FWHM / FWTM 42.0° / 71.0°
 Efficiency 80 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C15196_FLORENTINA-2X2-SHD-OPEN




Light distribution files

OPTICAL RESULTS (MEASURED):

OSRAM
Opto Semiconductors


LED OSLON Square CSSRM2/CSSRM3
FWHM / FWTM 35.0° / 65.0°
Efficiency 69 %
Peak intensity 1.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C14734_FLORENTINA-2X2-SHD



Light distribution files

OSRAM
Opto Semiconductors



LED OSLON Square CSSRM2/CSSRM3
FWHM / FWTM 35.0° / 66.0°
Efficiency 72 %
Peak intensity 1.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C14960_FLORENTINA-2X2-SHD-WHT



Light distribution files

SAMSUNG

LED HiLOM SC16 (LH181B)
FWHM / FWTM 42.0° / 68.0°
Efficiency 49 %
Peak intensity 0.8 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C14734_FLORENTINA-2X2-SHD




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED LUXEON XR-7070 (L224-xxxx004MLU010)
FWHM / FWTM 50.0° / 78.0°
Efficiency 63 %
Peak intensity 0.8 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

**Ledil Optics Technology
(Shenzhen) Co., Ltd.**
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

**Local sales and technical
support**
www.ledil.com/
where_to_buy

Shipping locations
Poznan, Poland
Hong Kong, China

Distribution Partners
www.ledil.com/
where_to_buy