
STRADELLA-IP-64-VSM

IESNA Type V (square) beam for wide areas lighting such as car parks.

SPECIFICATION:

Dimensions 253.0 x 74.0 Height 9.7 mm Fastening screw Ingress protection classes IP66, IP67 **ROHS** compliant yes 🕕



MATERIALS:


Component	Type	Material	Colour	Finish	Length (mm)
STRADELLA-IP-64-VSM	Multi-lens	PMMA	clear		
STRADELLA-IP-64-SEAL	Seal	Silicone	milky		

ORDERING INFORMATION:

» Box size: 476 x 273 x 247 mm

Component	Qty in box	MOQ	MPQ	Box weight (kg)
CS17646_STRADELLA-IP-64-VSM	108	108	36	8.8






See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):



LED EHP-223.5x50-1604-xx-70-LS30-06-NTC

FWHM / FWTM Asymmetric
Efficiency 97 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

inventronics

LED PrevaLED Brick MP 4x16

FWHM / FWTM 129.0° / 138.0°
Efficiency 96 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1

Light colour/type White Required components:




Light distribution files



LED RecLED 223x50mm 4200lm 4x16 STRADELLA-IP-64

FWHM / FWTM 131.0° / 140.0° Efficiency 97 %

Peak intensity 0.6 cd/lm LEDs/each optic 1
Light colour/type White Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):



LED RecLED 223x50mm 4200lm 8x0 4x16 Opt G1

FWHM / FWTM Asymmetric
Efficiency 93 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED KAAX-VB-2300-840-48

FWHM / FWTM 132.0° / 141.0°

Efficiency 92 %
Peak intensity 0.5 cd/lm

LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):



J Series 2835 LED FWHM / FWTM Asymmetric Efficiency 92 % Peak intensity 0.4 cd/lm LEDs/each optic 1 White Light colour/type

Required components:




Light distribution files

OSRAM Opto Semiconductore

LFD **Duris E 2835** FWHM / FWTM Asymmetric Efficiency 96 % 0.5 cd/lm Peak intensity LEDs/each optic Light colour/type White

Required components:




Light distribution files

OSRAM

DURIS S5 (Single chip)

FWHM / FWTM Asymmetric 96 % Efficiency Peak intensity 0.6 cd/lm LEDs/each optic Light colour/type White Required components:



Light distribution files


OPTICAL RESULTS (SIMULATED):

OSRAM Opto Semiconductors

LED OSCONIQ C 3030
FWHM / FWTM Asymmetric
Efficiency 95 %
Peak intensity 0.5 cd/lm

LEDs/each optic 1
Light colour/type White

Required components:




Light distribution files

PHILIPS

LED Fortimo FastFlex LED 4x16 DHE G4

FWHM / FWTM Asymmetric
Efficiency 96 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White

Required components:




Light distribution files

SAMSUNG

LED HILOM RM64 (LM301B)

FWHM / FWTM Asymmetric
Efficiency 96 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

PRODUCT DATASHEET


CS17646_STRADELLA-IP-64-VSM

OPTICAL RESULTS (SIMULATED):

SAMSUNG

LFD LH351B FWHM / FWTM Asymmetric Efficiency 94 % Peak intensity 0.4 cd/lm LEDs/each optic 1 Light colour/type White

Required components:




Light distribution files

SAMSUNG

LH351C LFD FWHM / FWTM Asymmetric Efficiency 94 % 0.4 cd/lm Peak intensity LEDs/each optic Light colour/type White

Required components:



Light distribution files

SAMSUNG

LH351D FWHM / FWTM Asymmetric Efficiency 92 % Peak intensity 0.3 cd/lm LEDs/each optic Light colour/type White Required components:

Light distribution files

OPTICAL RESULTS (SIMULATED):


SAMSUNG

LED LM301B
FWHM / FWTM Asymmetric
Efficiency 96 %

Peak intensity 0.5 cd/lm

LEDs/each optic 1
Light colour/type White

Required components:




Light distribution files

TRIDONIC

LED RLE 4x16 4000lm MP ADV2 OTD

FWHM / FWTM Asymmetric
Efficiency 96 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White

Required components:



Light distribution files



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 7 FI-24100 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405, Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Poznan, Poland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

Published: 17/02/2021