

## **DAISY-MINI-FT-D**

Forward throwing beam for freestanding office luminaires

## **SPECIFICATION:**

Dimensions 275.0 x 16.1

Height 6.2 mm

Fastening pin, screw

ROHS compliant yes 1



## **MATERIALS:**

Component	Туре	Material	Colour	Finish	Length (mm)
F18248_DAISY-MINI-FT-D	Linear lens	PMMA	clear		
F17667_DAISY-MINI-SHD-MET-MATT	Shade	PC	metal	matt	
F17666_DAISY-MINI-SHD-MET	Shade	PC	metal	gloss	
F17465_DAISY-MINI-SHD-WHT-MATT	Shade	PC	white	matt	
F17034_DAISY-MINI-SHD-MATT	Shade	PC	black	matt	
F17033_DAISY-MINI-SHD-WHT	Shade	PC	white	gloss	
F17028 DAISY-MINI-SHD	Shade	PC	black	aloss	

## **ORDERING INFORMATION:**

## **Quantities for one set:**

Linear lens 1


Shade 1



## PRODUCT DATASHEET DAISY-MINI-FT-D

Component		Qty in box	MOQ	MPQ	Box weight (kg)
F18248_DAISY-MINI-FT-D  » Box size: 398 x 298 x 265 mm	Linear lens	252	252	12	6.0
F17034_DAISY-MINI-SHD-MATT  » Box size: 398 x 298 x 265 mm	Shade	252	252	4	6.1
F17465_DAISY-MINI-SHD-WHT-MATT  » Box size: 398 x 298 x 265 mm	Shade	252	252	4	6.2
F17666_DAISY-MINI-SHD-MET  » Box size: 398 x 298 x 265 mm	Shade	252	252	4	5.9
F17028_DAISY-MINI-SHD  » Box size: 398 x 298 x 265 mm	Shade	252	252	4	5.9
F17667_DAISY-MINI-SHD-MET-MATT  » Box size: 398 x 298 x 265 mm	Shade	252	252	4	6.2
F17033_DAISY-MINI-SHD-WHT  » Box size: 398 x 298 x 265 mm	Shade	252	252	4	5.9

# **PRODUCT DAISY-MINI-FT-D**



See also our general installation guide: www.ledil.com/installation\_guide



## **OPTICAL RESULTS (MEASURED):**

## **SAMSUNG**

LED LM28xB Series
FWHM / FWTM Asymmetric
Efficiency 69 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:


F17028\_DAISY-MINI-SHD

Light distribution files



LED LED-St-L28W2-840-C010-06 (Daisy-Mini)

FWHM / FWTM Asymmetric
Efficiency 67 %
Peak intensity 0.6 cd/lm
LEDs/each optic 2
Light colour/type White
Required components:
F17028\_DAISY-MINI-SHD



Light distribution files




LED LED-St-L28W2-927-C010-965-C010-07 (Daisy-Mini)

FWHM / FWTM Asymmetric
Efficiency 67 %
Peak intensity 0.6 cd/lm
LEDs/each optic 2

Light colour/type Tunable White

Required components: F17028\_DAISY-MINI-SHD



Light distribution files




## **OPTICAL RESULTS (SIMULATED):**



LED LUXEON 5050 Square LES

FWHM / FWTM Asymmetric
Efficiency 64 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White

Required components: F17028\_DAISY-MINI-SHD




Light distribution files

## **SAMSUNG**

LED LM28xB Series
FWHM / FWTM Asymmetric
Efficiency 61 %
Peak intensity 0.6 cd/lm
LEDs/each optic 2
Light colour/type White

Required components: F17028\_DAISY-MINI-SHD




Light distribution files

## **SAMSUNG**

LED LM28xB Series
FWHM / FWTM Asymmetric
Efficiency 66 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White

Required components: F17028\_DAISY-MINI-SHD



Light distribution files



# PRODUCT DATASHEET DAISY-MINI-FT-D

### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

### **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

## **LEDIL Oy**

Joensuunkatu 7 FI-24100 SALO Finland

#### **LEDIL Inc.**

228 West Page Street Suite D Sycamore IL 60178 USA

# Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

# Local sales and technical support

www.ledil.com/ where\_to\_buy

### **Shipping locations**

Poznan, Poland Hong Kong, China

### **Distribution Partners**

www.ledil.com/ where\_to\_buy