




LEOPARD
IMAGING

LI-OX05B1S-MIPI-137H



Address:

910 Auburn Ct
Fremont, CA 94538
USA



Phone:

+1 (408)263-0988

Fax:

+1 (408)217-1960



Sales:

sales@leopardimaging.com

Support:

support@leopardimaging.com

INTRODUCTION

The LI-OX05B1S-MIPI-137H is a MIPI CSI-2 camera with OmniVision 1/2.5" RGB-IR CMOS 5MP global shutter image sensor OX05B1S. This camera outputs 2592 x 1944 RAW data.

SPECIFICATIONS

Sensor	OmniVision 1/2.5" RGB-IR CMOS 5MP Image Sensor OX05B1S
Optical Format	1/2.5"
Resolution	2592 (H) x 1944 (V) (active pixels)
Pixel Size	2.2 x 2.2 μ m
Shutter	Global shutter
Output Format	RAW RGB-IR
Maximum Frame Rate	60 fps @ 1944p
ISP	Not included
Color / Mono	RGB-IR
Interface	4-lane MIPI CSI-2
Power Consumption	Approximate 100 mA @ 3.3 VDC (2592 x 1944 @ 30 fps)
Operating Temp	-20°C ~ +60°C
Storage Temp	-20°C ~ +60°C
Weight	~ 15 g
Part#	LI-OX05B1S-MIPI-137H

APPLICATIONS


- Automotive
 - Autonomous Driving
 - Driver Monitoring System
 - Occupant Monitoring System
 - In-Cabin Monitoring System

LENS SPECIFICATIONS

Focal Length	2.666 mm
Aperture, F/#	2.4
Field of View (FOV)	137° horizontal
Optical Distortion	-87.08% (F-tan θ)
Relative Illumination	43.99%
IR Filter	Visible + 940 nm IR filter
Lens Mount	M12 x P0.5




DIMENSIONS



INTERFACE J5

- Connector Part#: 20525-030E-02
- Number of Positions: 30
- Pitch: 0.4 mm
- Mating I-PEX cable: LI-FAW-1233
- Sensor I2C Address: 0x6C (8-bit)
- External Power Supply: 3.3V
- 2.8V (analog), 1.8V and 1.2V are generated from board



- REVISION HISTORY

Revision	Description	Release Date
1.0	First release.	15 Jan 2024

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

