

IE-C6ES8UG0020A45XXX-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	System cable, RJ45 IP 67 RockStar V05 metal, Open, Cat.6A / Class EA (ISO/IEC 11801 2010), 2 m
Order No.	2714590000
Type	IE-C6ES8UG0020A45XXX-X
GTIN (EAN)	4050118762433
Qty.	1 pc(s).

IE-C6ES8UG0020A45XXX-X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	2 m	Length (inches)	78.74 inch
Net weight	185.08 g		

Temperatures

Storage temperature	-40 °C...80 °C	Installation temperature	-15 °C...60 °C
---------------------	----------------	--------------------------	----------------

Cable specific standards

Corrosiveness of fumes	to IEC 60754-2	Generic communication cable facilities	EN 50173-1:2007, ISO / IEC 11801:2002
Standard, assembly	UL-Style 20963 (80°C/30V)		

Cable structure

Arrangement of wire cores	Twisted pair	Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown
Complete shielding	Shielding braid made from copper wiring	Cross-section	4*2*AWG 26/7 - 4*2*0.128 mm ²
Sheath diameter, max.	6.5 mm	Sheath diameter, min.	6.1 mm
Sheathing colour	green (RAL 6018)	Shielding	S/FTP
Shielding braid thickness	0.1 mm	Standard designations	S/FTP, LIO2YSC11Y 4x2x0.15 PIMF FRNC GN
Strands	7	Wire material	Stranded tin-plated copper wire
Wire pair shielding	Aluminium foil		

Electrical properties of cable

Capacity at 1 kHz	45 nF/km	Category	Cat.6A / Class EA (ISO / IEC 11801 2010)
Characteristic impedance	100 ± 5 Ω at 100MHz	Delay skew	3 ns/100m
Loop resistance	290 Ω/km	Test voltage: wire-wire-shield	700 V AC
Transfer impedance	15 mΩ/m at 1 MHz, 10 mΩ/m at 10 MHz, 30 mΩ/m at 30 MHz		

Mechanical and material properties of cable

Abrasion resistance	very good	Corrosiveness of fumes	to IEC 60754-2
Halogen	halogen-free, according to IEC 60754-2	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	10 x cable diameter	Pulling force	≤ 100 N
Resistance to oils	in accordance with IEC 60811-2-1	Resistance to spread of flame	in accordance with IEC 60332-1

Plug

Plug left	RJ45, IP67, male contact, straight, RockStar V05, Diecast aluminium, shielded	Plug right	free conductor end
-----------	---	------------	--------------------

IE-C6ES8UG0020A45XXX-X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Plug, left

Plug left	RJ45, IP67, male contact, straight, RockStar V05, Diecast aluminium, shielded
-----------	---

Plug, right

Plug right	free conductor end
------------	--------------------

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08
ECLASS 13.0	27-06-03-08	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/
ROHS	Conform

Downloads

Catalogues	Catalogues in PDF-format
------------	--