







QM22L 2.05 x 1.65 x 0.75 mm LCC Ceramic Package

Features

- A configurable Quartz crystal controlled precision square wave oscillator
- CMOS Output (will interface with TTL devices)
- Enable/Disable Function (low standby power option)
- Low Jitter
- 1.8V, 2.5V, or 3.3V nominal Supply Voltage
- 1-160 MHz Frequency Range (1-125MHz at 1.8V)
- Fundamental crystal

Applications

Driving A/Ds, D/As, FPGAs Digital Video Ethernet, GbE Medical Storage Area Networking COTS Broad Band Access SONET/ SDH/ DWDM Test & Measurement

Electrical Characteristics							
Parameter	Min	Тур	Max	Unit	Condition		
Frequency Range ²	1	-	160	MHz	(1.8V frequency range 1-125MHz)		
Frequency Stability ²	±20*	-	±50	ppm	For all supply voltages, load changes, aging for 1 year at 25°C ± 2°C, shock, vibration and temperatures. *Aging excluded		
Operating Temperature Range options ²	0 -20 -40 -40	- - -	+70 +70 +85 +105	°C	Standard range Extended range C option Extended range E option Extended range G option		
Supply Voltage 1,2 V _{CC}	1.8	-	3.3	V	± 5%, See Part Number options on page 3		
Supply Current I _{CC}	-	-	-	mA	See page 2		
Output Waveform		С	MOS		Cload = 15 pF		
Duty Cycle	45	-	55	%	At 50%Vcc level		
Output V _{HIGH}	0.9Vcc	-	-	V			
Output V _{LOW}	-	-	0.1Vcc	V	See Load Circuit and waveform page		
Output T _{RISE} and T _{FALL}	-	-	2	ns			
Startup Time	-	-	8	ms	After Vcc ≥ 1.62V, Time for output to reach specified frequency		
V _{DISABLE} VIL	-	-	0.3Vcc				
V _{ENABLE} VIH	0.7Vcc	-		V			
Output Enable Time	-	-	100	ns	Time for valid output (E/D version)		
Output Disable Time	-	-	100	ns	Time for output to reach a high Z state		
Disable Current	-	0.4	-	mA	Enable/Disable: Pad 1 low, output disabled; See page 2 Standby option: Pad 1 low, output disabled, oscillator shutdown		
Jitter	-	1.0	-	ps	12 kHz to 20 MHz @ 110 MHz		
Storage Temperature Range	-55	-	+125	°C			

Notes: Specifications with Pad 1 E/D open circuit

² Specified by part number

¹ Place an appropriate power supply bypass capacitor next to device for correct operation



Electrical Characteristics - Input Current											
Parameter	Min	Тур	Max	Unit	Condition Vcc = 3.3V						
Supply Current I _{CC}			27 30 35	mA	1MHz ≤ Fo < 75MHz 75MHz ≤ Fo < 125MHz 125MHz ≤ Fo < 160MHz	15pF load					

Parameter	Min	Тур	Max	Unit	Condition Vcc = 2.5V			
Supply Current I _{CC}			27 30 35	mA	1MHz ≤ Fo < 75MHz 75MHz ≤ Fo < 125MHz 125MHz ≤ Fo ≤ 160MHz	15pF load		

Parameter	Min	Тур	Max	Unit	Condition Vcc = 1.8V					
Supply Current I _{CC}			25	mA	1MHz ≤ Fo ≤ 125MHz	15pF load				



Part Number**

Series Model	Frequency Stability		Operating Temperature Range	Supply Voltage V _{cc}	Frequency in MHz	
QM22	45	ш	E	V	- 125.0M	
	45 = ± 50 ppm (STD) 44 = ± 25 ppm 20 = ± 20 ppm		Blank = -10 to +70°C (STD) C = -20 to +70°C E = -40 to +85°C G = -40 to +105°C	X = 1.8V ± 5% W = 2.5V ± 5% V = 3.3V ± 5%	1 - 160 MHz (1.8V: 1 -125MHz)	

^{**} A custom part number is assigned for parts using the standby option

Device Marking

PFF.F **YMxxx** P = Pletronics

FF.F = Frequency, max 4 digits includes decimal YM = Date Code, Year Month (see below)

xxx = internal factory codes

Note: Specifications such as frequency stability, supply voltage and operating temperature range, etc. are not identified from marking.

External packaging labels and packing list will correctly identify the ordered Pletronics part number.

Codes for Date Code YM (Year Month)

Co	ode	3	4	5	6	7	Code	Α	В	С	D	E	F	G	Н	J	K	L	М
Ye	ear	2023	2024	2025	2026	2027	Month	JAN	FEB	MAR	APR	MAY	JUN	JUL	AUG	SEP	OCT	NOV	DEC

Package Labeling

P/N Label is 1" x 2.6" (25.4mm x 66.7mm) Font is Courier New Bar code is 39-Full ASCII



Second Level Interconnect code: e4

RoHs Label is 1" x 2.6" (25.4mm x 66.7mm) Font is Arial

> **RoHS Compliant** 2nd LvL Interconnect

Category=e4

Max Safe Temp=260C for 10s 2X Max


Pletronics Inc. certifies this device is in accordance with the RoHS and REACH directives.

Pletronics Inc. guarantees the device does not contain the following: Cadmium, Hexavalent Chromium, Lead, Mercury, PBB's, PBDE's Weight of the Device: 0.013 grams Moisture Sensitivity Level: 1 As defined in J-STD-020D

Product information is current as of publication date. The product conforms to specifications per the terms of the Pletronics standard warranty. Dec 21, 2023 Rev. M Production processing does not necessarily include testing of all parameters.




Mechanical Dimensions





Pad Connections

Pad	Function
1	Enable/Disable
2	Ground
3	Output
4	Vcc



ENABLE/DISABLE						
Pad 1	Output					
Vi⊣/Open	Active					
Vı∟/Gnd	Disabled/Tristate					





Dimensions in mm

Pad Layout

Disclaimer: Recommended layout shown. Adjust layout as needed for individual process requirements.


Contacts (pads): Gold (0.3 to 1.0 µm) over Nickel (1.27 to 8.89 µm)

For Optimum Jitter Performance, Pletronics recommends:

- A ground plane under the device
- Do not route large transient signals (both current and voltage) under the device
- Do not place near a large magnetic field such as a high frequency switching power supply
- Do not place near piezoelectric buzzers or mechanical fans




Electrical Test / Load Circuit



Notes:

CL: 15pF Includes the input capacitance of oscilloscope * 0.01 $^{\sim}$ 0.1µF external by-pass filter is recommended



Environmental / ESD Ratings

Reliability: Environmental

Parameter	Condition
Mechanical Shock	MIL-STD-883, Method 2002, Condition B
Vibration	MIL-STD-883, Method 2007, Condition A
Solderability	IPC J-STD-002
Thermal Cycle	MIL-STD-883 Method 1010, Condition B

Thermal Characteristics:

The maximum die or junction temperature is 125°C

ESD Rating


Model	Min. Voltage	Condition		
Human Body Model	2000V	MIL-STD-883 3015.7		
Machine Model	200V	EIAJ ED-4701/304		

Absolute Maximum Ratings

Parameter	Unit
V _{CC} Supply Voltage	-0.5V to +7.0V
Vi Input Voltage	-0.5V to V _{CC} + 0.5V
Vo Output Voltage	-0.5V to V _{CC} + 0.5V




Reflow Cycle



The part may be reflowed 2 times without degradation (typical for lead free processing).

Tape and Reel

Tape and Reel available for quantities of 250 to 3000 per reel, cut tape for < 250. 8mm tape, 4mm pitch.




USER DIRECTION OF UNREELING -

	Tape Variable Dimensions Table 2											
Tape Size	E2 typ	F	P1	W max	Ao	Во	Ko					
8mm	6.25	3.5 ±0.05	4.0 ±0.1	8.2	1.9±0.1	2.3±0.1	0.9±0.1					

Dimensions in mm Drawing Not to scale Note 1: Embossed cavity to conform to EIA- 481-B

Tape Constant Dimensions Table 1										
Tape Size	Do	D1 min	E1	Po	P2	T max	T1 max			
8mm	1.5 +0.1 -0.0	1.0	1.75 ±0.1	4.0 ±0.1	2.0 ±0.05	0.3	0.1			



Reel Dimensions (may vary) Table 3											
	А		В		С	D					
Reel Size	Inches	mm	Inches	mm	mm	mm					
7	7.0	180	2.50	63.5	13.0 +0.5 -0.2	Tape size +0.4 +2.0 -0.0					
						-0.0					



Important Notice

Pletronics Incorporated (PLE) reserves the right to make corrections, improvements, modifications and other changes to this product at anytime. PLE reserves the right to discontinue any product or service without notice. Customers are responsible for obtaining the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to PLE's terms and conditions of sale supplied at the time of order acknowledgment.

PLE warrants performance of this product to the specifications applicable at the time of sale in accordance with PLE's limited warranty. Testing and other quality control techniques are used to the extent PLE deems necessary to support this warranty. Except where mandated by specific contractual documents, testing of all parameters of each product is not necessarily performed.

PLE assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using PLE components. To minimize the risks associated with the customer products and applications, customers should provide adequate design and operating safeguards.

PLE products are not designed, intended, authorized or warranted to be suitable for use in life support applications, weapons, weapon systems or space applications, devices or systems or other critical applications that may involve potential risks of death, personal injury or severe property or environmental damage. Inclusion of PLE products in such applications is understood to be fully at the risk of the customer. Use of PLE products in such applications requires the written approval of an appropriate PLE officer. Questions concerning potential risk applications should be directed to PLE.

PLE does not warrant or represent that any license, either express or implied, is granted under any PLE patent right, copyright, artwork or other intellectual property right relating to any combination, machine or process which PLE product or services are used. Information published by PLE regarding third-party products or services does not constitute a license from PLE to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from PLE under the patents or other intellectual property of PLE.

Reproduction of information in PLE data sheets or web site is permissible only if the reproduction is without alteration and is accompanied by associated warranties, conditions, limitations and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. PLE is not responsible or liable for such altered documents.

Resale of PLE products or services with statements different from or beyond the parameters stated by PLE for that product or service voids all express and implied warranties for the associated PLE product or service and is an unfair or deceptive business practice. PLE is not responsible for any such statements.

Contacting Pletronics Inc.

Pletronics, Inc. 19013 36th Ave. West Lynnwood, WA 98036-5761 U.S.A. Tel: 425.776.1880 Fax: 425.776.2760

email: ple-sales@pletronics.com URL: www.pletronics.com