Wire-wound Ferrite Power Inductors LMRN series for Medical Devices classified as GHTF Class C (Japan Class III)

Code in front of Series have been extracted from Part number, which describes the segment of products, such as kinds and characteristics.

REFLOW

■PART NUMBER

*Operating Temp.: -40~125°C (Including self-generated heat)

L	М	R	N	J	1	0	1	4	5	G	L	1	0	0	М	N		
	Ć)		2		3		(4	4)	(5)	6		(7)		8		9	

(1)Series

<u> </u>	
Code	
(1)(2)(3)(4)	
LMRN	Wire-wound Ferrite Power Inductor for Medical Devices classified as GHTE Class C (Japan Class III)

(1) Product Group

<u> </u>	•
Code	
L	Inductors

(2) Category

(=, ====,	5)	
Code	Recommended equipment	Quality Grade
М	Medical Devices classified as GHTF Class C (Japan Class III)	2

(3) Type

Code	
R	Ferrite Wire-wound (Drum-sleeve, pedestal type)

(4) Features, Characteristics

Code	,
N	Standard Power choke

2Feature

Code	Feature
L	Bottom electrode (Pedestal type)

3Dimensions (L × W)

Code	Dimensions (L × W) [mm]
101	10.1 × 10.1
125	12.5 × 12.5

4 Dimensions (H)

Code	Dimensions (H) [mm]
45	4.5
55	5.5
65	6.5
75	7.5

⑤Operating temperature

Code	Operating temperature [°C]
G	-40∼+125

6Packaging

Code	Packaging
	Taping

(7)Nominal inductance

© 110 mm and 111 and 1				
Code (example)	Nominal inductance[µH]			
1R0	1.0			
100	10			
101	100			

※R=Decimal point


8 Inductance tolerance

Code	Inductance tolerance				
М	±20%				
N	±30%				

9Internal code

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

■STANDARD EXTERNAL DIMENSIONS / MINIMUM QUANTITY



Type	L	W	Н	а	b	Minimum quantity [pcs]
10145	10.1±0.3	10.1±0.3	4.5±0.35	2.8±0.1	2.0±0.15	2000
	(0.398 ± 0.012)	(0.398 ± 0.012)	(0.177 ± 0.014)	(0.110 ± 0.004)	(0.079 ± 0.006)	2000
10155	10.1±0.3	10.1±0.3	5.5±0.35	2.8±0.1	2.0±0.15	2000
	(0.398 ± 0.012)	(0.398 ± 0.012)	(0.217 ± 0.014)	(0.110 ± 0.004)	(0.079 ± 0.006)	2000
10165	10.1±0.3	10.1±0.3	6.5±0.35	2.8±0.1	2.0±0.15	2000
	(0.398 ± 0.012)	(0.398 ± 0.012)	(0.256 ± 0.014)	(0.110 ± 0.004)	(0.079 ± 0.006)	
12555	12.5±0.3	12.5±0.3	5.5±0.35	3.0±0.1	2.0±0.15	2000
	(0.492 ± 0.012)	(0.492 ± 0.012)	(0.217 ± 0.014)	(0.118 ± 0.004)	(0.079 ± 0.006)	
12565	12.5±0.3	12.5±0.3	6.5±0.35	3.0±0.1	2.0±0.15	2000
	(0.492 ± 0.012)	(0.492 ± 0.012)	(0.256 ± 0.014)	(0.118 ± 0.004)	(0.079 ± 0.006)	2000
12575	12.5±0.3	12.5±0.3	7.5±0.35	3.0±0.1	2.0±0.15	2000
	(0.492 ± 0.012)	(0.492 ± 0.012)	(0.295 ± 0.014)	(0.118 ± 0.004)	(0.079 ± 0.006)	


Unit:mm(inch)

Recommended Land Patterns

Surface Mounting

• Mounting and soldering conditions should be checked beforehand.

• Applicable soldering process to these products is reflow soldering only.



Туре	Α	В	С
10145	2.5	5.6	3.2
10155	2.5	5.6	3.2
10165	2.5	5.6	3.2
12555	2.5	8.6	3.2
12565	2.5	8.6	3.2
12575	2.5	8.6	3.2

Unit:mm

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).