




A
B
C
D
E



Recommended terminal layout
Side of component
Tolerances as per DIN IEC 326
Item 3 very fine
Fix in mounting holes



Marking




Single pole normally open

1019.
6(2)/250~T85



Actuating force 1.5 ... 3.0 N
Movement differential ≤ 1.2 mm



1:1

-	-					-		1019.0201-XX			
Figure	Type					Customer No.		Art.No.-PI			
General tolerances						Sheet 01			Ident. K	Document number 10190201	Index c
All dimensions are in millimetres	Shape and location 	Angle $\pm 2^\circ$	Edge tolerance 		Length						
				0-6	± 0.1	± 0.2					
				>6-15	± 0.15	± 0.3					
				>15-30	± 0.2	± 0.5					
				>30-70	± 0.3	$\pm 10\%$					
				>70-120	± 0.4						
				>120	± 0.8						
						Format DIN A4	Projection	Scale 2:1			
						System NX V11.0					
						Replacement of Zg.gl.Nr.v.07.04.2000					
c	131778	2020-10-24	THAKARES			 MARQUARDT					
b	29172	2000-04-07	GUE								
a	16683	1985-05-30	Gü								
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by								

Ident.	Document number	Index
K	10190201	c
Snap Action Switch		
 MARQUARDT		