






A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
		0.75 to 1.25	19.2 -0.1	12.9+0.1
		1.25 to 2	19.4 -0.1	12.9+0.1
		2 to 3	19.8 -0.1	12.9+0.1
B	drawn in "ON" position			
				
				
C				
D	Marking 18.. 6(4)/250~ 5E4 T100/55 10(4)/250~ 5/50A 250V~  SPST Suitable for appliances of class II			
E	6A 125~250V AC 1/4 HP 125V AC 1/2 HP 250V AC R 30   Code of manufacture: place/year/week 			

-		-				-		1801.1119-XX				
Figure		Type				Customer Part No.		Art.No.-PI				
Shape and location 		Angle ± 2 ° Edge tolerance 		Length		Radii		Sheet 01		Ident. K	Document number 18011119	Index h
				0-6	± 0.2		±		± 0.2			
				>6-15	± 0.4		±		±			
				>15-30	± 0.4		±		±			
				>30-70	±		±		±			
				>70-120	±		±		±			
				>120-200	±		±		±			
					±		±		±			
					±		±		±			
										All dimensions are in millimetres		Appliance Switch
h	137838	2021-05-28		JOSHIO		System NX V1872						
g	61657	2009-01-20		VOR								
f	43724	2005-07-19		vor								
e	25088	1997-06-24		SIG		Replacement of Zg.gl.Nr.v.24.06.1997						
Index	MEC-No.	Date (YYYY-MM-DD)		Edited by								
 MARQUARDT												