




202 Series Fuse



Description

Fast-Acting and Slo-Blo® Fuse versions of the Flat-Pak® Fuse designs are available. Both designs are available in either a gull-wing surface mount package or a DIP configuration for through-hole mounting. These fuse designs feature a 250 VAC rating in a low profile, rectangular package.



Agency Approvals

AGENCY	AGENCY FILE NUMBER	AMPERE RANGE
	E10480	1/16mA - 5A
	LR29862	1/16mA - 5A

Electrical Characteristics for Series


% of Ampere Rating	Opening Time
100%	4 hours, Minimum
200%	2 seconds, Maximum

Electrical Specifications by Item

Ampere Rating (A)	Amp Code	Max Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I ² t (A ² sec)	Agency Approvals	
							
0.062	.062	250	50 amperes @250 VAC	7.9000	0.000220	x	x
0.125	.125	250		2.4500	0.00180	x	x
0.250	.250	250		0.8800	0.0147	x	x
0.500	.500	250		0.2980	0.0363	x	x
0.750	.750	250		0.1660	0.0980	x	x
1.00	001.	250		0.1190	0.192	x	x
1.50	01.5	250		0.0701	0.540	x	x
2.00	002.	250		0.0469	1.07	x	x
2.50	02.5	250		0.0455	1.76	x	x
3.00	003.	250		0.0327	1.71	x	x
4.00	004.	250		0.0244	3.00	x	x
5.00	005.	250		0.0174	4.68	x	x


202 Series

Temperature Derating Curve



Note:
 1. Derating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

Average Time Current Curves



Soldering Parameters


Wave Soldering	260°C, 3 seconds max.
Reflow Soldering	215°C, 30 seconds max.

Product Characteristics

Materials	Body: Thermoplastic Terminations: Tin/Lead Plated Copper
Solderability	MIL-STD-202, Method 208.


Cleaning	Board washable in most common solvents.
Operating Temperature	-55°C to 125°C

Dimensions




Part Numbering System

Surface Mount Fuses:



Through Hole Fuses:



202 Series

Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code
Surface Mount Fuses			
Bulk	—	100	HXG
24mm Tape and Reel	EIA RS-481-2 (IEC 286, part 3)	500	URG
Through Hole Fuses			
Antistatic Magazine	—	100	H

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[0202.062H](#) [0202.750H](#) [0202004.H](#) [0202.750URG](#) [020202.5H](#) [0202.250URG](#) [0202.062HXG](#) [0202.125HXG](#)
[0202.500H](#) [020201.5H](#) [0202002.HXG](#) [0202004.URG](#) [0202.125URG](#) [0202.250H](#) [0202001.HXG](#) [0202001.H](#)
[0202.750HXG](#) [0202003.HXG](#) [0202.500URG](#) [0202.500HXG](#) [0202003.URG](#) [020201.5URG](#) [0202001.URG](#)
[0202.062URG](#) [0202002.H](#) [0202003.H](#) [0202004.HXG](#) [020201.5HXG](#) [0202005.H](#) [0202002.URG](#) [0202005.URG](#)
[0202.125H](#) [0202005.HXG](#) [020202.5URG](#) [0202.250HXG](#) [020202.5HXG](#)