

Description


The DIODES™ AH1711/AH1712/AH1713/AH1714 is a low-voltage, high-sensitivity Hall effect latch IC designed for brushless DC-motor commutation speed measurement, angular or linear encoders and position sensors in industrial applications. To support a wide range of demanding applications, the design is optimized to operate at 2.4V to 5.5V. With chopper stabilized architecture and an internal bandgap regulator to provide temperature compensated supply for internal circuits, the AH1711/AH1712/AH1713/AH1714 provides a reliable solution over the whole operating range.

The open-drain output of AH1711/AH1712/AH1713 can be switched on when applying South pole with sufficient magnetic near the top of the package, while North pole with sufficient magnetic strength causes the open-drain output switched off. (AH1714 polarity inverted) When the magnetic flux density (B) perpendicular to the package is larger than the operate point (Bop) the output is switched on (pulled low). The output is held latched until magnetic flux density reverses and becomes lower than the release point (Brp).

Features

- Latch Operation
- High Sensitivity: Bop and Brp of ± 7 Gauss and ± 18 Gauss
- Open-Drain Output
- 2.4V to 5.5V Operating Voltage Range
- Chopper Stabilized Design Provides
 - Superior Temperature Stability
 - Minimal Switch Point Drift
 - Enhanced Immunity to Stress
- Good RF Noise Immunity
- -40°C to +125°C Operating Temperature
- ESD: HBM 8kV, CDM 2kV
- Industry Standard SOT23 Package
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green Device (Note 3)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](https://www.diodes.com/quality/product-definitions/) or your local Diodes representative.**
<https://www.diodes.com/quality/product-definitions/>

Pin Assignments




Applications

- Brushless DC-motor commutation
- Revolution per minute (RPM) measurements
- Wheel speed/angular/speed sensing
- Flow meters
- E-bikes
- Knobs

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

Typical Applications Circuit (Note 4)




Note: 4. C_{IN} is for power stabilization and to strengthen the noise immunity, the recommended capacitance is 10nF to 100nF. R_L is the pullup resistor.

Pin Descriptions

Package: SOT23

Pin Number	Pin Name	Function
1	V _{DD}	Power Supply Input
2	OUTPUT	Output
3	GND	Ground

Functional Block Diagram



Absolute Maximum Ratings (Notes 5 & 6) (@T_A = +25°C, unless otherwise specified.)

Symbol	Characteristic	Value	Unit
V _{DD}	Supply Voltage (Note 6)	-0.3 to 6.0	V
V _{OUT_MAX}	Output Off Voltage (Note 6)	6.0	V
I _{OUT}	Output Current	60	mA
B	Magnetic Flux Density	Unlimited	
P _D	Package Power Dissipation	SOT23 230	mW
T _S	Storage Temperature Range	-65 to +125	°C
T _J	Maximum Junction Temperature	+150	°C
ESD HBM	Electrostatic Discharge Withstand - Human Body Model (HBM)	8	kV
ESD CDM	Electrostatic Discharge Withstand - Charged Device Model (CDM)	2	kV

- Notes:
- Stresses greater than those listed under *Absolute Maximum Ratings* can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to *Absolute Maximum Ratings* for extended periods can affect device reliability.
 - The absolute maximum V_{DD} of 6V is a transient stress rating and is not meant as a functional operating condition. It is not recommended to operate the device at the absolute maximum rated conditions for any period of time.

Recommended Operating Conditions (@T_A = -40°C to +125°C, unless otherwise specified.)

Symbol	Parameter	Rating	Unit
V _{DD}	Supply Voltage	2.4 to 5.5	V
I _{OUT}	Output Sinking Current	0 to 20	mA
T _A	Operating Temperature Range	-40 to +125	°C

Electrical Characteristics (Notes 7 & 8) (@T_A = -40°C to +125°C, V_{DD} = 2.4V to 5.5V, unless otherwise specified.)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
V _{OL}	Low-Level Output Voltage	I _{OUT} = 20mA	—	0.2	0.4	V
I _{LKG}	Output Leakage Current (When Output is Off)	V _{OUT} = 5.5V, output off	—	< 0.1	3	μA
I _{DD}	Supply Current	Output open, T _A = +25°C	—	2.0	2.8	mA
		Output open, T _A = -40 to +125°C	—	—	3.2	mA
t _{P_ON}	Device Power-On Time (Startup Time)	V _{DD} ≥ 2.4V, B < Brp (min) - 10G B > Bop (max) + 10G (Note 7) dV _{DD} /dt > 2V/μs	—	38	70	μs
POS	Power-On State, Output	Power-up time < t _{P_ON} , B = 0	Low			—
f _c	Chopping Frequency	V _{DD} > 2.4V	—	800	—	kHz
t _d	Response Time Delay (Time from Magnetic Threshold Reached to the Start of the Output Rise or Fall)	(Note 9)	—	10	20	μs
t _r	Output Rising Time (External Pullup Resistor R _L and Load Capacitance Dependent)	R _L = 1kΩ, C _L = 20pF	—	0.2	1	μs
t _f	Output Falling Time (Internal Switch Resistance and Load Capacitance Dependent)	R _L = 1kΩ, C _L = 20pF	—	0.1	1	μs
f _{BW}	Sensing Bandwidth	B ≥ ±400G and square wave magnetic field (Note 9)	20	30	—	kHz
I _{OCL}	Output Current Limit	B > Bop (Note 10)	30	—	60	mA



- Notes:
- When power is initially turned on, V_{DD} must be within its correct operating range (2.4V to 5.5V) to guarantee the output sampling. The output state is valid after the startup time of 10μs typical from the operating voltage reaching 2.4V.
 - Typical values are defined at T_A = +25°C. Maximum and minimum values over the operating temperature range is not tested in production but guaranteed by design, process control and characterization.
 - Guaranteed by design, process control and characterization. Not tested in production.
 - The device will limit the output current to current limit of I_{OCL}.

Magnetic Characteristics (Notes 11 & 12) ($T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$, $V_{DD} = 2.4\text{V}$ to 5.5V , unless otherwise specified.)

(1mT = 10 Gauss)



Part Name	Symbol	Parameter	Conditions	Min	Typ	Max	Unit	Output Polarity
AH1711	Bop	Operation Point	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	-2	7	20	Gauss	Direct
	Brp	Release Point	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	-20	-7	2		
	B _{HY}	Hysteresis (Note 13)	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	3.5	14	—		
AH1712	Bop	Operation Point	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	5	18	37	Gauss	Direct
	Brp	Release Point	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	-37	-18	-5		
	B _{HY}	Hysteresis (Note 13)	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	23	36	—		
AH1713	Bop	Operation Point	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	16	50	81	Gauss	Direct
	Brp	Release Point	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	-81	-50	-16		
	B _{HY}	Hysteresis (Note 13)	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	60	100	—		
AH1714	Bop	Operation Point	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	5	18	37	Gauss	Inverted
	Brp	Release Point	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	-37	-18	-5		
	B _{HY}	Hysteresis (Note 13)	$T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	23	36	—		

- Notes:
- When power is initially turned on, V_{DD} must be within its correct operating range (2.4V to 5.5V) to guarantee the output sampling. The output state is valid after the startup time of 38 μs typical from the operating voltage reaching 2.4V.
 - Typical values are defined at $T_A = +25^{\circ}\text{C}$. Maximum and minimum values over the operating temperature range is not tested in production but guaranteed by design, process control and characterization.
 - Maximum and minimum hysteresis is guaranteed by design, process control and characterization.




Typical Operating Characteristics


Supply Current





Low-Level Output Voltage, $I_{OUT} = 20\text{mA}$



Output Leakage Current




Output Rising/Falling Time




Typical Operating Characteristics (continued)

Device Power-On Time (Startup Time)




Power On Time t_{P_ON} vs. Temperature

Output Current Limit (I_{OCL})




Current Limit I_{OCL} vs. Temperature


AH1711 - BOP/BRP Switch Point and Hysteresis B_{HY}




Switch Point vs. Supply Voltage V_{DD}



Operation Point BOP vs. Temperature







Release Point BRP vs. Temperature



Hysteresis B_{HY} vs. Temperature


Typical Operating Characteristics (continued)

AH1712/AH1714 - Switch Point B_{OP}/B_{RP} and Hysteresis B_{HY}



Application Information


Power-On State (POS)




Thermal Performance Characteristics

Package : SOT23

T_A (°C)	25	50	60	70	80	85	90	100	105	110	120	125
P_D (mW)	230	184	166	147	129	120	110	92	83	74	55	46



Ordering Information




Part Number	Part Number Suffix	Package Code	Package	Packing	
				Qty.	Carrier
AH1711-SA-7	-7	SA	SOT23	3,000	7" Tape & Reel
AH1712-SA-7	-7	SA	SOT23	3,000	7" Tape & Reel
AH1713-SA-7	-7	SA	SOT23	3,000	7" Tape & Reel
AH1714-SA-7	-7	SA	SOT23	3,000	7" Tape & Reel

Marking Information

Package Type: SOT23

(Top View)




XX : Identification Code
 Y : Year 0 to 9 (ex: 2 = 2022)
 W : Week : A to Z : week 1 to 26;
 a to z : week 27 to 52; z represents
 week 52 and 53
 X : Internal Code

Part Number	Package	Identification Code
AH1711-SA-7	SOT23	XK
AH1712-SA-7	SOT23	XM
AH1713-SA-7	SOT23	XN
AH1714-SA-7	SOT23	XP


Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.


SOT23



SOT23			
Dim	Min	Max	Typ
A	0.37	0.51	0.40
B	1.20	1.40	1.30
C	2.30	2.50	2.40
D	0.89	1.03	0.915
F	0.45	0.60	0.535
G	1.78	2.05	1.83
H	2.80	3.00	2.90
J	0.013	0.10	0.05
K	0.890	1.00	0.975
K1	0.903	1.10	1.025
L	0.45	0.61	0.55
L1	0.25	0.55	0.40
M	0.085	0.150	0.110
a	0°	8°	--
All Dimensions in mm			



TOP VIEW




Side VIEW

Sensor Location

Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

SO23



Dimensions	Value (in mm)
C	2.0
X	0.8
X1	1.35
Y	0.9
Y1	2.9

Mechanical Data

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish – Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (E3)
- Weight: 0.009 grams (Approximate)

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
DIODES is a trademark of Diodes Incorporated in the United States and other countries.
All other trademarks are the property of their respective owners.
© 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com