


# MI0-2375

## 11th Gen. Intel® Core™ i7/i5/i3 U-series Pico-ITX SBC

### Preliminary



### Specifications

Platform	Processor	i7-1185G7E	i7-1185GRE	i5-1145G7E	i3-1115G4E
	Max. Frequency	4.40 GHz	4.40 GHz	4.10 GHz	3.90 GHz
	Base Frequency	1.80 GHz	1.80 GHz	1.50 GHz	2.20 GHz
	Core/Tread	4/8	4/8	4/8	2/4
	LLC	12MB	12MB	8MB	6MB
	CPU TDP	15W	15W	15W	15W
	Chipset	Intel 300 Series Chipset (SoC Integrated)			
Memory	BIOS	AMI EFI 256Mbit			
	Technology	LPDDR4x-4267			
	Max. Capacity	Up to 32GB			
	Channel/Socket	Single or Dual Channels / Onboard			
Graphics	ECC Support	No	Yes	No	No
	Controller	Integrated Intel® Iris® Xe Graphics			
	Max. Frequency	1.35 GHz	1.35 GHz	1.30 GHz	1.25 GHz
	Graphics Memory	TBU	TBU	TBU	TBU
	3D/HW Acceleration	DX12, OGL4.0, OCL1.2, HW Encode: H.265/HEVC, H.264, MPEG2, HW Decode: H.264			
Display I/F	LCD	eDP1.4 HBR3, up to 4096x2304x36bpp@60Hz; with DSC 7680x4320x30bpp@60 Hz			
	HDMI/DP	Optional MIPI-DSI 2.56GHz, up to 3200x2000x24bpp@60Hz; with DSC 5120x3200x24bpp@60 Hz			
	Multiple Display	1 x DP1.4 (DP++), up to 4096x2304x36bpp@60Hz; with DSC 7680x4320x30bpp@60 Hz			
Ethernet	Controller	Dual simultaneous displays by eDP/MIPI-DSI + DP			
	Speed	LAN1: Intel 219LM, LAN2: Intel 210AT/IT			
	Speed	10/100/1000 Mbps			
External I/O	Ethernet	2 x RJ-45			
	VGA/HDMI/DP	-/-/1			
	USB3.2/USB2.0	2/-			
	Power DC-Jack	Optional			
Internal I/O	SATA	1 x SATA GenIII 6.0Gbps			
	USB2.0	2			
	Serial Bus	I2C (default), SMBus* (optional)			
	COM Port	1 x RS-232/422/485, 1 x RS-232			
	GPIO	4-bit general purpose input output I/O			
	Audio	Realtek ALC888s, Line-in/Line-out/MIC			
	Inverter	12V			
	Fan	12V, 1A (4-wire)			
	Front Panel Control	Power-on, Reset, Buzzer, SATA LED, CaseOpen			
	Watchdog Timer	65536 level, 0-65535 sec			
Board Feature	TPM	TPM2.0			
	iManager 3.0	SW API for Hardware Monitor, Smart Fan Control, Brightness Control, I2C, GPIO, WDT			
	M.2 E-Key	1 x E-Key 2230 (PCIe x1, USB2.0)			
Expansion	M.2 B-Key/ M.2 M-Key	1 x B-Key 3042/2242 (SATA x1, USB2.0 x1) w/ Nano-SIM			
		*Optional 1 x M-Key 2242 (PCIe x2 NVMe)			
Power	Supply Voltage	Vin: DC 12V ± 10%; RTC Battery: Lithium 3V/210mAh			
	Connector	ATX 2pin 180D, optional DC-Jack			
	Power Management	AT, ATX			
	Max. Consumption	20.491W	TBU	20.411W	21.198W
Environment	Idle Consumption	17.368W	TBU	16.872W	13.991W
	Temperature	Operating: Standard: 0 ~ 60 °C (32 ~ 140 °F) Operating: Extend: -40 ~ 85 °C (-40 ~ 185 °F) for Industrial Sku Storage: -40 ~ 85 °C (-40 ~ 185 °F)			
	Humidity	Operating: 40 °C @ 95% relative humidity, non-condensing Storage: 60 °C @ 95%relative humidity, non-condensing			
	Vibration Resistance	3.5 Grms			
Certification	EMC	CE, FCC Class B			
Mechanical	Dimensions	100 x 72 mm (3.9" x 2.8")			
	Net Weight	80g			

\*Note: Support by request

**ADVANTECH**

**MI/O Extension SBCs, Modules and Chassis**


All product specifications are subject to change without notice.

Last updated: 16-Aug-2021


### Features

- 11th Gen. Intel® Core™ Processor with Quad/Dual Cores, TDP 15W
- On-board LPDDR4x-4267 up to 32G with IB ECC for Industrial Sku
- Dual independent display: eDP/MIPI-DSI, DP up to 8K
- 2 GbE, 2 USB 3.2, COM Port, SMBus/I2C
- Expansion: M.2 E-Key, M.2 B-Key/M-Key NVMe x2
- Supports iManager & Software APIs, WISE-DeviceOn, and Edge AI Suite

#### Software APIs:



## Block Diagram



## Ordering Information

Part No.	CPU	Max. Frequency	Core	Memory	Sim Holder	TPM	Thermal Solution	Operating Temperature
MIO-2375C7P-Q4A1	i7-1185G7E	4.40 GHz	4	16GB	Yes	Yes	Active	0 ~ 60 °C
MIO-2375C5P-Q1A1	i5-1145G7E	4.10 GHz	4	16GB	Yes	Yes	Active	0 ~ 60 °C
MIO-2375C3P-P9A1	i3-1115G4E	3.90 GHz	2	8GB	Yes	Yes	Active	0 ~ 60 °C

## Packing List

Part No.	Description	Quantity
	MIO-2375 SBC	
	Startup Manual	
1700006291	SATA cable 30cm	1
1700027546-01	A CABLE SATA Power 15P/1*4P-2.5 15cm	1
1700030406-01	M Cable 2*5P-2.0/USB-A 4P(F)*2 20cm	1
1700030404-01	RS-232 9P(M)/1*10P-1.25 20cm	2
1700019584-01	A Cable 2*5P-2.0/Audio JACK*3 20cm	1
1700019705-01	AT power cable 12 cm	1
1970004956T001	MIO-2375 Cooler	1

## Optional Accessories

Part No.	Description
1970004968N001	MIO-2375 Heatspreader

## Embedded OS/API

OS	Part No.	Description
WIN10	TBD	64-bit (UEFI mode only)
Ubuntu 20.04 LTS	TBD	
Software API	Download by website	
Yocto BSP		


## Rear I/O View



# Reliable Embedded BIOS Solutions

## Custom BIOS services with long-term support

Advantech's high-quality embedded BIOS solutions deliver rapid execution and feature expert BIOS team support. These solutions feature multi-functional designs that ensure security and enable power/boot management. Advantech further provides 10+ years of BIOS version management, internal management, and longevity support for both hardware and BIOS — enhancing application efficiency, diversifying functionality, and optimizing performance.



### Embedded BIOS Solution Advantages

#### Sufficient Sources

- Strong partnership with BIOS vendors
- 50+ engineers with extensive industrial BIOS experience


#### Diverse BIOS Functions

- Multi-layer security
- 3 second fast boot
- Power management
- BIOS suite utility

#### Long-Term Maintenance Services

- Platform longevity support
- 10-year BIOS version control
- BIOS remote backup

### Value-Added Customization Process



# Embedded Linux Support and Design-in Services

## Hardware Certified Ubuntu and Yocto with Eco Partner Services

Linux is the most popular embedded OS for transportation, outdoor services, factory automation, and mission critical applications. Its open source and kernel reliability features ease security updates, and make it particularly adaptable to new AI and Edge computing technology. Advantech has cooperated with Canonical and other software partners to provide hardware certified Ubuntu image and Yocto BSP as Linux offerings. The Advantech, Embedded Linux, and Android Alliance (ELAA) delivers local software services and consultation.



### Features

Certified OS and BSP	Licensed Services	Numerous AI and Edge Resources	Local Partner Alliance
<ul style="list-style-type: none"> <li>Platform compatibility tests</li> <li>Preloaded functional driver and software stacks</li> </ul>	<ul style="list-style-type: none"> <li>License authorized Canonical delivers 10-years of bug fixes and security updates</li> <li>In-house bundled service</li> </ul>	<ul style="list-style-type: none"> <li>Containerized technology for service provision and deployment</li> <li>AI resources from Caffe, TensorFlow, and mxnet</li> </ul>	<ul style="list-style-type: none"> <li>Embedded Linux and Android Alliance (ELAA)</li> </ul>

# Edge AI Suite

## AI development for diverse application at the Edge

Increasing demand for AI inference/analytic capabilities at the Edge make AI training models, software development environments, and hardware configuration key factors in successful solution deployment. Advantech's Edge AI Suite helps users build AI demo devices quickly and choose optimal hardware solutions easily.



5x Performance Boost	All-in-one Installation	One Click AI Experience	Plug-and-play Environment	Discover Cost-effective Hardware
<ul style="list-style-type: none"> <li>Integrated Intel® OpenVINO™ technology</li> <li>Boost AI using Advantech hardware</li> </ul>	<ul style="list-style-type: none"> <li>Build AI environment in under 5 minutes</li> <li>Ready-to-use configuration</li> </ul>	<ul style="list-style-type: none"> <li>User friendly configuration guidance</li> <li>One-click Benchmark acquisition</li> </ul>	<ul style="list-style-type: none"> <li>Easy access to 100+ AI inference extensions</li> <li>Software development package available</li> </ul>	<ul style="list-style-type: none"> <li>Diverse CPU/RAM options</li> <li>Find hardware solutions for AI development</li> </ul>



# WISE-DeviceOn

## Massive IoT Device Management Utility

IoT deployment and management typically involves numerous disparate devices installed on multiple sites. These devices require effective monitoring, managing, and tracking. Advantech's easy-to-use WISE-DeviceOn interface enables users to remotely monitor device health, troubleshoot problems, and send software/firmware updates over-the-air (OTA). In sum, DeviceOn empowers quick real-time responsiveness to emerging problems.



### Features

#### Comprehensive Management

- Devices status
- Peripherals/firmware
- Open for extension

#### Remote Access

- Real-time monitoring
- Remote controls
- Troubleshooting

#### Efficient Operations

- Zero-touch on-boarding
- OTA updates
- Batch control

### Product Highlights



**SOM-6883**

High-performance 11<sup>th</sup> Gen Intel® COMe Type 6 Module



**MIO-5375**

Compact 11<sup>th</sup> Gen Intel® Outdoor Focused 3.5" SBC



**EPC-B5587**

10<sup>th</sup> Gen Intel® Xeon® based Edge server



**EPC-R3220**

Arm based IoT Edge Gateway