

EPM78Vx

Non-isolated DC-DC converter



Product features

- Switching regulator, Non-isolated DC-DC converter
- Convenient 3-Pin SIP Package compatible with LM78xx linear regulator
- Input voltages: 4.75 V to 32 Vdc
- 6 SKU's representing 6 output voltages (1.8 V – 15 V) @ 1A output current
- Efficiency up to 96%
- Operating ambient temperature -40 °C to +90 °C
- Continuous short circuit protection
- EN62368 safety approval

Applications

- Industrial
 - Automation & testing equipment
 - Displays
 - Lighting
 - IoT
 - Power Supply
- Energy
 - Solar and wind inverters
 - Battery management
- Medical
 - Hospital & home care equipment
 - Inventory tracking
 - Diagnostics
- Telecom
 - Networking and telecommunications
 - Infrastructure

Environmental compliance

RoHS

Ordering part number

	<u>EPM</u>	<u>78</u>	<u>Vx-</u>	<u>01R8-</u>	<u>01R0</u>	<u>R</u>
Eaton converter	_____	_____	_____	_____	_____	_____
Package type/size code	_____	_____	_____	_____	_____	_____
Vx= Version code	_____	_____	_____	_____	_____	_____
Output voltage maximum (R = decimal point)	_____	_____	_____	_____	_____	_____
Output current maximum (R = decimal point)	_____	_____	_____	_____	_____	_____
R=Standard, P=Positive logic, N= Negative logic	_____	_____	_____	_____	_____	_____



Powering Business Worldwide

Specifications

	Parameter	Conditions	Minimum	Typical	Maximum	Unit
Input	Input voltage range			24		Vdc
Output	Efficiency	Vo = 1.8 Vdc @ min. Vin		86		%
		Vo = 3.3 Vdc @ min. Vin		90		%
		Vo = 5.0 Vdc @ min. Vin		93		%
		Vo = 6.5 Vdc @ min. Vin		94		%
		Vo = 12 Vdc @ min. Vin		95		%
		Vo = 15 Vdc @ min. Vin		96		%
	Minimum load			1		%
	Line voltage regulation	LL-HL		0.2	0.4	%
	Load voltage regulation	10-100% Load		0.4	0.6	%
	Voltage accuracy			±3		%
	Operating frequency	100% Load at nominal Vin		500		kHz
	Ripple & noise	Vo = 1.8 Vdc			50 ⁽¹⁾	mVp-p
		Vo = 3.3 Vdc			50	mVp-p
		Vo = 5.0 Vdc			50	mVp-p
		Vo = 6.5 Vdc			75 ⁽²⁾	mVp-p
		Vo = 12 Vdc			100	mVp-p
		Vo = 15 Vdc			100	mVp-p
Environment	Operating temperature	With derating	-40		+90	°C
	Storage temperature		-55		+125	°C
	Relative humidity				95	%RH
	Temperature coefficient			0.015		%/°C
	Maximum case temperature				105	°C
	Vibration			MIL-STD-202G		
Function	Short circuit protection			Continuous, automatic recovery		
	Safety			EN 62368-1		
	MTBF	MIL-HDBK217F	13300			hours
Physical	Dimension			0.457 (L) x 0.402 (W) x 0.300 (H)		inches
	Weight			1.9		g
	Cooling method			Free air convection		
	Case material			Non conductive black plastic		
EMC	EMI	EN 55032		Class A/B		
	ESD	EN61000-4-2 Air ± 8 kV Contact ± 6 kV		Criteria A		
	Fast transient ³	EN 61000-4-4, ±2 kV		Criteria A		
	Surge ³	EN 61000-4-5, ±2 kV		Criteria A		

1. If you use 26 V input and the loading is less 5%, the R&N will be 100 mVp-p maximum

2. With a 4.7 µF/ 50 V X7R MLCC, the R&N will be 50 mVp-p maximum

3. External input capacitor required 1500 µF/ 50 V.

4. The product information and specifications are subject to change without prior notice.

5. All specifications valid at 24 V input, full load and +25 °C after warm-up time unless otherwise stated.

Selection guide


Part number	Input voltage	Output voltage	Output current @ full load	Input current @ no load	Efficiency (typical) ¹ Vin minimum/ Vin maximum	Capacitive load ² maximum
EPM78V1-01R8-01R0R	4.75 - 26 Vdc	1.8 Vdc	1000 mA	10 mA	86.0/77.5%	470 µF
EPM78V2-03R3-01R0R	4.75 - 32 Vdc	3.3 Vdc	1000 mA	12 mA	90.0/82.5%	470 µF
EPM78V2-05R0-01R0R	6.5 - 32 Vdc	5.0 Vdc	1000 mA	16 mA	93.0/86.0%	470 µF
EPM78V2-06R5-01R0R	8 - 32 Vdc	6.5 Vdc	1000 mA	20 mA	94.0/88.0%	470 µF
EPM78V2-12R0-01R0R	15 - 32 Vdc	12 Vdc	1000 mA	23 mA	95.0/92.0%	470 µF
EPM78V2-15R0-01R0R	18 - 32 Vdc	15 Vdc	1000 mA	25 mA	96.0/93.0%	330 µF

1. The efficiency is test by max./ min. input voltage and full load @ +25 °C, and ±2% tolerance


2. The capacitive load is test by minimum input and constant resistive load

3. All specifications valid at 24 V input voltage, full load and +25 °C after warm-up time unless otherwise stated

Measuring circuit




Derating curve




The derating curve was measured at 24 V input

Standard application circuit




EMC filtering circuit




Class	C1	L1	C2
Class A	1206 4.7 μ F 50 V MLCC	3.3 μ H	x
Class B	1210 10 μ F 50 V MLCC	10 μ H	1206 4.7 μ F 50 V MLCC

EFT and surge circuit




C1
1500 μ F/ 50 V

Mechanical dimension and pinning - inches




Pin	Function
1	+Vin
2	GND
3	+Vout

Recommended pad layout




Marking




xxx= lot code

Projection: Third angle projection
Tolerance: X.XX ± 0.02 X.XXX ± 0.01
PIN tolerance: ± 0.004

Packaging- Inches



Tolerance : ±0.02"
1 Tube = 42 pcs
Length : 20.47"±0.08"



Carton=21.46*5.71*3.94 inch
MOQ=42(pcs/tube)*12(tube/bundle)*3(bundle)=1512pcs~4Kg


General information

Storage and handling

The shelf life will be a minimum of 12 months, when stored at the following conditions: $< 40^{\circ}\text{C}$, $< 90\%$ relative humidity.

Wave solder profile

The wave solder profile is measured based on lead temperature. The internal temperature of the solder parts should not exceed $+210^{\circ}\text{C}$. The duration of solder dwell time should be between 3 to 5 seconds, and not to exceed 10 seconds.



Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2020 Eaton
All Rights Reserved
Printed in USA
Publication No. 11181 BU-MC20158
October 2020

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

