




# PRODUCT BRIEF

*Slim, intelligent, full colour GEN4 display modules powered by 4D LABS DIABLO-16 processors*



**4D SYSTEMS**  
 MAKING HUMAN INTELLIGENCE SMARTER  
[www.4dsystems.com.au](http://www.4dsystems.com.au)











# THE SOLUTION FOR EMBEDDED DISPLAYS & TOUCHSCREENS






The GEN4 series of display modules has been designed by 4D SYSTEMS to minimise the impact of display related circuitry and provide a platform suitable for integration into a product that will substantially benefit from an embedded display solution. Designed specifically for ease of integration and use, with careful consideration for space requirements and functionality, the GEN4 Series is 100% compatible with the Workshop4 IDE and its 4 different development environments, providing product designers and engineers with a wealth of options for programming and controlling their system.

## PROCESSOR SPECIFICATIONS

	PICASO	DIABLO-16
 DISPLAY SUPPORT	Supports OLED, LCD & TFT displays	
 SD CARD SUPPORT	Micro-SD: up to 2GB SDHC: 4GB and above	
 AUDIO SUPPORT	Audio support for wave files & complex sound generation with a dedicated 16-bit PWM audio output	
 FILE ACCESS	DOS compatible file access (FAT16 format)	
 MEMORY	Flash memory for user codes: 14KB  SRAM for user variables: 14KB	Flash memory for user codes: 6 banks x 32KB  SRAM for user variables: 32K
 SPECIAL FEATURES	Built in high performance virtual processor core(EVE) optimised for 4DGL,the high-level 4DGraphics Language, using ~ 1/10 of the code -space compared to most other processor implementations	30 pin FPC connection for all signals, power & communications, including 16 general purpose I/O pins for user interfacing, which include 4 variously configurable analogue inputs for alternative functions.



## DISPLAY SPECIFICATIONS

	DISPLAY SIZE	2.4" - 7.0" Cover lens bezel available for display sizes from 3.2" and above
	DISPLAY RESOLUTION	240 x 320; 480 x 272; 480 x 320; 800 x 480
	DISPLAY RESOLUTION	150 - 1000 nits
	DISPLAY TYPES	Resistive; Capacitive; non-touch
	SUPPORTED PROCESSORS	PICASO & DIABLO-16 by 4D LABS
	IDE	Fully supported by Workshop4 IDE
	FONT AVAILABILITY	Supports Window fonts
	MODULE CAPABILITY	Audio, full color images, animations, icons & video clips
	IoT CAPABILITY	Yes, upon request
	CUSTOM DESIGN CAPABILITY	Yes, upon request
	RoHS COMPLIANCE	Yes
	CE COMPLIANCE	Yes





#### OPTIMISED SPACE USE

When space is limited, our GEN4 Series provides sleek adaptability without compromising on the aesthetics. Applications like elevator call buttons should be more than a mechanical button; they can be an architectural expression of aesthetic design, just as display screens that might be needed in industrial applications with limited space but still maintaining aesthetic graphical user interface.



#### DIGITAL TRANSFORMATION

Transition your product from traditional knobs and buttons to a digital display interface, or when designing new range of products, the GEN4 Series is versatile and offers transformational benefits ranging from:

- Incorporating significantly increased number of choices, right at your fingertips;
- The ability to incorporate IoT options that help make smarter choices;
- Offering a hygienically safer surface by utilising touchscreen displays and remote interfaces;
- Reducing maintenance costs as well as digitally upgrading better options and choices.



#### INTERACTIVE ENVIRONMENT

From interactive features in cars, to industrial workspace the PICASO & DIABLO-16 processors that drive the GEN4 series of embedded display solutions, can be programmed using our Workshop4 IDE even by a novice. And engineers and product designers can incorporate functions limited only by their imagination.



+61 2 9625 9714



[sales@4dsystems.com.au](mailto:sales@4dsystems.com.au)



[www.4dsystems.com.au](http://www.4dsystems.com.au)



**4D SYSTEMS**  
MAKING HUMAN INTELLIGENCE SMARTER