

ACW4 IO-LINK


IO-LINK SPECIFICATION INFORMATION

Device specification

Specification	IO-Link description	Value
Transfer rate	COM3	230.4 kBaud
Minimum cycle time of device	Minimum cycle time	0x0A (1ms)
Frame specification Amount of preoperate data required Amount of operate data required Enhanced parameters	M-Sequence Capability: M-Sequence Type Preoperate M-Sequence Type Operate ISDU supported	TYPE_0 TYPE_2_V Supported
IO-Link protocol version	Revision ID	0x11 (Version 1.1)
Amount of process data from the device to the master	ProcessDataIn	0x81 (2 bytes)
Amount of process data from the master to the device	ProcessDataOut	0x00 (0 byte)
Manufacturer ID	Vendor ID	0x0468 (1128)
Device identification	Device ID	0x0002

Process data

Name	Description	Datatype	Bitoffset	Bitlength	Value Range	Unit
Position	Absolute position inside turn	IntegerT	2	14	0 to 4095	
Flag2	Reserved	BooleanT	1		False True	
Flag1	Magnetic field issue Problem with the magnet position	BooleanT	0		False True	




Note: bits 14 and 15 are '0'

Identification data

Index (hex)	Subindex	Name	Data type	Access	Contents	Comment
16 (0x10)	0	Vendor Name	StringT	RO	BEI Sensors	
17 (0x11)	0	Vendor Text	StringT	RO	Sensata Technologies Inc.	
18 (0x12)	0	Product Name	StringT	RO	ACW4-ZIO	
19 (0x13)	0	Product ID	StringT	RO	ACW4	
20 (0x14)	0	Product Text	StringT	RO	Absolute modular singleturn sensor	
21 (0x15)	0	Serial Number	StringT	RO		
22 (0x16)	0	Hardware Version	StringT	RO		
23 (0x17)	0	Firmware Version	StringT	RO	V1.1	
24 (0x18)	0	Application Specific Tag	StringT	RW	***	

ELECTRICAL INSTALLATION

BD : PUR Cable M12 5 pins (device class B)

Pin number	Color	Description	Illustration
1	Brown	L+ : power supply V+	
2	White	N.C.	
3	Blue	L-: power supply, 0V (ref)	
4	Black	IO-Link	
5	Grey	N.C.	

System command

Index (hex)	Subindex	Name	Data type	Access	Value range
2 (0x02)	0	System-Command	UIntegerT 8	WO	130 (0x82) : Restore factory settings
12 (0x6E)	0	Device Access Locks	UIntegerT 16	RW	<p>Byte 0</p> <p>Bit 0: parameter write protection 0: Parameters modification permitted 1: Parameters modification is locked</p> <p>Bit 1: data storage into the non-volatile memory. 0: Data storage modification permitted 1: Data storage modification is locked</p> <p>Byte 1 : unused</p>

Diagnosis parameters

Index (hex)	Subindex	Name	Data type	Access	Value range	Comment
110 (0x6E)	0	Operating hours	UIntegerT 32	RO	0 to 4294967295	

Sensata specific parameters, Observer and Maintenance access

Index	Subindex	Name	Data type	Access	Value range	Comment
64 (0x40)	0	Set Zero Point	Button	WO		Set zero point
65 (0x41)	0	Set Preset	Button	WO		Set Preset
66 (0x42)	0	Rotation direction	BooleanT	RW	false : CW true : CCW	Set the rotation direction
67 (0x43)	0	Preset value singleturn	UIntegerT	RW	0 to 4095	Preset for the position inside the turn
80 (0x50)	0	Singleturn Resolution	UIntegerT	RW	1 to 12	Resolution for the position in a turn (in bits)

Sensata specific parameters, Specialist access

Index	Subindex	Name	Data type	Access	Value range	Comment
252 (0xFC)	0	Test parameter 252	UIntegerT 8	RW	0 : A appears 1 : A disappears 2 : B appears 3 : B disappears	Do not use For IO-link test purpose.

Factory settings parameters

Name	Factory Setting	Comment
Rotation direction	false : CW	Set the rotation direction
Preset value singleturn	0	Preset for the position inside the turn
Singleturn Resolution	12	Resolution for the position in a turn (in bits)
Operating-hours	0	Number of hours with device on
Magnetic field issue flag	false	Process data flag

Events

Code	Name	Type	Description
16912 (0x4210)	Device temperature over-run	Warning	Temperature above limits
36350 (0x8DFE)	Test Event A	Error	Event appears by setting index 252 to value 1, Event disappears by setting index 252 to value 2
36351 (0x8DFF)	Test Event B	Error	Event appears by setting index 252 to value 3, Event disappears by setting index 252 to value 4

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

CONTACT US

Americas

+1 (800) 350 2727
sensors@sensata.com

Europe, Middle East & Africa

+33 (3) 88 20 8080
position-info.eu@sensata.com

Asia Pacific

sales.isasia@list.sensata.com
China +86 (21) 2306 1500
Japan +81 (45) 277 7117
Korea +82 (31) 601 2004
India +91 (80) 67920890
Rest of Asia +886 (2) 27602006
ext 2808