



Sample Kit 1007

TDK Part #	Case Size	Temperature Coefficient	Voltage (DC)	Value	Tolerance Code	Tolerance Value	Thickness
C0603COG1E0R2WTQ	0603	C0G	25	0.2pF	W	+/-0.05pF	0.30
C0603COG1E0R3WTQ	0603	C0G	25	0.3pF	W	+/-0.05pF	0.30
C0603COG1E0R4WTQ	0603	C0G	25	0.4pF	W	+/-0.05pF	0.30
C0603COG1E0R5WTQ	0603	C0G	25	0.5pF	W	+/-0.05pF	0.30
C0603COG1E0R6WTQ	0603	C0G	25	0.6pF	W	+/-0.05pF	0.30
C0603COG1E0R7WTQ	0603	C0G	25	0.7pF	W	+/-0.05pF	0.30
C0603COG1E0R8BTQ	0603	C0G	25	0.8pF	B	+/-0.10pF	0.30
C0603COG1E0R9WTQ	0603	C0G	25	0.9pF	W	+/-0.05pF	0.30
C0603COG1E010BTQ	0603	C0G	25	1pF	B	+/-0.10pF	0.30
C0603COG1E1R1BTQ	0603	C0G	25	1.1pF	B	+/-0.10pF	0.30
C0603COG1E1R2BTQ	0603	C0G	25	1.2pF	B	+/-0.10pF	0.30
C0603COG1E1R3BTQ	0603	C0G	25	1.3pF	B	+/-0.10pF	0.30
C0603COG1E1R5BTQ	0603	C0G	25	1.5pF	B	+/-0.10pF	0.30
C0603COG1E1R6BTQ	0603	C0G	25	1.6pF	B	+/-0.10pF	0.30
C0603COG1E1R8BTQ	0603	C0G	25	1.8pF	B	+/-0.10pF	0.30
C0603COG1E020BTQ	0603	C0G	25	2pF	B	+/-0.10pF	0.30
C0603COG1E2R2BTX	0603	C0G	25	2.2pF	B	+/-0.10pF	0.30
C0603COG1E2R4BTX	0603	C0G	25	2.4pF	B	+/-0.10pF	0.30
C0603COG1E2R7BTX	0603	C0G	25	2.7pF	B	+/-0.10pF	0.30
C0603COG1E030BTX	0603	C0G	25	3pF	B	+/-0.10pF	0.30
C0603COG1E3R3BTX	0603	C0G	25	3.3pF	B	+/-0.10pF	0.30
C0603COG1E3R6BTX	0603	C0G	25	3.6pF	B	+/-0.10pF	0.30
C0603COG1E3R9BTX	0603	C0G	25	3.9pF	B	+/-0.10pF	0.30
C0603COG1E040BTX	0603	C0G	25	4pF	B	+/-0.10pF	0.30
C0603COG1E4R3BTX	0603	C0G	25	4.3pF	B	+/-0.10pF	0.30
C0603COG1E4R7BTX	0603	C0G	25	4.7pF	B	+/-0.10pF	0.30
C0603COG1E050BTX	0603	C0G	25	5pF	B	+/-0.10pF	0.30
C0603COG1E5R1BTX	0603	C0G	25	5.1pF	B	+/-0.10pF	0.30
C0603COG1E5R6BTX	0603	C0G	25	5.6pF	B	+/-0.10pF	0.30
C0603COG1E060BTX	0603	C0G	25	6pF	B	+/-0.10pF	0.30
C0603COG1E6R2BTX	0603	C0G	25	6.2pF	B	+/-0.10pF	0.30
C0603COG1E6R8BTX	0603	C0G	25	6.8pF	B	+/-0.10pF	0.30
C0603COG1E070BTX	0603	C0G	25	7pF	B	+/-0.10pF	0.30
C0603COG1E7R5BTX	0603	C0G	25	7.5pF	B	+/-0.10pF	0.30
C0603COG1E080BTX	0603	C0G	25	8pF	B	+/-0.10pF	0.30
C0603COG1E8R2BTX	0603	C0G	25	8.2pF	B	+/-0.10pF	0.30
C0603COG1E090BTX	0603	C0G	25	9pF	B	+/-0.10pF	0.30
C0603COG1E9R1BTX	0603	C0G	25	9.1pF	B	+/-0.10pF	0.30
C0603COG1E100ETX	0603	C0G	25	10pF	E	+/-0.20pF	0.30