Light is freedom of design The new SYNIOS® P2720 platform

One family. One footprint. Full performance & flexibility.



Light is OSRAM

Full performance, high flexibility

OSRAM Opto Semiconductors' new SYNIOS[®] P2720 platform with 15 different products allows for outstanding flexibility with one footprint for various power classes and applications. Ease of scalability and great freedom of design are accompanied and amplified by high thermal reliability and high brightness, delivering new opportunities and cost advantages for automotive manufacturers and light designers.



Designed for a large number of applications from midpower to highpower

SYNIOS [®] family		InGaN white	InGaN CY yellow	InGaAIP yellow	InGaAIP red	InGaAIP superred
		÷.	Ç.	\$	\$ 20	\$ 2
	Туре	KW DMLS31.SG	KY DMLS31.FY	KY DMLS31.23	KR DMLS31.23	KS DMLS31.23
	Brightness (Im@mA)	190/245 min/typ	90/120 min/typ	63/95 min/typ	71/120 min/typ	56/85 min/typ
1mm²	Bin (brightness-cxcy)	5MF5N-ebvF46- fcbB46	7K6LF – 5F	8J7L – 4-6	5K8L – 2-6	7J8K – 1
	Rth real typ (K/W)	~7	~7	~7	~7	~7
	Binning If/Max If (mA)	700/1000	600/700	700/1000	700/1000	700/1000
	Vf typ	3.00	3.00	2.35	2.25	2.25
	Efficiency (Im/W)	~110	~60	~65	~80	~50
						Data may va

ay vary



	Туре	KW DMLQ31.SG	KY DMLQ31.FY	KY DMLQ31.23	KR DMLQ31.23	KS DMLQ31.23
	Brightness (Im@mA)	90/125 min/typ	42.4/55 min/typ	33/45 min/typ	33/55 min/typ	28/40 min/typ
Ē	Bin (brightness-cxcy)	7K6LF-ebvF46- fcbB46	8HF8J –5F	HYJZ – 4-6	HYKX – 2-6	HXJY – 1
20	Rth real typ (K/W)	~10	~10	~10	~10	~10
7	Binning If/Max If (mA)	350/700	300/400	350/500	350/500	350/500
	Vf typ	3.00	3.0	2.35	2.25	2.25
	Efficiency (Im/W)	~110	~60	~65	~80	~50

Data may vary







Туре	KW DMLN31.SG	KY DMLN31.FY	KY DMLN31.23	KR DMLN31.23	KS DMLN31.23
Brightness (Im@mA)	50/65 min/typ	22.4/30 min/typ	21/25 min/typ	21/35 min/typ	15/20 min/typ
Bin (brightness-cxcy)	6J6K-ebvF46- fcbB46	7G7H –5F	GYJX – 4-6	GYJX – 2-6	FZHX – 1
Rth real typ (K/W)	~20	~20	~30	~30	~30
Binning If/Max If (mA)	200/300	150/200	200/250	200/250	200/250
Vf typ	3.00	3.00	2.35	2.25	2.25
Efficiency (Im/W)	~110	~60	~65	~80	~50
Efficiency (Im/W)	~110	~60	~65	~80	~50

Data may vary



The SYNIOS® P2720 family allows special design flexibility

Advantages

More opportunities for innovative automotive light design. SYNIOS® P2720 is a very powerful and reliable LED package that excels through its high brightness, low thermal resistance and thermal stability. Featuring different chip size classes and colors with one common footprint, the SYNIOS® P2770 family also shines with high flexibility and full scalability. Another great advantage of the new SYNIOS® platform is its exceptional temperature cycle stability. The lead frame part is optimized for the thermal expansion coefficient of the circuit board, thus securing very stable soldered joints. Moreover SYNIOS[®] P2720 also allows significant cost savings. Thanks to a higher brightness at Tj the amount of the required LEDs can be reduced, and there is no need for the next brighter brightness bin. In addition, standard PCB materials can be used due to low thermal resistance. But perhaps the greatest strength of the new SYNIOS[®] family is the great design freedom that it offers. Even extremely compact and flexible light guide designs with high efficiency flux in can be easily implemented.



Ideal for light guide applications

Benefits

- Improved brightness and cost advantages
- Design freedom
- High reliability
- Scalability

Applications

- Forward lighting
- Signaling/DRL
- Rear combination light

Features

Highlights

- Large variety of color and brightness
 - 3 chip sizes: compact package for the electrical power range from 0.5 – 3W
 - 5 colors: white, conversion yellow, yellow, red, superred
- Narrow color-binning for white
- High reliability package
- High efficiency due to optimized design
- Good thermal performance
- Ideally suited for light guide applications

Package

- Small product size: 2.0×2.75×0.6 mm³
- White SMD epoxy package
- ThinGaN (UX:3); Thinfilm TF5
- White with chip-level conversion
- Yellow with volume conversion
- $T_j = 150 \ ^{\circ}C (T_{max})$
- Distance of electrical pads: 0.3 mm
- Automotive quality
- L80B50 @ 10.000 h

Processability

- For standard PCB's (FR4)
- Simple solder pad design
- Self-alignment to the solder pad @ soldering
- Side wetting indicator after soldering



SYNIOS[®] P2720 on the Internet: www.osram-os.com/synios-p2720

For further information on the available products please visit our product catalog at http://catalog.osram-os.com

Asia

OSRAM Opto Semiconductors (China) Co.,Ltd. 28/F Harbour Ring Plaza No. 18 Xi Zang Middle Road Shanghai 200001 P.R. China Phone: +86 21 5385-2669 Fax: +86 21 5385-2868 E-mail: prasia@osram-os.com

Europe

OSRAM Opto Semiconductors GmbH Leibnizstraße 4 D-93055 Regensburg, Germany Phone: +49 941 850 1700 Fax: +49 941 850 3302 E-mail: support@osram-os.com

USA

OSRAM Opto Semiconductors Inc. 1150 Kifer Road, Suite 100 Sunnyvale, CA 94086, USA Main Phone number: (408) 962-3700 Main Fax: (408) 738-9120 Inbound Toll Free: (866) 993-5211 E-mail: info@osram-os.com

