

HEIDI-O

~50° x 11° oval beam

SPECIFICATION:

Dimensions	Ø 21.6
Height	11.7 mm
Fastening	tape, pin
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
HEIDI-O	Single lens	PMMA	clear		
HEIDI-TAPE	Tape	Acryl tape	black		



ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CA12949_HEIDI-O	Single lens	3264	204	204	11.1
» Box size: 480 x 280 x 300 mm					




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):




LED XHP35 HD
FWHM / FWTM 51.0 + 18.0° / 84.0 + 50.0°
Efficiency 77 %
Peak intensity 2.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files





LED XHP35 HI
FWHM / FWTM 53.0 + 14.0° / 80.0 + 40.0°
Efficiency 79 %
Peak intensity 3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED XP-G2
FWHM / FWTM 52.0 + 12.0° / 78.0 + 33.0°
Efficiency 91 %
Peak intensity 3.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):





LED XP-G3
FWHM / FWTM 51.0 + 14.0° / 79.0 + 39.0°
Efficiency 90 %
Peak intensity 2.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files





LED XP-G4
FWHM / FWTM 54.0 + 11.5° / 77.0 + 31.0°
Efficiency 92 %
Peak intensity 3.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED XP-L HD
FWHM / FWTM 52.0 + 16.0° / 79.0 + 41.0°
Efficiency 81 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON Rebel ES
FWHM / FWTM 53.0 + 12.0° / 76.0 + 33.0°
Efficiency 82 %
Peak intensity 3.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files





LED SST-10-B130
FWHM / FWTM 54.0 + 9.5° / 77.0 + 28.0°
Efficiency 90 %
Peak intensity 3.8 cd/lm
LEDs/each optic 1
Light colour/type Blue
Required components:



Light distribution files



LED NVSW219D
FWHM / FWTM 51.0 + 13.0° / 78.0 + 40.0°
Efficiency 91 %
Peak intensity 2.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):





LED NVSW319B
FWHM / FWTM 51.0 + 15.0° / 80.0 + 38.0°
Efficiency 91 %
Peak intensity 2.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files





LED NVSW3x9A
FWHM / FWTM 51.0 + 15.0° / 80.0 + 39.0°
Efficiency 89 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED NVSW519A
FWHM / FWTM 50.0 + 18.0° / 81.0 + 44.0°
Efficiency 87 %
Peak intensity 2.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):





LED NWSx229A
FWHM / FWTM 50.0 + 18.0° / 80.0 + 44.0°
Efficiency 76 %
Peak intensity 2.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files





LED Z5M3
FWHM / FWTM 52.0 + 13.0° / 79.0 + 39.0°
Efficiency 92 %
Peak intensity 2.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED Z8Y22P
FWHM / FWTM 52.0 + 14.0° / 79.0 + 39.0°
Efficiency 90 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XP-E2
FWHM / FWTM 48.0 + 8.0° / 74.0 + 21.0°
Efficiency 91 %
Peak intensity 4.6 cd/Im
LEDs/each optic 1
Light colour/type Amber
Required components:



Light distribution files



LED XP-G2 HE
FWHM / FWTM 50.0 + 14.0° / 78.0 + 35.0°
Efficiency 88 %
Peak intensity 3 cd/Im
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED LUXEON A
FWHM / FWTM 51.0 + 12.0° / 76.0 + 30.0°
Efficiency 84 %
Peak intensity 3.4 cd/Im
LEDs/each optic 1
Light colour/type White
Required components:

Light distribution files

OPTICAL RESULTS (SIMULATED):



LED LUXEON HL2Z
FWHM / FWTM 54.0 + 10.0° / 76.0 + 28.0°
Efficiency 89 %
Peak intensity 3.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED LUXEON R
FWHM / FWTM 53.0 + 12.0°
Efficiency %
LEDs/each optic 1
Light colour/type White
Required components:

Light distribution files



LED LUXEON SunPlus 20 Line (120 deg)
FWHM / FWTM 52.0 + 9.0° / 76.0 + 22.0°
Efficiency 91 %
Peak intensity 4.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON SunPlus 20 Line (150 deg)
 FWHM / FWTM 52.0 + 10.0° / 76.0 + 20.0°
 Efficiency 87 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED NCSxE17A
 FWHM / FWTM 54.0 + 24.0° / 180.0 + 54.0°
 Efficiency 81 %
 Peak intensity 1.5 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:



Light distribution files



LED NV4WB35AM
 FWHM / FWTM 52.0 + 16.0° / 80.0 + 42.0°
 Efficiency 87 %
 Peak intensity 2.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED NVSW219C-V2
 FWHM / FWTM 52.0 + 8.0° / 74.0 + 21.0°
 Efficiency 89 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED OSLOM Black
 FWHM / FWTM 53.0 + 9.0° / 54.0 + 23.0°
 Efficiency 88 %
 Peak intensity 4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED OSLOM Black Flat (LUW HWQP)
 FWHM / FWTM 54.0 + 8.0° / 74.0 + 18.0°
 Efficiency 89 %
 Peak intensity 4.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors

LED	OSLON Pure 1414
FWHM / FWTM	52.0 + 8.0° / 74.0 + 17.0°
Efficiency	93 %
Peak intensity	5.2 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)