

ANGELA-XW-B

White version with ~70° wide beam compatible
with BJB and B+W connectors

SPECIFICATION:

Dimensions	Ø 119.5
Height	74.5 mm
Fastening	socket
ROHS compliant	yes ⓘ




MATERIALS:

Component	Type	Material	Colour	Finish	Coating
ANGELA-XW-B	Reflector	HRPC	white		

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
F13841_ANGELA-XW-B » Box size: 480 x 280 x 300 mm	160	80	40	7.7





See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):





LED BXRA ES Rectangle
 FWHM / FWTM 73.0° / 125.0°
 Efficiency 94 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2040



Light distribution files





LED V15 Gen6
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 89 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F13671_ANGE-RZ-LENS
 BJB: 47.319.2224



Light distribution files



LED V15 Gen6
 FWHM / FWTM 72.0° / 124.0°
 Efficiency 93 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2224





Light distribution files

OPTICAL RESULTS (MEASURED):





LED V18 Gen6
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 94 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2274



Light distribution files





LED V18 Gen6
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 89 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F13671_ANGE-RZ-LENS
 BJB: 47.319.2274



Light distribution files



LED V18 Gen7
 FWHM / FWTM 72.0° / 124.0°
 Efficiency 94 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2350




Light distribution files

OPTICAL RESULTS (MEASURED):





LED V22 Gen6
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 87 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F13671_ANGE-RZ-LENS
 A.A.G. STUCCHI: 8102-G2



Light distribution files





LED V22 Gen6
 FWHM / FWTM 71.0° / 124.0°
 Efficiency 92 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8102-G2



Light distribution files

CITIZEN

LED CLU03x
 FWHM / FWTM 73.0° / 126.0°
 Efficiency 88 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F13671_ANGE-RZ-LENS
 A.A.G. STUCCHI: 8101-G2





Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN


LED CLU03x
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 94 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8101-G2



Light distribution files

CITIZEN



LED CLU03x
 FWHM / FWTM 72.0° / 123.0°
 Efficiency 94 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2021



Light distribution files

CITIZEN

LED CLU04x
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 85 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F13671_ANGE-RZ-LENS
 A.A.G. STUCCHI: 8102-G2





Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN



LED CLU04x
FWHM / FWTM 72.0° / 125.0°
Efficiency 93 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
A.A.G. STUCCHI: 8102-G2



Light distribution files

CITIZEN



LED CLU04x
FWHM / FWTM 71.0° / 124.0°
Efficiency 93 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
BJB: 47.319.2030



Light distribution files

CITIZEN

LED CLU720/721/723
FWHM / FWTM 73.0° / 125.0°
Efficiency 94 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
BJB: 47.319.2021




Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN


LED CLU720/721/723
 FWHM / FWTM 72.0° / 127.0°
 Efficiency 94 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8101-G2



Light distribution files




LED CXA/B 25xx
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 89 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F13671_ANGE-RZ-LENS
 BJB: 47.319.2141



Light distribution files



LED CXA/B 25xx
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2141





Light distribution files

OPTICAL RESULTS (MEASURED):





LED CXA/B 25xx
 FWHM / FWTM 73.0° / 126.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8401-G2



Light distribution files





LED CXA/B 30xx
 FWHM / FWTM 71.0° / 124.0°
 Efficiency 92 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8404-G2



Light distribution files



LED LUXEON CoB 1204/1205
 FWHM / FWTM 73.0° / 125.0°
 Efficiency 94 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8301-G2





Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON CoB 1208
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 88 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F13671_ANGE-RZ-LENS
 A.A.G. STUCCHI: 8301-G2



Light distribution files





LED LUXEON CoB 1208
 FWHM / FWTM 73.0° / 126.0°
 Efficiency 94 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8301-G2



Light distribution files



LED LUXEON CoB 1211
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2030





Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON CoB 1211
 FWHM / FWTM 71.0° / 123.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8102-G2



Light distribution files





LED LUXEON CoB 1213/1216/1812
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2030



Light distribution files



LED LUXEON CoB 1213/1216/1812
 FWHM / FWTM 71.0° / 125.0°
 Efficiency 88 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F13671_ANGE-RZ-LENS
 BJB: 47.319.2030




Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON K12
 FWHM / FWTM 72.0° / 120.0°
 Efficiency 94 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2070



Light distribution files





LED LUXEON K16
 FWHM / FWTM 72.0° / 121.0°
 Efficiency 94 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2070



Light distribution files



LED CxM-14 (19x19)
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 94 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2021





Light distribution files

OPTICAL RESULTS (MEASURED):





LED CxM-22 (28x28)
 FWHM / FWTM 72.0° / 126.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2030



Light distribution files





LED Soleriq S13 19x19
 FWHM / FWTM 73.0° / 126.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2021



Light distribution files



LED Soleriq S19
 FWHM / FWTM 72.0° / 125.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8503-G2





Light distribution files

OPTICAL RESULTS (MEASURED):

OSRAM
Opto Semiconductors



LED Soleriq S19
FWHM / FWTM 72.0° / 125.0°
Efficiency 94 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
BJB: 47.319.2170



Light distribution files

SAMSUNG



LED LC016D / LC019D / LC026D / LC033D
FWHM / FWTM 73.0° / 125.0°
Efficiency 89 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F13671_ANGE-RZ-LENS
BJB: 47.319.2021



Light distribution files

SAMSUNG

LED LC016D / LC019D / LC026D / LC033D
FWHM / FWTM 73.0° / 124.0°
Efficiency 93 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
A.A.G. STUCCHI: 8101-G2





Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG



LED LC016D / LC019D / LC026D / LC033D
 FWHM / FWTM 73.0° / 125.0°
 Efficiency 89 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F13671_ANGE-RZ-LENS
 A.A.G. STUCCHI: 8101-G2



Light distribution files





LED ZC12/18
 FWHM / FWTM 72.0° / 123.0°
 Efficiency 93 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8101-G2



Light distribution files



LED ZC25/40/60
 FWHM / FWTM 71.0° / 124.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8102-G2





Light distribution files

OPTICAL RESULTS (MEASURED):

SHARP



LED Mega Zenigata (GW6DME)
 FWHM / FWTM 72.0° / 123.0°
 Efficiency 94 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 BJB: 47.319.2011



Light distribution files

SHARP


LED Mega Zenigata (GW6DME)
 FWHM / FWTM 73.0° / 125.0°
 Efficiency 94 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 A.A.G. STUCCHI: 8301-G2



Light distribution files

TRIDONIC

LED SLE G7 LES17 H
 FWHM / FWTM 71.0° / 123.0°
 Efficiency 93 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

TRIDONIC



LED SLE G7 LES21 H
FWHM / FWTM 71.0° / 124.0°
Efficiency 93 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

XICATO

LED XOB 14.5 mm
FWHM / FWTM 72.0° / 124.0°
Efficiency 94 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
BJB: 47.319.2021




Light distribution files

OPTICAL RESULTS (SIMULATED):

CITIZEN

LED CLU730/731/733
 FWHM / FWTM 70.0° / 105.0°
 Efficiency 90 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

BJB: 47.319.2030




Light distribution files

OSRAM

Opto Semiconductors

LED Soleriq S15
 FWHM / FWTM 72.0° / 116.0°
 Efficiency 86 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

BJB: 47.319.2021




Light distribution files

SAMSUNG

LED LC040D / LC060D / LC080D
 FWHM / FWTM 71.0° / 111.0°
 Efficiency 85 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

BJB: 47.319.2030



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)