


AMBER-2X2-SCL

Type II/III (long) beam for very wide pole to pole distances. Ideal for pedestrian paths and residential roads. EN13201 P-classes.

SPECIFICATION:

Dimensions	50.0 x 50.0
Height	7.8 mm
Fastening	pin, screw
ROHS compliant	yes ⓘ




MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
AMBER-2X2-SCL	Multi-lens	PMMA	amber		

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C18607_AMBER-2X2-SCL	800	160	160	8.3
» Box size: 480 x 280 x 300 mm				




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):




LED J Series 5050B 6V K Class
FWHM / FWTM Asymmetric
Efficiency 79 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files





LED J Series 5050B 6V K Class
FWHM / FWTM Asymmetric
Efficiency 71 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED J Series 5050B 6V K Class
FWHM / FWTM Asymmetric
Efficiency 74 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Amount of Blue light (380-500 nm) 0.3 %
CCT (LED/with lens)* 3763K/2250K
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED J Series 5050B 6V K Class
FWHM / FWTM Asymmetric
Efficiency 74 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED J Series 5050B 6V K Class
FWHM / FWTM Asymmetric
Efficiency 76 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED J Series 5050C 6V E Class
FWHM / FWTM Asymmetric
Efficiency 72 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED J Series 5050C 6V E Class
 FWHM / FWTM Asymmetric
 Efficiency 76 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED J Series 5050C 6V E Class
 FWHM / FWTM Asymmetric
 Efficiency 69 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XP-G3
 FWHM / FWTM Asymmetric
 Efficiency 74 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Amount of Blue light (380-500 nm) 0.4 %
 CCT (LED/with lens)* 3838K/2289K
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED LUXEON 5050 Square LES
FWHM / FWTM Asymmetric
Efficiency 71 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED LUXEON 5050 Square LES
FWHM / FWTM Asymmetric
Efficiency 79 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED LUXEON 5050 Square LES
FWHM / FWTM Asymmetric
Efficiency 75 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED LUXEON 5050 Square LES
FWHM / FWTM Asymmetric
Efficiency 69 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED LUXEON 5050 Square LES
FWHM / FWTM Asymmetric
Efficiency 67 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED LUXEON 5050 Square LES
FWHM / FWTM Asymmetric
Efficiency 81 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED LUXEON 5050 Square LES
FWHM / FWTM Asymmetric
Efficiency 69 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED LUXEON 5050 Square LES
FWHM / FWTM Asymmetric
Efficiency 76 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED LUXEON 5050 Square LES
FWHM / FWTM Asymmetric
Efficiency 73 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON 5050 Square LES
FWHM / FWTM Asymmetric
Efficiency 68 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files





LED LUXEON HL2X-D
FWHM / FWTM Asymmetric
Efficiency 74 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Amount of Blue light (380-500 nm) 0.4 %
CCT (LED/with lens)* 3902K/2312K
Required components:



Light distribution files



LED NVSW219F-V2
FWHM / FWTM Asymmetric
Efficiency 75 %
Peak intensity 0.8 cd/lm
LEDs/each optic 1
Light colour/type White
Amount of Blue light (380-500 nm) 0.4 %
CCT (LED/with lens)* 3836K/2292K
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

OSRAM

Opto Semiconductors

LED Duris S8
 FWHM / FWTM Asymmetric
 Efficiency 73 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OSRAM

Opto Semiconductors

LED OSLON Square CSSRM2/CSSRM3
 FWHM / FWTM Asymmetric
 Efficiency 74 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Amount of Blue light (380-500 nm) 0.4 %
 CCT (LED/with lens)* 3898K/2279K
 Required components:




Light distribution files

OSRAM

Opto Semiconductors

LED OSLON Square CSSRM2/CSSRM3
 FWHM / FWTM Asymmetric
 Efficiency 70 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS


LED Fortimo FastFlex LED 2x8 DA G4+
 FWHM / FWTM Asymmetric
 Efficiency 68 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

PHILIPS



LED Fortimo FastFlex LED 2x8 DA G5
 FWHM / FWTM Asymmetric
 Efficiency 72 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG

LED LH351C
 FWHM / FWTM Asymmetric
 Efficiency 74 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Amount of Blue light (380-500 nm) 0.4 %
 CCT (LED/with lens)* 3773K/2283K
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG



LED	LH502D
FWHM / FWTM	Asymmetric
Efficiency	74 %
Peak intensity	0.5 cd/lm
LEDs/each optic	1
Light colour/type	White
Amount of Blue light (380-500 nm)	0.3 %
CCT (LED/with lens)*	3785K/2231K
Required components:	



Light distribution files

SEOUL SEMICONDUCTOR



LED	SEOUL DC 5050 6V
FWHM / FWTM	Asymmetric
Efficiency	74 %
Peak intensity	0.5 cd/lm
LEDs/each optic	1
Light colour/type	White
Amount of Blue light (380-500 nm)	0.4 %
CCT (LED/with lens)*	3995K/2279K
Required components:	



Light distribution files

SEOUL SEMICONDUCTOR

LED	Z5M4
FWHM / FWTM	Asymmetric
Efficiency	76 %
Peak intensity	0.7 cd/lm
LEDs/each optic	1
Light colour/type	White
Amount of Blue light (380-500 nm)	0.3 %
CCT (LED/with lens)*	3561K/2219K
Required components:	



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

**Ledil Optics Technology
(Shenzhen) Co., Ltd.**
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

**Local sales and technical
support**
www.ledil.com/
where_to_buy

Shipping locations
Poznan, Poland
Hong Kong, China

Distribution Partners
www.ledil.com/
where_to_buy