

YASMEEN-35-WW

~60° wide beam

SPECIFICATION:

Dimensions	Ø 35.0
Height	18 mm
Fastening	socket
ROHS compliant	yes ⓘ



MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
YASMEEN-35-WW	Single lens	PMMA	clear	gloss	
YASMEEN-35-HLD-B	Holder B	PC	black		
YASMEEN-35-HLD-B-WHT	Holder B	PC	white		



ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C18521_YASMEEN-35-WW	840	120	60	8.9
Assembly				
CP19223_YASMEEN-35-WW-B-WHT	780	120	60	10.0
CP18526_YASMEEN-35-WW-B	780	120	60	10.1





See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):

CITIZEN


LED CLU7L3
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 56.0° / 69.0°
 Efficiency 88 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C19425_SOCKET-B-35-N



Light distribution files

CITIZEN



LED CLU7R3
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 57.0° / 74.0°
 Efficiency 88 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C19424_SOCKET-B-35-M



Light distribution files

CITIZEN

LED CLU7S3
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 56.0° / 72.0°
 Efficiency 88 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C19425_SOCKET-B-35-N





Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG

LED	LC010C G2
Ordering code	CP18526_YASMEEN-35-WW-B
FWHM / FWTM	52.0° / 72.0°
Efficiency	83 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	
BJB: 47.360.1020	



Light distribution files


OPTICAL RESULTS (SIMULATED):



LED V10 Gen 8-9
Ordering code CP18526_YASMEEN-35-WW-B
FWHM / FWTM 53.0° / 83.0°
Efficiency 82 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

Bender Wirth: 634b Bayonet35L


Light distribution files



LED V4 HD Gen 7
Ordering code CP18526_YASMEEN-35-WW-B
FWHM / FWTM 58.0° / 74.0°
Efficiency 85 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

BJB: 47.360.1020


Light distribution files



LED V6 HD Gen 8
Ordering code CP18526_YASMEEN-35-WW-B
FWHM / FWTM 59.0° / 80.0°
Efficiency 86 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

Bender Wirth: 634c Bayonet35L

Light distribution files




OPTICAL RESULTS (SIMULATED):



LED Vesta DTW 6mm
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 58.0° / 78.0°
 Efficiency 84 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Bender Wirth: 652b Bayonet35L


Light distribution files



LED Vesta DTW 9mm (4W/6W/12W)
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 52.0° / 80.0°
 Efficiency 84 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Bender Wirth: 652b Bayonet35L

Light distribution files




CITIZEN

LED CLU02x (LES10)
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 50.0° / 79.0°
 Efficiency 79 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

BJB: 47.360.1020

Light distribution files




OPTICAL RESULTS (SIMULATED):

CITIZEN

LED	CLU703 Type-F
Ordering code	CP18526_YASMEEN-35-WW-B
FWHM / FWTM	62.0° / 82.0°
Efficiency	83 %
Peak intensity	0.8 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	

BJB: 47.360.1020

Light distribution files




CITIZEN

LED	CLU7A2/7A3
Ordering code	CP18526_YASMEEN-35-WW-B
FWHM / FWTM	56.0° / 74.0°
Efficiency	84 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	

BJB: 47.360.1020

Light distribution files




CITIZEN

LED	CLU7A3 Type-F
Ordering code	CP18526_YASMEEN-35-WW-B
FWHM / FWTM	64.0° / 82.0°
Efficiency	86 %
Peak intensity	0.8 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	

BJB: 47.360.1020

Light distribution files




OPTICAL RESULTS (SIMULATED):

CITIZEN

LED CLU7B2
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 58.0° / 73.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


BJB: 47.360.1020



Light distribution files

CITIZEN


LED CLU7L3
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 56.0° / 72.0°
 Efficiency 85 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C19425_SOCKET-B-35-N



Light distribution files

CITIZEN

LED CLU7S3
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 57.0° / 73.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C19425_SOCKET-B-35-N




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED CHA0304
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 58.0° / 72.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1020

Light distribution files



LED CHA0410
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 57.0° / 74.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1020

Light distribution files



LED CHA0612
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 56.0° / 76.0°
 Efficiency 84 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



BJB: 47.360.1020



Light distribution files

OPTICAL RESULTS (SIMULATED):



LED XM-L RGBW (XMLDCL HD)
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 58.0° / 74.0°
 Efficiency 84 %
 Peak intensity 1 cd/Im
 LEDs/each optic 1
 Light colour/type White
 Required components:


BJB: 47.360.1010



Light distribution files




LED LUXEON 7070
 FWHM / FWTM 52.0° / 72.0°
 Efficiency 93 %
 Peak intensity 1 cd/Im
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON CX Plus CoB - HD S01H4
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 59.0° / 78.0°
 Efficiency 87 %
 Peak intensity 1 cd/Im
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 634c Bayonet35L

OPTICAL RESULTS (SIMULATED):



LED LUXEON CX Plus CoB - HD S02H6
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 58.0° / 80.0°
 Efficiency 86 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634c Bayonet35L

Light distribution files



LED LUXEON CX Plus CoB - HD S04H9
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 52.0° / 82.0°
 Efficiency 82 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634a Bayonet35L

Light distribution files



LED LUXEON CX Plus CoB L04 / L05 (Gen2)
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 44.0° / 78.0°
 Efficiency 74 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1040

Light distribution files

OPTICAL RESULTS (SIMULATED):



LED LUXEON CX Plus CoB S01 (Gen2)
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 58.0° / 78.0°
 Efficiency 86 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634c Bayonet35L

Light distribution files



LED CXM-3
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 58.0° / 74.0°
 Efficiency 88 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634a Bayonet35L

Light distribution files



LED CXM-4
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 58.0° / 75.0°
 Efficiency 86 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634a Bayonet35L

Light distribution files

OPTICAL RESULTS (SIMULATED):



LED CxM-6 (13.5x13.5)
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 54.0° / 74.0°
 Efficiency 84 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1020

Light distribution files



LED CxM-6 (13.5x13.5)
 Ordering code CP19223_YASMEEN-35-WW-B-WHT
 FWHM / FWTM 56.0° / 78.0°
 Efficiency 90 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634a Bayonet35L

Light distribution files



LED COB S-Type (LES 6)
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 58.0° / 78.0°
 Efficiency 86 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652a Bayonet35L

Light distribution files

OPTICAL RESULTS (SIMULATED):



LED COB S-Type (LES 7)
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 57.0° / 80.0°
 Efficiency 85 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652a Bayonet35L

Light distribution files



LED COB T-Type
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 58.0° / 78.0°
 Efficiency 86 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652a Bayonet35L

Light distribution files



LED NF1202EFC-V5
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 57.0 + 56.0° / 77.0°
 Efficiency 83 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



BJB: 47.360.1020

Light distribution files


OPTICAL RESULTS (SIMULATED):

SAMSUNG

LED LC003D / LC006D / LC009D / LC013D
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 50.0° / 78.0°
 Efficiency 81 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

BJB: 47.360.1020

Light distribution files




SAMSUNG

LED LC010C G2
 Ordering code CP18526_YASMEEN-35-WW-B
 FWHM / FWTM 56.0° / 76.0°
 Efficiency 83 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

BJB: 47.360.1020

Light distribution files



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)