





IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	62 Ω	160 Ω	300 Ω
Minimum	- Ω	128 Ω	- Ω



AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture REF 3216



- NOTES:
1. ASSEMBLED PART #: 28A2432-0A2.
 2. CASE COLOR: BLACK-0A2.
 3. CASE FLAMMABILITY RATING: UL94 V-2.
 4. CASE MATERIAL: Halogen Free Nylon
 5. COSMETIC SPECIFICATION REFER TO WI-QA-038.

CASE DIMENSIONS (SPEC): mm [in]

A	19.20 [.756]	+	0.30 [.012]
B	8.20 [.323]	+	0.20 [.008]
C	19.90 [.783]	+	0.30 [.012]
D	23.10 [.909]	+	0.38 [.015]
E	26.10 [1.028]	+	0.38 [.015]

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved. Laird™			
REV	DESCRIPTION	DATE	INT				
M	REMOVE CORE DIMENSIONS	08/22/2019	Jcal	PROJECT/PART NUMBER: 28A2432-0A2			
L	UPDATE COMPANY LOGO ,ADD NOTE 5	08/23/14	QIU				
K	UPDATED NOTE 3	09/15/10	JUN	REV M PART TYPE: FERRITE SNAP-ON DRAWN BY: TMB			
J	UPDATE COMPANY LOGO ADD NOTES 3 & 4	01/27/09	JRK				
H	CHANGE CORE "D" DIM TOLERANCE TO 0.20 [.008] REMOVE NOTES #1 & #3	10/31/07	TMB	DATE: 06/28/01 SCALE: NTS MATERIAL: Ferrite			
G	UPDATE COMPANY LOGO UPDATE MIN Z SPEC	07/03/07	JRK				
REV	DESCRIPTION	DATE	INT	CAD # 28A2432-0A2-M TOOL # -			