
Wire-wound Metal Power Inductors MCOIL™ LSEN series for General Electronic Equipment for Consumer

Code in front of Series have been extracted from Part number, which describes the segment of products, such as kinds and characteristics.

REFLOW

■PART NUMBER

* Operating Temp.:-40~+125°C (Including self-generated heat)



(1)Series

1001103	Doction				
Code					
(1)(2)(3)(4)					
LSFN	Wire-wound Metal Power Inductor for General Flectronic Equipment for Consumer				

(1) Product Group

Code	
L	Inductors

(2) Category

Code	Recommended equipment	Quality Grade
S	General Electronic Equipment for Consumer	3

Code

(3) Type

E	Metal Wire-wound (High filling type)

(4) Features. Characteristics

<u> </u>	*
Code	
N	Standard Power choke

2Features

Code	Feature
С	Bottom electrode (Ag-resin × Sn-plate)

③Dimensions (L×W)

Code	Dimensions (L × W) [mm]
2016	2.0 × 1.6
2520	2.5 × 2.0

4 Dimensions (T)

TO DITTIONS (1)	
Code	Dimensions (T) [mm]
KK	1.0

5Packaging

Code	Packaging
Т	Taping

6 Nominal inductance

©140mmai madetanee			
Code (example)	Nominal inductance[μH]		
R47	0.47		
1R0	1.0		
4R7	4.7		


XR=Decimal point

7 Inductance tolerance

<u> </u>			
Code	Inductance tolerance		
М	±20%		

8 Internal code


■STANDARD EXTERNAL DIMENSIONS / STANDARD QUANTITY



Recommended Land Patterns

Surface Mounting

- Mounting and soldering conditions should be checked beforehand.
- Applicable soldering process to these products is reflow soldering only.



Туре	Α	В	С
2016	0.7	8.0	1.8
2520	0.9	1.0	2.2
			Unit:mm

Туре	L	W	Т	е	Standard quantity[pcs] Taping
2016KK	2.0±0.2	1.6±0.2	1.0 max	0.5±0.3	3000
	(0.079 ± 0.008)	(0.063 ± 0.008)	(0.039 max)	(0.020 ± 0.012)	
2520KK	2.5±0.2	2.0 ± 0.2	1.0 max	0.65 ± 0.3	3000
	(0.098 ± 0.008)	(0.079 ± 0.008)	(0.039 max)	(0.026 ± 0.012)	

Unit:mm(inch)

Finis catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification.