
## **Interface Connectors for Miniature, Portable Terminal Devices**

#### **ST** Series



#### Overview

Developed as external input/output connectors for the portable and mobile devices used in consumer markets. As such, the connectors incorporate features required to assure reliable electrical and mechanical performance under extreme and unpredictable conditions.

#### Features

#### 1. Strong locking mechanism

To assure continuous reliability of the connection in an unpredictable consumer environment, mated connectors will withstand pull force of 49N max. applied in any direction.

## 2. Prevention against reversed or angle insertion

Multiple polarization keys will not allow incorrect insertion of the mating plug.

In addition, contacts will not be damaged when the user attempts to insert only the corner of the mating plug.

#### 3. Small size and low profile

Contact pitch of 0.5 mm and utilization of state-of-the-art manufacturing technologies has produced receptacle height of 3 mm above the board and maximum thickness of the plug of only 7 mm.

#### 4. EMI protection


Built-in ground continuity features and EMI shielding assure interference free performance.


#### 5. Wide variety of contact positions and mounting styles


Standard, reverse, vertical and cradle mountings, as well as utilization of variety of cables and conductors assure application of this connector in diversified applications.

### Applications

Digital Still Cameras, Personal Digital Assistance, Notebook computers, Cellular phones, Portable readers, Mobile recorders and any mobile or portable device requiring high reliability small size input/output connection.







## **■**Specifications

Pating	Current rating	0.5A (1 A max. can be carried via 4 random contacts)	Operating temperature range	: -30℃ to +80℃
Rating	Voltage rating	100V AC	Storage temperature range	: -40°C to +85°C (Note)

Characteristic	Specification	Conditions
Contact resistance	60m $Ω$ max.	100mA DC
2. Insulation resistance	100M Ω min.	250V DC
3. Dielectric withstanding voltage	No flashover or insulation breakdown.	350V AC/ one minute
4. Mating/un-mating forces	Mating: 29.4N max.	With corresponding connector.
5. Durability (mating/un-mating)	Contact resistance: 50 m Ω max.	10000 cycles
6. Shock	No electrical discontinuity of 10 $\mu$ sec. max.	Acceleration of 490 m/s2, 11 ms duration, sine half-wave
O. SHOCK	Contact resistance: 100m Ω max.	waveform, 3 cycles in each of the 3 axis.
7. Temperature cycle	Contact resistance: $100m\ \Omega$ max. Insulation resistance: $1000M\ \Omega$ min.	Temperature : $-55^{\circ}\text{C} \rightarrow +5^{\circ}\text{C}$ to $+35^{\circ}\text{C} \rightarrow +85^{\circ}\text{C} \rightarrow +5^{\circ}\text{C}$ to $+35^{\circ}\text{C}$ Time (Minutes): $30 \rightarrow 5 \rightarrow 30 \rightarrow 5$ $5 \text{ cycles}$
8. Salt spray	No corrosions	5±1% salt water solution at 35±3°C for 48 hours, after washing without salt, leave for 24 hours at room temperature
9. Lock strength	Fully inserted and locked corresponding connector. No physical damage or electrical failure.	Pull force: 49N max. applied in each of the 3 axis.
10. Shock	No electrical discontinuity of 10 $\mu$ sec. max. Contact resistance: 100m $\Omega$ max.	Frequency: 10 to 55 Hz, single amplitude of 0.75mm, 2 hours, 3 axis.

Note: Includes temperature rise caused by current flow.

#### ■Materials

#### Receptacles and cradles

Component	Material	Finish	Remarks
Insulator	Thermoplastic compound, glass reinforced	Color: Black	UL94V-0
Contacts	Copper alloy	Contact area: Gold plated	
Shield	Stainless steel	Tin alloy plating	

#### Plugs

Component	Material	Finish	Remarks
Insulator	Thermoplastic compound, glass reinforced	Color: Black	UL94V-0
Contacts	Copper alloy	Contact area: Gold plated	
Shield	Stainless steel		
Cover	Thermoplastic compound, glass reinforced		UL94-HB

## **■**Ordering information

Receptacles

Plugs

● Plug - Cradle type

ST	80	Χ-	18	S	(50)
0	2	3	4	6	8

0	Series name	: ST
2	Termination type	
	60	: Right angle SMT
	40	: Solder type
	80	: Cradle, vertical, SMT
3	Shield	
	Χ	: With shield
	Blank	: Without shield
4	Number of positions	3
6	Contact type	
	Р	: Male contact (Receptacle)
	S	: Female contact (Plug)
<b>6</b>	Contact arrangemen	nt /4
		: Combination, with 4 power contacts
7	Plug type	
	CV	: Standard type, for top PCB mount
	CVR	: Reverse type, for bottom PCB mount
	CV1	: For larger diameter cables
8	RoHS compliant	: (50), (80)

## **■**Receptacle

## ● 10 pos.



Part Number	CL No.	Packaging	RoHS
ST60-10P	CL241-0022-5	Reel packaging (1500 pieces/reel)	YES

#### 0.5 0.3(Land) 10.5 4.5 0.5 0.18 0.6 PCB edge (Through hole) 0.4 0.95 4(Land) (0.58)(11.5) 10.1 ZZ:Copper foil + plating resist No.1 No.10 ‱:Land 10.1 (4.4)


◆Recommended PCB

mounting pattern


#### ● 18 pos.




Part Number	CL No.	Packaging	RoHS
ST60-18P(50)	CL241-0011-9-50	Reel packaging (1500 pieces/reel)	YES




#### • 18 pos. with 4 power contacts




Part Number	CL No.	Packaging	RoHS
ST60-18P/4(50)	CL241-0005-6-50	Reel packaging (1000 pieces/reel)	YES



#### • 24 pos.




Part Number	CL No.	Packaging	RoHS
ST60-24P(50)	CL241-0003-0-50	Reel packaging (1500 pieces/reel)	YES




#### 36 pos.




Part Number	CL No.	Packaging	RoHS
ST60-36P	CL241-0033-1	Reel packaging (1500 pieces/reel)	YES



#### • 36 pos. reverse type



Part Number	CL No.	Packaging	RoHS
ST60-36PR	CL241-0036-0	Reel packaging (1500 pieces/reel)	YES




## ■Plug – cradle type(Horizontal)


### • 18 pos.




F	Part Number CL No.		Packaging	RoHS
ST60X-18S CL241-0028-1		CL241-0028-1	Reel packaging (900 pieces/reel)	YES



#### ● 36 pos.




Part Number	CL No.	Packaging	RoHS
ST60X-36S	CL241-0035-7	Reel packaging (900 pieces/reel)	YES




## ■Plug – cradle type(Vertical)


● 10 pos.




Part Number	CL No.	L No. Packaging	
ST80X-10S	CL241-0030-3	Reel packaging (400 pieces/reel)	YES




#### ● 18 pos.




Part Number CL No.		Packaging	RoHS
ST80X-18S(50)	CL241-0020-0-50	Reel packaging (400 pieces/reel)	YES



#### 24 pos.



Part	Number	CL No.	Packaging	RoHS
ST80X-24S(50) CL2		CL241-0037-2-50	Reel packaging (400 pieces/reel)	YES




## **■Plug**

• 10 pos. (Non-shielded type, for 4mm max. cable diameter)





Part Number	CL No.	RoHS
ST40-10S-CV(80)	CL241-0021-2-80	YES



• 10 pos. (Reverse, non-shielded type, for 4mm max. cable diameter)









#### • 10 pos. (Shielded type, for 4mm max. cable diameter)



Part Number	CL No.	RoHS
ST40X-10S-CV(80)	CL241-0041-0-80	YES






#### ● 10 pos. (Reverse, shielded type, for 4mm max. cable diameter)





Part Number	CL No.	RoHS
ST40X-10S-CVR(80)	CL241-0029-4-80	YES



#### • 18 pos. (Shielded type, for 4mm max. cable diameter)









#### • 18 pos. (Reverse, shielded type, for 4mm max. cable diameter)









#### 4 pos. (For opening size as 18 pos., reverse, non-shielded, for 4mm max. cable diameter)








#### • 24 pos. (Shielded type, for 4mm max. cable diameter)




Part Number	CL No.	RoHS
ST40X-24S-CV(80)	CL241-0004-3-80	YES




#### • 24 pos. (Shielded type, for 5.8mm max. cable diameter)



Part Number	CL No.	RoHS
ST40X-24S-CV1(80)	CL241-0023-8-80	YES






#### • 36 pos. (Shielded type, for 7mm max. cable diameter)




Part Number	CL No.	RoHS
ST40X-36S-CV(80)	CL241-0034-4-80	YES




Note: Plug assemblies will require additional components. Contact Hirose Electric representative for detailed descriptions and installation instructions.

# ▶ Packaging Specification◆ Embossed Carrier Tape Dimensions




#### Reel Dimensions



#### Reel Dimensions

Part Number	Α	В	С	D	Е	pcs. / reel
ST60-10P	24		11.5	12	5	1500
ST60-18P(50)	24		11.5	12	5	1500
ST60-24P(50)	32	28.4	14.2	12	5	1500
ST60-36P	44	40.4	20.2	12	5	1500
ST60-18P/4(50)	44	40.4	20.2	12	6.2	1000
ST60-36PR	44	40.4	20.2	12	5	1500
ST80X-10S	24		11.5	16	12.2	400
ST80X-18S(50)	44	40.4	20.2	16	12.7	400
ST80X-24S(50)	44	40.4	20.2	16	12.7	400
ST60X-18S	32	28.4	14.2	20	4.95	900
ST60X-36S	44	40.4	20.2	20	4.85	900

## ▶ Recommended Temperature Profile (Lead-free soldering compound)



#### HRS test conditions

Solder composition: Paste, 96.5%Sn/3.0%Ag/0.5%Cu Test board: Glass epoxy 35mm×35mm×0.8mm thick

The temperature profiles are based on the above conditions. In individual applications the actual temperature may vary, depending on solder paste type, volume/thickness and board size/thickness. Consult your solder paste and equipment manufacturer for specific recommendations.

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## **Hirose Electric:**

<u>ST40X-CM(5.8)/CK-MP(61)</u> <u>ST40X-CM(5.8)/CK-MP</u> <u>ST40X-CM(5.8)/CK-MP(62)</u> <u>ST40X-CM(5.8)/CK-MP(01)</u> <u>ST40X-CM(40-50)/CK-MP(01)</u> <u>ST40X-CM(40-50)/CK-MP</u> <u>ST40X-CM(40-50)/CK-MP(62)</u> <u>ST40X-CM(40-50)/CK-MP(61)</u>