

### Radial Lead Type

Series: **GA** Type: **A**

#### ■ Features

- Endurance : 105 °C 1000 h
- RoHS directive compliant



#### ■ Specifications


Category Temp. Range	-55 °C to +105 °C	
Rated W.V. Range	10 V.DC to 50 V.DC	
Nominal Cap. Range	1.5 μF to 220 μF	
Capacitance Tolerance	±20 % (120 Hz/+20 °C)	
DC Leakage Current	$I \leq 0.01 CV$ or 3 (μA) After 2 minutes (Whichever is greater)	
tan δ	Please see the attached standard products list	
Endurance	After following life test with DC voltage and +105 °C±2 °C ripple current value applied (The sum of DC and ripple peak voltage shall not exceed the rated working voltage), for 1000 hours, when the capacitors are restored to 20 °C, the capacitors shall meet the limits specified below.	
	Capacitance change	±20 % of initial measured value
	tan δ	≤ 200 % of initial specified value
	DC leakage current	≤ initial specified value
Shelf Life	After storage for 1000 hours at +105 °C±2 °C with no voltage applied and then being stabilized at +20 °C, capacitors shall meet the limits specified in Endurance. (With voltage treatment)	

#### ■ Frequency correction factor for ripple current

W.V.(V.DC)	Cap (μF)	Frequency (Hz)				
		60	120	1 k	10 k	100 k to
10 to 50	1.5 to 220	0.85	1.00	1.30	1.40	1.55

#### ■ Dimensions in mm(not to scale)

(Unit : mm)



	4	5	6.3	8
Body Dia. φD	4	5	6.3	8
Lead Dia. φd	0.45	0.45	0.45	0.45
Lead space F	1.5	2.0	2.5	2.5

### ■ Standard Products

Endurance : 105 °C 1000 h

W.V. (V)	Cap. (±20 %) (μF)	Case size		Specification			Lead Length			Part No.	Min. Packaging Qty		
		Dia. (mm)	Length (mm)	Ripple Current (120 Hz) (+105 °C) (mA r.m.s.)	tan δ (120 Hz) (+20 °C)	Endurance (hours)	Lead Dia. (mm)	Lead Space			Straight Leads (pcs)	Taping (pcs)	
								Straight (mm)	Taping *B (mm)				Taping *H (mm)
10	22	4	7	30	0.22	1000	0.45	1.5	5.0	2.5	EEAGA1A220( )	200	2000
	33	5	7	50	0.22	1000	0.45	2.0	5.0	2.5	EEAGA1A330( )	200	2000
	47	6.3	7	65	0.22	1000	0.45	2.5	5.0	2.5	EEAGA1A470( )	200	2000
	68	6.3	7	75	0.22	1000	0.45	2.5	5.0	2.5	EEAGA1A680( )	200	2000
	100	6.3	7	110	0.22	1000	0.45	2.5	5.0	2.5	EEAGA1A101( )	200	2000
	220	8	7	160	0.22	1000	0.45	2.5	5.0	2.5	EEAGA1A221( )	200	1000
16	10	4	7	30	0.18	1000	0.45	1.5	5.0	2.5	EEAGA1C100( )	200	2000
	15	4	7	33	0.18	1000	0.45	1.5	5.0	2.5	EEAGA1C150( )	200	2000
	22	5	7	50	0.18	1000	0.45	2.0	5.0	2.5	EEAGA1C220( )	200	2000
	33	6.3	7	65	0.18	1000	0.45	2.5	5.0	2.5	EEAGA1C330( )	200	2000
	47	6.3	7	77	0.18	1000	0.45	2.5	5.0	2.5	EEAGA1C470( )	200	2000
	100	8	7	120	0.18	1000	0.45	2.5	5.0	2.5	EEAGA1C101( )	200	1000
25	10	4	7	33	0.16	1000	0.45	1.5	5.0	2.5	EEAGA1E100( )	200	2000
	15	5	7	45	0.16	1000	0.45	2.0	5.0	2.5	EEAGA1E150( )	200	2000
	22	5	7	50	0.16	1000	0.45	2.0	5.0	2.5	EEAGA1E220( )	200	2000
	33	6.3	7	75	0.16	1000	0.45	2.5	5.0	2.5	EEAGA1E330( )	200	2000
	68	8	7	100	0.16	1000	0.45	2.5	5.0	2.5	EEAGA1E680( )	200	1000
35	6.8	4	7	33	0.13	1000	0.45	1.5	5.0	2.5	EEAGA1V6R8( )	200	2000
	10	5	7	35	0.13	1000	0.45	2.0	5.0	2.5	EEAGA1V100( )	200	2000
	15	6.3	7	50	0.13	1000	0.45	2.5	5.0	2.5	EEAGA1V150( )	200	2000
	22	6.3	7	70	0.13	1000	0.45	2.5	5.0	2.5	EEAGA1V220( )	200	2000
	47	8	7	96	0.13	1000	0.45	2.5	5.0	2.5	EEAGA1V470( )	200	1000
50	1.5	4	7	16	0.10	1000	0.45	1.5	5.0	2.5	EEAGA1H1R5( )	200	2000
	2.2	4	7	18	0.10	1000	0.45	1.5	5.0	2.5	EEAGA1H2R2( )	200	2000
	3.3	4	7	22	0.10	1000	0.45	1.5	5.0	2.5	EEAGA1H3R3( )	200	2000
	4.7	4	7	26	0.10	1000	0.45	1.5	5.0	2.5	EEAGA1H4R7( )	200	2000
	6.8	5	7	35	0.10	1000	0.45	2.0	5.0	2.5	EEAGA1H6R8( )	200	2000
	10	6.3	7	39	0.10	1000	0.45	2.5	5.0	2.5	EEAGA1H100( )	200	2000
	15	6.3	7	55	0.10	1000	0.45	2.5	5.0	2.5	EEAGA1H150( )	200	2000
	22	8	7	70	0.10	1000	0.45	2.5	5.0	2.5	EEAGA1H220( )	200	1000
33	8	7	91	0.10	1000	0.45	2.5	5.0	2.5	EEAGA1H330( )	200	1000	

- When requesting taped product, please put the letter "B" or "H" between the "( )". Lead wire pitch \*B=5 mm, H=2.5 mm.  
Suffix "BQ" for ø8×7, 5mm pitch products
- Please refer to the page of "Taping Dimensions".

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Panasonic:

[EEA-GA1A101](#) [EEA-GA1E220H](#) [EEA-GA1H4R7B](#) [EEA-GA1A220](#) [EEA-GA1A221](#) [EEA-GA1A330](#) [EEA-GA1A470](#)  
[EEA-GA1A680](#) [EEA-GA1C101](#) [EEA-GA1C150](#) [EEA-GA1C220](#) [EEA-GA1C330](#) [EEA-GA1C470](#) [EEA-GA1E100](#) [EEA-](#)  
[GA1E150](#) [EEA-GA1E220](#) [EEA-GA1E680](#) [EEA-GA1H100](#) [EEA-GA1H150](#) [EEA-GA1H1R0](#) [EEA-GA1H1R5](#) [EEA-](#)  
[GA1H220](#) [EEA-GA1H330](#) [EEA-GA1H3R3](#) [EEA-GA1H4R7](#) [EEA-GA1H6R8](#) [EEA-GA1HR68](#) [EEA-GA1V150](#) [EEA-](#)  
[GA1V220](#) [EEA-GA1V470](#) [EEA-GA1V6R8](#) [EEA-GA1A101B](#) [EEA-GA1A101H](#) [EEA-GA1A220B](#) [EEA-GA1A220H](#)  
[EEA-GA1A221B](#) [EEA-GA1A221H](#) [EEA-GA1A330B](#) [EEA-GA1A330H](#) [EEA-GA1A470B](#) [EEA-GA1A470H](#) [EEA-](#)  
[GA1A680B](#) [EEA-GA1A680H](#) [EEA-GA1C100B](#) [EEA-GA1C100H](#) [EEA-GA1C101B](#) [EEA-GA1C101H](#) [EEA-GA1C150B](#)  
[EEA-GA1C150H](#) [EEA-GA1C220B](#) [EEA-GA1C220H](#) [EEA-GA1C330B](#) [EEA-GA1C330H](#) [EEA-GA1C470B](#) [EEA-](#)  
[GA1C470H](#) [EEA-GA1E100B](#) [EEA-GA1E150B](#) [EEA-GA1E150H](#) [EEA-GA1E220B](#) [EEA-GA1E330B](#) [EEA-GA1E330H](#)  
[EEA-GA1E680B](#) [EEA-GA1E680H](#) [EEA-GA1H100B](#) [EEA-GA1H150B](#) [EEA-GA1H150H](#) [EEA-GA1H1R0B](#) [EEA-](#)  
[GA1H1R0H](#) [EEA-GA1H1R5B](#) [EEA-GA1H1R5H](#) [EEA-GA1H220B](#) [EEA-GA1H220H](#) [EEA-GA1H2R2B](#) [EEA-](#)  
[GA1H2R2H](#) [EEA-GA1H330B](#) [EEA-GA1H330H](#) [EEA-GA1H3R3B](#) [EEA-GA1H3R3H](#) [EEA-GA1H4R7H](#) [EEA-](#)  
[GA1H6R8B](#) [EEA-GA1H6R8H](#) [EEA-GA1HR68B](#) [EEA-GA1HR68H](#) [EEA-GA1V100B](#) [EEA-GA1V150B](#) [EEA-](#)  
[GA1V150H](#) [EEA-GA1V220B](#) [EEA-GA1V220H](#) [EEA-GA1V470B](#) [EEA-GA1V470H](#) [EEA-GA1V6R8B](#) [EEA-GA1V6R8H](#)  
[EEA-GA1E100H](#) [EEA-GA1E330](#) [EEA-GA1H100H](#) [EEA-GA1V100](#) [EEA-GA1V100H](#) [EEA-GA1H2R2](#) [EEA-GA1C100](#)