



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01	REDRAWN ON CAD ECN 92-0009	8/30/93	<i>[Signature]</i>
02	REVISED PER ECN 95-0247	6/06/95	<i>[Signature]</i>

ELECTRICAL
Nominal Impedance (Ohms) <u>50</u>
Frequency Range (GHz) DC to <u>18.0</u>
Volt Rating (VRMS MAX) @ Sea Level <u>335</u>
VSWR <u>1.07 + .01 f(GHz)</u>
Insertion Loss (dB MAX) <u>.03 √f(GHz)</u>
RF Leakage (dB MIN) <u>-[60-f(GHz)]</u>
Corona, 70,000 Ft (VRMS MIN) <u>250</u>
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level <u>1000</u>
Contact Resistance (Milliohms MAX) Center Contact <u>2.0</u> Outer Contact <u>2.0</u> Cable to Housing <u>N/A</u>
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) <u>670</u>
I.R.(Megohms MIN) <u>10000</u>

MECHANICAL
Interface Dimensions MIL-STD-348A, Fig. <u>310.2</u>
Recommended Mating Torque <u>7-10 IN LBS</u>
Mating Characteristics: Insertion (MAX Lbs) <u>3.0</u> Withdrawal (MIN Oz) <u>1.0</u>
Force to Engage and Disengage (In-Lbs MAX) <u>2.0</u>
Center Contact Captivation Axial (Lbs) <u>6.0</u> Radial (In-Oz) <u>4.0</u>
Cable Retention Axial Force (Lbs) <u>N/A</u> Torque (In-Oz) <u>N/A</u>
Weight (Grams) <u>1.6</u>

ENVIRONMENTAL
Temperature Rating <u>-65°C to +125°C</u>
Vibration MIL-STD-202, Method 204, Condition D
Shock MIL-STD-202, Method 213, Condition I
Thermal Shock MIL-STD-202, Method 107, Condition A
Moisture Resistance MIL-STD-202, Method 106
Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray

.XXX = in  
XX.X = mm

HOUSING
STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303
DIELECTRIC TFE FLUOROCARBON PER ASTM-D-1457
CENTER CONTACT BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H

COMPONENT	MATERIAL	FINISH												
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± °	<table border="1"> <tr> <td>DRAWN BY</td> <td>DATE</td> </tr> <tr> <td>JB</td> <td>3/31/76</td> </tr> <tr> <td>CHECKED BY</td> <td></td> </tr> <tr> <td>RMF</td> <td>3/31/76</td> </tr> <tr> <td>APPD BY</td> <td></td> </tr> <tr> <td>BWC</td> <td>4/1/76</td> </tr> </table>	DRAWN BY	DATE	JB	3/31/76	CHECKED BY		RMF	3/31/76	APPD BY		BWC	4/1/76	PASSIVATE PER QQ-P-35  N/A  GOLD PLATE PER MIL-G-45204
DRAWN BY	DATE													
JB	3/31/76													
CHECKED BY														
RMF	3/31/76													
APPD BY														
BWC	4/1/76													

These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.

USE ASS'Y PROCEDURE	<table border="1"> <tr> <td>NO. AP.</td> <td>N/A</td> </tr> </table>	NO. AP.	N/A
NO. AP.	N/A		

AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599			
TITLE OSM 2 HOLE FLANGE MOUNT JACK RECEPTACLE STRAIGHT TERMINAL			
SIZE B	CODE IDENT NO. 26805	2052-5674-02	REV 02 <sub>0</sub>
SCALE 4 : 1			SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2052-5674-02](#)