

SMD LOW OHMIC - CURRENT SENSE RESISTORS

TYPE RLC73 SERIES

TE Connectivity (TE) introduces a new range of current sense resistors to be offered as a low-cost alternative to legacy solutions characterised by noble metal construction (Ag /Pd / RU) and terminations. The RLC73 series has the additional benefit of being fully RoHS compliant, and features power ratings up to 2W and TCRs down to 50ppm/°C in the high-power version. Furthermore, these resistors satisfy the demand for low ohmic shunt resistors to act as current sensors towards ICs for battery charge management and low voltage power supplies produced by global semiconductor manufacturers.



FEATURES

- Resistance values from 10mΩ
- Low TCR version available for many values
- High purity alumina substrate for high power dissipation
- RoHS Compliance
- MSL Level 1

APPLICATION

- Power management applications
- Switching power supply
- Over current protection in audio applications
- Voltage regulation module (VRM)
- DC-DC converter, battery pack, charger, adaptor
- Disk driver

SMD Low Ohmic - Current Sense Resistors

Type RLC73 Series

Characteristics – Electrical - Standard

Type	Size	Power Rating (W)	Operating Temp.	Max Operating Current (A)	Resistance Range (mΩ)			TCR (PPM/C°)
					±1% E24 & E96*	±2% E24	±5% E24	
RLC73	0805	0.125	-55 ~ 155°C	2.5	20 - 50 51 - 100 102 - 196 200 - 1000	20 - 50 51 - 100 110 - 180 200 - 1000		±600 ±400 ±300 ±200
RLC73	1206	0.25		5.0	10 - 20 22 - 50 51 - 91 100 - 1000	10 - 20 22 - 50 51 - 91 100 - 1000		±600 ±400 ±300 ±200
RLC73	1210	0.5		7.07	10 - 20 22 - 50 51 - 91 100 - 1000	10 - 20 22 - 50 51 - 91 100 - 1000		±600 ±400 ±300 ±200
RLC73	2010	0.75		8.66	10 - 20 22 - 50 51 - 91 100 - 1000	10 - 20 22 - 50 51 - 91 100 - 1000		±600 ±400 ±300 ±200
RLC73	2512	1		10.0	10 - 20 22 - 50 51 - 91 100 - 1000	10 - 20 22 - 50 51 - 91 100 - 1000		±600 ±400 ±300 ±200

*The nominal resistance value range for less than 100mΩ is in E24 series


Characteristics – Electrical - High Power

Type	Size	Power Rating (W)	Operating Temp. Range	Max Operating Current (A)	Resistance Range (mΩ)			TCR (PPM/°C)
					±1% E24 & E96*	±2% E24	±5% E24	
RLC73P	0805	0.25	-55 ~ 155°C	2.21	20 – 50 51 – 91	20 – 50 51 – 91	±600 ±400	
				1.58	100 – 196 200 – 499 500 – 1000	100 – 180 200 – 470 500 – 1000	±100 ±75 ±50	
RLC73P	1206	0.5		7.07	10 – 20 22 – 50 51 – 68	10 – 20 22 – 50 51 – 68	±600 ±400 ±300	
RLC73P	1206	1		3.65	75 – 100 102 – 147 150 – 1000	75 – 100 110 – 140 150 – 1000	±100 ±75 ±50	
RLC73P	1210	0.75		8.66	10 – 20 22 – 47	10 – 20 22 – 47	±600 ±400	
				3.87	50 – 147 150 – 1000	50 – 140 150 – 1000	±75 ±50	
RL73P	2010	1		10.0	10 – 20 22 – 47	10 – 20 22 – 47	±600 ±400	
				4.47	50 – 147 150 – 1000	50 – 140 150 – 1000	±75 ±50	
RL73P	2512	2		14.1	10 – 18	10 – 18	±600	
				10.0	20 – 47	20 – 47	±100	
				6.32	50 – 147 150 – 1000	50 – 140 150 – 1000	±75 ±50	

SMD Low Ohmic - Current Sense Resistors

Type RLC73 Series

Construction and Dimensions



- 1 Alumina Substrate

2 Bottom Electrode

3 Top Electrode

4 Edge Electrode
- 5 Barrier Layer


6 External Electrode

7 Resistor Layer

8 Overcoat

Type	Size	L (mm) ±0.10	W (mm)	T (mm)	D1 (mm)	D2 (mm)	Weight (g) / K pcs	
RLC73 / RLC73P	0805	2.00	1.25 ±0.10	0.55 ±0.10	0.30 ±0.20	0.40 ±0.25	4.6	
RLC73 / RLC73P	1206	3.10	1.55 ±0.10	0.55 ±0.10	0.50 ±0.30	0.40 ±0.25	8.7	
RLC73 / RLC73P	1210	3.10	2.60 ±0.15	0.55 ±0.10	0.50 ±0.30	0.50 ±0.25	16.0	
RLC73 / RLC73P	2010	5.00	2.50 ±0.15	0.60 ±0.15	0.60 ±0.30	0.50 ±0.25	23.7	
RLC73	2512	6.35	3.10 ±0.15	0.60 ±0.10	0.60 ±0.30	0.55 ±0.25	40.0	
RLC73P	2512 10-18mΩ		3.10 ±0.15	0.74 ±0.10		2.10 ±0.10	53.6	
	20 - 43mΩ		3.15 ±0.15	0.90 ±0.30		0.60 ±0.30	65.3	
	47mΩ		3.10 ±0.15	0.74 ±0.10		210 ±0.10	53.6	
	51 - 976mΩ						53.6	

Derating Curve




SMD Low Ohmic - Current Sense Resistors

Type RLC73 Series

Soldering Profile

■Soldering Condition (Ref. IPC/JEDEC J-STD-020 & J-STD-002)



Profile Feature	Pb-Free Assembly
Preheat	
Min. Temperature (T _{min})	150 °C
Max Temperature (T _{max})	200 °C
Preheating time (t _s) from (T _{min} to T _{max})	60-120 seconds
Ramp-up rate (T _L to T _p)	3°C/second max.
Liquidous temperature (T _L)	217 °C
Time (t _L) maintained above T _L	60-150 seconds
Min. Peak temperature (T _p min)	235°C
Max. Peak temperature (T _p max)	260°C
Time (t _p) within 5 °C of the specified classification temperature (T _c)	30 seconds max.
Ramp-down rate (T _p to T _L)	6°C/second max.
Time 25 °C to peak temperature	8 minutes max.

SMD Low Ohmic - Current Sense Resistors

Type RLC73 Series

Environmental Characteristics

Item	Requirement	Test Method
Temperature Coefficient of resistance (T.C.R.)	As Spec.	JIS-C-5201-1 4.8 IEC-60115-1 4.8 At 25°C/-55°C and 25°C/+125°C, 25°C is the reference temperature Low TCR: At 25°C/+125°C, 25°C is the reference temperature
Short Time Overload	$\pm(0.5\%+0.05\Omega)$	JIS C 5201-1 4.13 IEC 60115-1 4.13 RCWV*2.5 or Max. Overload Voltage whichever is lower for 5 seconds
	$\pm(1.0\%+0.05\Omega)$ For $\leq 50m\Omega$ & all High power	
Insulation Resistance	$\geq 10G$	JIS-C-5201-1 4.6 IEC-60115-1 4.6 Max. Overload Voltage for 1 minute
Endurance	$\pm(1.0\%+0.05\Omega)$	JIS-C-5201-1 4.25 IEC-60115-1 4.25.1 70 $\pm$ 2°C, RCWV for 1000 hrs with 1.5 hrs "ON" and 0.5 hr "OFF"
	$\pm(2.0\%+0.05\Omega)$ For $\leq 50m\Omega$ & all High power	
Damp Heat with Load	$\pm(0.5\%+0.05\Omega)$	JIS-C-5201-1 4.24 IEC-60115-1 4.24 40 $\pm$ 2°C, 90-95% R.H., RCWV for 1000 hrs with 1.5 hrs "ON" and 0.5 hr "OFF"
	$\pm(1.0\%+0.05\Omega)$ For $\leq 50m\Omega$ & all High power	
Dry Heat	$\pm(1.0\%+0.05\Omega)$	JIS-C-5201-1 4.23 IEC-60115-1 4.23.2 at +155°C for 1000 hrs
	$\pm(2.0\%+0.05\Omega)$ For $\leq 50m\Omega$ & all High power	
Bending Strength	$\pm(1.0\%+0.05\Omega)$	JIS-C-5201-1 4.33 IEC-60115-1 4.33 Bending once for 60 seconds with 3mm 2010, 2512 sizes: 2mm
Solderability	95% min. coverage	JIS-C-5201-1 4.17 IEC-60115-1 4.17 245 $\pm$ 5°C for 3 seconds
Resistance to Soldering Heat	$\pm(0.5\%+0.05\Omega)$	JIS-C-5201-1 4.18 IEC-60115-1 4.18 260 $\pm$ 5°C for 10 seconds
Voltage Proof	No breakdown or flashover	JIS-C-5201-1 4.7 IEC-60115-1 4.7 1.42 times Max. Operating Voltage for 1 minute CSN05:300V CSN06/13/10:400V; CSN12:500V
Leaching	Individual leaching area $\leq 5\%$ Total leaching area $\leq 10\%$	JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1 260 $\pm$ 5°C for 30 seconds
Rapid Change of Temperature	$\pm(0.5\%+0.05\Omega)$	JIS-C-5201-1 4.19 IEC-60115-1 4.19 -55°C to +155°C, 5 cycles

RCWV(Rated Continuous Working Voltage)= $\sqrt{P \cdot R}$ or Max. Operating Voltage whichever is lower.

Storage Temperature: 15-28°C; Humidity < 80%RH


Shelf Life: 2 years from production date

SMD Low Ohmic - Current Sense Resistors

Type RLC73 Series


Packaging

Reel Dimensions (mm)



Size	Type	Qty	Tape Width	Reel Diameter	ϕA (mm)	ϕB (mm)	ϕC (mm)	W (mm)	T (mm)
0805 1206 1210	Paper	5K / 1K	8mm	7 inch	178.5 ± 1.5	60 +0/-1	13.0 ± 0.2	9.0 ± 0.5	12.5 ± 0.5
2010 2512	Embossed	4K / 1K	12mm	7 inch	178.5 ± 1.5	60 +0/-1	13.0 ± 0.5	13.0 ± 0.5	15.5 ± 0.5
2512 2W	Embossed	2K/ 1K	12mm	7 inch	178.5 ± 1.5	60 +0/-1	13.0 ± 0.5	13.0 ± 0.5	15.5 ± 0.5

Paper Tape Specifications




Size	A (mm) ± 0.10	B (mm) ± 0.20	W (mm) ± 0.20	E (mm) ± 0.10	F (mm) ± 0.05	P ₀ (mm) ± 0.10	P ₁ (mm) ± 0.05	P ₂ (mm) ± 0.05	ϕD_0 (mm) +0.1	T (mm) ± 0.1
0805	1.60	2.40	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85
1206	1.90	3.50	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85
1210	2.90	3.50	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85

SMD Low Ohmic - Current Sense Resistors


Type RLC73 Series

Embossed plastic tape specifications



Size	A (mm)	B (mm)	W (mm)	E (mm)	F (mm)	P ₀ (mm)	P ₁ (mm)	P ₂ (mm)	øD ₀ (mm)	T (mm)
2010	2.80 ±0.10	5.40 ±0.20	12.0 ±0.30	1.75 ±0.10	5.5 ±0.05	4.00 ±0.05	4.00 ±0.10	2.00 ±0.05	1.50 ±0.10	1.00 ±0.20
2512	3.50 ±0.10	6.70 ±0.10	12.0 ±0.30	1.75 ±0.10	5.5 ±0.05	4.00 ±0.05	4.00 ±0.10	2.00 ±0.05	1.50 ±0.10	1.00 ±0.20
2512 2W 20 - 49mΩ	3.50 ±0.10	6.70 ±0.10	12.0 ±0.30	1.75 ±0.10	5.5 ±0.05	4.00 ±0.10	4.00 ±0.10	2.00 ±0.05	1.50 ±0.10	1.45 ±0.20
2512 2W 10 - 18mΩ >49mΩ	3.38 ±0.10	6.68 ±0.10	12.0 ±0.30	1.75 ±0.10	5.5 ±0.10	4.00 ±0.10	4.00 ±0.10	2.00 ±0.05	1.55 ±0.05	1.45 ±0.20

Recommended Land Pattern



Size	A (mm)	B (mm)	W (mm)
0805	1.00	1.00	1.35
1206	2.00	1.15	1.70
1210	2.00	1.15	2.50
2010	3.60	1.40	2.50
2512	4.90	1.60	3.20
2512 2W 20 - 43mΩ	4.90	1.60	3.20
2512 2W 10 - 18mΩ ≥47mΩ	1.00	3.55	3.20

Marking

4 digit marking for all models

Example

Resistance	10mΩ	51mΩ	100mΩ	549mΩ
Marking	R010	R051	R100	R549

How To Order

Common Part	T.C.R	Size	Resistance Value	Tolerance	Packaging
RLC73 - Standard Power	D - 50ppm W - 75ppm H - 100ppm	2A - 0805 2B - 1206	R010 - 10mΩ R051 - 51mΩ R100 - 100mΩ	F - 1%	TDF - 1K RL (all models)
RLC73P - High Power	K - 200ppm N - 300ppm M - 400ppm V - 600ppm	2E - 1210 2H - 2010 3A - 2512		G - 2%	TD - 5K RL
				J - 5%	(0805, 1206, 1210)
					TE - 4K RL (2010, 2512) TDG - 2K RL (2512 2W)

te.com

©2023 TE Connectivity. All Rights Reserved.

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

1773269-3 03/23 Original