






## Heyco® Self-Closing Braided Sleeving

MAXIMUM DIAMETER		PART NO. Black	DESCRIPTION	PART DIMENSIONS				INSTALLATION TOOL Part No.
in.	mm			Nominal Diameter		Spool Qty		
				in.	mm	ft.	m	
.28	7,0	<b>8880</b>	SCBS-250 BLACK	.25	6,4	100	30,5	<b>8889</b>
.39	10,0	<b>8881</b>	SCBS-375 BLACK	.38	9,7			
.55	14,0	<b>8882</b>	SCBS-500 BLACK	.50	12,7	100	30,5	<b>8890</b>
.67	17,0	<b>8883</b>	SCBS-625 BLACK	.63	16,0			
.79	20,0	<b>8884</b>	SCBS-750 BLACK	.75	19,1	100	30,5	<b>8891</b>
1.02	26,0	<b>8885</b>	SCBS-1000 BLACK	1.00	25,4			
1.30	33,0	<b>8886</b>	SCBS-1250 BLACK	1.25	31,8	100	30,5	<b>8892</b>
1.57	40,0	<b>8887</b>	SCBS-1500 BLACK	1.50	38,1			
2.05	52,0	<b>8888</b>	SCBS-2000 BLACK	2.00	50,8	100	30,5	*

\*No tool provided for the 2.00" bundle.



- Self-Closing Braided Sleeving (SCBS) can be used on pre-terminated wires due to the self closing concept. SCBS makes maintenance fast and effective. Simply open SCBS, make adjustments, and reinstall after service.
- The installation tool makes routing wire fast and easy.
- The 25% edge overlap allows coverage around inline connectors/plugs.
- Full cable flexibility is maintained in any direction, even at low temperatures. Wires encased in Heyco Self Closing Braided Sleeving can flex and bend as readily as if they had no protective oversleeving. Bundles can be flexed repeatedly without damage.
- Tough, cut-resistant sleeving is designed for protecting wire bundles and harnesses, hoses, tubing, and cable assemblies from mechanical damage and environmental hazards.
- Preferred cutting method: hot knife.

## Heyco® Braided Sleeving

BUNDLE RANGE				PART NO.		DESCRIPTION	PART DIMENSIONS			
Minimum Diameter		Maximum Diameter		Black	FR Black		Nominal Diameter		Quantity Per Spool	
in.	mm.	in.	mm.			in.	mm.	ft.	mtrs.	
.09	2,3	.25	6,4	<b>8980</b>	<b>8983</b>	BS 125	.13	3,2	1000	305
.13	3,2	.44	11,1	<b>8985</b>	<b>8988</b>	BS 250	.25	6,4		
.25	6,4	.75	19,1	<b>8990</b>	<b>8993</b>	BS 500	.50	12,7	500	152
.50	12,7	1.25	31,8	<b>8995</b>	<b>8998</b>	BS 750	.75	19,1		
.75	19,1	1.75	44,5	<b>9000</b>	<b>9003</b>	BS 1250	1.25	31,8	250	76
1.25	31,8	2.75	69,9	<b>9005</b>	<b>9008</b>	BS 1750	1.75	44,5		
1.50	38,1	3.50	88,9	<b>9010</b>	<b>9013</b>	BS 2.0	2.00	50,8	200	61

Standard color black.

FR sleeving flammability rating-UL VW-1.



- Braided sleeve slips on quickly and is self-fitting over irregular shapes and contours. No wire pulling compounds are required due to its low surface friction. Slight tensioning after application makes for an even tighter fit.
- Expandable up to three times its own diameter, the open-weave construction can fit many applications, simplifying inventory. The open-weave allows for easy inspection of sleeved components and easy break out of individual cables.
- Full cable flexibility is maintained in any direction, even at low temperatures. Wires encased in Heyco Braided Sleeving can flex and bend as readily as if they had no protective oversleeving. Bundles can be flexed repeatedly without damage.
- Tough, cut-resistant sleeving is designed for protecting wire bundles and harnesses, hoses, tubing, and cable assemblies from mechanical damage and environmental hazards.
- Preferred cutting method: hot knife.

SC Braided Sleeving		Braided Sleeving	
Material	Polyester	Materials	Polyester Monofilament Yarns or Flame Retardant Polyester Yarn
Flammability Rating	UL 94 V2	Certifications	Recognized under the Component Program of Underwriters' Laboratories File E173954
Temperature Range	-58°F (-50°C) to 302°F (150°C)	Monofilament Dia.	.010"
		Temperature Range	-103°F (-75°C) to 257°F (125°C)