


**Technical Data**

Self-laminating labels, thermal transfer
Helatag 1232

11.07.2022

TAG32-230TD1

Article Number 596-01903



Material:	Type 1232, Polyester, white transparent, self-laminating (1232)
Colour:	White (WH), Transparent (CL)
Operating Temperature - °C:	-40 °C to +150 °C
Curing Temperature:	from +2 °C
Bundle Ø min.:	30.24 mm
Bundle Ø max.:	50.8 mm
Self adhesive (Yes/No):	Yes
Width (W):	32.00 mm
Height (H):	60.00 mm
Height (H2):	228.6 mm
Width of Liner (WL):	38.00 mm
Labels per Row:	1 pc.
Thickness of Foil:	50 µm
Adhesive:	Acrylic

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved



Technical Data

Self-laminating labels, thermal transfer
Helatag 1232

11.07.2022

Resistance to:

Brake cleaner: 720h (at room temperature),
Alcohol 94%: 720h (at room temperature),
Hydraulic oil: 720h (at room temperature)

Print Method:

Thermal transfer print

Application Tool:

TT431, TT4030

Recommended Ribbon Type:

TT822OUT

Application Method:

The functionality and durability of the labels can be negatively affected if improperly processed or applied. All surfaces to be bonded must be clean, dry as well as free from dust and grease. Avoid touching the adhesive surface of the label as this could impair the application performance.

RoHS