



Sample Kit 1006

TDK Part #	Case Size	Temperature Coefficient	Voltage (DC)	Value	Tolerance Code	Tolerance Value	Thickness
CGA2B3X7S2A102K	1005	X7S	100	1000pF	K	+/-10%	0.50
CGA2B3X7S2A103K	1005	X7S	100	0.01uF	K	+/-10%	0.50
CGA3E2C0G2A101J	1608	C0G	100	100pF	J	+/-5%	0.80
CGA3E2C0G2A102J	1608	C0G	100	1000pF	J	+/-5%	0.80
CGA3E3C0G2E101J	1608	C0G	250	100pF	J	+/-5%	0.80
CGA3E2X7R2A102K	1608	X7R	100	1000pF	K	+/-10%	0.80
CGA3E2X7R2A103K	1608	X7R	100	0.01uF	K	+/-10%	0.80
CGA3E3X7S2A104K	1608	X7S	100	0.1uF	K	+/-10%	0.80
CGA3E2X8R2A102K	1608	X8R	100	1000pF	K	+/-10%	0.80
CGA3E2X8R2A103K	1608	X8R	100	0.01uF	K	+/-10%	0.80
CGA4C2C0G2A101J	2012	C0G	100	100pF	J	+/-5%	0.60
CGA4C2C0G2A102J	2012	C0G	100	1000pF	J	+/-5%	0.60
CGA4F3C0G2E102J	2012	C0G	250	1000pF	J	+/-5%	0.85
CGA4F2X7R2A102K	2012	X7R	100	1000pF	K	+/-10%	0.85
CGA4F2X7R2A103K	2012	X7R	100	0.01uF	K	+/-10%	0.85
CGA4J2X7R2A104K	2012	X7R	100	0.1uF	K	+/-10%	1.25
CGA4F3X7R2E102K	2012	X7R	250	1000pF	K	+/-10%	0.85
CGA4J3X7R2E103K	2012	X7R	250	0.01uF	K	+/-10%	1.25
CGA4J3X7S2A105K	2012	X7S	100	1uF	K	+/-10%	1.25
CGA4J3X7T2E104K	2012	X7T	250	0.1uF	K	+/-10%	1.25
CGA4F4X7T2W103K	2012	X7T	450	0.01uF	K	+/-10%	0.85
CGA5H2C0G2A103J	3216	C0G	100	0.01uF	J	+/-5%	1.15
CGA5C4C0G2J101J	3216	C0G	630	100pF	J	+/-5%	0.60
CGA5F4C0G2J102J	3216	C0G	630	1000pF	J	+/-5%	0.85
CGA5L2X7R2A104K	3216	X7R	100	0.1uF	K	+/-10%	1.60
CGA5L2X7R2A105K	3216	X7R	100	1uF	K	+/-10%	1.60
CGA5L3X7R2E104K	3216	X7R	250	0.1uF	K	+/-10%	1.60
CGA5H4X7R2J102K	3216	X7R	630	1000pF	K	+/-10%	1.15
CGA5H4X7R2J103K	3216	X7R	630	0.01uF	K	+/-10%	1.15
CGA5L4X7T2W104K	3216	X7T	450	0.1uF	K	+/-10%	1.60
CGA5F1X7T2J103K	3216	X7T	630	0.01uF	K	+/-10%	0.85
CGA5H2X8R2A104K	3216	X8R	100	0.1uF	K	+/-10%	1.15
CGA6L3C0G2E103J	3225	C0G	250	0.01uF	J	+/-5%	1.60
CGA6M2X7R2A105K	3225	X7R	100	1uF	K	+/-10%	2.00
CGA6M3X7R2E104K	3225	X7R	250	0.1uF	K	+/-10%	2.00
CGA6L1X7T2J104K	3225	X7T	630	0.1uF	K	+/-10%	1.60