



TDK Part #	Case Size	Temperature Coefficient	Voltage (DC)	Value	Tolerance Code	Tolerance Value	Thickness
<u>CGA2B2C0G1H102J</u>	1005	C0G	50	1000pF	J	+/-5%	0.50
<u>CGA2B3X7R1H104K</u>	1005	X7R	50	0.1uF	K	+/-10%	0.50
<u>CGA2B1X7R1A224K</u>	1005	X7R	10	0.22uF	K	+/-10%	0.50
<u>CGA2B2X8R1E103K</u>	1005	X8R	25	0.01uF	K	+/-10%	0.50
<u>CGA3E2C0G1H103J</u>	1608	C0G	50	0.01uF	J	+/-5%	0.80
<u>CGA3E3X7R1H224K</u>	1608	X7R	50	0.22uF	K	+/-10%	0.80
<u>CGA3E1X7R1V474K</u>	1608	X7R	35	0.47uF	K	+/-10%	0.80
<u>CGA3E1X7R0J225K</u>	1608	X7R	6.3	2.2uF	K	+/-10%	0.80
<u>CGA3E1X5R0J475K</u>	1608	X5R	6.3	4.7uF	K	+/-10%	0.80
<u>CGA3E2X8R1H473K</u>	1608	X8R	50	0.047uF	K	+/-10%	0.80
<u>CGA4J2C0G1H333J</u>	2012	C0G	50	0.033uF	J	+/-5%	1.25
<u>CGA4J3X7R1H105K</u>	2012	X7R	50	1uF	K	+/-10%	1.25
<u>CGA4J1X7R1V225K</u>	2012	X7R	35	2.2uF	K	+/-10%	1.25
<u>CGA4J3X5R1A106K</u>	2012	X5R	10	10uF	K	+/-10%	1.25
<u>CGA4J2X8R1H104K</u>	2012	X8R	50	0.1uF	K	+/-10%	1.25
<u>CGA4J2X8R1E334K</u>	2012	X8R	25	0.33uF	K	+/-10%	1.25
<u>CGA5L2C0G1H104J</u>	3216	C0G	50	0.1uF	J	+/-5%	1.60
<u>CGA5L3X7R1H225K</u>	3216	X7R	50	2.2uF	K	+/-10%	1.60
<u>CGA5L1X7R1V475K</u>	3216	X7R	35	4.7uF	K	+/-10%	1.60
<u>CGA5L2X8R1H474K</u>	3216	X8R	50	0.47uF	K	+/-10%	1.60
<u>CGA5L2X8R1E105K</u>	3216	X8R	25	1uF	K	+/-10%	1.60
<u>CGA6P2C0G1H104J</u>	3225	C0G	50	0.1uF	J	+/-5%	2.50
<u>CGA6P3X7R1H475K</u>	3225	X7R	50	4.7uF	K	+/-10%	2.50
<u>CGA6P1X7R1C226M</u>	3225	X7R	16	22uF	M	+/-20%	2.50
<u>CGA6P3X7S1H106K</u>	3225	X7S	50	10uF	K	+/-10%	2.50
<u>CGA6P2X8R1E335K</u>	3225	X8R	25	3.3uF	K	+/-10%	2.50