

Amphenol Sensors

Connecting your world through
Sensing Innovations


HVAC for Medical Facilities

Amphenol Sensors is a leading innovator in sensing technologies and measurement solutions. Offering the most diverse sensor portfolio of standard and customized products for the world's most demanding regulatory and industry-driven applications, Amphenol creates value by providing critical information for real-time decisions.

The demands of today's healthcare industry require not only the highest criteria in the direct care of a patient, but also the highest quality, accuracy and efficiency in those facilities that allow for that care.


Within a medical facility, the proper operation of its heating, ventilating and air conditioning (HVAC) systems also ensures proper operation of various medical support functions to provide for the health, comfort and safety of that facility's occupants, including patients, visitors and staff.


Amphenol Sensors' diverse portfolio of world class sensing solutions touches nearly every facet of a medical facility's HVAC systems to ensure not only the utmost in conditions for patient care and recovery, but also long-term efficiency to achieve green building status.



Amphenol Sensors

HVAC for Medical Facilities

Application		Solution	Technology & Features	
Carbon Dioxide (CO ₂)	Fresh Air Ventilation Control	- Monitors patient/staff occupancy to ensure proper CO₂ levels - For use in temporary medical facilities with no standard Building Automation System (BAS) in place	- Dual channel automatic calibration - Outputs: 0-10v, 0-5v, 4-20mA, relay, BACnet	
	Inline Oxygen Measurement	Aids patient breathing in ventilator equipment	0-100% Volume Oxygen - Wide pressure range - Realtime measurements - Linear - Low power electrochemical sensor	
Humidity	Humidity Control	- Prevents condensation that can cause mold growth, in addition to harmful respiratory conditions - Ensures human comfort and energy efficiency	- Accuracy Options: 2%, 3%, 5% - Outputs: 0-10v, 0-5v, 4-20mA - Field replaceable Relative Humidity (RH) sensor	
Pressure	Differential Pressure Measurement	Negative-pressure patient isolation room monitoring	- Outputs: 0-10v, 0-5v, 4-20mA - Range: 0-0.3"WC T30 - Range: 0-0.5"WC, T10, T20 - Piezoresistive sensor - Offsets: 0, 1/4, 1/2 span - Units: In. WC, Pa, or mm H₂O - Accuracy: ±1% of span	
		- Negative-pressure patient isolation room monitoring - Fan/filter monitoring - Sensing components for ventilators, sleep apnea, and oxygen concentrators	±0.5" H₂O and above - High volume - Accuracy: ±1.5 % of span	
	Climate Control Systems	Measures coolant pressure in HVAC systems	- Stainless steel pressure sensing element, aluminum housing, RD-connector - Pressure Range: -1-10bar to -1-100bar, gauge - Temperature Range: -40°C to 125°C (150°C) - Outputs: LIN, PWM, analog voltage	
	HVAC Refrigerant	Measures low and high pressures of HVAC refrigerant	- Stainless steel, media-isolated 3psi – 7500psi - Gauge, sealed and absolute piezoresistive transducers - Output Options: 5V, 4-20mA, 4.5V - Accuracy: 1% - Variety of ports - Harness accessories available	

Application		Solution	Technology & Features	
Combined Pressure & Temperature	Climate Control Systems	Measures pressure and temperature of coolants in HVAC systems	- Compatible to all currently used coolants (R134a, R1234yf, R744) - High temperature accuracy and fast response time - Stainless steel pressure sensing element, aluminum or steel housing, RD-connector or MQS-connector - Pressure Range: -1-10bar to -1-200bar, gauge - Temperature Range: -40°C to 125°C (150°C) - Output: LIN	 
	Equipment Temperature Conditions	Monitors critical equipment for over-temperature conditions	- Sensing element isolated from tag - Dielectric 750 Vac - Eyelets to fit M3/M4/M5 screw sizes; additional diameters available - Suitable for surface temperature measurement	 
Temperature	HVAC Systems Temperature	Provides temperature control for nearly every aspect of a medical facility, from maintaining the air temperature in an operating room to monitoring hot water temperature supplied to restroom sinks	- Configuration: Pipe Clip - Designed for 250,000 thermal cycles between 25°C to 85°C - Pipe Diameter Range: 13-30 mm (1/2-1-1/8 in)	 
			- Configuration: Integrated Pipe Clip - IP57 Ingression Protection Rating - AEC Q200 REV (D) - pending - Sensing Element: Dielectric 750 Vac - Pipe Diameter Range: 15-18 mm (5/8-1 in) - Self-adjusts to irregular pipe surfaces	 
			- Configuration: Boiler Probe - Connector Series: Molex Minifit - Full range of TCO temperature ratings according to EN60691 - Range of connectors available	 
			- Configuration: Cable Probe - IP66 Rating - Long-term stability - Good thermal response time	 
	Floor Heating	Provides uniform temperature for in-floor heating	- Various resistance values available - Various lead lengths available	 
	Air Conditioning	Directly measures object temperature for automatic adjustments	- Auto control of fan and blowing rate - Long detection range (~5M)	 
Position	Medical Equipment	Provides position feedback for respiratory devices, infusion pumps, and electrophoresis devices	- Programmable measuring angle with built-in redundancy - Truly contactless operation with no wear; maintenance free - Immunity to dust, moisture, vibration and extreme temperatures - Robust, compact, and low profile up to IP69K Protection - Absolute position feedback; position is not lost even on power loss - High resolution up to 14-bit	 
	Hospital Beds and Wheelchairs	Provides rotary angle/position feedback for power beds and power wheelchairs		 
	HMI Controls	Provides linear and rotary position sensing for centrifugators, X-ray and imaging systems, ventilators, patient monitor equipment, and HVACR		 

Sensing Technologies

MAJOR MARKETS SERVED	Thermometrics, Inc. Temperature	Telaire Gas & Moisture	NovaSensor Pressure	Protimeter Moisture Meters	Kaye Thermal Validation	SGX Sensortech Gas	Piher Sensing Systems Position	Wilcoxon Sensing Technologies Vibration	Piezo Technologies Ultrasonic	i2s Pressure & Temperature	All Sensors Ultra Low Pressure	SSI Technologies Level, Quality & Pressure
Aerospace (Commercial)	•		•			•	•				•	•
Agriculture	•	•		•		•	•			•		•
Air Quality		•		•		•					•	•
Automotive	•	•	•			•	•			•		•
Automation	•	•					•	•			•	
Construction & Restoration				•								•
Electrification (EV/HEV)	•	•	•			•	•			•		•
Energy	•					•		•	•			
Environmental Monitoring					•	•					•	
HVAC - Industrial	•	•	•			•	•	•		•	•	•
HVAC - Medical Facilities	•	•	•			•	•			•	•	•
Air-Conditioning	•											
Climate Control Systems										•		
Differential Pressure Measurement		•	•								•	•
Equipment Conditions	•											
Floor Heating	•											
Fresh Air Ventilation Control		•										
HMI Controls							•					
Hospital Beds and Wheelchairs							•					
Humidity Control		•										
HVAC Refrigerant												•
HVAC Systems	•									•		
Inline Oxygen Measurement						•						
Medical Equipment							•					
Industrial	•	•	•	•		•	•	•		•	•	•
Marine	•					•	•	•				•
Medical	•	•	•				•		•		•	•
Military	•		•			•	•	•	•		•	•
Non-Destructive Testing (NDT)									•			
Oil & Gas	•		•			•	•	•	•		•	•
Pharmaceutical & Biotech					•						•	•
Railway	•							•				•
Thermal Validation					•							

**Amphenol
Sensors**

www.amphenolsensors.com

© 2020 Amphenol Corporation. All Rights Reserved. Specifications are subject to change without notice.

Other company names and product names used in this document are the registered trademarks of their respective owners.