



User Manual
SKU: TPX00256



Description

The Arduino® USB-C Power Supply (65 W) is a compact wall adapter providing up to 65 W via USB-C using the USB Power Delivery (PD) protocol. It is the recommended power source for the Arduino® VENTUNO Q and its peripherals. The adapter supports 5 VDC, 9 VDC, 12 VDC, 15 VDC (up to 3.0 A), and 20 VDC (up to 3.25 A), automatically matching the device's needs. It features a foldable plug for easy transport and interchangeable EU and UK plugs.



CONTENTS

1 Features	4
1.1 General Specifications	4
1.2 Input Specifications	5
1.3 Output Specifications	5
1.4 Supported Charging Protocols	6
1.5 Regional Plug Options	6
2 Usage	8
2.1 Key Use Cases	8
2.2 Connection Method	8
3 Technical Specifications	9
3.1 Output Characteristics	9
3.1.1 Voltage Regulation	9
3.1.2 Ripple and Noise	9
3.1.3 Dynamic Response	10
3.2 Efficiency	10
3.3 EU Ecodesign (ErP) Compliance	10
3.4 Protection Features	11
3.5 Operating Conditions	11
3.6 Safety and EMC Specifications	11
3.6.1 Electrical Safety	11
3.6.2 EMI/EMC Compliance	12
4 Mechanical Information	13
4.1 Dimensions	13
4.2 Package Contents	14
5 Environmental and Reliability	15
5.1 Reliability Requirements	15
5.2 Mechanical Stress Tests	15
5.3 Environmental Compliance	15
6 Certifications	16
6.1 Safety Certifications	16
6.2 Declaration of Conformity CE DoC (EU)	16
6.3 Declaration of Conformity to EU RoHS & REACH	17
6.4 Conflict Minerals Declaration	17



7 FCC Caution	18
8 Company Information	18
9 Related Products	18
10 Reference Documentation	19
11 Document Revision History	19



1 Features

1.1 General Specifications



Arduino USB-C Power Supply (65 W)

The table below summarizes the general specifications of the power supply:


Feature	Specification
Model Number	TPX00256
Adapter Type	Plug-in wall adapter (foldable plug)
Output Connector	USB-C (USB Type-C)
Dimensions (Body)	64 × 64 × 30 mm (folded plug)/64 × 80.06 × 30 mm (unfolded plug)
Material	PC (Polycarbonate) housing

1.2 Input Specifications

The following table lists the AC input characteristics of the power supply:

Parameter	Specification
Rated Input Voltage	100 - 240 VAC
Input Voltage Range	90 - 264 VAC
Input Frequency	47 - 63 Hz (50/60 Hz)
Maximum Input Current	1.5 A

1.3 Output Specifications



Arduino USB-C Power Supply Output (65 W)



The power supply delivers the following USB Power Delivery output profiles:

Output Voltage	Maximum Current	Maximum Power
5.0 VDC	3.0 A	15 W
9.0 VDC	3.0 A	27 W
12.0 VDC	3.0 A	36 W
15.0 VDC	3.0 A	45 W
20.0 VDC	3.25 A	65 W

Combined maximum output power: 65 W


Important note: The power supply negotiates voltage and current using the PD protocol based on device needs.

1.4 Supported Charging Protocols

In addition to USB Power Delivery (PD), the adapter supports the following charging protocols:

Protocol	Support
USB PD 3.0	Supported
Qualcomm QC 2.0/3.0	Supported
AFC	Supported
FCP	Supported
Apple 5 V / 2.4 A	Supported

1.5 Regional Plug Options



Regional Plug Options

The power supply is available with the following regional plug options:



Region	Plug Type	IEC Type	Dimensions (W × H × D)
United States (Default)	Foldable	Type A	Integrated (foldable)
Europe (EU)	Interchangeable	Type C	34.6 - 36.0 × 27.5 × 37 mm
United Kingdom (UK)	Interchangeable	Type G	48.98 × 39.83 × 22.23 - 23.23 mm

Important note: The EU and UK plugs are interchangeable and can be replaced without tools. Make sure the correct plug is attached for your region before use.



2 Usage

The Arduino® USB-C Power Supply (65 W) provides power for USB-C devices and their peripherals through the USB Power Delivery (PD) protocol. Within the Arduino ecosystem, it is the recommended power source for the Arduino® VENTUNO Q. When used with USB-C hubs or docks, the power supply can sustain a connected device together with multiple peripherals such as displays, USB devices, and network adapters.

2.1 Key Use Cases

The power supply supports the following use cases:

- **Direct device power:** Powers USB-C devices directly during development and operation.
- **Hub or dock power delivery:** Supplies USB-C hubs and docks with enough headroom to power a device and several peripherals at once.
- **Fast charging:** Charges USB-C devices through automatic power negotiation.
- **Multi-device support:** Compatible with single-board computers, microcontroller boards, and other USB-C devices.

2.2 Connection Method

For standalone operation, connect the power supply's USB-C output directly to the device's USB-C port, then plug the adapter into a mains outlet within the rated input range of 100 - 240 VAC. The adapter and the connected device automatically negotiate the appropriate voltage and current, so no manual configuration is needed.

For expanded I/O, connect the power supply to a USB-C hub or dock through its PD input port, then connect the hub to the device. The hub distributes power to the device and the attached peripherals simultaneously.

Important note: When powering USB-C hubs or docks with multiple high-power peripherals, connect the power supply to the hub's PD input port. The hub distributes power to the device and the connected peripherals simultaneously. Make sure the total power consumption does not exceed 65 W.



3 Technical Specifications

3.1 Output Characteristics

3.1.1 Voltage Regulation

The output voltage range for each Power Delivery profile is shown below.

Output Voltage	Voltage Range
5.0 VDC	4.65 - 5.25 VDC
9.0 VDC	8.55 - 9.45 VDC
12.0 VDC	11.4 - 12.6 VDC
15.0 VDC	14.25 - 15.75 VDC
20.0 VDC	19.0 - 21.0 VDC

3.1.2 Ripple and Noise

The ripple and noise characteristics are specified as follows:

Parameter	Specification
Ripple and Noise (all modes)	200 mVp-p maximum (at full load)
Measurement Bandwidth	20 MHz

Measurement conditions: Ripple and noise are measured using a 20 MHz oscilloscope, with a 0.1 μ F ceramic and 10 μ F electrolytic capacitor at rated input/output.



3.1.3 Dynamic Response

The dynamic response of the power supply is characterized by the following parameters:

Parameter	Specification
Turn-on Delay	3 seconds maximum @ 115 VAC, full load
Hold-up Time	5 ms minimum @ 230 VAC, full load
Rise Time	80 ms maximum (10% to 90% of rated output)

3.2 Efficiency

The minimum average efficiency for each output mode, measured at 115 VAC and 230 VAC, is listed below.

Output Mode	Average Efficiency
5.0 VDC/3.0 A	81.39% minimum
9.0 VDC/3.0 A	86.62% minimum
12.0 VDC/3.0 A	87.40% minimum
15.0 VDC/3.0 A	87.73% minimum
20.0 VDC/3.25 A	88.00% minimum

No-load power consumption: ≤ 0.21 W @ 115 - 230 VAC

3.3 EU Ecodesign (ErP) Compliance

The following table lists the efficiency and no-load power values reported for compliance with EU Regulation 2019/1782 on ecodesign requirements for external power supplies.

Parameter	Value
Average Active Efficiency	89.76%
Efficiency at 10% Load	80.21%
No-Load Power Consumption	0.122 W

Important note: These values are measured according to the test conditions defined by EU Regulation 2019/1782. The minimum efficiency values per output profile listed in the Efficiency section are derived from the manufacturer specification and represent guaranteed minimums, whereas the ErP values reflect measured compliance results.



3.4 Protection Features

The power supply includes three built-in protection mechanisms that safeguard both the adapter and the connected device against fault conditions:

Protection	Description
Over Current Protection (OCP)	Triggers when the output current reaches 105% - 150% of the maximum rated load. The output enters hiccup mode and recovers automatically once the fault is removed.
Short Circuit Protection (SCP)	Reduces the input power if the output is short-circuited, preventing damage. The supply recovers automatically once the short circuit is removed.
Over Voltage Protection (OVP)	Triggers if the output voltage exceeds its rated value. The output enters hiccup mode and recovers automatically once the fault is removed.

3.5 Operating Conditions

The power supply is designed to operate and be stored within the following conditions:

Parameter	Range
Operating Temperature	0 - 35 °C
Operating Humidity	10 - 90% RH (non-condensing)
Storage Temperature	-40 - 70 °C
Storage Humidity	5 - 95% RH (non-condensing)

3.6 Safety and EMC Specifications

3.6.1 Electrical Safety

The electrical safety characteristics are listed in the table below.

Parameter	Specification
Dielectric Strength	3000 VAC @ 50 Hz, 5 mA max, 60 seconds
Production Hi-Pot Test	3600 VAC @ 50 Hz, 5 mA max, 3 seconds
Leakage Current	0.25 mA maximum @ 230 VAC/50 Hz
Insulation Resistance	10 MΩ minimum @ 500 VDC, 90% RH
Flammability Rating	UL94V-0 (minimum)
Protection Class	Class II (double insulated)



3.6.2 EMI/EMC Compliance

The power supply complies with the following EMI and EMC standards:


Standard	Compliance
Conducted & Radiated Emissions	EN 55032/35, BS EN 55032/35, FCC Part 15
ESD Immunity	EN 61000-4-2 (± 4 kV contact, ± 8 kV air)
EFT/Burst Immunity	EN 61000-4-4 (± 1 kV, AC input)
Surge Immunity	EN 61000-4-5 (± 2 kV common mode, ± 1 kV differential mode)



4 Mechanical Information

4.1 Dimensions

The power supply has a compact form factor. The integrated US plug folds flat for easy transport and storage, and interchangeable EU and UK plugs are available for regional use, as described in the Regional Plug Options section.



Power Supply Dimensions

The overall dimensions in the folded and unfolded configurations are listed below.

Configuration	Dimensions (W × L × H)
With US plug folded	64 × 64 × 30 mm
With US plug unfolded	64 × 80.06 × 30 mm



4.2 Package Contents

The package includes the following items:

- Arduino® USB-C Power Supply (65 W) (x1)
- Region-specific plug (x1)



5 Environmental and Reliability

5.1 Reliability Requirements

The reliability requirements for the power supply are summarized below.

Parameter	Specification
MTBF	30,000 hours minimum @ 25 °C, 80% load, nominal input
High Temperature Test	Normal operation @ 240 VAC, full load, 35 °C ambient
Salt Spray Test	24 hours @ 5% salt mist; no corrosion or oxidation on USB and metal parts

5.2 Mechanical Stress Tests

The power supply is validated against the following mechanical stress tests:

Test Type	Specification
Vibration Test	10 - 300 Hz sweep, 1.0 G constant (3.5 mm displacement), 1 hour per axis (X, Y, Z)
Vibration Criteria	No visible damage, normal operation after test
Drop Test	6 faces, 1 meter height onto a concrete surface (one drop per face)
Drop Criteria	Plug may bend, and housing may scratch, but no structural damage; normal operation after test

5.3 Environmental Compliance

The power supply complies with the following environmental regulation:

Regulation
RoHS



6 Certifications

6.1 Safety Certifications

The Arduino USB-C Power Supply holds the following safety certifications:

Certification	Region	Standard
UL/CUL	USA/Canada	UL62368-1, CSA C22.2
ETL	USA	UL62368
TUV/GS	Europe	EN62368
CE	Europe	EN62368
UKCA	United Kingdom	EN62368
FCC	USA	Part 15 Class B

Important note: All certifications are maintained and updated regularly. For the most current certification status, please contact Arduino support or refer to product documentation.

6.2 Declaration of Conformity CE DoC (EU)

English: We declare under our sole responsibility that the products above are in conformity with the essential requirements of the following EU Directives and therefore qualify for free movement within markets comprising the European Union (EU) and European Economic Area (EEA).

French: Nous déclarons sous notre seule responsabilité que les produits indiqués ci-dessus sont conformes aux exigences essentielles des directives de l'Union européenne mentionnées ci-après, et qu'ils remplissent à ce titre les conditions permettant la libre circulation sur les marchés de l'Union européenne (UE) et de l'Espace économique européen (EEE).



6.3 Declaration of Conformity to EU RoHS & REACH

Arduino products are in compliance with Directive 2011/65/EU of the European Parliament and Directive 2015/863/EU of the Council of 4 June 2015 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

Substance	Maximum Limit (ppm)
Lead (Pb)	1000
Cadmium (Cd)	100
Mercury (Hg)	1000
Hexavalent Chromium (Cr6+)	1000
Poly Brominated Biphenyls (PBB)	1000
Poly Brominated Diphenyl ethers (PBDE)	1000
Bis(2-Ethylhexyl) phthalate (DEHP)	1000
Benzyl butyl phthalate (BBP)	1000
Dibutyl phthalate (DBP)	1000
Diisobutyl phthalate (DIBP)	1000

Exemptions: No exemptions are claimed.

Arduino products are fully compliant with the related requirements of European Union Regulation (EC) 1907/2006 concerning the Registration, Evaluation, Authorization and Restriction of Chemicals (REACH). We declare none of the SVHCs (<https://echa.europa.eu/web/guest/candidate-list-table>), the Candidate List of Substances of Very High Concern for authorization currently released by ECHA, is present in all products (and also package) in quantities totaling in a concentration equal or above 0.1%. To the best of our knowledge, we also declare that our products do not contain any of the substances listed on the "Authorization List" (Annex XIV of the REACH regulations) and Substances of Very High Concern (SVHC) in any significant amounts as specified by the Annex XVII of Candidate list published by ECHA (European Chemical Agency) 1907/2006/EC.

6.4 Conflict Minerals Declaration

As a global supplier of electronic and electrical components, Arduino is aware of our obligations with regards to laws and regulations regarding Conflict Minerals, specifically the Dodd-Frank Wall Street Reform and Consumer Protection Act, Section 1502. Arduino does not directly source or process conflict minerals such as Tin, Tantalum, Tungsten, or Gold. Conflict minerals are contained in our products in the form of solder, or as a component in metal alloys. As part of our reasonable due diligence Arduino has contacted component suppliers within our supply chain to verify their continued compliance with the regulations. Based on the information received thus far we declare that our products contain Conflict Minerals sourced from conflict-free areas.



7 FCC Caution

Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:

- (1) This device may not cause harmful interference.
- (2) This device must accept any interference received, including interference that may cause undesired operation.

FCC RF Radiation Exposure Statement:

This equipment complies with FCC radiation exposure limits set forth for an uncontrolled environment.

8 Company Information

The power supply is manufactured by the company listed below.

Company name	Arduino S.r.l.
Company address	Via Andrea Appiani 25, 20900 Monza (Italy)

9 Related Products

This power supply can be used with the following Arduino products:

- Arduino® UNO™ Q 2GB (SKU: ABX00162)
- Arduino® UNO™ Q 4GB (SKU: ABX00173)
- Arduino® VENTUNO™ Q (SKU: ABX00181)



10 Reference Documentation

The following table lists additional resources related to this product.

No.	Reference	Link
1	Arduino Store	https://store.arduino.cc/products/usb-c-power-supply-45w
2	65 W Power Supply Product Page	https://docs.arduino.cc/hardware/usb-c-power-supply-45w/

11 Document Revision History

The table below records the revision history of this document.

Date	Revision	Changes
27/05/2026	1	First release