swissbit®

Product Data Sheet

Industrial M.2 PCle SSD

N3000 Series
PCle 4.0, 3D TLC

Industrial Temperature Grade

March 27, 2025 Date:

Revision:





Contents

1.	PRODUCT SUMMARY	. 3
2.	PRODUCT FEATURES	. 4
3.	SECURITY FEATURES	. 4
4.	ORDERING INFORMATION	. 5
5.	PRODUCT DESCRIPTION	
	5.1 PERFORMANCE SPECIFICATIONS 5.2 CURRENT CONSUMPTION 5.3 ENVIRONMENTAL SPECIFICATIONS 5.4 REGULATORY COMPLIANCE 5.5 MECHANICAL SPECIFICATIONS 5.6 RELIABILITY AND ENDURANCE 5.7 DRIVE GEOMETRY SPECIFICATION	. 9
6.	ELECTRICAL INTERFACE	.1
7.	PACKAGE MECHANICAL	13
8.	NVME COMMANDS	15
9.	IDENTIFY DEVICE INFORMATION	.17
10.	HEALTH MONITORING FUNCTIONALITY	20
11.	PART NUMBER DECODER	23
12.	MARKING SPECIFICATION	24
	12.1 TOP VIEW	
40	DEVICION LISTORY	٦-



N3000 Series - Industrial M.2 PCIe SSD 240 GBytes up to 3840 GBytes

1. Product Summary

Capacities: 240 GBytes, 480 GBytes, 960 GBytes, 1920 GBytes, 3840 GBytes Form Factor: PCI Express M.2 2242/2280 (42/80 mm x 22 mm x 3.8 mm)

Compliance¹: PCI Express (PCIe) Base Specification Revision 4.0

Interface: Gen4 x 4 Lanes

Drive operates in x1 mode in x1 M.2 PCle slots Drive operates in x2 mode in x2 M.2 PCle slots Drive operates in x4 mode in x4 M.2 PCle slots

Command Sets: Supports NVMe 1.4

Target Performance:

Read Performance: Sequential Read up to 3,850 MBytes/s, Random Read 4K up to 455,900 IOPS

Write Performance: Sequential Write up to 3,340 MBytes/s, Random Write 4K up to 505,200 IOPS

Operating Temperature Range²:

o Industrial: -40 °C to 85 °C

Storage Temperature Range:

Industrial: -40 °C to 85 °C

Power:

Power States PSo, PS1, PS2, PS3 and PS4

Thermal Throttling supported

Data Retention³: 10 Years @ Life Begin; 1 Year @ Life End, @40 °C

Shock/Vibration: 1,500 g / 50 g

High-Performance Processor with Integrated, Parallel Flash Interface Engines:

- Triple-Level Cell (TLC) 3D NAND Flash
- o DDR4 DRAM based Controller architecture
- o 240 bit LDPC correction per 2 KByte

High Reliability:

Swissbit AG

Switzerland

Industriestrasse 4

CH-9552 Bronschhofen

Mean Time Between Failure (MTBF): > 3,000,000 hours

Data Reliability: < 1 non-recoverable error per 10¹⁶ bits read

To check the compatibility of the customer system and the storage device is part of the customer's responsibility. Swissbit can provide guidance and support on request.

Adequate airflow is required to ensure the temperature, as reported in the S.M.A.R.T. data, does not exceed 110 °C (industrial temperature drive).

³ NAND Flash suppliers refer to JEDEC JESD47 and JESD22 for Data Retention testing. Based on the information provided by the NAND Flash suppliers, Data Retention is targeted as shown.



2. Product Features

- Diagnostic features
- Life end read only mode
- RAID engine
- Drive self-test
- Data Care Management
 - o Active: Adaptive Read Refresh
 - Passive: Background Media Scan
- Active State Power Management (ASPM) Support
- In-Field Firmware Update⁴
- Adaptive Thermal control
- DRAM-Buffer
- Self-Monitoring, Analysis, and Reporting Technology (S.M.A.R.T., Telemetry)
- SMBus⁵ (NVMe Management Interface Basic Management Command, NVMe-MI v1.2)
- 30 µinch (0.8 µm) Gold-Plated Connector (IPC-6012C Class 2 Compliant)
- End-to-End (E2E) Data Protection
- Controlled "Locked" BOM
- RoHS / REACH Compliant
- Swissbit Device Manager Tool (SBDM)

3. Security features

- AES256 encryption
- TCG OPAL 2.0
- Secure Boot
- Crypto erase
- IEEE 1667



























⁴ The support of In-Field FW update capabilities on host systems is recommended.

⁵ SMBus commands are not supported in PS4 power state. Swissbit AG



4. Ordering Information

Table 1: Standard Product List

Capacity	Part Number	Numbers of Lanes
240 GBytes	SN3000Mx240GI-yMA2-zGB-STD	
480 GBytes	SN3000Mx480GI-yMA2-zGB-STD	
960 GBytes	SN3000Mx960GI-yMA2-zGB-STD	4
1920 GBytes	SN3000Mx1T92I-yMA2-zGB-STD	
3840 GBytes	SN3000Mx3T84I-yMA4-zGB-STD	

x = from factor; y = Product Generation; z= Firmware Revision

Table 2: Available Part Numbers

Canacity	FW ARR51000		
Capacity	2242	2280	
240 GBytes	SN3000MB240GI-1MA2-1GB-STD	SN3000MD240GI-1MA4-1GB-STD	
480 GBytes	SN3000MB480GI-1MA2-1GB-STD	SN3000MD480GI-1MA2-1GB-STD	
960 GBytes	SN3000MB960GI-1MA2-1GB-STD	SN3000MD960GI-1MA4-1GB-STD	
1920 GBytes	SN3000MB1T92I-1MA2-1GB-STD	SN3000MD1T92I-1MA4-1GB-STD	

Table 3: Available Part Numbers

Canacity	FW ARR51005		
Capacity	2242	2280	
240 GBytes	SN3000MB240GI-2MA2-2GB-STD	SN3000MD240GI-2MA4-2GB-STD	
480 GBytes	SN3000MB480GI-2MA2-2GB-STD	SN3000MD480GI-2MA2-2GB-STD	
960 GBytes	SN3000MB960GI-2MA2-2GB-STD	SN3000MD960GI-2MA4-2GB-STD	
1920 GBytes	SN3000MB1T92I-2MA2-2GB-STD	SN3000MD1T92I-2MA4-2GB-STD	

Table 4: Available Part Numbers

Capacity	FW ARR71003		
Capacity	2242	2280	
3840 GBytes	ı	SN3000MD3T841-2MA4-2GB-STD	



5. Product Description

The Swissbit® N3000 Solid State Drive (SSD) leverages the M.2 standard and NVMe standard to support a PCle electrical interface as well as AES encryption, E2E data protection and TCG Opal standards. The NVMe controller and the newest 3D NAND flash technology provides robust, non-volatile storage solution for today's embedded computing applications. A functional block diagram of the N3000 SSD is provided below in Figure 1.

NAND Flash NAND Flash PCle PCIe Lanes 4 Controller Host NAND Flash DRAM Power NAND Cache Manager Flash

Figure 1: N3000 Functional Block Diagram

The N3000 SSD incorporates a 75-position edge connector with M key to support host read/write, control, and power activity per the applicable JEDEC specification.

The on-board NVMe controller manages the interface between the host and the non-volatile NAND flash memory array. The controller is designed to support PCle interface speeds and utilizes a dual processing core, providing an optimum balance between read/write performance, Data Care Management, and power fail protection.

Swissbit's N3000 SSDs deliver an impressive IOPS rate and highest endurance by combining 3D NAND flash technology with a high-end controller architecture, firmware, and an optimized configuration. The SSDs are designed for applications requiring high data transfer rates (see Table 5: Read/Write Performance 2280). This performance is achieved through a 4-channel flash controller and 4-lane PCIe interface.

An on-controller LDPC Error Correction Code (ECC) engine provides the N3000 hardware ECC, which is capable of correcting up to 240 bits per 2 KByte page. This engine, combined with Swissbit's Data Care Management firmware, provides both passive and active data management strategies to ensure data integrity and extract the maximum possible endurance and reliability from the NAND flash array. These strategies include, but are not limited to, Global Wear Leveling, Adaptive Read Refresh, and Dynamic Block Remapping.

Related Documentation

- NVM Express Revision 1.4, (https://nvmexpress.org/)
- PCI Express M.2 standard PCI Express M.2 Specification, Revision 3.0, June 26, 2019 (https://pcisig.com)



5.1 Performance Specifications

The N3000 read/write sequential and random CDM performance benchmarks are detailed in Table 5.

Table 5: Read/Write Performance 22806

Capacity	Sequential Read (MBPS)	Sequential Write (MBPS)	Random Read 4k (IOPS)	Random Write 4k (IOPS)
240 GBytes	3,650	1,480	108,300	177,500
480 GBytes	3,790	2,820	210,000	298,800
960 GBytes	3,850	3,340	392,800	457,000
1920 GBytes	3,790	3,330	455,900	394,300
3840 GBytes	3,210	2,850	429,200	505,200

5.2 Current Consumption

The drive-level current consumption as a function of operating mode is shown in Table 6.

Table 6: Current Consumption7, 8, 9

Capacity	Sequential Read	Sequential Write	Random Read 4k	Random Write 4k	Idle ¹⁰	PS3 ¹⁰	PS4 ¹⁰	Unit
240 GBytes	1,150	910	740	930			1	mA
480 GBytes	1,180	1,230	870	1,150				
960 GBytes	1,210	1,470	1,090	1,290	49	9		
1920 GBytes	1,250	1,660	1,210	1,350		12		
3840 GBytes	1,250	1,250	1,200	1,100				

⁶ The values are measured using Crystal Disk Mark 8 with a file size of 1GiB. Performance depends on flash type and number, file/cluster size, and burst speed.

⁷ All values are typical total values recorded at 25 °C and 3.3V power supply

⁸ Active values measured during burst workload using fio with QD=8 and threads=1 for 1MiB sequential read/write and QD=32 and threads=16 for 4kiB random read/write with file size = 1GiB.

⁹ Active and idle based on highest averaged current peak over a 1s-window with a sample rate of 250kS/s. Peak based on highest averaged current peak over a 100us-window with a sample rate of 250kS/s.

¹⁰ Measured with enabled ASPM L1.2



5.3 Environmental Specifications

5.3.1 Recommended Operating Conditions

The recommended operating conditions for the N3000 SSD are provided in Table 7.

Table 7: Recommended Operating Conditions¹¹

Parameter	Value
Industrial Operating Temperature	-40 °C to 85 °C
Power Supply V _{CC} Voltage	3.3 V ± 5%

5.3.2 Recommended Storage Conditions

The recommended storage conditions are listed in Table 8.

Table 8: Recommended Storage Conditions

Parameter	Value	
Industrial Storage Temperature	-40 °C to 85 °C	

5.3.3 Shock, Vibration and Humidity

The maximum shock, vibration and humidity conditions are listed in Table 9.

Table of Shock Vibration and Humidity

Table 9. Shock, Vibration and numbers				
Parameter	Value			
Non-Operating Shock	1,500 g , 0.5 ms pulse duration, half-sine wave (IEC 60068-2-27 and JESD22-B110 cond. B)			
Non-Operating Vibration	50 g, 80-2,000 Hz, 3 axes, 12 cycles (IEC 60068-2-6, MIL-STD-883 H Method 2007.3)			
Humidity (Non-Condensing)	85% RH 85 °C, 1000 hrs, max. supply voltage (JESD22–A101B)			

[&]quot; Adequate airflow is required to ensure the temperature, as reported in the S.M.A.R.T. data, does not exceed 110 °C (industrial temperature drive).





5.4 Regulatory Compliance

The N3000 devices comply with the regulations / standards listed in Table 10.

Table 10: Regulatory Compliance

Abbreviation	Regulation/ Standard
EMC	CE - 2014/30/EU FCC - 47 CFR Part 15 UKCA - S.I. 2016 No. 1091 and S.I. 2012 No. 3032
RoHS	2011/65/EU with 2015/863/EU and 2017/2102/EU
REACh	1907/2006/EU and 207/2011/EU
WEEE	2012/19/EU

5.5 Mechanical Specifications

Physical dimensions are detailed in Table 11. Figure 3 and Figure 4 on page 13 illustrates the N3000 dimensions.

Table 11: Physical Dimensions

Physical Dimensions		
Length	ength 42.00/80.00±0.15	
Width	22.00±0.15	mm
Thickness (nominal)	3.8	
Weight (Max Capacity)	≤ 9.0	g



5.6 Reliability and Endurance

The Mean Time Between Failure (MTBF) is specified to exceed the value listed in Table 12. Data reliability with effective error tolerance and data retention at the beginning and end of life is also provided.

Table 12: Reliability

Parameter	Value
MTBF (at 25 °C)	> 3,000,000 hours
Data Reliability	< 1 Non-Recoverable Error per 10 ¹⁶ Bits Read
Data Retention	10 Years at Start (JESD47), 1 Year at EOL

Endurance represented as both TeraBytes Written (TBW) and full Drive Writes Per Day (DWPD) for different application scenarios is provided in Table 13.

Table 13: Endurance12, 13

Carra elfa	Sequential		Client		Enterprise	
Capacity	TBW	DWPD ¹⁴	TBW	DWPD ¹⁴	TBW	DWPD ¹⁴
240 GBytes	856	3.26	271	1.03	207	0.79
480 GBytes	1,684	3.20	503	0.96	379	0.72
960 GBytes	3,334	3.17	903	0.86	699	0.66
1920 GBytes	6,774	3.22	1,399	0.67	1,620	0.77
3840 GBytes	13,920	3.31	2,390	0.56	3,670	0.87

5.7 Drive Geometry Specification

The N3000 drive geometry is set to report industry standard LBA settings per the IDEMA standard (LBA1-03). The values for each capacity are shown in Table 14.

Table 14: Drive Geometry

Day Canacity	Hear Campain 15	Total LBA	User Addressable Bytes
Raw Capacity	User Capacity¹⁵	Decimal	(Unformatted)
256 GBytes	240 GBytes	468,862,128	240,057,409,536
512 GBytes	480 GBytes	937,703,088	480,103,981,056
1024 GBytes	960 GBytes	1,875,385,008	960,197,124,096
2048 GBytes	1920 GBytes	3,750,748,848	1,920,383,410,176
4096 GBytes	3840 GBytes	7,501,476,528	3,840,755,982,336

Page 10 of 25

¹² Client and Enterprise workloads follow the JEDEC JESD219 standard. Enterprise workload values are measured based on 240 hours of runtime. 1 TByte = 10¹² bytes

¹³ According to JEDEC (JESD471), the time to write the full TBW is a minimum of 18 months. Higher average daily data volume reduces the specified TBW. The values listed are estimates and are subject to change without notice.

¹⁴ DWPD values are based on a service life of 3 years.

¹⁵ 1 GByte = 10⁹ bytes



6. Electrical Interface

This 75-position m.2 connector (Figure 2) incorporates M key for Socket 3 PCle-based SSDs and follows the applicable PCle m.2 specification. The signal/pin assignments and descriptions are listed in the following Table 15.

Figure 2: N3000 M.2 Electrical Interface




Table 15: Pin Assignment, Name and Description

Description	Assignment	Pin	Pin	Assignment	Description
Config_3	GND	1	2	+3.3V	3.3V Source
Ground	GND	3	4	+3.3V	3.3V Source
PCIe TX Differential Signal	PETn3*	5	6	NC	No Connect
PCIe TX Differential Signal	PETp3*	7	8	NC	No Connect
Ground	GND	9	10	DAS/DSS	DEVACT Device Activity Signal
PCIe RX Differential Signal	PERn3*	11	12	+3.3V	3.3V Source
PCIe RX Differential Signal	PERp3*	13	14	+3.3V	3.3V Source
Ground	GND	15	16	+3.3V	3.3V Source
PCIe TX Differential Signal	PETn2*	17	18	+3.3V	3.3V Source
PCIe TX Differential Signal	PETp2*	19	20	NC	No Connect
Config_o	GND	21	22	NC	No Connect
PCIe RX Differential Signal	PERn2*	23	24	NC	No Connect
PCIe RX Differential Signal	PERp2*	25	26	NC	No Connect
Ground	GND	27	28	NC	No Connect
PCIe TX Differential Signal	PETn1*	29	30	NC	No Connect
PCIe TX Differential Signal	PETp1*	31	32	NC	No Connect
Ground	GND	33	34	NC	No Connect
PCIe RX Differential Signal	PERn1*	35	36	NC	No Connect
PCIe RX Differential Signal	PERp1*	37	38	NC	No Connect
Ground	GND	39	40	SMB_CLK	SMBus Clock
PCIe TX Differential Signal	PETno*	41	42	SMB_DATA	SMBus Data
PCIe TX Differential Signal	PETpo*	43	44	ALERT#	SMBus Alert Notification
Ground	GND	45	46	NC	No Connect
PCIe RX Differential Signal	PERno*	47	48	NC	No Connect
PCIe RX Differential Signal	PERpo*	49	50	PERST#	PE-Reset (Functional Reset)
Ground	GND	51	52	CLKREQ#	Clock Request Signal; L1 PM
PCIe Reference Clock Signal	REFCLKn	53	54	NC	PCIe PME Wake
PCIe Reference Clock Signal	REFCLKp	55	56	NC	MFG Data
Ground	GND	57	58	NC	MFG Clock



Mechanical Notch M	-	59-65	60-66	_	Mechanical Notch M
No Connect	NC	67	00-00	_	Mechanical Noteri M
Config_1	NC	69	68	NC	32.768 kHz Clock Supply
Ground	GND	71	70	3.3V	Supply Pin, 3.3V
Ground	GND	73	72	3.3V	Supply Pin, 3.3V
Config_2	GND	75	74	3.3V	Supply Pin, 3.3V

^{*}TX (transmit) and RX (receive) pins are labeled from the SSD view and must be connected with the reversed RX and TX signals of the host (i.e., TX to RX and RX to TX).



7. Package Mechanical

Figure 3: N3000 M.2 2242 dimensions in mm






Figure 4: N3000 M.2 2280 dimensions in mm





Figure 5: M.2 Connector Dimensions in mm





8. NVMe Commands

This section provides information on the NVMe commands supported by the SSD. The commands are issued by loading the DWords in the command block with the supplied parameter, and then writing the command code to the register. See the following Table 16 for a list of NVMe commands the device supports. For details about setting up the command registers, see the latest NVMe Specification.

Table 16: NVMe Command Set - Supported Commands

Command	Code			
Admin Command Set				
Delete I/O Submission Queue	ooh			
Create I/O Submission Queue	01h			
Get Log Page	o2h			
Delete I/O Completion Queue	04h			
Create I/O Completion Queue	05h			
Identify	o6h			
Abort	o8h			
Set Features	09h			
Get Features	oAh			
Asynchronous Event Request	oCh			
Firmware Commit	10h			
Firmware Image Download	11h			
Device Self-test	14h			
Format NVM	80h			
Sanitize	84h			
NVM Command Set				
Flush	ooh			
Write	o1h			
Read	o2h			
Write Uncorrectable	04h			
Compare	05h			
Write Zeroes	08h			
Dataset Management	o9h			

Table 17: NVMe Set/Get Features – Supported Features

Feature	FID
Arbitration	01h
Power Management	02h
LBA Range Type	03h
Temperature Threshold	04h
Error Recovery	05h
Volatile Write Cache	o6h
Number of Queues	o7h
Interrupt Coalescing	o8h
Interrupt Vector Configuration	ogh



Feature	FID
Write Atomicity Normal	oAh
Asynchronous Event Configuration	oBh
Autonomous Power State Transition	oCh
Timestamp	oEh
Host Controlled Thermal Management	10 h
Non-Operational Power State Config	11h
Software Progress Marker	8oh

Table 18: Supported Log Pages

Log Page	Log Identifier
Error Information	o1h
SMART/Health Information	o2h
Firmware Slot Information	o3h
Commands Supported and Effects	05h
Device Self-Test Log	o6h
Telemetry Host-Initiated	o7h
Telemetry Controller-Initiated	o8h
Endurance Group Information	09h



9. Identify Device Information

The following table describes the 4096 bytes of data the drive returns for the Identify command (06h).

Table 19: Identify Namespace Data Structure (CNS ooh)

	able 19: Identify Namespace Data Structure (CNS 00h)					
Byte(s)	Value	Data Field Type Information				
0-7	XXXXh ¹⁶	Namespace Size (NSZE)				
8-15	XXXXh ¹⁶	Namespace Capacity (NCAP)				
16-23	XXXXh ¹⁶	Namespace Utilization (NUSE)				
24	ooh	Namespace Features (NSFEAT)				
25	ooh	Number of LBA Formats (NLBAF)				
26	ooh	Formatted LBA Size (FLBAS)				
27	ooh	Metadata Capabilities (MC)				
28	ooh	End-to -end Data Protection Capabilities (DPC)				
29	ooh	End-to -end Data Protection Type Settings (DPS)				
30	ooh	Namespace Multi-path I/O and Namespace Sharing Capabilities (NMIC)				
31	ooh	Reservation Capabilities (RESCAP)				
32	8oh	Format Progress Indicator (FPI)				
33	01h	Deallocate Logical Block Features (DLFEAT)				
34-35	ooooh	Namespace Atomic Write Unit Normal (NAWUN)				
36-37	ooooh	Namespace Atomic Write Unit Power Fail (NAWUPF)				
38-39	ooooh	Namespace Atomic Compare & Write Unit (NACWU)				
40-41	ooooh	Namespace Atomic Boundary Size Normal (NABSN)				
42-43	ooooh	Namespace Atomic Boundary Offset (NABO)				
44-45	ooooh	Namespace Atomic Boundary Size Power Fail (NABSPF)				
46-47	ooooh	Namespace Optimal IO Boundary (NOIOB)				
48-63	All ooh	NVM Capacity (NVMCAP)				
64-65	ooooh	Namespace Preferred Write Granularity (NPWG)				
66-67	ooooh	Namespace Preferred Write Alignment (NPWA)				
68-69	ooooh	Namespace Preferred Deallocate Granularity (NPDG)				
70-71	ooooh	Namespace Preferred Deallocate Alignment (NPDA)				
72-73	ooooh	Namespace Optimal Write Size (NOWS)				
74-91	All ooh	Reserved				
92-95	oooooooh	ANA Group Identifier (ANAGRPID)				
96-98	ooooooh	Reserved				
99	ooh	Namespace Attributes (NSATTR)				
100-101	ooooh	NVM Set Identifier (NVMSETID)				
102-103	ooooh	Endurance Group Identifier (ENDGID)				
104-119	537769737362 69748C6078X XXXXX0001h ¹⁶	Namespace Globally Unique Identifier (NGUID)				
120-127	8C6078XXXXXX 0001h ¹⁶	IEEE Extended Unique Identifier (EUI64)				
128-131	00090000h	LBA Format o Support (LBAFo)				
132-191	All ooh	LBA Format 1 to 15 Support (LBAF1 – LBAF15)				



Byte(s)	Default Value	Data Field Type Information
192-383	All ooh	Reserved
384-4095	All ooh	Vendor Specific (VS)

Table 20: Identify Controller Data Structure (CNS 01h)

Byte(s)	Default Value	Data Field Type Information
0-1	1DD4h	PCI Vendor ID (VID)
2-3	1DD4h	PCI Subsystem Vendor ID (SSVID)
4-23	XXXXh ¹⁶	Serial Number (SN)
24-63	XXXXh ¹⁶	Model Number (MN)
64-71	XXXXh ¹⁶	Firmware Version (FR)
72	06h	Recommended Arbitration Burst (RAB)
73-75	8C6078h	IEEE OUI Identifier (IEEE)
76	ooh	Controller Multi-Path I/O and Namespace Sharing Capabilities (CMIC)
77	o6h	Maximum Data Transfer Size (MDTS)
78-79	ooooh	Controller ID (CNTLID)
80-83	00010400h	Version (VER)
84-87	000186A0h	Runtime D3 Resume Latency (RTD3R)
88-91	004C4B40h	Runtime D3 Entry Latency (RTD3E)
92-95	00000200h	Optional Asynchronous Events Supported (OAES)
96-99	00000002h	Controller Attributes (CTRATT)
100-101	ooooh	Read Recovery Levels Supported (RRLS)
102-110	All ooh	Reserved
112-127	All ooh	FRU Globally Unique Identifier (FGUID)
128-129	ooooh	Command Retry Delay Time 1 (CRDT1)
130-131	ooooh	Command Retry Delay Time 2 (CRDT2)
132-133	ooooh	Command Retry Delay Time 3 (CRDT3)
134-255	All ooh	Reserved
256-257	0017h	Optional Admin Command Support (OACS)
258	o4h	Abort Command Limit (ACL)
259	o7h	Asynchronous Event Request Limit (AERL)
260	14h	Firmware Updates (FRMW)
261	oFh	Log Page Attributes (LPA)
262	FFh	Error Log Page Entries (ELPE)
263	o4h	Number of Power States Supported (NPSS)
264	ooh	Admin Vendor-Specific Command Configuration (AVSCC)
265	01h	Autonomous Power State Transition Attributes (APSTA)
266-267	o16Bh	Warning Composite Temperature Threshold in Degrees Kelvin (WCTEMP)
268-269	017Fh	Critical Composite Temperature Threshold in Degrees Kelvin (CCTEMP)
270-271	0032h	Maximum Time for Firmware Activation (MTFA)
272-275	oooooooh	Host Memory Buffer Preferred Size (HMPRE)
276-279	oooooooh	Host Memory Buffer Minimum Size (HMMIN)
280-295	All ooh	Total NVM Capacity (TNVMCAP)
296-311	All ooh	Unallocated NVM Capacity (UNVMCAP)



Byte(s)	Default Value	Data Field Type Information
312-315	00000000h	Replay Protected Memory Block Support (RPMBS)
316-317	0005h	Extended Device Self-test Time (EDSTT)
318	01h	Device Self-test Options (DSTO)
319	ooh	Firmware Update Granularity (FWUG)
320-321	0000h	Keep Alive Support (KAS)
322-323	0001h	Host Controlled Thermal Management Attributes (HCTMA)
324-325	012Fh	Minimum Thermal Management Temperature (MNTMT)
326-327	0175h	Maximum Thermal Management Temperature (MXTMT)
328-331	60000003h	Sanitize Capabilities (SANICAP)
332-335	000000000h	Host Memory Buffer Minimum Descriptor Entry Size (HMMINDS)
336-337	0000h	Host Memory Maximum Descriptors Entries (HMMAXD)
338-339	0000h	NVM Set Identifier Maximum (NSETIDMAX)
340-341	0000h	Endurance Group Identifier Maximum (ENDGIDMAX)
342	ooh	ANA Transition Time (ANATT)
	ooh	Asymmetric Namespace Access Capabilities (ANACAP)
343		ANA Group Identifier Maximum (ANAGRPMAX)
344-347	00000000h	
348-351	00000000h	Number of ANA Group Identifiers (NANAGRPID)
352-355	00000000h	Persistent Event Log Size (PELS)
356-511	All ooh	Reserved
512	66h	Submission Queue Entry Size (SQES)
513	44h	Completion Queue Entry Size (CQES)
514-515	0000h	Maximum Outstanding Commands (MAXCMD)
516-519	000000001h	Number of Namespaces (NN)
520-521	005Fh	Optional NVM Command Support (ONCS)
522-523	0000h	Fused Operation Support (FUSES)
524	04h	Format NVM Attributes (FNA)
525	01h	Volatile Write Cache (VWC)
526-527	0001h	Atomic Write Unit Normal (AWUN)
528-529	0001h	Atomic Write Unit Power Fail (AWUPF)
530	ooh	NVM Vendor-Specific Command Configuration (NVSCC)
531	ooh	Namespace Write Protection Capabilities (NWPC)
532-533	0000h	Atomic Compare and Write Unit (ACWU)
534-535	0000h	Reserved
536-539	00000000h	Scatter Gather List Support (SGLS)
540-543	00000000h	Maximum Number of Allowed Namespaces (MNAN)
544-767	All ooh	Reserved
768-1023	XXXXh16	NVM Subsystem NVMe Qualified Name (SUBNQN)
1024-2047	All ooh	Reserved
2048-2079	XXXXh ¹⁶	Power State o Descriptor
2080-2111	XXXXh ¹⁶	Power State 1 Descriptor
2112-2143	XXXXh ¹⁶	Power State 2 Descriptor
2144-2175	XXXXh ¹⁶	Power State 3 Descriptor
2176-2207	XXXXh ¹⁶	Power State 4 Descriptor



Byte(s)	Default Value	Data Field Type Information
2208-3071	All ooh	Power State 5 – 31 Descriptor (Not Applicable)
3072-4095	-	Vendor Specific (VS)

10. Health Monitoring Functionality

The N3000 SSDs support Self-Monitoring, Analysis, and Reporting Technology. The SSD supports log information as defined in the NVMe specification.

See the following table for the 512-byte data structure of the SMART/Health Information log page:

Table 21: SMART/Health Information (Log Identifier 02h)

Byte(s)	Description		
0	 Critical warning: for the state of the controller Bit o: If set to '1', then the available spare capacity has fallen below the threshold Bit 1: If set to '1', then a temperature is greater than or equal to an over temperature threshold; or less than or equal to an under temperature threshold Bit 2: If set to '1', then the NVM subsystem reliability has been degraded due to significant media related errors or any internal error that degrades NVM subsystem reliability. Bit 3: If set to '1', then all of the media has been placed in read only mode 		
1-2	Composite Temperature: in degrees Kelvin		
3	Available Spare: as a percentage of remaining spare capacity		
4	Available Spare Threshold		
5	Percentage Used: Estimate of the percentage of the NVM subsystem life left based on usage		
6-31	Reserved		
32-47	Data Units Read: Number of 512-byte sectors read by the host (in 1000 increments)		
48-63	Data Units Written: Number of 512-byte sectors written by the host (in 1000 increments)		
64-79	Host Read Commands: Number of Read commands completed by the controller		
80-95	Host Write Commands: Number of Write commands completed by the controller		
96-111	Controller Busy Time: Amount of time, in minutes, the controller was busy with I/O commands		
112-127	Power Cycles: Number of power cycles that has occurred over the life of the drive		
128-143	Power On Hours: Number of hours the device has been powered over the life of the drive (does not include the time the device is in low power state conditions)		
144-159	Unsafe Shutdowns: Number of shutdowns that occurred without a shutdown notification		
160-175	Media and Data Integrity Errors: Number of unrecoverable errors, including UECC, CRC checksum failures, and LBA mismatches, that occurred over the life of the drive		
176-191	Number of Error Information Log Entries: Number of entries recorded in the Error Information log over the life of the drive		
192-195	Warning Composite Temperature Time: Amount of time, in minutes, the controller was operational and the Composite Temperature was equal to or greater than the Warning Composite Temperature Threshold (WCTEMP) but less than the Critical Composite Temperature Threshold (CCTEMP)		
196-199	Critical Composite Temperature Time: Amount of time, in minutes, the controller was operational and the Composite Temperature was equal to or greater than the Critical Composite Temperature Threshold (CCTEMP)		
200-201	Temperature Sensor 1: Current controller Tjunction temperature, in degrees Kelvin		
202-203	Temperature Sensor 2: Current composite temperature, in degrees Kelvin		
204-205	Temperature Sensor 3: Current maximum NAND temperature, in degrees Kelvin		
206-215	Not used		



216-219	Thermal Management Temperature 1 Transition Count: number of times the controller transitioned to lower power active power states or performed vendor specific thermal management actions while minimizing the impact on performance
220-223	Thermal Management Temperature 2 Transition Count: number of times the controller transitioned to lower power active power states or performed vendor specific thermal management actions regardless of the impact on performance
224-227	Total Time For Thermal Management Temperature 1: number of seconds that the controller had transitioned to lower power active power states or performed vendor specific thermal management actions while minimizing the impact on performance
228-231	Total Time For Thermal Management Temperature 2: number of seconds that the controller had transitioned to lower power active power states or performed vendor specific thermal management actions regardless of the impact on performance
232-511	Reserved

The following data structure is applied to both Telemetry Host-Initiated log and Telemetry Controller-Initiated log:

Table 22: Telemetry Log (Log Identifier 07h)


Byte(s)	Description		
Telemetry Header			
0	Log Identifier: This field shall be 07h		
1-4	Reserved		
5-7	IEEE OUI Identifier (IEEE)		
4	Telemetry Host-Initiated Data Area 1 Last Block: This field shall be ooo1h		
10-381	Reserved		
382	Telemetry Controller-Initiated Data Available		
383	Telemetry Controller-Initiated Data Generation Number		
384-511	Reserved		
Telemetry Data Bloo	k1		
528-529	Minimum Temperature, in degrees Kelvin		
530-531	Current Temperature, in degrees Kelvin		
532-533	Maximum Temperature, in degrees Kelvin		
560-561	Number of valid spare blocks		
562-563	Number of initial spare blocks		
564-565	Run Time Bad Block Count		
596-599	Maximum Erase Count on system blocks		
604-607	Average Erase Count on system blocks		
612-615	Maximum Erase Count on data storage blocks		
620-623	Average Erase Count on data storage blocks		
624-627	Rated Erase Count on system blocks		
636-639	Rated Erase Count on data storage blocks		
640	Remaining Life Percentage on system blocks based on P/E		
641	Remaining Life Percentage based on spare blocks		
646	Remaining Life Percentage on data storage blocks based on P/E		
647	Cap Health Status		



772-776	NVMe/PCIe Reset Count
804-807	PCIe Gen1 Link Speed Count
808-811	PCIe Genz Link Speed Count
812-815	PCIe Gen3 Link Speed Count
816-823	PCIe ECRC Event Count
824-831	PCIe LCRC Event Count
873	PCIe Power On Link Speed
876	PCIe Current Link Speed
877	PCIe Current Link Width
932-935	PCIe x1 Link Width Count
936-939	PCle x2 Link Width Count
940-943	PCle x4 Link Width Count
944-951	PCIe L1 Event Count




11. Part Number Decoder





12. Marking Specification


12.1 Top View





12.2 Print on the label

Figure 7: N3000 label details





13. Revision History

Table 23: Document Revision History

Date	Revision	Description	Revision Details
24-10-2023	0.90	Preliminary release	Doc. req. no. 6642
11-01-2024	0.91	PN Update	Doc. req. no. 6809
20-03-2024	0.92	Figure 1 Update	Doc. req. no. 6968
13-05-2024	1.00	Initial release	Doc. req. no. 7079
24-10-2024	1.01	Added new variants with hardware generation "2" and firmware "2" and updated product illustrations.	-
27-03-2025	1.02	Added 3.8TB variant	-

Disclaimer:

No part of this document may be copied or reproduced in any form or by any means, or transferred to any third party, without the prior written consent of an authorized representative of Swissbit AG ("SWISSBIT"). The information in this document is subject to change without notice. SWISSBIT assumes no responsibility for any errors or omissions that may appear in this document and disclaims responsibility for any consequences resulting from the use of the information set forth herein. SWISSBIT makes no commitments to update or to keep current information contained in this document. The products listed in this document are not suitable for use in applications such as, but not limited to, aircraft control systems, aerospace equipment, submarine cables, nuclear reactor control systems and life support systems. Moreover, SWISSBIT does not recommend or approve the use of any of its products in life support devices or systems or in any application where failure could result in injury or death. If a customer wishes to use SWISSBIT products in applications not intended by SWISSBIT, said customer must contact an authorized SWISSBIT representative to determine SWISSBIT willingness to support a given application. The information set forth in this document does not convey any license under the copyrights, patent rights, trademarks or other intellectual property rights claimed and owned by SWISSBIT. The information set forth in this document is considered to be "Proprietary" and "Confidential" property owned by SWISSBIT.

ALL PRODUCTS SOLD BY SWISSBIT ARE COVERED BY THE PROVISIONS APPEARING IN SWISSBIT'S TERMS AND CONDITIONS OF SALE ONLY, INCLUDING THE LIMITATIONS OF LIABILITY, WARRANTY AND INFRINGEMENT PROVISIONS. SWISSBIT MAKES NO WARRANTIES OF ANY KIND, EXPRESS, STATUTORY, IMPLIED OR OTHERWISE, REGARDING INFORMATION SET FORTH HEREIN OR REGARDING THE FREEDOM OF THE DESCRIBED PRODUCTS FROM INTELLECTUAL PROPERTY INFRINGEMENT AND EXPRESSLY DISCLAIMS ANY SUCH WARRANTIES INCLUDING WITHOUT LIMITATION ANY EXPRESS, STATUTORY OR IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

© 2025 SWISSBIT AG All rights reserved.