

# Antenna YC0011AA Datasheet

#### **Antenna Services**

Version: 1.1

Date: 2021-01-12

Status: Released



www.quectel.com



Our aim is to provide customers with timely and comprehensive service. For any assistance, please contact our company headquarters:

**Quectel Wireless Solutions Co., Ltd.** 

Building 5, Shanghai Business Park Phase III (Area B), No.1016 Tianlin Road, Minhang District, Shanghai 200233, China Tel: +86 21 5108 6236 Email: info@guectel.com

Or our local office. For more information, please visit: http://www.quectel.com/support/sales.htm.

For technical support, or to report documentation errors, please visit: http://www.quectel.com/support/technical.htm Or email to support@quectel.com.

#### **General Notes**

Quectel offers the information as a service to its customers. The information provided is based upon customers' requirements. Quectel makes every effort to ensure the quality of the information it makes available. Quectel does not make any warranty as to the information contained herein, and does not accept any liability for any injury, loss or damage of any kind incurred by use of or reliance upon the information. All information supplied herein is subject to change without prior notice.

#### Disclaimer

While Quectel has made efforts to ensure that the functions and features under development are free from errors, it is possible that these functions and features could contain errors, inaccuracies and omissions. Unless otherwise provided by valid agreement, Quectel makes no warranties of any kind, implied or express, with respect to the use of features and functions under development. To the maximum extent permitted by law, Quectel excludes all liability for any loss or damage suffered in connection with the use of the functions and features under development, regardless of whether such loss or damage may have been foreseeable.

## **Duty of Confidentiality**

The Receiving Party shall keep confidential all documentation and information provided by Quectel, except when the specific permission has been granted by Quectel. The Receiving Party shall not access or use Quectel's documentation and information for any purpose except as expressly provided herein. Furthermore, the Receiving Party shall not disclose any of the Quectel's documentation and information to any third party without the prior written consent by Quectel. For any noncompliance to the above requirements, unauthorized use, or other illegal or malicious use of the documentation and information, Quectel will reserve the right to take legal action.



# Copyright

The information contained here is proprietary technical information of Quectel. Transmitting, reproducing, disseminating and editing this document as well as using the content without permission are forbidden. Offenders will be held liable for payment of damages. All rights are reserved in the event of a patent grant or registration of a utility model or design.

Copyright © Quectel Wireless Solutions Co., Ltd. 2021. All rights reserved.



# **About the Document**

# **Revision History**

Version	Date	Author	Note
-	2020-09-22	Kenny YIN	Creation of the document
1.0	2020-09-22	Kenny YIN	First official release
1.1	2021-01-12	Kenny YIN	Updated the antenna image in Chapter 2.



## Contents

		2 Document
1	Prod	uct Description5
2	Prod	uct Features5
3	Prod	uct Specifications
4	Overa	all Performance7
	4.1.	Test Environment7
	4.2.	Return Loss
	4.3.	Radiation Patterns9
	4.4.	Reference PCB Design (Unit: mm)10
5	Prod	uct Size (mm)11
6	Relia	bility Test12
	6.1.	Vibration Resist
	6.2.	Drop Shock
	6.3.	Resistance to Soldering Heat12
	6.4.	Adhesive Strength of Termination12
	6.5.	Bending Resist Test
	6.6.	Moisture Proof13
	6.7.	High Temperature Endurance
	6.8.	Low Temperature Endurance
	6.9.	Temperature Cycle Test
7	Reflo	w Soldering Standard Condition14
8	Packa	aging and Dimensions14
	8.1.	Plastic Tape
	8.2.	Reel (1000 pcs/reel)



# **1 Product Description**

The antenna is designed for superior performance, and can be widely used for wireless applications.

We provide comprehensive antenna design support such as simulation, testing and manufacturing for custom antenna solutions to meet your specific application needs.

## 2 Product Features

- Wi-Fi/BT
- High efficiency
- Excellent performance





# **3** Product Specifications

Passive Electrical Specifications				
Frequency Range	2400–2500 MHz 5150–5850 MHz			
Input Impendence	50 Ω			
Return Loss	Max7 dB			
Gain	≤ 4 dBi			
Polarization Type	Linear			
Mechanical Specifications				
Antenna Size	5.0 mm × 2.0 mm × 1.0 mm			
Casing	/			
Radiator	Ceramic patch			
Connector Type	SMD			
Working Temperature	-40 °C to +85 °C			
Radome Color	/			




## **4** Overall Performance

### 4.1. Test Environment

- KEYSIGHT VNA Network Analyzer E5063A, 100 kHz 6.5 GHz
- RayZone<sup>®</sup> 2800 Chamber 5G (FR1) SISO/MIMO, 400 MHz 6.0 GHz








## 4.2. Return Loss


▶ [[m] S33 Smith (R+jX) Scale 1.000U [F1 D&M]
1 2.4180180 GHz 18.692 0 -4.8079-0 13,690 pF 2 2.5180180 GHz 53.638 0 -49,085 0 1.2877 pF 3 2.4500000 GHz 40.701 0 5.9617 0 387.28 pH 4 5.1500000 GHz 21.918 0 10.386.0 282.57 pH >6 5.5000000 GHz 35.883 0 -9.6158 0 3.0093 pF ↓ 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0
Tr2 S33 Log Mag 10.00dB/ Ref 0.000dB [F1]
1 2.4180180 GHz -6.7457 dB 40.00 2 2.5180180 GHz -7.3448 dB
3 2.4500000 GHz -18.307 dB 30.00 4 5.1500000 GHz -8.8999 dB
5 5.8500000 GHz -7.7011 dB 20.00 >6 5.5000000 GHz -14.082 dB
10.00
0.000
-30.00
-40.00

Frequency (MHz)	2418	2518	2450	5150	5850	5500
Return Loss	-6.75	-7.34	-18.3	-8.90	-7.70	-14.1



#### 4.3. Radiation Patterns






XY Plane ( + Z View )	XZ Plane ( - Y View )	XZ Plane ( + Y View )	XY Plane ( + Z View )	XZ Plane ( - Y View )	XZ Plane (+Y View )
x	x	x	x	x	x
	u a	z			z
XY Plane ( - Z View )	YZ Plane ( + X View )	YZ Plane ( - X View )	XY Plane ( - Z View )	YZ Plane ( + X View )	YZ Plane ( - X View )
×			s and	Y Z	Y N




# 4.4. Reference PCB Design (Unit: mm)



50 ohms feeding line T type matching circuit



# 5 Product Size (mm)



Symbol	L	W	Т	а	b	С
Dimensions	5.00 ±0.20	2.0 ±0.20	1.0 ±0.2	0.8 ±0.1	2.0 ±0.2	0.6 ±0.2



# 6 Reliability Test

Temperature Range	25 ±5 °C
Relative Humidity Range	55–75 %
Operating Temperature Range	-40 °C to +85 °C
Storage Temperature Range	-40 °C to +85 °C

#### 6.1. Vibration Resist

The device should fulfil the electrical specification after being applied to the vibration of 10–55 Hz with amplitude of 1.5 mm for 2 hours in X, Y and Z directions respectively.

#### 6.2. Drop Shock

The device should have no mechanical damage after dropping onto the hard wooden board from the height of 100 cm for 3 times at each facet of the 3 dimensions of the device.

#### 6.3. Resistance to Soldering Heat


The device should have no damage after pre-heating at 120–150 °C for 120 seconds and immersion in solder Sn at 255 °C  $\pm$ 10 °C for 5  $\pm$ 0.5 seconds, or electric iron at 300 °C  $\pm$ 10 °C for 3  $\pm$ 0.5 seconds.

#### 6.4. Adhesive Strength of Termination

The device have no remarkable damage or removal of the termination after horizontal force of 5 N ( $\leq$  0603); 10 N (> 0603) for 10 ±1 seconds.



## 6.5. Bending Resist Test



Weld the product to the central part of the PCB with the thickness  $1.6 \pm 0.2$  mm or  $0.8 \pm 0.1$  mm as the illustration shows, and keep exerting force arrow-ward on it at speed of 1 mm/s, and hold for  $5 \pm 1$  s at the position of 1.5 mm bending distance, so far, any peeling-off of the product metal coating should not be detected.

#### 6.6. Moisture Proof

The device should fulfil the electrical specification after being exposed to the temperature 60  $\pm$ 2 °C and the relative humidity 90–95 % for 96 hours and 1–2 hours recovery time under normal condition.

#### 6.7. High Temperature Endurance

The device should fulfil the electrical specification after being exposed to temperature 85  $\pm$ 5 °C for 96  $\pm$ 2 hours and 1–2 hours recovery time under normal temperature.

#### 6.8. Low Temperature Endurance


The device should fulfil the electrical specification after being exposed to the temperature -40 °C  $\pm$ 5 °C for 96  $\pm$ 2 hours and to 2 hours recovery time under normal temperature.

#### 6.9. Temperature Cycle Test

The device should fulfil the electrical specification after being exposed to the low temperature -40 °C and high temperature +85 °C for 30 ±2 min each by 5 cycles and 1 to 2 hours recovery time under normal temperature.




# 7 Reflow Soldering Standard Condition



# 8 Packaging and Dimensions

#### 8.1. Plastic Tape




Remarks for Package:

Reserve a length of 150–200 mm for the trailer of the carrier and 250–300 mm for the leader of the carrier and further 250 mm of cover tape at the leading part of the carrier.



# 8.2. Reel (1000 pcs/reel)



# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Quectel: YC0011AA