



Antenna Datasheet

Product OC: YETN001L1A

Version: 1.2

Date: 2024-01-24

Status: Released

Product Name: L-Band & GNSS L1 & Iridium Antenna

Key Features:

Frequency Band:

GNSS L1: 1559–1606 MHz

Iridium: 1616–1626.5 MHz

L-Band: TX: 1626.5–1660.5 MHz, 1668–1675 MHz

RX: 1518–1559 MHz

Peak Gain: 4.3 dBic (Max)

RoHS and REACH Compliant

IP67

IK09

Overview

This Quectel satellite communication antenna adopts a diversity of forms to guarantee the most suitable polarization type. Quectel's satellite communication antenna products support L band, S band and L+S combination to meet various requirements of customers' products. Such antenna supports different installation or connection methods such as pin mount, surface mount, magnetic mount, internal cable, and external SMA. Customized connector type and cable length are provided according to requirements.

Contents

Overview.....	1
Contents	2
1 Specification.....	3
1.1. Electrical.....	3
1.2. Mechanical & Environmental	4
2 Drawing	5
3 Detailed Performance	6
3.1. S-Parameter Test	6
3.1.1. VSWR.....	6
3.1.2. Return Loss	7
3.2. Radiation Performance Test.....	8
3.2.1. Efficiency.....	8
3.2.2. Peak Gain.....	9
3.2.3. Axial Ratio	10
3.2.4. 2D RHCP and LHCP Gain	11
3.2.5. 3D & 2D Radiation Pattern.....	13
4 Packaging	17
Contact Us.....	19
Legal Notices	20
Revision History	22

1 Specification

Test Condition: Free Space

1.1. Electrical

Electrical		
Frequency Range	L-Band	TX: 1626.5–1660.5 MHz, 1668–1675 MHz RX: 1518–1559 MHz
	GNSS	1559–1606 MHz
	Iridium	1616–1626.5 MHz
Impedance		50 Ω
Polarization		RHCP
Radiation Pattern		Directional



Band Frequency (MHz)	L-Band TX					L-Band RX				GPS L1 GALILEO E1 BEIDOU B1C QZSS L1	GLONASS G1	Iridium		
	1626	1645	1661	1668	1675	1518	1525	1543	1559	1575	1600	1616	1621	1626
VSWR	1.3	1.3	1.5	1.5	1.6	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.3
Return Loss (dB)	-17	-15	-13	-13	-12	-19	-19	-20	-19	-20	-22	-20	-19	-17
Efficiency (%)	70.0	71.2	71.5	71.4	68.8	45.1	47	52.6	58.3	61.5	65.3	68.2	69.3	70.0
Peak Gain (dBic)	3.8	3.7	4.1	4.2	4.1	2.8	2.9	2.8	3.0	3.5	4.3	4.2	4.0	3.8
Axial Ratio (dB)	2.7	3.3	3.8	3.9	3.9	1.4	1.4	1.2	1.7	2.4	2.6	2.6	2.6	2.7

1.2. Mechanical & Environmental

Mechanical	
Antenna Dimensions	106.15 mm × 87.21 mm × 26.5 mm
Casing Material & Color	PC + ADC12 & Black + Silver
Cable Type & Color & Length	ALS302 & Black & 524 ±24 mm
Connector Type	SMA Male (The current state of the SMA connector is not waterproof. If a waterproof connector is required, it can be customized.)
Mounting Type	Screw
Weight	Typ. 167.2 g
Environmental	
Operation Temperature	-40 °C to +85 °C
Storage Temperature	-40 °C to +85 °C
Ingress Protection (IP) Rating	IP67 (After Installation) IP69K (After Installation)
Impact Protection (IK) Rating	IK09 (Only the surface of the housing with a silk screen Q was tested.)
RoHS & REACH Compliant	Yes
Housing Flame Rating	UL 94 V-0
Housing UV Resistant	UL 746c f1

2 Drawing


ROHS



3 Detailed Performance

3.1. S-Parameter Test


3.1.1. VSWR



VSWR

Frequency (MHz)	1518	1525	1543	1559	1575	1600	1616	1621	1626	1645	1661	1668	1675
VSWR	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.3	1.3	1.5	1.5	1.6

3.1.2. Return Loss




Return Loss (dB)

Frequency (MHz)	1518	1525	1543	1559	1575	1600	1616	1621	1626	1645	1661	1668	1675
Return Loss (dB)	-19	-19	-20	-19	-20	-22	-20	-19	-17	-15	-13	-13	-12

3.2. Radiation Performance Test


3.2.1. Efficiency



Efficiency (%)

Frequency (MHz)	1518	1525	1543	1559	1575	1600	1616	1621	1626	1645	1661	1668	1675
Efficiency (%)	45.1	47.0	52.6	58.3	61.5	65.3	68.2	69.3	70.0	71.2	71.5	71.4	68.8


3.2.2. Peak Gain



Peak Gain (dBic)

Frequency (MHz)	1518	1525	1543	1559	1575	1600	1616	1621	1626	1645	1661	1668	1675
Peak Gain (dBic)	2.8	2.9	2.8	3.0	3.5	4.3	4.2	4.0	3.8	3.7	4.1	4.2	4.1



3.2.3. Axial Ratio



Axial Ratio (dB)

Frequency (MHz)		1518	1525	1543	1559	1575	1600	1626	1645	1661	1668	1675
Axial Ratio (dB)	Phi=0 (deg) Theta=0 (deg)	1.4	1.4	1.2	1.7	2.4	2.6	2.7	3.3	3.8	3.9	3.9
	Phi=90 (deg) Theta=0 (deg)	1.4	1.4	1.2	1.7	2.4	2.6	2.7	3.3	3.8	3.9	3.9

3.2.4. 2D RHCP and LHCP Gain




2D RHCP and LHCP Gain (dBic)


Frequency (MHz)		1518	1525	1543	1559	1575	1600	1626	1645	1661	1668	1675
RHCP Gain (dBic)	Phi = 0 (deg) Theta = 0 (deg)	2.8	2.9	2.8	3.0	3.5	4.3	3.8	3.7	4.1	4.2	4.1
	Phi = 90 (deg) Theta = 0 (deg)	2.8	2.9	2.8	3.0	3.5	4.3	3.8	3.7	4.1	4.2	4.1
LHCP Gain (dBic)	Phi = 0 (deg) Theta = 0 (deg)	-18.9	-18.8	-19.9	-17.1	-13.5	-12	-12.3	-10.6	-9.1	-8.8	-8.8
	Phi = 90 (deg) Theta = 0 (deg)	-18.9	-18.8	-19.9	-17.1	-13.5	-12	-12.3	-10.6	-9.1	-8.8	-8.8

3.2.5. 3D & 2D Radiation Pattern



- Test Condition: Free Space
- Test Chamber: SH-SY-16M




1518 MHz




1525 MHz




Phi=0



Phi=90




Phi=0





Phi=90


1543 MHz




1559 MHz




Phi=0



Phi=90




Phi=0





Phi=90


1575 MHz




1600 MHz




Phi=0



Phi=90




Phi=0





Phi=90


1626 MHz




1645 MHz




Phi=0



Phi=90




Phi=0





Phi=90


1661 MHz




1668 MHz




Phi=0



Phi=90





Phi=0




Phi=90

1675 MHz






Phi=0



Phi=90

4 Packaging

Step	Packaging Picture / 2D Picture	Description
1		1 pc antenna product in a bubble bag; (1 PC / Bubble Bag)
2		2 pcs antenna products in an inner box; (2 PCS / Inner box)
3		(14 Inner Boxes / Carton Box) (28 PCS Antennas / Carton Box) Products that cannot fill the entire carton box are packed in a suitable size carton box. <u>Carton Size:</u> <u>L × W × H = 390 × 270 × 295 mm</u>

4		Position for Attaching Labels ① Carton Label ② Quality Label
5		Sealing Cartons “I” type sealing cartons

Contact Us

At Quectel, our aim is to provide timely and comprehensive services to our customers. If you require any assistance, please contact our headquarters:

Quectel Wireless Solutions Co., Ltd.

Building 5, Shanghai Business Park Phase III (Area B), No.1016 Tianlin Road, Minhang District, Shanghai 200233, China

Tel: +86 21 5108 6236

Email: info@quectel.com

Or our local offices. For more information, please visit:

<http://www.quectel.com/support/sales.htm>.

For technical support, or to report documentation errors, please visit:

<http://www.quectel.com/support/technical.htm>.

Or email us at: support@quectel.com.

Legal Notices

We offer information as a service to you. The provided information is based on your requirements and we make every effort to ensure its quality. You agree that you are responsible for using independent analysis and evaluation in designing intended products, and we provide reference designs for illustrative purposes only. Before using any hardware, software or service guided by this document, please read this notice carefully. Even though we employ commercially reasonable efforts to provide the best possible experience, you hereby acknowledge and agree that this document and related services hereunder are provided to you on an “as available” basis. We may revise or restate this document from time to time at our sole discretion without any prior notice to you.

Use and Disclosure Restrictions

License Agreements

Documents and information provided by us shall be kept confidential, unless specific permission is granted. They shall not be accessed or used for any purpose except as expressly provided herein.

Copyright

Our and third-party products hereunder may contain copyrighted material. Such copyrighted material shall not be copied, reproduced, distributed, merged, published, translated, or modified without prior written consent. We and the third party have exclusive rights over copyrighted material. No license shall be granted or conveyed under any patents, copyrights, trademarks, or service mark rights. To avoid ambiguities, purchasing in any form cannot be deemed as granting a license other than the normal non-exclusive, royalty-free license to use the material. We reserve the right to take legal action for noncompliance with abovementioned requirements, unauthorized use, or other illegal or malicious use of the material.

Trademarks

Except as otherwise set forth herein, nothing in this document shall be construed as conferring any rights to use any trademark, trade name or name, abbreviation, or counterfeit product thereof owned by Quectel or any third party in advertising, publicity, or other aspects.

Third-Party Rights

This document may refer to hardware, software and/or documentation owned by one or more third parties (“third-party materials”). Use of such third-party materials shall be governed by all restrictions and obligations applicable thereto.

We make no warranty or representation, either express or implied, regarding the third-party materials, including but not limited to any implied or statutory, warranties of merchantability or fitness for a particular purpose, quiet enjoyment, system integration, information accuracy, and non-infringement of any third-party intellectual property rights with regard to the licensed technology or use thereof. Nothing herein constitutes a representation or warranty by us to either develop, enhance, modify, distribute, market, sell, offer for sale, or otherwise maintain production of any our products or any other hardware, software, device, tool, information, or product. We moreover disclaim any and all warranties arising from the course of dealing or usage of trade.

Privacy Policy

To implement module functionality, certain device data are uploaded to Quectel's or third-party's servers, including carriers, chipset suppliers or customer-designated servers. Quectel, strictly abiding by the relevant laws and regulations, shall retain, use, disclose or otherwise process relevant data for the purpose of performing the service only or as permitted by applicable laws. Before data interaction with third parties, please be informed of their privacy and data security policy.

Disclaimer

- a) We acknowledge no liability for any injury or damage arising from the reliance upon the information.
- b) We shall bear no liability resulting from any inaccuracies or omissions, or from the use of the information contained herein.
- c) While we have made every effort to ensure that the functions and features under development are free from errors, it is possible that they could contain errors, inaccuracies, and omissions. Unless otherwise provided by valid agreement, we make no warranties of any kind, either implied or express, and exclude all liability for any loss or damage suffered in connection with the use of features and functions under development, to the maximum extent permitted by law, regardless of whether such loss or damage may have been foreseeable.
- d) We are not responsible for the accessibility, safety, accuracy, availability, legality, or completeness of information, advertising, commercial offers, products, services, and materials on third-party websites and third-party resources.

Copyright © Quectel Wireless Solutions Co., Ltd. 2024. All rights reserved.

Revision History

Version	Date	Author	Note
-	2023-11-09	Xiaodong YANG/ Rojin LUO/ David LIU/ Vinnie LIU	Creation of the document
1.0	2023-11-09	Xiaodong YANG/ Rojin LUO/ David LIU/ Vinnie LIU	Preliminary document
1.1	2023-11-27	Xiaodong YANG/ Rojin LUO/ David LIU/ Vinnie LIU	Updated Iridium frequency band (Chapter 1.1).
1.2	2024-01-24	Rojin LUO	1. Added Housing Flame Rating and Housing UV Resistant (Chapter 1.2). 2. Updated the packaging (Chapter 4).



www.quectel.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Quectel:](#)

[YETN001L1A](#)