

Description

The AZ431L series ICs are low-voltage three-terminal adjustable regulators with guaranteed thermal stability over a full operation range. These ICs feature sharp turn-on characteristics, low temperature coefficient and low output impedance, which make them ideal substitutes for zener diodes in applications such as switching power supply, charger, motherboard and other adjustable regulators.

The output voltage can be set to any value between 1.24V and 18V with two external resistors.

The AZ431L precision reference is offered in two voltage tolerance: 0.5% and 1.0%.

These ICs are available in 4 packages: TO92 (Ammo Packing), SOT23, SOT25 and SOT89.

Features

- Wide Programmable Precise Output Voltage from 1.24V to 18V
- High Stability under Capacitive Load
- Low Temperature Deviation: 3mV Typical
- Low Equivalent Full-Range Temperature Coefficient: 20PPM/°C Typical
- Low Dynamic Output Resistance: 0.05Ω Typical
- High Sink Current Capacity from 0.1mA to 100mA
- Low Output Noise
- Wide Operating Range of -40 to +125°C
- Lead-Free Package: SOT23
 - **Totally Lead-Free; RoHS Compliant (Notes 1 & 2)**
- Lead-Free Packages, Available in "Green" Molding Compound: TO92 (Ammo Packing), SOT23, SOT25, SOT89
 - **Totally Lead-Free & Fully RoHS Compliant (Note 1 & 2)**
 - **Halogen and Antimony Free. "Green" Device (Note 3)**
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](#) or your local Diodes representative.
<https://www.diodes.com/quality/product-definitions/>


Applications

- Graphic cards
- PC motherboards
- Voltage adapters
- Switching power supplies
- Chargers

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
 2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
 4. Pin 2 is attached to substrate and must be connected to ANODE or open.


Pin Assignments

(Top View)




TO92 (Ammo Packing)

(Top View)




SOT23

(Top View)




SOT25

(Top View)




SOT89 (Option 1)

(Top View)




SOT89 (Option 2)

Typical Applications Circuit




$$V_{OUT} = (1 + R1/R2) \cdot V_{REF}$$

Shunt Regulator



$$V_{OUT} = (1 + R2/R3) \cdot V_{REF}$$

High Current Shunt Regulator




$$I_{OUT} = V_{REF}/R2 + I_{KA}$$


AZ431L

Current Source or Current Limit

Typical Applications Circuit (continued)




Precision 5V 1A Regulator



PWM Converter with Reference

Functional Block Diagram



Absolute Maximum Ratings (Note 5)

Symbol	Parameter		Rating	Unit
V_{KA}	Cathode Voltage		20	V
I_{KA}	Cathode Current Range (Continuous)		-100 to 100	mA
I_{REF}	Reference Input Current Range		10	mA
P_D	Power Dissipation	TO92 (Ammo Packing)	770	mW
		SOT89		
		SOT23	370	
		SOT25		
T_J	Junction Temperature		+150	°C
T_{STG}	Storage Temperature Range		-65 to +150	°C

Note: 5. Stresses greater than those listed under *Absolute Maximum Ratings* can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to *Absolute Maximum Ratings* for extended periods can affect device reliability.


Recommended Operating Conditions

Symbol	Parameter	Min	Max	Unit
V_{KA}	Cathode Voltage	V_{REF}	18	V
I_{KA}	Cathode Current	0.1	100	mA
—	Operating Ambient Temperature Range	-40	+125	°C


Electrical Characteristics (Operating Conditions: $T_A = +25^{\circ}\text{C}$, unless otherwise noted.)

Symbol	Parameter	Test Circuit	Conditions	Min	Typ	Max	Unit
V_{REF}	Reference Voltage	4	$V_{KA} = V_{REF}$, $I_{KA} = 10\text{mA}$	1.234	1.240	1.246	V
				1.228	1.240	1.252	
ΔV_{REF}	Deviation of Reference Voltage Over Full Temperature Range	4	$V_{KA} = V_{REF}$ $I_{KA} = 10\text{mA}$	0°C to +70°C	2	10	mV
				-40°C to +85°C	3	10	
				-40°C to +125°C	4	15	
$\frac{\Delta V_{REF}}{\Delta V_{KA}}$	Ratio of Change in V_{REF} to the Change in Cathode Voltage	5	$I_{KA} = 10\text{mA}$ ΔV_{KA} : V_{REF} to 16V	—	-0.5	-1.5	mV/V
I_{REF}	Reference Input Current	5	$I_{KA} = 10\text{mA}$, $R_1 = 10\text{k}\Omega$, $R_2 = \infty$	—	0.15	0.4	μA
ΔI_{REF}	Deviation of Reference Current Over Full Temperature Range	5	$I_{KA} = 10\text{mA}$, $R_1 = 10\text{k}\Omega$, $R_2 = \infty$ $T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$	—	0.1	0.4	μA
I_{KA} (Min)	Minimum Cathode Current for Regulation	4	$V_{KA} = V_{REF}$	—	55	80	μA
I_{KA} (Off)	Off-State Cathode Current	6	$V_{REF} = 0$, $V_{KA} = 18\text{V}$	—	0.04	0.10	μA
			$V_{KA} = 6$, $V_{REF} = 0$	—	0.01	0.05	
Z_{KA}	Dynamic Impedance	4	$V_{KA} = V_{REF}$, $I_{KA} = 1$ to 100mA $f \leq 1.0\text{kHz}$	—	0.05	0.15	Ω
θ_{JC}	Thermal Resistance	—	SOT23	—	84.84	—	$^{\circ}\text{C/W}$
			SOT25	—	84.84	—	
			TO92 (Ammo Packing)	—	140.80	—	
			SOT89	—	29.80	—	


Electrical Characteristics (continued)



Test Circuit 4 for $V_{KA} = V_{REF}$




Test Circuit 5 for $V_{KA} > V_{REF}$




Test Circuit 6 for I_{OFF}

Performance Characteristics


Reference Voltage vs. Ambient Temperature




Reference Current vs. Ambient Temperature





Cathode Current vs. Cathode Voltage



Cathode Current vs. Cathode Voltage





Small-Signal Voltage Gain vs. Frequency





Performance Characteristics (continued)



Dynamic Impedance vs. Frequency




Pulse Response of Input and Output Voltage



Ratio of Delta Reference Voltage to the Ratio of Cathode Voltage vs. Ambient Temperature



Ordering Information




Orderable Part Number	Voltage Tolerance	Package (Note 6)	RoHS Compliant Lead Free / Green	Marking ID	Packing		Status (Note 7)	Alternative
					Qty.	Carrier		
AZ431LAZTR-G1	0.5%	TO92 (Ammo Packing)	Green	AZ431LAZ-G1	2000	Ammo	In Production	—
AZ431LBZTR-G1	1.0%	TO92 (Ammo Packing)	Green	AZ431LBZ-G1	2000	Ammo	In Production	—
AZ431LANTR-E1	0.5%	SOT23	Lead Free	EA6	3000	Tape & Reel	NRND	AZ431LANTR-G1
AZ431LANTR-G1	0.5%	SOT23	Green	GA6	3000	Tape & Reel	In Production	—
AZ431LBNTR-G1	1.0%	SOT23	Green	GA7	3000	Tape & Reel	In Production	—
AZ431LAKTR-G1	0.5%	SOT25	Green	G5A	3000	Tape & Reel	In Production	—
AZ431LBKTR-G1	1.0%	SOT25	Green	G6A	3000	Tape & Reel	In Production	—
AZ431LARTR-G1	0.5%	SOT89	Green	G41A	1000	Tape & Reel	In Production	—
AZ431LBRTR-G1	1.0%	SOT89	Green	G41B	1000	Tape & Reel	In Production	—

Notes: 6. For packaging details, go to our website at: <https://www.diodes.com/design/support/packaging/diodes-packaging/>.
7. NRND: Not Recommended for New Design.

Marking Information

(1) TO92 (Ammo Packing)


(Front View)




First and Second Lines: Logo and Marking ID
(See *Ordering Information*)
Third Line: Date Code
Y: Year
WW: Work Week of Molding
A: Assembly House Code
XX: Internal Code

(2) SOT23

(Top View)




 : Logo
XXX: Marking ID (See *Ordering Information*)

Marking Information (continued)

(3) SOT89


(Top View)




First Line: Logo and Marking ID (See *Ordering Information*)
 Second Line: Date Code
 Y: Year
 WW: Work Week of Molding
 A: Assembly House Code
 XX: Internal Code

(4) SOT25

(Top View)




 : Logo
 XXX: Marking ID (See *Ordering Information*)

Package Outline Dimensions (All dimensions in mm(inch).)

Please see <http://www.diodes.com/package-outlines.html> for the latest version.


(1) Package Type: TO92 (Ammo Packing)



Package Outline Dimensions (continued) (All dimensions in mm(inch).)

Please see <http://www.diodes.com/package-outlines.html> for the latest version.


(2) Package Type: SOT23



Package Outline Dimensions (continued) (All dimensions in mm(inch).)

Please see <http://www.diodes.com/package-outlines.html> for the latest version.


(3) Package Type: SOT25



Package Outline Dimensions (continued) (All dimensions in mm(inch).)

Please see <http://www.diodes.com/package-outlines.html> for the latest version.


(4) Package Type: SOT89



Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

(1) Package Type: SOT23




Dimensions	Z (mm)/(inch)	G (mm)/(inch)	X (mm)/(inch)	Y (mm)/(inch)	E (mm)/(inch)
Value	2.900/0.114	1.100/0.043	0.800/0.031	0.900/0.035	0.950/0.037

Suggested Pad Layout (continued)

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

(2) Package Type: SOT25




Dimensions	Z (mm)/(inch)	G (mm)/(inch)	X (mm)/(inch)	Y (mm)/(inch)	E1 (mm)/(inch)	E2 (mm)/(inch)
Value	3.600/0.142	1.600/0.063	0.700/0.028	1.000/0.039	0.950/0.037	1.900/0.075

Suggested Pad Layout (continued)


Please see <http://www.diodes.com/package-outlines.html> for the latest version.

(3) Package Type: SOT89



Dimensions	Z (mm)/(inch)	X (mm)/(inch)	X1 (mm)/(inch)	X2 (mm)/(inch)	Y (mm)/(inch)	Y1 (mm)/(inch)	E (mm)/(inch)
Value	4.600/0.181	0.550/0.022	1.850/0.073	0.800/0.031	1.300/0.051	1.475/0.058	1.500/0.059

Mechanical Data

- Moisture Sensitivity: Level 3 per J-STD-020
- Terminals: Finish — Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 
- Weight:
 - SOT23: 0.009 grams (Approximate)
 - SOT25: 0.0153 grams (Approximate)
 - SOT89: 0.055 grams (Approximate)
 - TO92 (Ammo Packing): 0.157 grams (Approximate)

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
All other trademarks are the property of their respective owners.
© 2024 Diodes Incorporated. All Rights Reserved.

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Diodes Incorporated:](#)

[AZ431LBNTR-G1](#) [AZ431LAZTR-G1](#) [AZ431LBRTR-G1](#) [AZ431LBKTR-E1](#) [AZ431LBZTR-E1](#) [AZ431LAKTR-E1](#)
[AZ431LARTR-G1](#) [AZ431LBZTR-G1](#) [AZ431LAKTR-G1](#) [AZ431LAZTR-E1](#) [AZ431LBNTR-E1](#) [AZ431LANTR-E1](#)
[AZ431LANTR-G1](#) [AZ431LBKTR-G1](#) [AZ431LBRTR-E1](#) [AZ431LBZ-G1](#)