

Preliminary Product Specification

| Rev. 0.86 |

G1 Emerald

Industrial SD Card 6.10 datasheet
8GB – 64GB



FC RoHS CE 

Table of Contents

1. PRODUCT SUMMARY	4
2. ORDER INFORMATION	5
3. PRODUCT INFORMATION	6
3.1 COMPLIANT SPECIFICATIONS – SD MEMORY CARD SPECIFICATIONS:.....	6
3.2 BUS SPEED MODE (USE 4 PARALLEL DATA LINES)	6
3.3 PRODUCT FEATURES.....	6
3.4 SD CARD COMPARISON	8
4. PRODUCT SPECIFICATION.....	9
4.1 PERFORMANCE	9
4.2 ENDURANCE AND RELIABILITY	10
5. ELECTRICAL SPECIFICATIONS	11
5.1 POWER CONSUMPTION	11
5.2 DC CHARACTERISTIC	11
5.3 BUS SIGNAL LINE LEVELS	12
5.4 POWER UP TIME OF HOST	13
5.5 POWER UP TIME OF CARD	14
5.6 SD INTERFACE TIMING (DEFAULT).....	15
5.7 SD INTERFACE TIMING (HIGH-SPEED MODE)	16
5.8 SD INTERFACE TIMING (SDR12, SDR25, SDR50 AND SDR104 MODES).....	17
6. ENVIRONMENTAL SPECIFICATIONS	18
7. INTERFACE	19
7.1 PIN ASSIGNMENT AND DESCRIPTIONS	19
8. PHYSICAL DIMENSION	20
9. REVISION HISTORY	21

List of Figures

FIGURE 1 – POWER UP TIME OF HOST	13
FIGURE 2 – POWER UP TIME OF CARD	14
FIGURE 3 – INPUT/OUTPUT TIMING (DEFAULT SPEED MODE).....	15
FIGURE 4 – INPUT/OUTPUT TIMING (HIGH-SPEED MODE)	16
FIGURE 5 – CLOCK SIGNAL TIMING.....	17
FIGURE 6 – CARD INPUT TIMING	17
FIGURE 7 – PIN LOCATIONS	19
FIGURE 8 – DEVICE PHYSICAL DIMENSION.....	20

List of Tables

TABLE 1 – PART NUMBERS	5
TABLE 2 – SDSC, SDHC, AND SDXC COMPARISON TABLE.....	8
TABLE 3 – PEAK PERFORMANCE.....	9
TABLE 5 – TERA BYTES WRITTEN.....	10
TABLE 6 – RELIABILITY	10
TABLE 7 – POWER CONSUMPTION	11
TABLE 8 – BUS OPERATING CONDITIONS – THRESHOLD LEVEL.....	11
TABLE 9 – PEAK VOLTAGE AND LEAKAGE CURRENT.....	11
TABLE 10 – BUS OPERATION CONDITIONS – SIGNAL LINE’S LOAD	12
TABLE 11 – BUS OPERATION CONDITIONS – SIGNAL LINE’S LOAD	15
TABLE 12 – INTERFACE TIMING (HIGH-SPEED MODE).....	16
TABLE 13 – INTERFACE TIMING (HIGH-SPEED MODE).....	17
TABLE 14 – ENVIRONMENTAL SPECIFICATIONS.....	18
TABLE 15 – SIGNAL SEGMENT PIN ASSIGNMENT AND DESCRIPTIONS	19

1. Product Summary

<u>Capacity Range</u>	8GB –64GB
<u>Form Factor</u>	SD Card
<u>Host Interface</u>	SD6.1
<u>Speed Class</u>	CLASS10, UHS-I Grade 3, V30, A2
<u>Performance</u>	Sequential read: up to 100 MB/s Sequential write: up to 88 MB/s
<u>Reliability</u>	MTBF: 2 million hours UBER: <1 sector / 10¹⁶ bits read
<u>Operating Temperature</u>	
Or	Mobile: -25°C ~ 85°C Industrial: -40°C ~ 85°C
<u>Storage Temperature</u>	-40°C ~ 85°C
<u>Special Features</u>	CPRM (Content Protection for Recordable Media) * Password Protection of cards (optional)
<u>Compliances</u>	RoHS*, CE*, FCC*, WEEE* *Note: Please contact with Intelligent Memory represent for the detail of compliance conformity.

2. Order Information

Table 1 – Part Numbers

Part Number	Capacity	Speed Class	Operating Temperature range
IMSDSDA8D2A2A1E1A4A0000	8GB	CLASS10, UHS-I Grade 3, V30, A2	-25°C ~ 85°C
IMSDSDB1D2A2A1E1A5A0000	16GB	CLASS10, UHS-I Grade 3, V30, A2	
IMSDSDB2D2A2A1E1A6A0000	32GB	CLASS10, UHS-I Grade 3, V30, A2	
IMSDSDB4D2A2A1E1A8A0000	64GB	CLASS10, UHS-I Grade 3, V30, A2	
IMSDSDA8D2A2A1I1A4A0000	8GB	CLASS10, UHS-I Grade 3, V30, A2	-40°C ~ 85°C
IMSDSDB1D2A2A1I1A5A0000	16GB	CLASS10, UHS-I Grade 3, V30, A2	
IMSDSDB2D2A2A1I1A6A0000	32GB	CLASS10, UHS-I Grade 3, V30, A2	
IMSDSDB4D2A2A1I1A8A0000	64GB	CLASS10, UHS-I Grade 3, V30, A2	

3. Product Information

3.1 Compliant Specifications – SD Memory Card Specifications:

Compliant with Part 1 Physical Layer Specification Ver. 6.10

Compliant with Part 2 File System Specification Ver. 3.00

Compliant with Part 3 Security Specification Ver. 7.00

Standard Size SD Card Mechanical Addendum Ver . 7.0

3.2 Bus Speed Mode (use 4 parallel data lines)

Non-UHS mode

- Default Speed Mode: 3.3V signaling, frequency up to 25MHz, data transfer up to 12.5MB/sec
- High Speed Mode: 3.3V signaling, frequency up to 50MHz, data transfer up to 25MB/sec

UHS-I mode

- SDR12: SDR up to 25MHz, 1.8V signaling
- SDR25: SDR up to 50MHz, 1.8V signaling
- SDR50: 1.8V signaling, frequency up to 100MHz, up to 50 MB/sec
- SDR104: 1.8V signaling, frequency up to 208MHz, up to 104MB/sec.
- DDR50: 1.8V signaling, frequency up to 50MHz, sampled on both clock edges, up to 50MB/sec

Note: Timing in 1.8V signaling is different from that of 3.3V signaling.

3.3 Product Features

Electrical/Physical Interface: SD

- Support SD SPI mode
- Designed for read-only and read/write cards
- The command list supports [Part 1 Physical Layer Specification Ver 6.01] definitions
- Support CPRM (Content Protection for Recordable Media) of SD Card (optional)
- Support Hot Plug
 - Card removal during read operation will never harm the content
- Password Protection of cards (optional)
- Built-in write protection features (mechanical switch, permanent and temporary)
- +4KV/-4KV ESD protection in contact pads
- Operation voltage range: 2.7 ~ 3.6V

Copyrights Protection Mechanism

- Compliant with Part 1 Physical Layer Specification ver. 6.10, CPRM is Optional in SDHC/SDXC.

Advanced Flash Management

LDPC ECC (Low Density Parity Check Error Correction Code)

The deterioration of the flash memory cell over time and the disruptions from neighboring flash memory pages can lead to random bit errors in the stored data. While the chances of any given data bit being corrupted is quite small, the vast number of data bits in a storage system makes the likelihood of data corruption a very real possibility. Error detection and correction codes are used in flash memory storage systems to protect the data from corruption.

Static and Dynamic Wear Leveling

Wear leveling is a process that helps reduce premature wearing out of NAND Flash devices. The Flash controller manages access to the NAND Flash memory devices and determines how the NAND Flash blocks are used. In most cases, the NAND Flash controller maintains a lookup table to translate the memory array's physical block address (PBA) to the logical block address (LBA) used by the host system known as Physical to Logical Address Translation Table.

Bad Block Management

Bad blocks are blocks that include one or more invalid bits, and their reliability is not guaranteed. Blocks that are identified and marked as bad by the manufacturer are referred to as "Initial Bad Blocks". Bad blocks that are developed during the lifespan of the flash are named "Later Bad Blocks"

pSLC (pseudo SLC)

The pSLC configuration on 3D TLC NAND only takes 2 bits for data storage from original 3 bits TLC NAND. It can dramatically increase the reliability, endurance of NAND Flash. It makes the SD card meet high P/E cycle, high TBW demand in industrial and embedded applications and also increases data access performance.

Overprovision

Over provisioning is a technique used in the design of flash media cards. By providing extra memory capacity (which the user can't access) the SD card controller can more easily create pre-erased blocks ready to be used in the virtual pool.

Overprovisioning improves:

- Write performance & IOPS
- Reliability & endurance

3.4 SD Card Comparison

Table 2 – SDSC, SDHC, and SDXC Comparison table

Comparison Table			
	SDSC	SDHC	SDXC
File System	FAT 12/16	FAT32	exFAT
Addressing Mode	Byte (1 byte unit)	Block (512 byte unit)	Block (512 byte unit)
HCS/CCS bits of ACMD41	Support	Support	Support
CMD8 (SEND_IF_COND)	Support	Support	Support
CMD16 (SET_BLOCKLEN)	Support	Support (Only CMD42)	Support (Only CMD42)
Partial Read	Support	Not Support	Not Support
Lock/Unlock Function	Mandatory	Mandatory	Mandatory
Write Protect Groups	Optional	Not Support	Not Support
Supply Voltage 2.0V – 2.7V (for operation)	Support	Support	Support
Total Bus Capacitance for each signal line	40pF	40pF	40pF
CSD Version (CSD_STRUCTURE Value)	1.0 (0x0)	2.0 (0x1)	2.0 (0x1)
Speed Class	Optional	Mandatory (Class 2 / 4 / 6 / 10)	Mandatory (Class 2 / 4 / 6 / 10)

4. Product Specification

4.1 Performance

We specify the performance of our NAND products in following way:

- **“Peak”** describes the measured performance when the product is new and unused. It is commonly used by vendors in their datasheets. However, SSDs by design reduce performance after a relatively short usage period, so peak values cannot be used to predict an application’s longer-term performance.

Table 3 – Peak Performance

Capacity	Speed Class	Sequential performance	
		Read (MB/s)	Write (MB/s)
8GB	A2, V30, CL10, UHS-I Grade 3	100	85
16GB		100	88
32GB		100	88
64GB		100	88
Notes: 1. Peak performance measured in Fresh Out of the Box (FOB) condition 2. Sequential performance is measured with 128KB transfer size; QD32 and 4KB align with TestMetrix A2 Test. 3. Performance may differ depending on application and platform.			

4.2 Endurance and Reliability

Endurance

The lifetime of our NAND products is specified in TBW (Tera Bytes Written), i.e. the total amount of data that the host can write to the NAND media in a defined pattern. In our case this pattern is based on the workload definitions set by JEDEC in JESD219A.

Table 4 – Tera Bytes Written

Capacity	TBW
8GB	457
16GB	914
32GB	1828
64GB	3656
Notes: 1. TBW values are specified based on JEDEC 219A client workload 2. Actual lifetime may vary depending on platform and application	

Reliability

Table 5 – Reliability

Parameter	Value
MTBF	2,000,000 Hours

5. Electrical Specifications

5.1 Power Consumption

Table 6 – Power Consumption

Power Consumption					
Mode		Max Power Consumption			
		Power Up Current (uA)	Read (mA)@3.6V	Write (mA)@3.6V	Standby (mA)
Default Speed Mode		250	150	150	1
High Speed Mode		250	200	200	1
UHS-1 Mode	UHS50/DDR50	250	400	400	1
	UHS104/DDR50	250	400	400	1

Notes:
 1.Power consumption are measured at room temperature.
 2.Power consumption of Max. Standby Current is for SD cards uwith the max. capacity
 3.For SDXC, up to 100mA from VDD1 when XPC=0; up to 150mA from VDD1 when XPC=1.

5.2 DC Characteristic

Table 7 – Bus Operating Conditions – Threshold Level

Bus Operating Conditions – Threshold Level					
Parameter	Symbol	Min	Max	Unit	Condition
Supply Voltage	VDD	2.7	3.6	V	
Output High Voltage	VOH	0.75*VDD		V	IOH=-2mA VDD Min
Output Low Voltage	VOL		0.125*VDD	V	IOL=2mA VDD Min
Input High Voltage	VIH	0.625*VDD	VDD+0.3	V	
Input Low Voltage	VIL	VSS-0.3	0.25*VDD	V	
Power Up Time			250	ms	From 0V to VDD min

Table 8 – Peak Voltage and Leakage Current

Peak Voltage and Leakage Current			
Parameter	Min	Max	Unit
Peak voltage on all lines	-0.3	VDD+0.3	V
All inputs			
Input Leakage Current	-10	10	uA
All outputs			
Output Leakage Current	-10	10	uA

5.3 Bus Signal Line Levels

Table 9 – Bus Operation Conditions – Signal Line's Load

Bus Operation Conditions – Signal Line's Load					
Parameter	Symbol	Min	Max	Unit	Remark
Pull-up resistance	R_{CMD} R_{DAT}	10	100	k Ω	To prevent bus floating
Total bus capacitance for each signal line	C_L		40	pF	1 card $C_{HOST} + C_{BUS}$ shall not exceed 30 pF
Card Capacitance for each signal pin	C_{CARD}		10	pF	
Maximum signal line inductance			16	nH	
Pull-up resistance inside card (pin1)	R_{DAT3}	10	90	k Ω	May be used for card detection
Capacity Connected to Power Line	C_C		5	μ F	To prevent inrush current
Notes: 1. The total capacitance C_L the CLK line of the SD Memory Card bus is the sum of the bus master capacitance C_{HOST} , the bus capacitance C_{BUS} itself and the capacitance C_{CARD} of each card connected to this line: $C_L = C_{HOST} + C_{BUS} + N \cdot C_{CARD}$, Where N is the number of connected cards.					

5.4 Power up Time of Host

Host needs to keep power line level less than 0.5V and more than 1ms before power ramp up.




Figure 1 – Power up Time of Host

Power On or Power Cycle

Followings are requirements for Power on and Power cycle to assure a reliable SD Card hard reset.

- (1) Voltage level shall be below 0.5V
- (2) Duration shall be at least 1ms.

Power Supply Ramp Up

The power ramp up time is defined from 0.5V threshold level up to the operating supply voltage which is stable between VDD (min.) and VDD (max.) and host can supply SDCLK.

Followings are recommendation of Power ramp up:

- (1) Voltage of power ramp up should be monotonic as much as possible.
- (2) The minimum ramp up time should be 0.1ms.
- (3) The maximum ramp up time should be 35ms for 2.7-3.6V power supply.
- (4) Host shall wait until VDD is stable.
- (5) After 1ms VDD stable time, host provides at least 74 clocks before issuing the first command.

Power Down and Power Cycle

When the host shuts down the power, the card VDD shall be lowered to less than 0.5Volt for a minimum period of 1ms. During power down, DAT, CMD, and CLK should be disconnected or driven to logical 0 by the host to avoid a situation that the operating current is drawn through the signal lines.

If the host needs to change the operating voltage, a power cycle is required. Power cycle means the power is turned off and supplied again. Power cycle is also needed for accessing cards that are already in Inactive State. To create a power cycle the host shall follow the power down description before power up the card (i.e. the card VDD shall be once lowered to less than 0.5Volt for a minimum period of 1ms).

5.5 Power Up Time of Card

A device shall be ready to accept the first command within 1ms from detecting VDD min. Device may use up to 74 clocks for preparation before receiving the first command.




Figure 2 – Power up Time of Card

5.6 SD Interface Timing (Default)




Figure 3 – Input/Output Timing (Default Speed Mode)

Table 10 – Bus Operation Conditions – Signal Line's Load

Interface timing (Default)					
Parameter	Symbol	Min	Max	Unit	Remark
Clock CLK (All values are referred to min(V_{IH}) and max(V_{IL}))					
Clock frequency Data Transfer Mode	f_{PP}	0	25	MHz	$C_{card} \leq 10\text{pF}$ (1 card)
Clock frequency Identification Mode	f_{OD}	$0_{A1}/100$	400	kHz	$C_{card} \leq 10\text{pF}$ (1 card)
Clock low time	t_{WL}	10		n	$C_{card} \leq 10\text{pF}$ (1 card)
Clock high time	t_{WH}	10		ns	$C_{card} \leq 10\text{pF}$ (1 card)
Clock rise time	t_{TLH}		10	ns	$C_{card} \leq 10\text{pF}$ (1 card)
Clock fall time	t_{THL}		10	ns	$C_{card} \leq 10\text{pF}$ (1 card)
Inputs CMD, DAT (referenced to CLK)					
Input set-up time	t_{ISU}	5		ns	$C_{card} \leq 10\text{pF}$ (1 card)
Input hold time	t_{IH}	5		ns	$C_{card} \leq 10\text{pF}$ (1 card)
Outputs CMD, DAT (referenced to CLK)					
Output Delay time during Data Transfer Mode	t_{ODLY}	0	14	ns	$C_L \leq 40\text{pF}$ (1 card)
Output Delay time during Identification Mode	t_{ODLY}	0	50	ns	$C_L \leq 40\text{pF}$ (1 card)
Notes:					
*1: 0Hz means to stop the clock. The given minimum frequency range is for cases where continuous clock is required.					

5.7 SD Interface Timing (High-Speed Mode)




Figure 4 – Input/Output Timing (High-Speed Mode)

Table 11 – Interface timing (High-Speed Mode)

Interface timing (High-Speed Mode)					
Parameter	Symbol	Min	Max	Unit	Remark
Clock CLK (All values are referred to min(V_{IH}) and max(V_{IL}))					
Clock frequency Data Transfer Mode	f_{PP}	0	50	MHz	$C_{card} \leq 10\text{pF}$ (1 card)
Clock low time	t_{WL}	7		ns	$C_{card} \leq 10\text{pF}$ (1 card)
Clock high time	t_{WH}	7		ns	$C_{card} \leq 10\text{pF}$ (1 card)
Clock rise time	t_{TLH}		3	ns	$C_{card} \leq 10\text{pF}$ (1 card)
Clock fall time	t_{THL}		3	ns	$C_{card} \leq 10\text{pF}$ (1 card)
Inputs CMD, DAT (referenced to CLK)					
Input set-up time	t_{ISU}	6		ns	$C_{card} \leq 10\text{pF}$ (1 card)
Input hold time	t_{IH}	2		ns	$C_{card} \leq 10\text{pF}$ (1 card)
Outputs CMD, DAT (referenced to CLK)					
Output Delay time during Data Transfer Mode	t_{ODLY}		14	ns	$C_L \leq 40\text{pF}$ (1 card)
Output Hold time	T_{OH}	2.5		ns	$C_L \leq 15\text{pF}$ (1 card)
Total System capacitance of each line*1	C_L		40	nF	$C_L \leq 15\text{pF}$ (1 card)
Notes:					
*1: In order to satisfy severe timing, the host shall drive only one card. AC Characteristic (SDR12, SDR25, SDR50 and SDR10)					

5.8 SD Interface Timing (SDR12, SDR25, SDR50 and SDR104 Modes)




Figure 5 – Clock Signal Timing




Figure 6 – Card Input Timing

Table 12 – Interface timing (High-Speed Mode)

Interface timing (SDR12, SDR25, SDR50 and SDR104 Modes Input)				
Symbol	Min	Max	Unit	Remark
t _{CLK}	4.8	-	ns	208MHz (Max.), Between rising edge, V _{CT} = 0.975V
t _{CR} , t _{CF}	-	0.2* t _{CLK}	ns	t _{CR} , t _{CF} < 0.96ns (max.) at 208MHz, CCARD =10pF t _{CR} , t _{CF} < 2.00ns (max.) at 100MHz, CCARD =10pF The absolute maximum value 17ft he, t _{CF} is 10ns regardless of clock frequency
Clock Duty	30	70	%	
Symbol	Min	Max	Unit	SDR 104 Mode
t _{IS}	1.40	-	ns	CCARD =10pF, V _{CT} = 0.975V
t _{IH}	0.81	-	ns	CCARD = 5pF, V _{CT} = 0.975V
Symbol	Min	Max	Unit	SDR50 Mode
t _{IS}	3.00	-	ns	CCARD =10pF, V _{CT} = 0.975V
t _{IH}	0.81	-	ns	CCARD = 5pF, V _{CT} = 0.975V

6. Environmental Specifications

Table 13 – Environmental Specifications

Environmental Specifications		
Test		Test Condition
Temperature	Operation	Mobile temperature: -25°C ~ 85°C, 0% RH, 96 hours Industrial temperature: -40°C ~ 85°C, 0% RH, 300 hours
	Storage	Mobile temperature: -40°C, 0% RH, 168 hours ; 85°C, 0% RH, 500 hours Industrial temperature: -40°C, 0% RH, 500 hours ; 85°C, 0% RH, 500 hours
Humidity	Operation	Mobile temperature: 25°C, 95% RH 1 hours Industrial temperature: 55°C, 95% RH 4 hours
	Storage	Mobile temperature: 40°C, 95% RH 500 hours Industrial temperature: 55°C, 95% RH 500 hours
Shock	Mobile temperature: 500G, 0.5ms Industrial temperature: 1500G, 0.5ms	
Vibration	20Hz~80Hz/1.52mm (frequency/displacement) 80Hz~2000Hz/20G (frequency/displacement) X, Y, Z axis/30mins each	
Drop	150cm free fall, 6 face of each	
Bending	≥10N, hold 1Min / 5 Times	
Torque	0.15N-m or +/-2.5deg, hold 30 seconds / 5 Times	
Durability	10,000 times mating cycle	
ESD	Non-operation	Contact: +/- 4KV each item; 5 times/Pin Air: +/- 15KV ; 5 times/Position
	Operation	Air: +/- 8KV ; 10 times/Position (B-Grade)

7. Interface

7.1 Pin Assignment and Descriptions




Figure 7 – Pin Locations

Table 14 – Signal Segment Pin Assignment and Descriptions

Pin Assignment and Descriptions						
Pin #	SD Mode			SPI Mode		
	Name	Type1	Description	Name	Type	Description
1	DAT2	I/O/PP	Data Line[bit2]	RSV		
2	CD/DAT3 ²	I/O/PP ³	Card Detect/ Data Line[bit3]	CS	I ³	Chip Select (negtrue)
3	CMD	PP	Command/Response	DI	I	Data In
4	VDD	S	Supply voltage	VDD	S	Supply voltage
5	CLK	I	Clock	SCLK	I	Clock
6	VSS	S	Supply voltage ground	VSS	S	Supply voltage ground
7	DAT0	I/O/PP	Data Line[bit0]	DO	O/PP	Data Out
8	DAT1	I/O/PP	Data Line[bit1]	RSV		
Note: S: power supply I: input O: output using push-pull drivers PP:I/O using push-pull drivers The extended DAT lines (DAT1-DAT3)are input on power up. They start to operate as DAT lines after SET_BUS_WIDTH command. The Host shall keep its own DAT1-DAT3 lines in input mode, as well, while they are not used. It is defined so, in order to keep compatibility to MultiMedia Cards. At power up this line has a 50Kohm pull up enabled in the card. This resistor serves two functions Card detection and Mode Selection. For Mode Selection, the host can drive the line high or let it be pulled high to select SD mode. If the host wants to select SPI mode it should drive the line low. For Card detection, the host detects that the line is pulled high. The user should disconnect this pull-up during regular data transfer period, with SET_CLR_CARD_DETECT (ACMD42) command.						

8. Physical Dimension

23.0 mm(L) x 24.0 mm(W) x 1.00 mm(T)




Figure 8 – Device Physical Dimension

9. Revision History

Revision	Descriptions	Release Date
0.1	Preliminary release	Mar, 2022
0.2	Update Performance	Mar, 2022
0.85	Update TBW	Aug, 2022
0.86	Revised TBW for all capacities	Nov, 2022

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Intelligent Memory:

[IMSDSDA8D2A2A1I1A4A0000](#) [IMSDSDB1D2A2A1I1A5A0000](#) [IMSDSDB2D2A2A1I1A6A0000](#)