



MIL-PRF-28876 QPL and MIL-DTL-28840 QPL

U.S. Navy Approved Connectors and Accessories

United States ■ United Kingdom ■ Germany ■ France ■ Nordic ■ Italy ■ Spain ■ Japan

First Edition • September 2011

All Dressed Up with Nowhere To Go?

*Glenair Rapid-Response Manufacturing
and Same-Day Stocking
Gets You Underway On-Time*



1211 Air Way
Glendale, California 91201-2497
Telephone: 818-247-6000 • Facsimile: 818-500-9912 • E-mail: sales@glenair.com
United States • United Kingdom • Germany • Nordic • France • Italy • Spain • Japan
www.glenair.com

**U.S. Navy Approved
Connectors and Accessories**



Table of Contents

**Introduction to MIL-PRF-28876 QPL
Shipboard Fiber Optic Connectors**



A

**M29504 Fiber Optic Termini and Tools for
MIL-PRF-28876 Connectors**



B

**MIL-PRF-28876 QPL Fiber Optic
Connectors and Accessories**



C

**MIL-DTL-28840 Shipboard Electrical Connectors
Introduction, Tools, and Contacts**



D

**MIL-DTL-28840 QPL Electrical
Connectors and Accessories**



E

**Glenair Commercial Equivalent
MIL-DTL-28840 Type Connectors and Accessories**



F

Index



G

Qualified military specification slash sheets covered in this catalog include the following:

M22520/34 and /35	M29504/3,
M28840/1 through /30	M29504/14 and /15
M28876/1, /2, /3, /4,	M39029/83 and /84
/6, /7, /8, /9, /10, /11, /12, /13, /14 and /15	M81969/33 and /34

**MIL-PRF-28876 QPL
Introduction****A**

Qualified MIL-PRF-28876 Fiber Optic Connectors and MIL-PRF-29504 Termini

Navy Approved, In Stock, and Ready for Immediate Shipment

The use of fiber optics in shipboard and ship-to-shore data transmissions is growing rapidly, and the tight-tolerance MIL-PRF-28876 interconnect has become the universal standard for Navy shipboard applications. Glenair's qualified offering—including QPL'd MIL-PRF-29504/14 and /15 termini and the broad range of connectors, backshells, and dust cap accessories—delivers all the necessary performance from precise optical alignment to environmental protection and corrosion resistance. Glenair MIL-PRF-28876 QPL connectors and termini are ready for deployment in shipboard, surface and submarine applications, as well as mission-critical combat communication systems such as mobile tactical shelters. They are specifically geared for upgrade and retrofit applications where extending system life-cycles and reducing cost of ownership are principal requirements. For more information, or for product samples, please consult the factory or visit us at www.glenair.com.



PRODUCT FEATURES

- Connectors and Dust Covers Qualified to the Complete Requirements of MIL-PRF-28876 including Plugs, Wall-Mount Receptacles, Jam-Nut Mount Receptacles and In-Line Receptacles
- Multiple Shell Sizes and Insert Arrangements, Including 2, 4, 6, 8, 18 and 31 Channel Layouts
- Backshells in Straight, 45° and 90° Configurations
- Corrosion-Resistant and Environmentally Sealed
- Qualified MIL-PRF-29504/14 and /15 Pin and Socket Termini and /3 Dummy Terminus
- Same-Day Availability

MIL-PRF-28876 QPL Connector Performance Specifications



MIL-PRF-28876
Introduction

A

Test Description	Performance Requirements/Specifications
Optical Insertion Loss, Multimode	-0.3 dB Typical (62.5/125)
Optical Insertion Loss, Singlemode	-0.3 dB Typical (9/125)
Optical Back Reflection, Singlemode	Better than -40 dB - PC Polish Better than -50 dB - Enhanced PC Polish
Operating Temperature	-28°C to +65°C using MIL-Spec Qualified Epoxy and Cable, or -55°C to +125°C using alternative Epoxy and Cable (consult factory)
Temperature (Thermal) Shock	-40°C to +70°C, 5 Cycles, per TIA/EIA-455-71, Test Schedule C
Temperature Cycling	-28°C to +65°C, 5 Cycles, per TIA/EIA-455-3
Temperature/Humidity Cycling	-10°C to +65°C, 10 Cycles, 240 hours, 98% RH, per TIA/EIA-455-5, Test Method B
Temperature Life Aging	+110°C, 240 hours, Dry Air, per TIA/EIA-455-4
Mating Durability	500 cycles, per TIA/EIA-455-21
Vibration - Sinusoidal	10 g Peak, 5-500 Hz, 12 Cycles (3 hours) per Axis at Ambient Temperature, per TIA/EIA-455-11, Test Condition II
Vibration - Random	10.2 g RMS, 50-2000 Hz, 30 minutes per Axis at Ambient Temperature, per TIA/EIA-455-11, Test Condition VII-C
Mechanical Shock (High Impact)	Per MIL-S-901, Lightweight, Grade A, Class I (Hammer Shock)
Impact	8 Drops from 8 feet, per TIA/EIA-455-2, Test Method B
Crush Resistance	281 lbs, 7 Loading Cycles, per TIA/EIA-455-26
External Bending Moment	300 inch-lbs min for 1 minute
Cable Pull Out Force - Termini	22 lbs min for 1 minute, per TIA/EIA-455-6
Cable Pull Out Force - Connector	162 lbs min for 10 minutes, per TIA/EIA-455-6
Cable Seal Flexing	180° Flex, 200 Cycles, per TIA/EIA-455-1
Cable Twist	360°±180° Twist, 50 Cycles, 11 lbs min Tension, per TIA/EIA-455-36
Ozone Exposure	150 ppm for 2 hours at +70°C, per TIA/EIA-455-189
Fungus Resistance	28 days at +30°C, 95% RH, per TIA/EIA-455-56
Fluid Immersion	Turbine Fuel, Isopropyl Alcohol, Hydraulic Fluid, Lubricating Oil, Coolant, Tap Water, and Seawater, 24 hour immersion duration, per TIA/EIA-455-12
Water Pressure	Equivalent depth of 32 feet for 48 hours at +10°C to +35°C
Freezing Water	1 hour, per TIA/EIA-455-98, Test Method A, Procedure 1
Corrosion Resistance (Salt Spray)	500 hours at +35°C, per TIA/EIA-455-16, Test Condition I
Sand and Dust	12 hours, per TIA/EIA-455-35
Flammability	0.75 inch flame for 10 seconds mated, 1.50 inch flame for 60 seconds unmated, per EIA/ECA-364-81
* Performance Specifications/Requirements based on the use of MIL-PRF-24792 Epoxy and MIL-PRF-85045 Simplex and Breakout Shipboard Optical Fiber.	

1000 Hour Grey™

The Advanced Formula Ni-PTFE Plating Process for EMC Navy Applications




 **Cadmium Free
RoHS-Compliant
Plating Process Breaks
1000 Hour Corrosion
Protection Barrier!**

The MIL-PRF-28876 specification does not, as of yet, establish any next-generation cadmium-free conductive plating options. But the Glenair advanced Nickel PTFE formula **1000 Hour Grey™** plating process (available in all of our M28876 commercial equivalent 180-040 series parts) meets all key performance requirements including shell-to-shell conductivity and long-term salt spray durability. **1000 Hour Grey™** delivers outstanding performance in a broad range of land, sea, and air interconnect applications. The non-reflective, non-magnetic, gun-metal gray surface finish is an ideal choice for naval applications with severe corrosion protection and EMI/EMC requirements.

Advanced Durability, Conductivity, and Lubricity Plus Outstanding Corrosion Resistance!

The mechanical, electrical and environmental performance of **1000 Hour Grey™** is truly outstanding, far surpassing that of other metal alloy/fluorocarbon polymer plating solutions:

- | | |
|---|------------------------------------|
| ■ Salt spray 1000 Hrs. static, 500 hrs. dynamic | ■ Hexavalent chromium free |
| ■ Low shell-to-shell resistance | ■ Potassium formate resistant |
| ■ -55°C to 175°C temp. Rating | ■ Max 2.5 Millivolt drop potential |
| ■ 336+ hrs. sulfur dioxide resistance | ■ 500+ Mating cycles |
| ■ Non-magnetic | ■ Low outgassing |
| ■ Cadmium free | ■ RoHS compliant |
| ■ Low coefficient of friction | ■ Plating code: MT |



Glenair, Inc.

1211 Air Way • Glendale, CA 91201-2497 • Tel: 818-247-6000 • Fax: 818-500-9912 • E-Mail: sales@glenair.com • Rev. 04.12.16

M29504/14

181-039

Size 16 Fiber Optic Pin Terminus
For MIL-PRF-28876 ConnectorsM29504
Fiber Optic Connectors

Size 16 M29504/14 Fiber Optic Pin Terminus for MIL-PRF-28876 Connectors



Table I: Part Number				
Mil-Spec Part Number	ØA (Microns)	Fiber Type	Fiber Size Core/Cladding (Microns)	Commercial Part Number
M29504/14-4140C	125.0	Single Mode	9/125	181-039-1250C
Not listed in Mil-Spec	125.5	Single Mode	9/125	181-039-1255C
M29504/14-4141C	126.0	Single Mode	9/125	181-039-1260C
M29504/14-4131C	126.0	Multi Mode	50/125, 62.5/125	181-039-1260C
M29504/14-4132C	127.0	Multi Mode	50/125, 62.5/125	181-039-1270C
M29504/14-4135C	142.0	Multi Mode	100/140	181-039-1420C
Consult factory for additional sizes and QPL status.				

B





Table II: Tools and Accessories

Part Number	Description
265-008	Crimp Sleeve Ø2.4mm Max Jacket (Mil-Spec Type)
182-012	Crimp Tool
182-013	Insertion Tool, Straight
182-014	Insertion Tool, 90°
182-015	Removal Tool
182-035	Hand Polishing Tool

Material and Finish

Ferrule: Zirconia Ceramic
 Terminus Assembly: Stainless Steel/ Passivate
 Retaining Clip, Spring Washers: Spring Alloy
 Seal: Fluorosilicone
 Crimp Sleeve: Brass Alloy/Nickel

Notes

- Crimp sleeve is supplied with terminus assembly and may be ordered separately (see Table II). For terminus less crimp sleeve, omit **C** from end of part number.
- See Glenair GAP-036 for termination procedure and assembly tools.
- Dummy terminus part number: 181-051 or M29504/3-4038.

Dimensions in Inches (millimeters) are subject to change without notice.

**M29504/15****181-040**

**Size 16 Fiber Optic Socket Terminus
For MIL-PRF-28876 Connectors**

Size 16 M29504/15 fiber optic socket terminus for MIL-PRF-28876 connectors



Table I: Part Number				
Mil-Spec Part Number	ØA (Microns)	Fiber Type	Fiber Size Core/Cladding (Microns)	Commercial Part Number
M29504/15-4180C	125.0	Single Mode	9/125	181-040-1250C
Not listed in Mil-Spec	125.5	Single Mode	9/125	181-040-1255C
M29504/15-4181C	126.0	Single Mode	9/125	181-040-1260C
M29504/15-4171C	126.0	Multi Mode	50/125, 62.5/125	181-040-1260C
M29504/15-4172C	127.0	Multi Mode	50/125, 62.5/125	181-040-1270C
M29504/15-4175C	142.0	Multi Mode	100/140	181-040-1420C

Consult factory for additional sizes and QPL status.





Table II: Tools and Accessories

Part Number	Description
265-008	Crimp Sleeve Ø 2.4mm Max Jacket (Mil-Spec Type)
265-010	Alignment Sleeve Assembly
182-012	Crimp Tool
182-013	Insertion Tool, Straight
182-014	Insertion Tool, 90°
182-015	Removal Tool
182-016	Alignment Sleeve Assembly Insertion/Removal Tool
182-035	Hand Polishing Tool

Material and Finish

Alignment Sleeve, Ferrule: Zirconia Ceramic
 Protective cover: Spring Alloy / Nickel
 Terminus Assembly: Stainless Steel / Passivate
 Retaining Clip: Spring Alloy
 Seal: Fluorosilicone
 Crimp Sleeve: Brass Alloy / Nickel

Notes

- Crimp sleeve is supplied with terminus assembly and may be ordered separately (see Table II). For terminus less crimp sleeve omit **C** from end of part number.
- Alignment sleeve assembly is supplied with terminus assembly (packaged loose) and may be ordered separately (see Table II). For terminus less alignment sleeve assembly, add **N** to end of part number (e.g. 181-040-1260CN).
- See Glenair GAP-036 for termination procedure and assembly tools.
- Dummy Terminus: Part Number 181-051 or M29504/3-4038.

**M29504/3
181-051
Size 16 Dummy Terminus
for MIL-PRF-28876 Connectors**




Size 16 M29504/3 Fiber Optic Dummy Terminus for MIL-PRF-28876 Connectors



Table I: Part Number	
Mil-Spec Part Number	Commercial Part Number
M29504/3-4038	181-051

Table II: Tools and Accessories	
Part Number	Description
182-013	Insertion Tool, Straight
182-014	Insertion Tool, 90°
182-015	Removal Tool



Material and Finish

Terminus Body: Stainless Steel/Passivate

Retaining Clip: Spring Alloy/Nickel

Seal: Fluorosilicone

Notes

See Glenair GAP-036 for assembly tools and procedures.

Dimensions in Inches (millimeters) are subject to change without notice.




182-012 Fiber Optic Crimp Tool

Crimp Tool for M29504, GHD, GFOCA and NGCON Fiber Optic Termini

B

The Glenair fiber optic crimping tool enables users to quickly and effectively terminate the crimp sleeve to the cable strength member for a secure mechanical junction. The tool is compatible with many common termini styles, including M29504, Glenair High Density (GHD), GFOCA and NGCON.

Part Number	Compatible Termini	
182-012	181-039	M29504/14 Pin
	181-040	M29504/15 Socket
	181-011	Size 16 Socket
	181-012	Size 16 Pin
	181-047	GHD, Keyed
	181-056	GHD, Non-Keyed
	181-050	GFOCA
	181-043	NGCON



Dimensions in Inches (millimeters) are subject to change without notice.

182-013 Straight Insertion Tool For Fiber Optic Termini



M29504
Fiber Optic Contacts



Straight Insertion Tool for Fiber Optic Termini

The preferred tool of seasoned fiber optic technicians, the straight insertion tool is designed to aid users in populating connectors with fiber optic termini. Gone are the days of damaged fibers and sore fingers—this convenient tool features a comfortable handle and specially designed insertion tip for use with M29504, GHD and many other termini available from Glenair.

B

Part Number	Compatible Termini	
182-013	181-039	M29504/14 Pin
	181-040	M29504/15 Socket
	181-051	M29504/3 Dummy
	181-011	Size 16 Socket
	181-012	Size 16 Pin
	181-047	GHD, Keyed
	181-056	GHD, Non-Keyed
	181-043	NGCON

Ø.85
Max




Dimensions in Inches (millimeters) are subject to change without notice.

**182-014**
90° Insertion Tool
For Fiber Optic Termini**Right Angle (90°) Insertion Tool for Fiber Optic Termini****B**

The 90° terminus insertion tool is designed to help populate connectors with fiber termini in situations where space is limited—while offering users the same easy insertion as with the straight 182-013 tool. Ideal for use in boxes and on connectors with backshells that inhibit normal rear insertion. Designed for use with M29504, GHD and many other termini available from Glenair.

Part Number	Compatible Termini	
182-014	181-039	M29504/14 Pin
	181-040	M29504/15 Socket
	181-051	M29504/3 Dummy
	181-011	Size 16 Socket
	181-012	Size 16 Pin
	181-047	GHD, Keyed
	181-056	GHD, Non-Keyed
	181-043	NGCON



Dimensions in Inches (millimeters) are subject to change without notice.

182-015
Removal Tool
For Fiber Optic Termini




Removal Tool for Fiber Optic Termini

The fiber optic terminus removal tool is designed for use with size 16 front release/rear entry termini. Sliding the tool into the face of the insulator and depressing the plunger—after first removing the alignment sleeve from socket termini—enables users to quickly and easily remove the fiber terminus from the rear of the insert. Compatible with Glenair front release fiber optic termini.

B

Part Number	Compatible Termini	
182-015	181-039	M29504/14 Pin
	181-040	M29504/15 Socket
	181-051	M29504/3 Dummy
	181-011	Size 16 Socket
	181-012	Size 16 Pin
	181-047	GHD, Keyed
	181-056	GHD, Non-Keyed
	181-043	NGCON



Dimensions in Inches (millimeters) are subject to change without notice.




182-035 Polishing Tool for Fiber Optic Termini

Polishing Tool for Fiber Optic Termini

B

The Glenair fiber optic termini polishing tool is designed for polishing M29504/14 pin and /15 socket termini. Used with polishing film, this tool makes it easy to polish termini using a figure-8 pattern. Tool is stainless steel with passivate finish.

Part Number	Compatible Termini	
182-035	181-039	M29504/14 Pin
	181-040	M29504/15 Socket



Dimensions in Inches (millimeters) are subject to change without notice.

GAP-036
Glenair Termini Assembly Procedure
for M29504/14 (181-039) and M29504/15 (181-040)
Sheet 1 of 4



1.0 SCOPE

The following procedure is for termination of Glenair Fiber Optic Termini for use in Glenair front release 180-040 series connectors.

2.0 SAFETY NOTICE

Extreme care should be taken when handling optical fiber to avoid penetration of skin. Avoid eye contact with illuminated laser light which can cause eye damage.

3.0 ASSEMBLY TOOLS:

- A. P/N 182-012 = Tool, Crimp
- B. P/N 182-035 = Tool, Polishing
- C. P/N 182-013 = Tool, Insertion, Straight
- D. P/N 182-014 = Tool, Insertion, 90 Degree
- E. P/N 182-015 = Tool, Removal
- F. P/N 182-016 = Tool, Insertion/Removal, Alignment Sleeve (socket terminus only)

4.0 CABLE PREPARATION / TERMINATION

4.1 Verify cable to ensure correct type.

4.2 Select appropriate Terminus

- A. P/N 181-039 = Terminus, Pin
- B. P/N 181-040 = Terminus, Socket

4.3 Load terminus crimp sleeve onto simplex cable. Note - omit for buffered fiber applications.

4.4 Strip cable to the dimensions in inches that are indicated in Figure 1.




FIGURE 1
(not drawn to scale)

4.5 Wipe off bare fiber with Isopropyl alcohol immediately after stripping.

NOTE: Uncoated optical fiber can degrade when exposed to air. Termination must be done immediately within 10 minutes.

4.6 Prepare epoxy according to manufacturer's instructions.



4.7 Fill syringe with epoxy and eliminate all air bubbles.

4.8 Insert syringe into rear of terminus and fill ceramic ferrule with epoxy completely until a small bead of epoxy is present at the tip of ferrule. Retract the syringe while filling the entire terminus with epoxy.

4.9 Fiber insertion

- A. Carefully insert stripped fiber into terminus until it stops.
- B. Wipe off any excess epoxy that may emerge from the rear of the terminus due to insertion of the fiber.
- C. Bare fiber should protrude out the front of terminus approximately .20 inches (see Figure 2).
- D. Ensure that the exterior surfaces of terminus are free of epoxy.
- E. Carefully distribute strength members over rear body of terminus.
- F. Slide crimp sleeve up cable jacket, and position over terminus rear body and strength members.
- G. Crimp the sleeve using crimp tool (see Figure 2).

Dimensions in Inches (millimeters) are subject to change without notice.



5.0 EPOXY:

There are a variety of epoxy adhesives which maybe used depending on the application. Only 3 different adhesives are listed in this procedure (see 6.2).

6.0 EPOXY CURING

6.1 Using curing oven, carefully position terminated fiber into a cavity of curing block.

NOTE: Care must be taken not to break protruded fiber.

6.2 EPOXIES AND ASSOCIATED CURING PROCEDURES / SCHEDULES:

A. M24792A per MIL-PRF-24792A or equivalent (FOCI AngstromBond AB-9112, or Tra-Con TRA-BOND F112)
Heat cure 1 hour @ 65°C (or 24 hour air cure).

B. Tra-Con, TRA-BOND F113SC
Heat cure 1 hour @ 65°C (or 24 hour air cure).

C. EPO-TEK 353ND (for high temperature applications)
Ramped cure schedule: High temp fiber only
1) 30 minutes @ 80°C, then:
2) 30 minutes @ 100°C, then:
3) 10 minutes @ 150°C

7.0 FIBER SCRIBING

- Hold terminus with fiber pointing straight up, and lightly score fiber approximately .01 inches above ceramic.
- Gently move the blade across fiber to scribe glass using fiber scribe.
- Grasp fiber and pull gently upward until fiber breaks.
- Carefully discard piece of fiber.

8.0 POLISHING PROCEDURE

- Clean polishing film, tool, and tip of terminus using Isopropyl alcohol after each step.
- Dry all parts using wipes or compressed air.
- Wipe distilled water onto back of polishing film and place onto rubber pad.
- Insert terminus into polishing tool.
- Polish terminus in small figure "8" motion using the following procedure.
- Visually inspect terminus tip using microscope to prevent over polishing after each polishing step.
- Use light pressure through each polishing step.

Polishing Steps for Domed PC Polish					
Polish Step	Paper Grit Size	# of Figure 8's	Hand Pressure	Polishing Surface	Lubricant
1st Polish on Pad	15 micron Silicon Carbide	9	Light	90 Durometer Pad	Dry
2nd Polish on Pad	6 micron Diamond	9	Light	90 Durometer Pad	Distilled Water
3rd Polish on Pad	3 micron Diamond	10	Light	90 Durometer Pad	Distilled Water
4th Polish on Pad	1 micron Diamond	10	Light	90 Durometer Pad	Distilled Water
5th Polish on Pad	0.5 micron Diamond	5	Light	90 Durometer Pad	Distilled Water
6th Polish on Pad	Ultra Fine	3	Light	90 Durometer Pad	Distilled Water

Dimensions in Inches (millimeters) are subject to change without notice.

GAP-036
Glenair Termini Assembly Procedure
for M29504/14 (181-039) and M29504/15 (181-040)
Sheet 3 of 4



8.2 After completing final polishing step, core area must be free of epoxy, scratches, pits and cracks. See Figure 3.
 NOTE: Do not backlight fiber when inspecting for scratches.




FIGURE 3

9.0 SOCKET TERMINUS ALIGNMENT SLEEVE AND PROTECTIVE COVER INSTALLATION, SEE FIGURES 4 AND 5

9.1 Carefully push alignment sleeve assembly onto terminus ferrule until seated.
 Note: For proper retention, the fingers of the protective cover must snap into the groove at the front of the terminus metal body.




FIGURE 4




FIGURE 5

Step 1: Insert tip of alignment sleeve removal tool into alignment sleeve assembly.

Step 2: Depress the tool plunger and pull away from the connector.

Step 3: Release plunger to release alignment sleeve assembly from tool.

Dimensions in Inches (millimeters) are subject to change without notice.

10.0 TERMINUS REMOVAL, SEE FIGURE 6.

Step 1: Slide tip of tool over front of terminus until it bottoms inside connector insert.

Step 2: While pushing tool handle forward, simultaneously depress plunger to eject terminus from connector insert.




FIGURE 6

Dimensions in Inches (millimeters) are subject to change without notice.

Series 80 Mighty Mouse Size #16 Fiber Optic Termini



Series 801 Plug with 181-057
pin terminus



Series 801 receptacle with 181-075
socket terminus

- Single Mode and Multi Mode
- Snap-in, Rear Release
- Precision Ceramic Ferrules
- 0.5 dB Typical Attenuation
- 1 to 22 Channels

B

Reduce Size and Weight with Series 80 Mighty Mouse Fiber Optic Connectors

New size #16 fiber optic termini can be used in any standard Mighty Mouse connector. Available for single mode or multi mode fiber, these termini have low insertion loss and are intended for high-reliability aerospace applications. Series 80 connectors offer substantial reductions in size and weight compared to our D38999 type fiber optic connectors.

Series 80 Contact Arrangements For Use With #16 Fiber Optic Termini

1 #16	2 #16	4 #16	2 #16, 4 #23	5 #16	2 #16, 8 #23	7 #16	12 #16	14 #16	22 #16

See Series 80 Mighty Mouse catalog for connector ordering information. Order connectors less contacts and order fiber optic termini separately. Cavity numbers are mating face view of pin connectors.

The Series 801 9-4 receptacle is less than half the
size of our D38999 type connector.



Series 801
6 Grams
(less contacts)

D38999 Series III
27 Grams
(less contacts)

Dimensions in Inches (millimeters) are subject to change without notice.



Series 80 Mighty Mouse Contacts and Tools

Size #16 Fiber Optic Termini 181-057 and 181-075

Size #16 Fiber Optic Termini




181-057 Pin Terminus




181-075 Socket Terminus

Size #16 fiber optic termini are compatible with all Series 80 Mighty Mouse connectors with size #16 cavities. These snap-in, rear-release termini feature precision ceramic ferrules and sleeves for accurate fiber alignment. Typical insertion loss 0.5 dB. Fits 50/125 and 62.5/125 multi mode and 9/125 single mode fiber. Stainless steel bodies and springs.

Termini Type	Optical Fiber Type	Part Number	A Ferrule I.D.
Pin	Multi Mode	181-057-126	126.0 microns
Pin	Single Mode	181-057-125	125.5 microns
Socket	Multi Mode	181-075-126	126.0 microns
Socket	Single Mode	181-075-125	125.5 microns



181-057 Pin Terminus



181-075 Socket Terminus

Materials and Finishes

Terminus Body: stainless steel, passivated

Ferrule: zirconia ceramic

Protective cover: copper alloy, nickel plated

Spring: stainless steel, passivated

Alignment sleeve: zirconia ceramic

Specifications

Insertion Loss: 0.5 dB typical

Operating Temperature: -65° to + 200° C

Durability: 500 cycles

Insertion/extraction Tool

Standard size #16 plastic tool

Glenair Part Number 809-131

Military Part Number M81969/14-03

Termination Procedure

The assembly process is similar to industry-standard procedures for MIL-PRF-29504 termini. See following pages for assembly instructions.

Application Notes

1. Mighty Mouse fiber optic termini are intended for use in Glenair Series 801, 802 and 805 threaded coupling connectors.
2. Refer to technical manual NAVSEA 01-1A-505-4 "AIRCRAFT FIBER OPTIC CABLING" for installation and maintenance procedures applicable to military aircraft. Available on request from Glenair.
3. Glenair is an industry-leading supplier of factory-terminated fiber optic cable assemblies and molded cordsets. Contact Glenair for more information.

Dimensions in Inches (millimeters) are subject to change without notice.

Series 80 Mighty Mouse Contacts and Tools Size #16 Fiber Optic Termini Assembly Procedure



M29504
Fiber Optic Contacts

B

Size #16 Fiber Optic Termini Assembly Instructions

This assembly procedure applies to Glenair fiber optic termini part numbers 181-057 and 181-075. These instructions are to support operators who have had prior training in fiber optic assembly procedures. Operators will have been made aware of all health and safety issues.

CAUTION

Assembly of fiber optic termini entails the exposure of operators to fragile glass fibers, solvents and gases. Every precaution is to be taken against harmful effects by the use of protective gloves, safety glasses and good ventilation. All local health and safety regulations should be adhered to and operators should follow designated safe working practices. The use of protective gloves and barrier creams are recommended when using solvents and adhesives. Repeated skin contact should be avoided and care should be taken to wear safety glasses when handling these materials. Attention should be taken of the recommendations of the relevant MSDS sheets for the materials being used. Extreme care should be taken when handling optical fiber to avoid penetration of skin. Avoid eye contact with illuminated laser light which can cause permanent eye damage.


Assembly Tools and Consumables

Ruler with 6 inch scale	Syringe	Razor blade or exacto knife	Special polishing tools are available from Glenair:
Cable jacket cutter	Dispensing needle	Microscope (200X)	1. Tool for pin terminus
Mechanical stripper	Curing fixture	Bundle light source	182-001P
Kevlar shears	Cleaving tool	Compressed air	2. Tool for socket terminus
Buffer stripper	Glass polishing plate		182-045
Isopropyl Alcohol	Polishing films		


This assembly instruction lists two epoxies: A standard temperature epoxy and a high temperature epoxy. Ensure that the epoxy curing temperature is compatible with the temperature rating of the cable.	Recommended Epoxy	Fiber Type	Epoxy Curing Schedule
	M24792A or equivalent AngstromBond® AB-9112 (Fiber Optic Center, Inc) TRA-BOND™ F112 (Henkel)	Standard	1 Hour @ 650C or 24 Hour Air Cure
	EPO-TEK® 353ND (Epoxy Technology, Inc.)	Standard	2 Hours @ 800C
		High temperature	Stage 1: 30 min. @ 800C
			Stage 2: 30 min. @ 1000C
			Stage 3: 10 min. @ 1500C

Step 1 Cable Prep and Epoxy Filling

- Strip cable to length. Dimensions are in inches (millimeters).
- Wipe off bare fiber with isopropyl alcohol immediately after stripping. **NOTE: uncoated optical fiber can degrade when exposed to air. Termination must be done within 10 minutes of stripping the buffer.**
- Prepare epoxy according to manufacturer's instruction.
- Fill syringe with epoxy and eliminate all air bubbles.
- Insert syringe into rear of terminus and completely fill ceramic ferrule with epoxy. A small bead of epoxy should be visible at the tip of the ferrule. Retract the syringe while filling the entire terminus with epoxy.



Pin Terminus 181-057



Socket Terminus 181-075


Dimensions in Inches (millimeters) are subject to change without notice.

Series 80 Mighty Mouse Contacts and Tools


Size #16 Fiber Optic Termini Assembly Procedure

Step 2 Fiber Insertion

1. Fold back strength members and distribute evenly over outer jacket of cable.



2. Carefully insert stripped fiber into terminus until the cable jacket bottoms inside the terminus body.
3. Wipe off any excess epoxy that may emerge from the rear of the terminus upon insertion of the cable.
4. Bare fiber should protrude approximately .15 inches (3.8mm) from the front of the terminus.
5. Be sure that the exterior surfaces of terminus are free of epoxy.



Step 3 Epoxy Curing

6. Using curing oven, carefully position terminated fiber into a cavity of curing block. **NOTE** care must be taken to avoid breaking the protruding fiber.
7. See "Recommended Epoxies and Curing Schedules" (previous page) for cure times.

Step 4 Scribe and Remove Excess Fiber

8. Hold terminus with fiber pointing straight up and lightly score fiber approximately .01 inch (0.3mm) above the ceramic ferrule.
9. Using fiber cleaving tool, gently move the blade across fiber to scribe glass. Do not use a sawing motion.
10. Grasp fiber and pull gently upward until fiber breaks.
11. Carefully discard piece of fiber.

Step 5 Polishing Procedure


12. Clean polishing film, tool, and tip of terminus using distilled water after each step.
13. Dry all parts using lint-free wipes or compressed air.
14. Wipe distilled water onto back of polishing film and place onto rubber pad.

15. Insert terminus into polishing tool. Polish terminus in small figure 8 motions using the following procedures.
16. Visually inspect terminus tip using microscope to prevent overpolishing after each polishing step.
17. Use light pressure through each polishing step.

Step 6 Workmanship Inspection


After completing final polishing step, core area must be free of epoxy, scratches, pits and cracks.

NOTE do not backlight fiber when inspecting for scratches.




Step 7 Install Alignment Sleeve on Socket Terminus

Carefully slide alignment sleeve onto terminus ferrule until seated.




Step 8 Install Protective Sleeve on Socket Terminus

Push on protective metal sleeve until you feel it snap into place.



Step 9 Clean and Install Dust Cap on Socket Terminus

Clean end of terminus and install dust cap over protective cover.



Polishing Steps for Domed PC Polish

Polish Step	Paper Grit Size	# of Figure 8's	Hand Pressure	Polishing Surface	Lubricant
1st Polish	3 micron Silicon Carbide	15-20	Light	90 Durometer Pad	Dry
2nd Polish	3 micron Diamond	10	Light	90 Durometer Pad	Distilled Water
3rd Polish	1 micron Diamond	10	Light	90 Durometer Pad	Distilled Water
4th Polish	0.5 micron Diamond	5	Light	90 Durometer Pad	Distilled Water
5th Polish	Ultra Fine	3	Light	90 Durometer Pad	Distilled Water

Dimensions in Inches (millimeters) are subject to change without notice.

Dry Action Cleaning Tool for Fiber Optic Termini



Dry Action Cleaning Tool—The Fast Fiber Optic End Face Cleaner



The Glenair Dry Action Cleaning Tool is an easy-to-handle fiber optic terminus cleaning device, highly effective at removing oil and dust contamination from pin and socket termini—either inside or outside connector shells. Traditional wet-swab cleaning methods add drying time and can even introduce new contaminants to the polished terminus end-face. The Dry Action Cleaning Tool's novel dry cleaning strand gently sweeps and lifts away dust and residue from the terminus end-face without the problems associated with wet swab methods. The tool features a convenient single-unit configuration and an extendable tip for easy access to installed fiber optic termini—saving time and avoiding potential additional contamination. Choose part number GCLT-H200 for MIL-PRF-28876 connectors.

B

Glenair Part number	Used on
GCLT-H200	2.0MM MIL-PRF-28876
GCLT-HC250	GFOCA (MIL-DTL-83526)
GCLT-H160	MIL-DTL-38999
GCLT-H125	Glenair High Density (GHD), LUXCIS
GCLT-C125	LC, MU
GCLT-C250	SC, ST, FC
GCLT-MPO	MTP, MPO, MT (FEMALE AND MALE)
GCLT-MTC	MT MALE
GCLT-MTC-RE	MT MALE refill cartridge

Effectively Removes:

- Arizona Road Dust (ISO 12103-1)
- Skin Oil Residue
- Salt Water Residue
- Alcohol Residue
- Vegetable Residue
- Hand Lotion
- Distilled Water Residue
- Graphite
- T-Shirt Lint

Features and Benefits

- Simple pushing motion to engage tool
- Audible CLICK to alert the operator when tool is fully engaged
- Repeatable process that eliminates operator error
- No experience required
- Over 525+ cleanings per unit
- Dry cleaning strand eliminates the need for solvents
- Crush resistant to over 250N
- Impact resistant to survive drops over 1.5m

Dimensions in Inches (millimeters) are subject to change without notice.

MIL-PRF-28876

FIBER OPTIC

CONNECTORS AND ACCESSORIES



The tight-tolerance MIL-PRF-28876 interconnect has become the universal standard for Navy shipboard applications. Glenair's qualified connectors deliver all the necessary performance, from precise optical alignment to environmental protection and corrosion resistance. Glenair MIL-PRF-28876 QPL connectors are ready for deployment in shipboard, surface and submarine applications, as well as mission-critical combat communication systems such as mobile tactical shelters. They are specifically geared for upgrade and retrofit applications where extending system life-cycles and reducing cost of ownership are principal requirements. For more information, or for product samples, please consult the factory or visit us at www.glenair.com.



MIL-PRF-28876 Fiber Optic Connectors Selection Guide



MIL-PRF-28876 QPL
Connectors/Accessories

Wall Mount Receptacles		
MIL-PRF-28876	M28876/1 Wall Mount Receptacle without Backshell	M28876/2 Wall Mount Receptacle with Straight Backshell M28876/3 Wall Mount Receptacle with 45° Backshell (not shown) M28876/4 Wall Mount Receptacle with 90° Backshell (not shown)
Jam Nut Mount Receptacles		
MIL-PRF-28876	M28876/11 Jam Nut Mount Receptacle without Backshell	M28876/12 Jam Nut Mount Receptacle with Straight Backshell M28876/13 Jam Nut Mount Receptacle with 45° Backshell (not shown) M28876/14 Jam Nut Mount Receptacle with 90° Backshell (not shown)
Plug Connectors		
MIL-PRF-28876	M28876/6 Plug without Backshell	M28876/7 Plug with Straight Backshell M28876/8 Plug with 45° Backshell (not shown) M28876/9 Plug with 90° Backshell (not shown)
In-Line Receptacles	Wall Mount Receptacle Mounting Gaskets	Dust Covers
MIL-PRF-28876 M28876/5 In-Line Receptacle with Straight Backshell	M28840 and Commercial M28840/24 Mounting Gasket (Mil-Spec) 930-006 Mounting Gasket (commercial)	MIL-PRF-28876 M28876/10 Plug Cover M28876/15 Receptacle Cover

Dimensions in Inches (millimeters) are subject to change without notice.




MIL-PRF-28876 QPL Fiber Optic Connectors M28876/1 through /14 180-040 How to Order




Fiber Optic Connectors

How To Order: Military QPL



How To Order: Glenair Commercial



Dimensions in Inches (millimeters) are subject to change without notice.

MIL-PRF-28876 QPL Fiber Optic Connectors
M28876/1 through /14
180-040
How to Order



MIL-PRF-28876 QPL
Connectors/Accessories

Table I: Commercial Shell Finish Options

Code	Material	Finish
NF	Aluminum Alloy	Cadmium Plate, Olive Drab (1000 Hrs. Salt Spray)
MT*	Aluminum Alloy	Nickel-PTFE Grey (1000 Hrs. Salt Spray)

*MT plating available only with Glenair commercial equivalent part numbers. Consult factory for additional material/finish options.

Table III: Keying Position

Shell Size	Keying Position	A°	B°	C°	D°
11 and 13	0*	-	-	-	-
	1	95	141	208	236
	2	113	156	182	292
	3	90	145	195	252
	4	53	156	220	255
	5	119	146	176	298
	6	51	141	184	242
15 and 23	0*	-	-	-	-
	1	80	142	196	293
	2	135	170	200	310
	3	49	169	200	244
	4	66	140	200	257
	5	62	145	180	280
	6	79	153	197	272

*0 indicates universal keying arrangement and is available on commercial equivalent plug connector only.

Table V: Backshell Designator

Backshell Designator	Max Allowable Cable Diameter by Shell Size			
	A (11)	B (13)	C (15)	F (23)
1	.250 (6.4)	.285 (7.2)	.500 (12.7)	.866 (22.0)
2	.346 (8.8)	.346 (8.8)	.250 (6.4)	1.000 (25.4)
3		.453 (11.5)	.375 (9.5)	.600 (15.2)

Table II: Shell Size and Insert Arrangement

Mil-Spec		Commercial	
Shell Size	Insert Arrangement	Shell Size	Number of Cavities
A	1	11	02
B	1	13	04
C	2	15	06
	1		08
F	2	23	18
	1		31

Consult factory for QPL status

Table IV: Connector Type

Connector Type	Backshell Type	MIL-Spec	Commercial
Wall Mount Receptacle	None	M28876/1	03
	Straight	M28876/2	13
	45°	M28876/3	23
	90°	M28876/4	33
In-Line Receptacle	Straight	M28876/5	15
Plug	None	M28876/6	06
	Straight	M28876/7	16
	45°	M28876/8	26
	90°	M28876/9	36
Jam Nut Receptacle	None	M28876/11	04
	Straight	M28876/12	14
	45°	M28876/13	24
	90°	M28876/14	34

Material and Finish

A. M28876 part numbers supplied standard with Cad plate/olive drab over aluminum alloy. See Table I for commercial plating options.

B. Hardware: Aluminum alloy/chem film, stainless steel/passivate

C. Insert: Aluminum alloy/anodize

D. Seals: Fluorosilicone

Specifications

Backnut retained using thread-locking compound.

Operating Temperature Range: -55° to +125°C.

Tools, Accessories and Assembly Notes

Termini (Not Supplied with Connector):

M29504/14 - Pin terminus, MIL-Spec

M29504/15 - Socket Terminus, MIL-Spec

M29504/3 - Dummy Terminus, MIL-Spec

181-039 - Pin Terminus, MIL-Spec Style

181-040 - Socket terminus, MIL-Spec

Style

181-051 - Dummy Terminus MIL-Spec

Style

Consult factory for appropriate termination and assembly tools/procedures.

Dimensions in Inches (millimeters) are subject to change without notice.



**M28876
180-040
MIL-PRF-28876 Fiber Optic Connectors
Keying Arrangements**

Keying Arrangements for MIL-PRF-28876 (180-040) Fiber Optic Connectors





Table III: Keying Position

Shell Size	Keying Arrangement Designators	A°	B°	C°	D°
11 and 13	0*	-	-	-	-
	1	95	141	208	236
	2	113	156	182	292
	3	90	145	195	252
	4	53	156	220	255
	5	119	146	176	298
	6	51	141	184	242
15 and 23	0*	-	-	-	-
	1	80	142	196	293
	2	135	170	200	310
	3	49	169	200	244
	4	66	140	200	257
	5	62	145	180	280
	6	79	153	197	272

*0 indicates universal keying arrangement and is available on commercial equivalent plug connector only.


Dimensions in Inches (millimeters) are subject to change without notice.

**M28876
180-040
MIL-PRF-28876 Fiber Optic Connectors
Insert Arrangements**



MIL-PRF-28876 QPL
Connectors/Accessories

Insert Arrangements for MIL-PRF-28876 (180-040) Fiber Optic Connectors



Dimensions in Inches (millimeters) are subject to change without notice.




**M28876 (/1, /2, /3, /4)
180-040 (-03, -13, -23, -33)
MIL-PRF-28876 Wall Mount Receptacle Connector
for use with MIL-PRF-29504/14 and /15 Termini**



Wall Mount Receptacle Connector





Receptacle without backshell



**M28876/1 • 180-040-03 WALL MOUNT
RECEPTACLE WITHOUT BACKSHELL**



Receptacle with straight backshell



**M28876/2 • 180-040-13 WALL MOUNT RECEPTACLE
WITH STRAIGHT BACKSHELL**

Dimensions in Inches (millimeters) are subject to change without notice.

M28876 (/1, /2, /3, /4)
180-040 (-03, -13, -23, -33)
MIL-PRF-28876 Wall Mount Receptacle Connector
 for use with MIL-PRF-29504/14 and /15 Termini



Table I: Dimensions

Shell Size	ØA Max	ØB Max	ØC Max	D	E ±.020	F Max.	G Max.	H Max.	J Max.
11	0.750 (19.1)	0.960 (24.4)	0.960 (24.4)	0.750 (19.1)	1.022 (26.0)	6.150 (156.2)	3.540 (89.9)	4.250 (108.0)	4.250 (108.0)
13	0.875 (22.2)	1.085 (27.6)	1.085 (27.6)	0.843 (21.4)	1.137 (28.9)	6.220 (158.0)	3.580 (90.9)	4.250 (108.0)	4.250 (108.0)
15	1.062 (27.0)	1.255 (31.9)	1.257 (31.9)	0.968 (24.6)	1.257 (31.9)	6.500 (165.1)	3.850 (97.8)	4.500 (114.3)	4.500 (114.3)
23	1.500 (38.1)	1.695 (43.1)	1.763 (44.8)	1.281 (32.5)	1.718 (43.6)	7.500 (190.5)	5.000 (127.0)	5.000 (127.0)	5.000 (127.0)






TABLE II: Dimension Panel Cutout, Wall Mount Receptacles

Shell Size	Ø X ± .005 (0.13)	Y ± .005 (0.13)
11	.812 (20.6)	.750 (19.1)
13	.937 (23.8)	.843 (21.4)
15	1.124 (28.6)	.968 (24.6)
23	1.562 (39.7)	1.281 (32.5)

Dimensions in Inches (millimeters) are subject to change without notice.


M28876

MIL-PRF-28876 QPL jam nut receptacle connector




Shell Size	Table I						
	G Max	H ± .010 (0.3)	J ± .005 (0.1)	Ø K ± .005 (0.1)	Ø C Max	Ø L Max	Ø A Max
11	1.290 (32.8)	1.264 (32.1)	.848 (21.5)	.885 (22.5)	.960 (24.4)	.960 (24.4)	.750 (19.1)
13	1.435 (35.9)	1.389 (35.3)	.973 (24.7)	1.010 (25.7)	1.085 (27.6)	1.085 (27.6)	.875 (22.2)
15	1.650 (41.9)	1.577 (40.1)	1.160 (29.5)	1.198 (30.4)	1.255 (31.9)	1.255 (31.9)	1.062 (27.0)
23	2.093 (53.2)	2.004 (50.9)	1.593 (40.5)	1.635 (41.5)	1.695 (43.1)	1.763 (44.8)	1.500 (38.1)


Receptacle without backshell



Recommended Panel Cutout
(Jam Nut Mounting)
As Viewed from Face of Panel



**04 - JAM NUT MOUNT RECEPTACLE
WITHOUT BACKSHELL
M28876/11 • 180-040 (-04)**




**M28876/12 • 180-040 (-14) JAM NUT MOUNT RECEPTACLE
WITH STRAIGHT BACKSHELL**


180-040 (-04, -14, -24, -34)
MIL-PRF-28876 Jam Nut Mount Receptacle Connector
 for use with MIL-PRF-29504/14 and /15 Termini



MIL-PRF-28876
Connectors



**M28876/14 180-040 (-34) JAM NUT
MOUNT, WITH 90° BACKSHELL,
RECEPTACLE**



**M28876/13 180-040 (-24) JAM
NUT MOUNT, WITH
45° BACKSHELL, RECEPTACLE**




**M28876 (/6, /7, /8, /9)
180-040 (-06, -16, -26, -36)
MIL-PRF-28876 Plug Connector
for use with MIL-PRF-29504/14 and /15 Termini**



Plug Connector





Plug without backshell



**M28876/6 • 180-040-06
PLUG WITHOUT BACKSHELL**



Plug with straight backshell



M28876/7 • 180-040-16 PLUG WITH STRAIGHT BACKSHELL


Dimensions in Inches (millimeters) are subject to change without notice.

M28876 (/6, /7, /8, /9)
180-040 (-06, -16, -26, -36)
MIL-PRF-28876 Plug Connector
for use with MIL-PRF-29504/14 and /15 Termini




Table I: Dimensions							
Shell Size	ØA Max	ØB Max	ØC Max	D Max	E Max	F Max	G Max.
11	1.028 (26.1)	0.960 (24.4)	0.960 (24.4)	6.090 (154.7)	3.540 (89.9)	4.190 (106.4)	4.250 (108.0)
13	1.141 (29.0)	1.085 (27.6)	1.085 (27.6)	6.160 (156.5)	3.580 (90.9)	4.190 (106.4)	4.250 (108.0)
15	1.263 (32.1)	1.255 (31.9)	1.255 (31.9)	6.440 (163.6)	3.850 (97.8)	4.440 (112.8)	4.500 (114.3)
23	1.705 (43.3)	1.695 (43.1)	1.763 (44.8)	7.350 (186.7)	5.000 (127.0)	4.850 (123.2)	5.000 (127.0)

All dimensions are
per M28876/6



All dimensions are
per M28876/6



Dimensions in Inches (millimeters) are subject to change without notice.





**M28876 (/5)
In-Line Receptacle**
for use with MIL-PRF-29504/14 and /15 Termini



In-Line Receptacle Connector

Table I: Dimensions				
Shell Size	ØA Max	ØB Max	ØC Max	D
11	0.750 (19.1)	0.960 (24.4)	0.963 (24.5)	0.768 (19.5)
13	0.875 (22.2)	1.085 (27.6)	1.088 (27.6)	0.893 (22.7)
15	1.062 (27.0)	1.255 (31.9)	1.275 (32.4)	1.080 (27.4)
23	1.500 (38.1)	1.763 (44.8)	1.719 (43.7)	1.518 (38.6)



Dimensions in Inches (millimeters) are subject to change without notice.


M28840 (/24) and 930-006
Wall-Mount Receptacle Mounting Gaskets
 for use with MIL-PRF-28876 (/1, /2, /3, /4)
 and 180-040 (-03, -13, -23, -33) Commercial Connectors



MIL-PRF-28876 QPL
 Connectors/Accessories

MIL-PRF Wall-Mount Receptacle Mounting Gasket


Shell Size	A	B Dia.	C	D Dia.
A (11)	.760 (19.30) .740 (18.80)	.766 (19.46) .750 (19.05)	1.039 (26.39) 1.023 (25.98)	.130 (3.30) .110 (2.79)
B (13)	.853 (21.67) .833 (21.16)	.891 (22.63) .875 (22.22)	1.154 (29.31) 1.138 (28.90)	
C (15)	.978 (24.84) .958 (24.33)	1.078 (27.38) 1.062 (26.97)	1.274 (32.36) 1.258 (31.95)	
D (17)	1.025 (26.04) 1.005 (25.53)	1.141 (28.98) 1.125 (28.58)	1.399 (26.39) 1.383 (35.13)	
E (19)	1.150 (29.21) 1.130 (28.70)	1.338 (33.98) 1.312 (33.32)	1.524 (38.71) 1.508 (38.30)	
F (23)	1.291 (32.79) 1.271 (32.28)	1.516 (38.51) 1.500 (38.10)	1.734 (44.04) 1.718 (43.64)	
G (25)	1.402 (35.61) 1.382 (35.10)	1.641 (41.68) 1.625 (41.28)	1.834 (46.58) 1.818 (46.18)	.157 (3.99) .137 (3.48)
H (29)	1.578 (40.08) 1.558 (39.57)	1.891 (48.03) 1.875 (47.62)	2.154 (54.71) 2.138 (54.30)	.183 (4.65) .163 (4.14)
J (33)	1.744 (44.30) 1.724 (43.79)	2.078 (52.78) 2.062 (52.37)	2.344 (59.54) 2.328 (59.13)	



Commercial Wall-Mount Receptacle Mounting Gasket

Table I: Material	
Symbol	Material Description
F	Fluorosilicone
M	Silver Plated Glass Filled Silicone
N	Neoprene

Shell Size	A ± .010	Ø B +.016 -.000	C .016 -.000	Ø D ± .010	F Radius ± .010
11	.750	.750	1.023	.120	.141
13	.843	.875	1.138		
15	.968	1.062	1.258		
17	1.015	1.125	1.383		
19	1.140	1.312	1.508		
23	1.281	1.500	1.718	.147	.188
25	1.392	1.625	1.818		
29	1.568	1.875	2.138		
33	1.734	2.062	2.328		




Dimensions in Inches (millimeters) are subject to change without notice.




Plug and receptacle dust covers

Table I: Cover Type		
Connector	MIL-Spec Basic P/N	Glenair Commercial Basic P/N
Plug	M28876/10	660-072
Receptacle	M28876/15	660-073

**M28876/10 • 660-072
Plug Cover**



**M28876/15 • 660-073
Receptacle Cover**



**M28876/10 and M28876/15
660-072 and 660-073
MIL-PRF-28876 Dust Covers**



MIL-PRF-28876
Connectors

How to order: Military QPL




Table II: Material and Finish (Commercial)		
Code	Material	Finish Description
M	Aluminum Alloy	Electroless Nickel
NF		Cadmium, Olive Drab
MT		Nickel-PTFE, Grey
ZR		Zinc-Nickel, Black
Consult Factory for Additional Options		

Refer to Appendix for material/finish details

*MT plating available only with Glenair commercial equivalent part numbers

Table III: Shell Size	
Symbol	A Thread
A	.750-0.1P-0.2L-D.S.
B	.875-0.1P-0.2L-D.S.
C	1.062-0.1P-0.2L-D.S.
F	1.500-0.1P-0.2L-D.S.

How To Order: Glenair Commercial




Table VI: Attachment Type (Commercial)			
Shell Size	Attachment Type	Connector Type	Code
A	Ring	Plug	13
		Recp	15
B	Ring	Plug	15
		Recp	17
C	Ring	Plug	17
		Recp	20
F	Ring	Plug	23
		Recp	27
All	Fastener (Eyelet)	All	01




Table IV: Lanyard/Attachment (MIL-Spec)	
Symbol	Description
A	Chain (Sash) with Fastener (Eyelet) Attachment
B	Chain (Sash) with Ring Attachment
C	Wire Rope with Fastener (Eyelet) Attachment
D	Wire Rope with Ring Attachment
E	Without Chain (Sash) or Wire Rope

Table V: Lanyard Type (Commercial)	
Symbol	Type
H	Wire Rope, Coated
S	Chain (Sash), Passivated
N	No Lanyard
Consult Factory for Additional Options	

MIL-DTL-28840

TOOLS · CONTACTS · CONNECTORS AND ACCESSORIES

NAVY QPL COMPONENT SELECTION GUIDE

 Crimping Tools	 Insertion & Removal Tools	 Pin Contact	 Socket Contact
M22520/34-01 Basic Crimp Tool M22520/34-02 Positioner M22520/35 Gage	M81969/33-01 Straight Insertion Tool M81969/33-02 Offset Insertion Tool M81969/34-01 Removal Tool	M39029/83 Standard Duty Electrical Pin Contact	M39029/84 Standard Duty Electrical Socket Contact
 Environmental Backshells	 EMI/RFI Environmental Backshells	 Connector Sockets	 "E" Nuts
			 Strain Reliefs
M28840/6 B Straight M28840/9 B 45° M28840/8 B 90°	M28840/6 A Straight M28840/8 A 90° M28840/9 A 45°	600G005*	M28840/23
			M28840/1 Straight M28840/3 45° M28840/2 90°
 Dummy Stowage Receptacles	 Protective Plug Covers	 Protective Receptacle Covers	 Jam Nuts
			 Mounting Flanges and Gaskets
			 MIL-PRF-24758A Conduit Fittings
M28840/7	M28840/15	M28840/13	MS3186
			M28840/24 Gasket
			M24758-14 Straight (M24758/14 Straight.)* M28840/5 Straight • M28840/25 90° • M28840/27 45° • M28840/30 Coupling



Qualified Military Standard Electrical Connectors and Accessories for Shipboard Applications

Ideal for All Rugged Environmental Applications

The standard connector and backshell series for shipboard use, MIL-DTL-28840 offers high-density insert arrangement and high-shock performance. Glenair's qualified product line is fully tooled and highly available.

The MIL-DTL-28840 features RFI/EMI shielding, scoop-proof shells and corrosion resistant materials and finishes. In addition to all the connector types and styles, Glenair makes all the backshell accessory slash numbers as well. The addition of the MIL-DTL-28840 connector product line is part of Glenair's total commitment to meeting all your shipboard interconnect requirements. So, if a rugged, environmental M28840 solution is in your future, think Glenair—from connectors to accessories.

PRODUCT FEATURES

- High Density, Scoop Proof Insert Arrangements
- Flange Mount, Box Mount, Jam-Nut and In-Line Receptacles
- Straight, 45° and 90° Strain Reliefs and Backshell Assemblies
- Sav-Con[®] Connector Savers
- MIL-DTL-28840 Qualified
- Additional Glenair Commercial Part Numbers with Features Not Available in the Mil-Spec

MIL-DTL-28840 In a Nutshell:

MIL-DTL-28840 connectors were developed for the Navy for use in shipboard applications. They are a high density, environmental, circular connector series utilizing a high shock, threaded coupling system with front release crimped contacts. Note the splined backshell interface and the integrated wire sealing grommet that both add to the environmental and mechanical performance of this ruggedized connector.



Dimensions in Inches (millimeters) are subject to change without notice.



MIL-DTL-28840

Shipboard Electrical Connectors

Performance Specifications, Class and Finishes

Performance Specifications

Current Rating (Maximum)	Size #20 Contact; 20AWG 7.5A, 22AWG 5.0A, 28AWG 1.5A, 30AWG 1.0A
Test Voltage (Dielectric Withstanding Voltage)	1000 VAC RMS at sea level. Test per EIA-364-20
Insulation Resistance	5000 megohms minimum (at ambient temperature) per EIA-364-21
Contact Resistance	Per SAE-AS39029
Operating Temperature	-55° C. to +200° C.
Immersion	per test method EIA-364-09
Shock	in accordance with MIL-S-901 grade A
Vibration	per EIA-364-28 test procedure
Magnetic Permeability	2.0 μ (Aluminum), 5.0 μ (Stainless Steel) maximum; ASTM-A342/A342M

Materials and Finishes

Shells, Coupling Nuts, Jam Nuts	Aluminum alloy per ASTM B211, or stainless steel per AMS-QQ-S-763
Contacts	Copper alloy, 50 μ inch gold plated per ASTM B488 Type 3, Code C, Class 1,27 over nickel underplate per QQ-N-290 Class 2. Socket contact hood: stainless steel, passivated.
Insulators	High Grade Engineering Plastic per ASTM D5948
Contact Retention Clip	Beryllium copper
Shells, Coupling Nuts, Jam Nut Plating Finish	Stainless Steel, Black Cadmium plated
Grommet, Seal	Blended elastomer, 30% silicone per ZZ-R-765, 70% fluorosilicone per MIL-R-25988

Contact Code	Type	Contact Spec.	Contact Size	Acceptable Wire Size	Outside Diameter of Finished Wire	
					Minimum	Maximum
F	Pin	SAE-AS39029/83-508	20-20	24	.040 (1.02)	.070 (1.78)
G	Socket	SAE-AS39029/84-509		22		
				20		
P	Pin	SAE-AS39029/83-450	20-22	26		
S	Socket	SAE-AS39029/84-452		24		
				22		
D	Pin	SAE-AS39029/83-451	20-28	32		
E	Socket	SAE-AS39029/84-453		30		
				28		

Notes

To achieve sealing, wires must be built up to finished wire diameter.
In accordance with MIL-DTL-24643 and MIL-DTL-16878.

Dimensions in Inches (millimeters) are subject to change without notice.

**M22520/34-01, M22520/34-02, M22520/35,
M81969/33-01, M81969/33-02, and M81969/34-01**
Contact Crimping, Insertion and Removal Tools
for MIL-DTL-28840 Connectors



MIL-DTL-28840
Introduction


M22520/34-01 Basic Crimp Tool

Qualified to M22520/34-01, this crimp tool prevents improper crimps and overcrimping and is based on the AFM8 miniature adjustable crimp tool. It performs a modified eight impression crimp with a precision cycle controlled ratcheting mechanism for gas-tight wire terminations and excellent tensile strength. Also featured is a four-step crimp-depth selector knob, and is designed for use with the M22520/34-02 bayonet-type Positioner. Gaging is accomplished with the M22520/35 "go/No-Go" Gage. The adjustment wheel has eight settings. Check calibration with the M22520/35 gage. Length is 6.75 inches, weight is approximately 10 oz.



M22520/34-02 Positioner

This bayonet-type positioner locates and holds contacts at the correct position for crimping with the M22520/34-01 Basic Crimp Tool. The face plate shows the correct tool settings.



M22520/35 Gage


Periodic Gaging is recommended to ensure accurate calibration, and is easily accomplished by setting the tool selector knob to the proper position and checking the indenter closure with the M22520/35 "Go/No-Go" Gage. Color coded anodized aluminum with stainless steel probes.

Insertion and Removal Tools



M81969/33-01 Straight Insertion Tool

The M81969/33-01 Straight Insertion Tool is approved for use on MIL-DTL-28840 connectors and features an anodized aluminum handle and stainless steel insertion tip.



M81969/33-02 Offset Insertion Tool

Approved for use on MIL-DTL-28840 connectors, the M81969/33-02 Offset Insertion Tool features an anodized aluminum handle and stainless steel offset insertion tip.



M81969/34-01 Removal Tool

Designed and approved for removal of contacts and in MIL-DTL-28840 connectors, the M81969/34-01 Removal Tool's anodized aluminum handle and stainless steel tip will provide many years of reliable service.

Dimensions in Inches (millimeters) are subject to change without notice.

Contact Insertion

1. Tools:

Be sure that all proper assembly tools are on hand and properly calibrated (Figure 1). See previous page for complete descriptions of required tools.


1



2. Stripping:

Strip wire ends to 3/16" for 20-32 AWG, taking care not to nick or cut wire strands (Figure 2). Hold insulation and twist strands to eliminate any splaying.

2




3. Wire Insertion:

Insert wire into crimp well of contact. **Do Not Force.** Wire strands must be visible through inspection hole (Figure 3).

Inspection Hole


3



4. Crimping:

Using crimp tool and positioner noted above, insert wire and contact into locator jaws. Squeeze tool handle completely until ratchet releases. Remove wired contact from tool (Figure 4).

4



5. Backshell Preparation:

Slide backshell/strain relief over jacketed cable or wires in proper order for re-assembly. Consult Glenair backshell catalog or contact factory for proper jacketed cable assembly (Figure 5).

5



6. Contact Preparation:

Slide wired contact into insertion tool of choice so that the tip of the tool butts against the shoulder of the contact (Figure 6).

6




Dimensions in Inches (millimeters) are subject to change without notice.

MIL-DTL-28840 Connector Contact Insertion/Extraction Instructions



7. Insertion of Contacts:

Insert wired contacts and tool into contact cavity until contact “clicks” into retention clip (Figure 7). A straight pull on the wire will assure the contact is properly seated. Note: Isopropyl alcohol may be used as a lubricant. Use sparingly.



8. Assembly:

After all contacts are inserted, assemble backshell or strain relief according to Glenair backshell catalog instructions.

Contact Extraction

1. Contact Extraction:



Remove backshell or strain relief from connector.

2. Contact Extraction:

MIL-DTL-28840 connector contacts are extracted from the rear but released from the front of the connector. Using an extraction tool, slide tool tip into front of contact cavity (mating face of connector, figure 8) until tool tip engages against contact retention clip. Push plunger with minimum force to release contact (Figure 9). Note: Isopropyl alcohol may be used as a lubricant. Use sparingly.

3. Contact Extraction:

Pull wired contact from rear grommet of connector.



Contact Replacement:

After replacing contact, re-insert starting with assembly instruction number 7.


Dimensions in Inches (millimeters) are subject to change without notice.




MIL-DTL-28840 Connectors Standard Insert Arrangements




Shell Size 11
7 Contacts




Shell Size 13
12 Contacts




Shell Size 15
21 Contacts




Shell Size 17
31 Contacts




Shell Size 19
42 Contacts




Shell Size 23
64 Contacts



Shell Size 25
92 Contacts



Shell Size 29
121 Contacts





Shell Size 33
155 Contacts

Dimensions in Inches (millimeters) are subject to change without notice.

MIL-DTL-28840 Polarization Keyways



MIL-DTL-28840
Introduction



D

Table I: Panel Cutout

Designator	P Dia.	LL Flat	O Ref. Mtg. Hole
A (11)	.890 .880	.853 .843	.812
B (13)	1.015 1.005	.978 .968	.937
C (15)	1.203 1.193	1.165 1.155	1.124
D (17)	1.265 1.255	1.228 1.218	1.187
E (19)	1.453 1.443	1.415 1.405	1.374
F (23)	1.640 1.630	1.603 1.593	1.562
G (25)	1.765 1.755	1.728 1.718	1.687
H (29)	1.953 1.943	1.915 1.905	1.874
J (33)	2.140 2.130	1.103 2.093	2.062

Table II: Alternate Keyways

Designator	Key and Keyway Arrangement	AR° or AP° BSC	BR° or BP° BSC	CR° or CP° BSC	DR° or DP° BSC
A (11) B (13)	1	95	141	208	236
	2	113	156	182	292
	3	90	145	195	252
	4	53	156	220	255
	5	119	146	176	298
	6	51	141	184	242
C (15) D (17)	1	80	142	196	293
	2	135	170	200	310
	3	49	169	200	244
	4	66	140	200	257
	5	62	145	180	280
	6	79	153	197	272
E (19) F (23) G (25) H (29) J (33)	1	80	142	196	293
	2	135	170	200	310
	3	49	169	200	244
	4	66	140	200	257
	5	62	145	180	280
	6	79	153	197	272

Dimensions in Inches (millimeters) are subject to change without notice.


M28840

Standard Pin Crimp Contact for MIL-DTL-28840 Connectors



Mating End Size	Wire Accomodation	Military Part Number	Glenair Part Number
20	28-32 AWG	M39029/83-451	850-004-20-451
20	22-26 AWG	M39029/83-450	850-004-20-450
20	20-24 AWG	M39029/83-508	850-004-20-508

D



Material and Finish

Pin Contact: copper alloy per ASTM B197, 50 microinches gold plated per ASTM B488 Type II Code C Class 1,27 over nickel plate per QQ-N-290 Class 2, 50-100 microinches. Approved for space flight.

Dimensions in Inches (millimeters) are subject to change without notice.

**M39029/83
850-004
Standard Duty Electrical Pin Contact**



MIL-DTL-28840
Introduction

Table I: Contact Dimensions

Size	Part Number	Military Number	Ø B	Ø C	Color Bands		
					1st	2nd	3rd
20	850-004-20-508	M39029/83-508	.050 .048	.032 .026	Green	Black	Grey
20	850-004-20-450	M39029/83-450	.0355 .0335	.032 .026	Yellow	Green	Black
20	850-004-20-451	M39029/83-451	.0200 .0180	.022 .018	Yellow	Green	Brown

Table II: Tool Compatibility

Size	Part Number	Military Number	AWG Handling	Crimp Tool	Positioner	Insertion Tool	Extraction Tool
20	850-004-20-508	M39029/83-508	20, 22, 24	M22520/34-01	M22520/34-02	M81969/33-01	M81969/34-01
20	850-004-20-450	M39029/83-450	22, 24, 26	M22520/34-01	M22520/34-02	M81969/33-01	M81969/34-01
20	850-004-20-451	M39029/83-451	28, 30, 32	M22520/34-01	M22520/34-02	M81969/33-01	M81696/34-01

D

Test

Performance Specifications

Durability	(meets SAE-AS39029, paragraph 3.5.9) No electrical or mechanical defects after 500 cycles of engagement and disengagement
Contact Retention	(meets MIL-DTL-38999, paragraph 3.23) The axial displacement of the contact shall not exceed .012 inch (0.30 mm). No damage to contacts or inserts shall result.
Pin Engagement End	(meets SAE-AS39029 paragraph 3.4.1) Unless otherwise specified, the mating end of all contacts (except size 22 and smaller) shall be formed with an approximate spherical radius.
Permeability	(meets SAE-AS39029, paragraph 3.5.1) When tested as specified in paragraph 4.7.2, the relative magnetic permeability of the contact shall be no greater than 2.0.
Vibration	(meets SAE-AS39029, paragraph 3.5.10) When contacts are tested as specified in paragraph 4.7.11, there shall be no electrical discontinuity of 1 microsecond or greater. There shall be no defects detrimental to the mechanical or electrical performance.
Salt Spray (corrosion)	(meets SAE-AS39029, paragraph 3.5.12) When tested as specified in 4.7.13, mated contacts shall withstand 48 hours of salt spray conditioning without defects detrimental to the mechanical or electrical performance.
Temperature life	(meets SAE-AS39029, paragraph 3.5.13) When tested as specified in paragraph 4.7.14, mated contacts shall withstand temperature conditioning for 1,000 hours without defects detrimental to mechanical or electrical performance. There shall be no diffusion/migration of the base metal through the contact outer plating. Class A - Maximum operating temperature +125°C. per paragraph 1.2.2
Dielectric withstanding voltage	(meets SAE-AS39029, paragraph 3.5.19) When tested as specified in paragraph 4.7.20, crimped contacts shall show no evidence of breakdown or flashover.
Workmanship	(meets SAE-AS39029, paragraph 3.7) Contacts shall be processed in such a manner as to be uniform in quality and shall be free from foreign material and burrs or sharp corners that might damage the connector or affect mating of the contacts. Burrs and sharp edges shall be removed 0.005 inch maximum.

Dimensions in Inches (millimeters) are subject to change without notice.


M28840

Standard Socket Crimp Contact for MIL-DTL-28840 Connectors



Mating End Size	Wire Accomodation	Military Part Number	Glenair Part Number
20	28-32 AWG	M39029/84-453	850-005-20-453
20	22-26 AWG	M39029/84-452	850-005-20-452
20	20-24 AWG	M39029/84-509	850-005-20-509

D



Material and Finish

Socket Contact: Copper alloy per ASTM B197, 50 microinches gold plated per ASTM B488
Type II Code C Class 1, 27 over nickel plate per QQ-N-290 Class 2, 50-100 microinches.
Approved for space flight.

Socket Contact Hood: Stainless steel, passivated per AMS-QQ-P-35. Approved for space flight.

Dimensions in Inches (millimeters) are subject to change without notice.

**M39029/84
850-005
Standard Duty Electrical Socket Contact**



MIL-DTL-28840
Introduction

Table I: Contact Dimensions

Size	Part Number	Military Number	Ø B	Ø C	Color Bands		
					1st	2nd	3rd
20	850-005-20-509	M39029/84-509	.050 .048	.032 .026	Green	Black	White
20	850-005-20-452	M39029/84-452	.0355 .0335	.032 .026	Yellow	Green	Red
20	850-005-20-453	M39029/84-453	.0200 .0180	.022 .018	Yellow	Green	Orange

Table II: Tool Compatibility

Size	Part Number	Military Number	AWG Handling	Crimp Tool	Positioner	Insertion Tool	Extraction Tool
20	850-005-20-509	M39029/84-509	20, 22, 24	M22520/34-01	M22520/34-02	M81969/33-01	M81969/34-01
20	850-005-20-452	M39029/84-452	22, 24, 26	M22520/34-01	M22520/34-02	M81969/33-01	M81969/34-01
20	850-005-20-453	M39029/84-453	28, 30, 32	M22520/34-01	M22520/34-02	M81969/33-01	M81969/34-01

D

Test

Performance Specifications

Durability	(meets SAE-AS39029, paragraph 3.5.9) No electrical or mechanical defects after 500 cycles of engagement and disengagement
Contact Retention	(meets MIL-DTL-38999, paragraph 3.23) The axial displacement of the contact shall not exceed .012 inch (0.30 mm). No damage to contacts or inserts shall result.
Pin Engagement End	(meets SAE-AS39029 paragraph 3.4.1) Unless otherwise specified, the mating end of all contacts (except size 22 and smaller) shall be formed with an approximate spherical radius.
Permeability	(meets SAE-AS39029, paragraph 3.5.1) When tested as specified in paragraph 4.7.2, the relative magnetic permeability of the contact shall be no greater than 2.0.
Vibration	(meets SAE-AS39029, paragraph 3.5.10) When contacts are tested as specified in paragraph 4.7.11, there shall be no electrical discontinuity of 1 microsecond or greater. There shall be no defects detrimental to the mechanical or electrical performance.
Salt Spray (corrosion)	(meets SAE-AS39029, paragraph 3.5.12) When tested as specified in 4.7.13, mated contacts shall withstand 48 hours of salt spray conditioning without defects detrimental to the mechanical or electrical performance.
Temperature life	(meets SAE-AS39029, paragraph 3.5.13) When tested as specified in paragraph 4.7.14, mated contacts shall withstand temperature conditioning for 1,000 hours without defects detrimental to mechanical or electrical performance. There shall be no diffusion/migration of the base metal through the contact outer plating. Class A - Maximum operating temperature +125°C. per paragraph 1.2.2
Dielectric withstanding voltage	(meets SAE-AS39029, paragraph 3.5.19) When tested as specified in paragraph 4.7.20, crimped contacts shall show no evidence of breakdown or flashover.
Workmanship	(meets SAE-AS39029, paragraph 3.7) Contacts shall be processed in such a manner as to be uniform in quality and shall be free from foreign material and burrs or sharp corners that might damage the connector or affect mating of the contacts. Burrs and sharp edges shall be removed 0.005 inch maximum.

Dimensions in Inches (millimeters) are subject to change without notice.

MIL-DTL-28840

SHIPBOARD ELECTRICAL CONNECTORS

THE RUGGEDIZED, ENVIRONMENTAL MIL-DTL-28840 SOLUTION




Glenair offers a fully tooled, high availability line of MIL-DTL-28840 shipboard electrical connectors. Developed for Navy shipboard applications, the MIL-DTL-28840 is a high-density environmental circular connector series which utilizes a high shock threaded coupling system, front release crimp contacts, RFI/EMI shielding, scoop-proof shells, and corrosion resistant materials and finishes. Glenair manufactures all of the connector types and styles, as well as all of the backshell accessory slash numbers—the full range of MIL-DTL-28840 QPL connectors and accessories.



M28840/1 Straight Strain Relief



MIL-DTL-28840
Electrical Connectors




Designator	A Thread Class 2B	B Max. Diameter	C Max.	D Max.	Screw Size Ref.	Cable Entry	
						Min.	Max.
A (11)	.750-20 UNEF	1.028 (26.11)	1.091 (27.71)	.903 (22.94)	.114-40	.177 (4.50)	.286 (7.26)
B (13)	.875-20 UNEF	1.141 (28.98)	1.091 (27.71)	.977 (24.82)	.114-40	.177 (4.50)	.286 (7.26)
C (15)	1.000-20 UNEF	1.263 (32.08)	1.091 (27.71)	1.151 (29.24)	.114-40	.250 (6.35)	.416 (10.57)
D (17)	1.125-18 UNEF	1.387 (35.23)	1.206 (30.63)	1.281 (32.54)	.114-40	.291 (7.39)	.476 (12.09)
E (19)	1.250-18 UNEF	1.513 (38.43)	1.320 (33.53)	1.406 (35.71)	.114-40	.348 (8.84)	.626 (15.90)
F (23)	1.438-18 UNEF	1.703 (43.26)	1.445 (36.70)	1.576 (40.03)	.134-32	.429 (10.90)	.831 (21.11)
G (25)	1.562-18 UNEF	1.825 (46.36)	1.570 (39.88)	1.666 (42.32)	.134-32	.523 (13.28)	.956 (24.28)
H (29)	1.875-16 UN	2.143 (54.43)	1.721 (43.71)	2.046 (51.97)	.134-32	.643 (16.33)	1.081 (27.46)
J (33)	2.062-16 UNS	2.329 (59.16)	1.908 (48.46)	2.209 (56.11)	.162-32	.704 (17.88)	1.187 (30.15)

Dimensions in Inches (millimeters) are subject to change without notice.



E



M28840/2 90° Strain Relief



Material and Finish
W - Aluminum, Cadmium Plate,
 O.D. over Electroless Nickel
D - Corrosion Resistant Steel,
 Cadmium Plate, Black




Designator	A Thread Class 2B	B Max. Diameter	C Max.	D Max.	Screw Size Ref.	Cable Entry	
						Min.	Max.
A (11)	.750-20 UNEF	1.028 (26.11)	1.071 (27.20)	.929 (23.60)	.114-40	.177 (4.50)	.286 (7.26)
B (13)	.875-20 UNEF	1.141 (28.98)	1.071 (27.20)	.929 (23.60)	.114-40	.177 (4.50)	.286 (7.26)
C (15)	1.000-20 UNEF	1.263 (32.08)	1.280 (32.51)	1.056 (26.82)	.114-40	.250 (6.35)	.416 (10.57)
D (17)	1.125-18 UNEF	1.387 (35.23)	1.392 (35.36)	1.233 (31.32)	.114-40	.291 (7.39)	.476 (12.09)
E (19)	1.250-18 UNEF	1.513 (38.43)	1.517 (38.53)	1.296 (32.92)	.114-40	.348 (8.84)	.626 (15.90)
F (23)	1.438-18 UNEF	1.703 (43.26)	1.642 (41.71)	1.358 (34.49)	.134-32	.429 (10.90)	.831 (21.11)
G (25)	1.562-18 UNEF	1.825 (46.36)	1.767 (44.88)	1.420 (36.07)	.134-32	.523 (13.28)	.956 (24.28)
H (29)	1.875-16 UN	2.143 (54.43)	1.905 (48.39)	1.634 (41.50)	.134-32	.643 (16.33)	1.081 (27.46)
J (33)	2.062-16 UNS	2.329 (59.16)	1.968 (49.99)	1.859 (47.22)	.162-32	.704 (17.88)	1.187 (30.15)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/3 45° Strain Relief



MIL-DTL-28840
Electrical Connectors





E

Designator	A Thread Class 2B	B Max. Diameter	C Max.	D Max.	E Max.	Screw Size Ref.	Cable Entry	
							Min.	Max.
A (11)	.750-20 UNEF	1.028 (26.11)	1.091 (27.71)	.929 (23.60)	.903 (22.94)	.114-40	.177 (4.50)	.286 (7.26)
B (13)	.875-20 UNEF	1.141 (28.98)	1.091 (27.71)	.929 (23.60)	.977 (24.82)	.114-40	.177 (4.50)	.286 (7.26)
C (15)	1.000-20 UNEF	1.263 (32.08)	1.091 (27.71)	1.056 (26.82)	1.151 (29.24)	.114-40	.250 (6.35)	.416 (10.57)
D (17)	1.125-18 UNEF	1.387 (35.23)	1.206 (30.63)	1.233 (31.32)	1.281 (32.54)	.114-40	.291 (7.39)	.476 (12.09)
E (19)	1.250-18 UNEF	1.513 (38.43)	1.320 (33.53)	1.296 (32.92)	1.406 (35.71)	.114-40	.348 (8.84)	.626 (15.90)
F (23)	1.438-18 UNEF	1.703 (43.26)	1.445 (36.70)	1.358 (34.49)	1.576 (40.03)	.134-32	.429 (10.90)	.831 (21.11)
G (25)	1.562-18 UNEF	1.825 (46.36)	1.570 (39.88)	1.420 (36.07)	1.666 (42.32)	.134-32	.523 (13.28)	.956 (24.28)
H (29)	1.875-16 UN	2.143 (54.43)	1.721 (43.71)	1.634 (41.50)	2.046 (51.97)	.134-32	.643 (16.33)	1.081 (27.46)
J (33)	2.062-16 UNS	2.329 (59.16)	1.908 (48.46)	1.859 (47.22)	2.209 (56.11)	.162-32	.704 (17.88)	1.187 (30.15)

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/4 Metal Core Conduit





Size	Nominal Conduit Inside Diameter	A Diameter Over Shield ± .010 (0.25)	L	B Diameter Max Over Jacket
03	.375 (9.52)	.525 (13.34)	50 ft. Max.	.688 (17.47)
04	.500 (12.70)	.650 (16.51)		.812 (20.62)
05	.625 (15.87)	.765 (19.43)		.937 (23.79)
06	.750 (19.05)	.925 (23.50)		1.078 (27.38)
08	1.00 (25.40)	1.210 (30.73)		1.437 (36.49)
10	1.25 (31.75)	1.455 (36.96)		1.695 (43.05)
12	1.500 (38.10)	1.725 (43.82)		1.956 (49.68)
16	2.000 (50.80)	2.200 (55.88)		2.469 (62.71)

Dimensions in Inches (millimeters) are subject to change without notice.


M28840/5 Backshell for Metal Core Conduit



MIL-DTL-28840
Electrical Connectors



STYLE A - EMI/Non-Environmental
(Plain Conduit)



STYLE B - EMI/Environmental
(Jacket Conduit)

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/5 Backshell for Metal Core Conduit

Dash Number	Designator	Conduit Size	L ± .12 (± 3.05)	Working Room Ref.	V Thread Class 2*	M Max. Diameter	Y Max. Diameter
01	A (11)	03	1.75 (44.45)	1.00 (25.4)	1.00-20 UNEF	1.12 (28.45)	1.19 (30.23)
02	B (13)				1.188-18 UNEF	1.25 (31.8)	1.38 (35.1)
03		C (15)			1.000-20 UNEF	1.12 (28.5)	1.19 (30.23)
04	1.188-30 UNEF				1.25 (31.8)	1.38 (35.1)	
05	1.438-18 UNEF				1.43 (36.3)	1.63 (41.4)	
06	1.750-18 UNS				1.62 (41.2)	1.94 (49.3)	
07	D (17)	06	3.00 (76.2)				
08		05	2.25 (57.15)	1.50 (38.10)	1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
09					1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
10	08	2.00 (50.80)		2.00-18 UNS	1.81 (46.0)	2.19 (55.6)	
11	E (19)	05		1.50 (38.10)	1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
12					1.750-18 UNEF	1.62 (41.2)	1.94 (49.3)
13					2.00-18 UNS	1.81 (46.2)	2.19 (55.6)
14	F (23)	06	2.75 (69.85)	2.00 (50.80)	1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
15		08			2.00-18 UN	1.81 (46.0)	2.19 (55.6)
16		10			3.50 (88.90)	2.00-16 UN	2.18 (55.4)
17	G (25)	06	2.75 (60.85)		1.750-18 UN	1.62 (41.2)	1.94 (49.3)
18		08			2.00-18 UN	1.81 (46.0)	2.19 (55.6)
19		10			2.250-16 UN	2.18 (55.4)	2.44 (62.0)
20	H (29)	12	4.00 (101.6)		2.50 (63.50)	2.500-16 UN	2.56 (65.0)
21		10	3.25 (82.55)	2.250-16 UN		2.18 (55.4)	2.44 (62.0)
22		12		2.500-16 UN		2.56 (65.0)	2.66 (68.3)
23		J (33)				12	2.56 (65.0)
24	16				3.00-16 UN	3.06 (77.8)	3.18 (81.0)
25	A (11)	04	1.75 (44.45)	1.00 (25.4)	1.188-18 UNEF	1.75 (31.75)	1.38 (35.0)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/5 Backshell for Metal Core Conduit



MIL-DTL-28840
Electrical Connectors




Dash Number	Designator	A Thread Class 2B	B Diameter Max.	C Thread Class 2*	Sealing Range	
					Max.	Min.
01	A (11)	.750-20 UNEF	1.028 (26.11)	.875-20 UNEF	.63 (16.0)	.50 (12.7)
02	B (13)	.875-20 UNEF	1.141 (28.98)			
03				1.000-20 UNEF	.75 (19.1)	.63 (16.0)
04	C (15)	1.000-20 UNEF	1.263 (32.08)	.875-20 UNEF	.63 (16.0)	.50 (12.7)
05				1.000-20 UNEF	.75 (19.1)	.63 (16.0)
06				1.125-18 UNEF	.88 (22.4)	.75 (19.1)
07				1.250-18 UNEF	1.00 (25.4)	.88 (22.4)
08	D (17)	1.125-18 UNEF	1.387 (35.23)	1.125-18 UNEF	.88 (22.4)	.75 (19.1)
09				1.250-18 UNEF	1.00 (25.4)	.88 (22.4)
10				1.625-18 UNEF	1.38 (35.1)	1.19 (30.2)
11	E (19)	1.250-18 UNEF	1.513 (38.43)	1.125-18 UNEF	.88 (22.4)	.75 (19.1)
12				1.250-18 UNEF	1.00 (25.4)	.88 (22.4)
13				1.625-18 UNEF	1.38 (35.1)	1.19 (30.2)
14	F (23)	1.438-18 UNEF	1.703 (45.51)	1.250-18 UNEF	1.00 (25.4)	.88 (22.4)
15				1.625-18 UNEF	1.38 (35.1)	1.19 (30.2)
16				1.875-18 UNS	1.63 (41.4)	1.44 (36.6)
17	G (25)	1.562-18 UNEF	1.825 (46.35)	1.250-18 UNEF	1.00 (25.4)	.88 (22.4)
18				1.625-18 UNEF	1.38 (35.1)	1.19 (30.2)
19				1.875-18 UNS	1.63 (41.4)	1.44 (36.6)
20				2.125-16 UN	1.88 (47.8)	1.63 (41.4)
21	H (29)	1.875-16 UN	2.143 (54.43)	1.875-18 UNS	1.63 (41.4)	1.44 (36.6)
22				2.125-16 UN	1.88 (47.8)	1.63 (41.4)
23	J (33)	2.062-16 UNS	2.329 (59.16)	2.1225-16 UN	1.88 (47.8)	1.63 (41.4)
24				2.750-16 UN	2.38 (60.5)	2.13 (54.1)
25	A (11)	.750-20 UNEF	1.028 (26.11)	.875-20 UNEF	.75 (19.05)	.63 (16.00)

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/6 EMI/RFI Environmental Backshell



Dimensions in Inches (millimeters) are subject to change without notice.

M28840/6 EMI/RFI Environmental Backshell



MIL-DTL-28840
Electrical Connectors

DASH NO.	Designator	A Thread Class 2B	L ± .12	C Max Dia	X Max	Cable Range		Y Ref		
						Max	Min			
01	A (11)	.750-20 UNEF	3.62 (91.95)	1.156 (29.36)	1.281 (32.54)	.312 (7.92)	.188 (4.77)	.938 (23.83)		
02	B (13)	.875-20 UNEF		1.156 (29.36)		.312 (7.92)	.188 (4.77)	.938 (23.83)		
03						.438 (11.12)	.281 (7.14)	1.125 (28.58)		
04	C (15)	1.00-20 UNEF		1.281 (32.54)		.312 (7.92)	.188 (4.77)	.938 (23.83)		
05						.438 (11.12)	.281 (7.14)	1.125 (28.58)		
06						.562 (14.27)	.344(8.74)	1.312 (33.32)		
07	D (17)	1.125-18UNEF	4.12 (104.65)	1.406 (35.71)	1.312 (33.32)	.750 (19.05)	.438(11.12)	1.593 (40.46)		
08					1.281 (32.54)	.625 (15.87)	.675(15.88)	1.312 (33.32)		
09				1.531 (38.89)	1.312 (33.32)	.750(19.05)	.438(11.12)	1.593 (40.46)		
10					1.406 (35.71)	.938 (23.82)	.625(15.88)	1.750 (44.45)		
11	E (19)	1.250-18 UNEF		1.531 (38.89)	1.281 (32.54)	.625(15.87)	.375 (9.53)	1.312 (33.32)		
12					1.406 (35.71)	.938(23.82)	.625 15.87)	1.750 (44.45)		
13	F (23)	1.438-18 UNEF	4.62 (117.35)	1.656 (42.06)	1.312 (33.32)	.750 (19.05)	.438(11.12)	1.593 (40.46)		
14					1.406 (35.71)	.938(23.82)	.625(15.87)	1.250 (31.75)		
15				1.781 (45.24)	1.593 (40.46)	1.188 (30.17)	.812 (20.62)	2.093 (53.16)		
16	G (25)	1.562-18 UNEF			1.406 (35.71)	.938 (23.82)	.625 (15.88)	1.750 (44.45)		
17					1.593 (40.46)	1.188 (30.17)	.812 (20.62)	2.093 (53.16)		
18					1.593 (40.46)	1.250 (31.75)	.875 (22.23)	2.093 (53.16)		
19	H (29)	1.875-16 UNS	5.12 (130.01)	2.156 (54.76)	1.625 (41.28)	1.380 (35.05)	1.000(25.4)	2.343 (59.51)		
20					1.593 (40.46)	1.188 (30.17)	.812 (20.62)	2.093 (53.16)		
21				2.281 (57.94)	1.625 (41.28)	1.380 (38.05)	1.000(25.4)	2.343 (59.51)		
22	J (33)	2.062-16 UNS			1.625 (41.28)	1.380 (35.05)	1.000(25.4)	2.343 (59.51)		
23					1.900 (48.26)	1.625(41.28)	1.250 (25.4)	2.750 (69.85)		
24	A (11)	.750-20 UNEF		3.62 (91.95)	1.156 (29.36)	1.281 (32.54)	.438 (11.12)	.281 (7.14)	1.125 (28.58)	
25			1.281 (32.54)		.562 (14.27)		.344 (8.74)	1.312 (33.32)		
26	B (13)	.875-20 UNEF			.562 (14.27)		.344 (8.74)	1.312 (33.32)		
27			4.12 (104.65)	1.406 (35.71)			.625 (15.87)	.375 (9.52)	1.312 (33.32)	
28	C (15)	1.000-20 UNEF								

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/6

EMI/RFI Environmental Backshell


Dash Number	Designator 1/	L ± .12 (± 3.05)	Working Room Ref.	V Thread Class 2*	X Max. Diameter	Y Max. Diameter		
01	A (11)	3.62 (91.55)	2.00 (50.80)	.625-24 UNEF	1.281 (32.53)	.038 (23.82)		
02	B (13)			.625-24 UNEF		1.125 (23.82)		
03				.750-20 UNEF				
04	C (15)			.625-24 UNEF		.938 (23.82)		
05				.750-20 UNEF		1.125 (28.57)		
06				.875-20 UNEF		1.312 (33.32)		
07	D (17)	4.12 (104.65)	2.50 (63.50)	1.188-18 UNEF	1.312 (33.32)	1.593 (40.62)		
08				1.000-20 UNEF	1.281 (32.54)	1.312 (33.32)		
09				1.188-19 UNEF	1.312 (33.32)	1.593 (40.62)		
10				1.438-18 UNEF	1.406 (35.71)	1.750 (44.45)		
11	E (19)	4.62 (117.35)	3.00 (76.20)	1.000-20 UNEF	1.281 (32.54)	1.312 (33.32)		
12				1.438-18 UNEF	1.406 (35.71)	1.750 (44.45)		
13				F (23)	3.50 (88.90)	1.188-18 UNEF	1.312 (33.32)	1.593 (40.62)
14	1.438-18 UNEF					1.406 (35.71)	1.750 (44.45)	
15	1.750-18 UNS					1.593 (40.46)	2.003 (53.16)	
16	1.438-18 UNEF					1.406 (35.71)	1.750 (44.45)	
17	G (25)	5.12 (130.05)	3.50 (88.90)	1.750-18 UNS	1.593 (40.46)	2.093 (53.16)		
18				1.750-18 UNS		2.093 (53.16)		
19				2.000-18 UNS	1.625 (41.28)	2.343 (59.51)		
20				1.750-18 UNS	1.593 (40.46)	2.093 (53.16)		
21	H (29)	5.12 (130.05)	3.50 (88.90)	2.000-18 UNS	1.625 (41.28)	2.343 (59.51)		
22				2.000-18 UNS				
23	J (33)			5.12 (130.05)	3.50 (88.90)	2.250-16 UNS	1.900 (48.26)	2.750 (69.85)
24						.750-20 UNEF	1.281 (32.54)	1.125 (28.57)
25	A (11)	.875-20 UNEF	1.312 (33.32)					
26	B (13)							

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/7 Dummy Stowage Receptacle



MIL-DTL-28840
Electrical Connectors





Designator	N Diameter Max.	O Reference Mating Hole	R T.P. Centerline to Centerline	S	T
A (11)	.750 (19.05)	.812 (20.62)	.750 (19.05)	1.043 (26.49) 1.003 (25.48)	.130 (3.30) .115 (2.92)
B (13)	.875 (22.22)	.937 (23.80)	.843 (21.41)	1.158 (29.41) 1.118 (28.40)	
C (15)	1.062 (26.97)	1.124 (28.55)	.968 (24.59)	1.278 (32.46) 1.238 (31.45)	
D (17)	1.125 (28.58)	1.187 (30.15)	1.015 (25.78)	1.403 (35.64) 1.363 (34.62)	
E (19)	1.312 (33.32)	1.374 (34.90)	1.140 (28.96)	1.528 (38.81) 1.488 (37.80)	
F (23)	1.500 (38.10)	1.562 (39.67)	1.281 (32.54)	1.738 (44.15) 1.698 (43.13)	
G (25)	1.625 (41.28)	1.687 (42.85)	1.392 (35.36)	1.838 (46.69) 1.798 (45.67)	.157 (3.99) .142 (3.61)
H (29)	1.812 (46.02)	1.874 (47.60)	1.568 (39.83)	2.158 (54.81) 2.118 (53.80)	
J (33)	2.000 (50.80)	2.062 (52.37)	1.734 (44.04)	2.348 (59.64) 2.308 (58.62)	.183 (4.65) .168 (4.27)


Dimensions in Inches (millimeters) are subject to change without notice.



M28840/8 90° EMI/RFI Environmental Backshell



BACKSHELL STYLE A



BACKSHELL STYLE B

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/8
90° EMI/RFI Environmental Backshell



MIL-DTL-28840
 Electrical Connectors

Backshell Size	Dash Number	Designator	A Thread Class 2B	B Max. Diameter	C Max. Diameter	D Max. Diameter
A	01	A (11)	.750-20 UNEF	1.028 (26.11)	1.188 (30.17)	1.031 (26.19)
A	02	B (13)	.875-20 UNEF	1.141 (28.98)		
B	03	B (13)				
A	04	C (15)	1.00-20 UNEF	1.263 (32.08)	1.438 (36.52)	1.156 (29.36)
B	05	C (15)				
C	06	C (15)			1.688 (42.87)	1.281 (32.54)
D	07	C (15)				
A	08	D (17)	1.125-18 UNEF	1.387 (35.23)		
B	09	D (17)				
C	10	D (17)				
A	11	E (19)	1.250-18 UNEF	1.513 (38.43)	1.938 (49.22)	1.406 (35.71)
B	12	E (19)				
A	13	F (23)	1.438-18 UNEF	1.703 (43.51)		
B	14	F (23)				
C	15	F (23)				
A	16	G (25)	1.562-18 UNEF	1.825 (46.35)	2.188 (54.43)	1.531 (38.89)
B	17	G (25)				
C	18	G (25)				
D	19	G (25)				
A	20	H (29)	1.875-16 UN	2.143 (54.43)		
B	21	H (29)				

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/8

90° EMI/RFI Environmental Backshell

Backshell Size	Dash Number	Designator	Cable Range		E Max. Dim.	F Max. Dim.	V Thread Class 2
			Max.	Min.			
A	01	A (11)	.312 (7.92)	.188 (4.77)	1.156 (29.36)	2.614 (66.40)	.625-24 UNEF
A	02	B (13)	.312 (7.92)	.188 (4.77)			.625-24 UNEF
B	03	B (13)	.438 (11.12)	.281 (7.14)			.750-20 UNEF
A	04	C (15)	.312 (7.92)	.188 (4.77)	1.281 (32.54)	2.864 (72.75)	.625-24 UNEF
B	05	C (15)	.438 (11.12)	.281 (7.14)			.750-20 UNEF
C	06	C (15)	.562 (14.27)	.344 (8.74)			.875-20 UNEF
D	07	C (15)	.750 (19.05)	.438 (11.12)	1.406 (35.71)	3.114 (79.10)	1.188-18 UNEF
A	08	D (17)	.625 (15.87)	.375 (9.82)			1.000-20 UNEF
B	09	D (17)	.750 (19.05)	.438 (11.12)			1.188-18 UNEF
C	10	D (17)	.938 (23.82)	.625 (15.87)	1.531 (38.89)		1.438-18 UNEF
A	11	E (19)	.625 (15.87)	.375 (9.52)	1.406 (35.71)		1.00-20 UNEF
B	12	E (19)	.938 (23.82)	.625 (15.87)	1.531 (38.89)	3.364 (85.45)	1.438-18 UNEF
A	13	F (23)	.750 (19.05)	.438 (11.12)	1.406 (25.71)		1.188-18 UNEF
B	14	F (23)	.938 (23.82)	.625 (15.87)	1.531 (38.89)		1.438-18 UNEF
C	15	F (23)	1.188 (30.17)	.812 (20.62)	1.781 (45.24)		1.750-18 UNEF
A	16	G (25)	.938 (23.82)	.625 (15.87)	1.531 (38.89)		1.438-18 UNEF
B	17	G (25)	1.188 (30.17)	.812 (20.62)	1.781 (45.24)	3.614 (91.80)	1.750-18 UNS
C	18	G (25)	1.250 (31.75)	.875 (22.23)			2.000-16 UNS
D	19	G (25)	1.380 (35.05)	1.000 (25.40)	2.156 (54.76)		1.750-18 UNS
A	20	H (29)	1.188 (30.17)	.812 (20.62)	1.781 (45.24)		2.000-18 UNS
B	21	H (29)	1.380 (35.05)	1.000 (25.40)	2.156 (54.76)		

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/8
90° EMI/RFI Environmental Backshell



MIL-DTL-28840
 Electrical Connectors

Backshell Size	Dash Number	Designator	X Ref. Dimension	Y Ref. Dimension	H Max. Style A	N Max. Style B
A	01	A (11)	1.281 (32.54)	.938 (23.82)	5.332 (134.43)	2.962 (75.23)
A	02	B (13)		.938 (23.82)	5.332 (134.43)	2.962 (75.23)
B	03	B (13)		1.125 (28.57)	5.332 (134.43)	2.962 (75.23)
A	04	C (15)		.938 (23.82)	5.457 (138.61)	3.087 (78.41)
B	05	C (15)		1.125 (28.57)	5.457 (138.61)	3.087 (78.41)
C	06	C (15)		1.312 (33.32)	5.457 (138.61)	3.087 (78.41)
D	07	C (15)		1.593 (40.62)	5.682 (144.32)	3.312 (84.12)
A	08	D (17)		1.312 (33.32)	5.682 (144.32)	3.312 (84.12)
B	09	D (17)	1.312 (33.32)	1.593 (40.62)	5.713 (145.11)	3.343 (84.91)
C	10	D (17)	1.406 (35.71)	1.750 (44.45)	5.807 (147.50)	3.437 (87.30)
A	11	E (19)	1.281 (32.54)	1.312 (33.32)	5.682 (144.32)	3.312 (84.12)
B	12	E (19)	1.406 (35.71)	1.750 (44.45)	5.832 (148.13)	3.462 (87.93)
A	13	F (23)	1.312 (33.32)	1.593 (40.62)	5.738 (145.28)	3.368 (85.55)
B	14	F (23)	1.406 (35.71)	1.750 (44.45)	5.832 (148.13)	3.462 (87.93)
C	15	F (23)	1.593 (40.46)	2.093 (53.16)	6.019 (152.88)	3.649 (92.68)
A	16	G (25)	1.406 (35.71)	1.750 (44.45)	5.832 (148.13)	3.462 (87.93)
B	17	G (25)	1.593 (40.46)	2.093 (53.16)	6.019 (152.88)	3.649 (92.68)
C	18	G (25)	1.593 (40.46)	2.093 (53.16)	6.144 (156.06)	3.774 (95.86)
D	19	G (25)	1.625 (41.28)	2.343 (59.51)	6.176 (156.87)	3.806 (96.62)
A	20	H (29)	1.593 (40.46)	2.093 (53.16)	6.144 (156.06)	3.774 (95.86)
B	21	H (29)	1.625 (41.28)	2.343 (59.51)	6.176 (156.87)	3.806 (96.62)

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/8

90° EMI/RFI Environmental Backshell

Backshell Size	Dash Number	Designator	A Thread Class 2B	B Max. Diameter	C Max. Diameter	D Max. Diameter
A	22	J (33)	2.062-16 UNS	2.329 (59.16)	2.688 (68.26)	1.781 (45.24)
A	23	J (33)				
B	24	A (11)	.750-20 UNEF	1.028 (26.11)	1.188 (30.17)	1.031 (26.19)
C	25	A (11)			1.438 (36.52)	1.156 (29.36)
C	26	B (13)	.875-20 UNEF	1.141 (28.98)		
D	27	B (13)				
E	28	C (15)	1.000-20 UNEF	1.263 (32.08)		

Backshell Size	Dash Number	Designator	Cable Range		E Max. Dimensions	F Max. Dimensions	V Thread Class 2
			Max.	Min.			
A	22	J (33)	1.380 (35.05)	1.000 (25.40)	2.281 (57.94)	4.114 (104.50)	2.000-18 UNS
A	23	J (33)	1.625 (41.26)	1.250 (31.75)			2.250-16 UNS
B	24	A (11)	.438 (11.12)	.281 (7.14)	1.156 (29.36)	2.614 (66.40)	.750-20 UNEF
C	25	A (11)	.562 (14.27)	.344 (8.74)	1.281 (32.54)	2.864 (72.75)	.875-20 UNEF
C	26	B (13)	.562 (14.27)	.344 (8.74)			
D	27	B (13)	.625 (15.87)	.375 (9.52)	1.406 (35.71)	3.114 (79.10)	1.000-20 UNEF
E	28	C (15)	.625 (15.87)	.375 (9.50)			



Backshell Size	Dash Number	Designator	X Ref. Dimensions	Y Ref. Dimensions	H Max. Style A	N Max. Style B
A	22	J (33)	1.625 (41.28)	2.343 (59.51)	6.426 (163.22)	4.056 (103.02)
A	23	J (33)	1.900 (48.26)	2.750 (59.85)	6.701 (170.21)	4.33 (110.01)
B	24	A (11)	1.281 (32.54)	1.125 (28.57)	5.332 (135.43)	2.962 (75.23)
C	25	A (11)		1.312 (33.32)	5.457 (138.61)	3.087 (78.41)
C	26	B (13)			5.457 (138.61)	3.087 (78.41)
C	27	B (13)			5.682 (144.32)	3.312 (84.12)
B	28	C (15)			5.682 (144.32)	3.312 (84.12)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/9 45° EMI/RFI Environmental Backshell



MIL-DTL-28840
Electrical Connectors



Dimensions in Inches (millimeters) are subject to change without notice.



M28840/9

45° EMI/RFI Environmental Backshell

Backshell Size	Dash Number	Designator	A Thread	B Max. Diameter	C Max. Diameter	D Max.
A	01	A (11)	.750-20 UNEF	1.028 (26.11)	1.031 (26.19)	1.031 (26.19)
A	02	B (13)	.875-20 UNEF	1.141 (28.98)		
B	03	B (13)				
A	04	C (15)	1.00-20 UNEF	1.263 (32.08)	1.281 (32.54)	1.156 (29.36)
B	05	C (15)				
C	06	C (15)				
D	07	C (15)				
A	08	D (17)	1.125-18 UNEF	1.387 (35.23)	1.513 (38.89)	1.281 (32.54)
B	09	D (17)				
C	10	D (17)				
A	11	E (19)	1.250-18 UNEF	1.513 (38.43)	1.781 (45.24)	1.406 (35.71)
B	12	E (19)				
A	13	F (23)	1.438-18 UNEF	1.703 (43.51)		
B	14	F (23)				
C	15	F (23)				
A	16	G (25)	1.562-18 UNEF	1.825 (46.35)	2.031 (51.59)	1.531 (38.89)
B	17	G (25)				
C	18	G (25)				
D	19	G (25)				
A	20	H (29)	1.875-16 UN	2.143 (54.43)	2.031 (51.59)	1.531 (38.89)
B	21	H (29)				

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/9 45° EMI/RFI Environmental Backshell



MIL-DTL-28840
Electrical Connectors

Backshell Size	Dash Number	Designator	Cable Range		E Max. Dim.	F Max. Style A	H Max. Style B
			Max.	Min.			
A	01	A (11)	.312 (7.92)	.188 (4.77)	1.156 (29.36)	5.879 (149.33)	4.199 (106.65)
A	02	B (13)	.312 (7.92)	.188 (4.77)		5.879 (149.33)	4.199 (106.65)
B	03	B (13)	.438 (11.12)	.281 (7.14)		5.932 (150.67)	4.252 (108.00)
A	04	C (15)	.312 (7.92)	.188 (4.77)	1.281 (32.54)	6.092 (154.74)	4.412 (112.06)
B	05	C (15)	.438 (11.12)	.281 (7.14)		6.146 (156.11)	4.466 (113.44)
C	06	C (15)	.562 (14.27)	.344 (8.74)		6.202 (157.53)	4.522 (114.86)
D	07	C (15)	.750 (19.05)	.438 (11.12)	1.406 (35.71)	6.533 (165.94)	4.853 (123.27)
A	08	D (17)	.625 (15.87)	.375 (9.82)		6.413 (1626.89)	4.733 (120.22)
B	09	D (17)	.750 (19.05)	.438 (11.12)		6.533 (165.94)	4.853 (123.27)
C	10	D (17)	.938 (23.82)	.625 (15.87)	1.531 (38.89)	6.636 (168.55)	4.956 (125.88)
A	11	E (19)	.625 (15.87)	.375 (9.52)	1.406 (35.71)	6.413 (162.89)	4.733 (120.22)
B	12	E (19)	.938 (23.82)	.625 (15.87)	1.531 (38.89)	6.846 (173.89)	5.166 (131.22)
A	13	F (23)	.750 (19.05)	.438 (11.12)	1.406 (25.71)	6.747 (171.37)	5.067 (128.70)
B	14	F (23)	.938 (23.82)	.625 (15.87)	1.531 (38.89)	6.846 (173.89)	5.166 (131.22)
C	15	F (23)	1.188 (30.17)	.812 (20.62)	1.781 (45.24)	7.103 (180.42)	5.423 (138.23)
A	16	G (25)	.938 (23.82)	.625 (15.87)	1.531 (38.89)	6.846 (173.89)	5.156 (130.96)
B	17	G (25)	1.188 (30.17)	.812 (20.62)	1.781 (45.24)	7.103 (180.42)	5.4239 (138.23)
C	18	G (25)	1.250 (31.75)	.875 (22.23)		7.316 (185.83)	5.636 (143.15)
D	19	G (25)	1.380 (35.05)	1.000 (25.40)	2.156 (54.76)	7.425 (188.60)	5.745 (145.92)
A	20	H (29)	1.188 (30.17)	.812 (20.62)	1.781 (45.24)	7.316 (185.83)	5.636 (143.15)
B	21	H (29)	1.380 (35.05)	1.000 (25.40)	2.156 (54.76)	7.425 (188.60)	5.745 (145.92)

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/9

45° EMI/RFI Environmental Backshell

Backshell Size	Dash Number	Designator	V Thread Class	X Ref. Dimension	Y Ref. Dimension
A	01	A (11)	.625-24 UNEF	1.281 (32.54)	.938 (23.82)
A	02	B (13)	.625-24 UNEF		.938 (23.82)
B	03	B (13)	.750-20 UNEF		1.125 (28.57)
A	04	C (15)	.625-24 UNEF		.938 (23.82)
B	05	C (15)	.750-20 UNEF		1.125 (28.57)
C	06	C (15)	.875-20 UNEF		1.312 (33.32)
D	07	C (15)	1.188-18 UNEF	1.312 (33.32)	1.593 (40.62)
A	08	D (17)	1.000-20 UNEF	1.281 (32.54)	1.312 (33.32)
B	09	D (17)	1.188-18 UNEF	1.312 (33.32)	1.593 (40.62)
C	10	D (17)	1.438-18 UNEF	1.406 (35.71)	1.750 (44.45)
A	11	E (19)	1.000-20 UNEF	1.281 (32.54)	1.312 (33.32)
B	12	E (19)	1.438-18 UNEF	1.406 (35.71)	1.750 (44.45)
A	13	F (23)	1.188-18 UNEF	1.312 (33.32)	1.593 (40.62)
B	14	F (23)	1.438-18 UNEF	1.406 (35.71)	1.750 (44.45)
C	15	F (23)	1.750-18 UNS	1.593 (40.46)	2.093 (53.16)
A	16	G (25)	1.438-18 UNEF	1.406 (35.71)	1.750 (44.45)
B	17	G (25)	1.750-18 UNS	1.593 (40.46)	2.093 (53.16)
C	18	G (25)	1.750-18 UNS	1.593 (40.46)	2.093 (53.16)
D	19	G (25)	2.000-16 UNS	1.625 (41.28)	2.343 (59.51)
A	20	H (29)	1.750-18 UNS	1.593 (40.46)	2.093 (53.16)
B	21	H (29)	2.000-18 UNS	1.625 (41.28)	2.343 (59.51)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/9 45° EMI/RFI Environmental Backshell



MIL-DTL-28840
Electrical Connectors

Backshell Size	Dash Number	Designator	A Thread	B Max. Diameter	C Max. Diameter	D Max.
A	22	J (33)	2.062-16 UNEF	2.329 (59.16)	2.531 (64.29)	1.781 (45.24)
B	23	J (33)				
B	24	A (11)	.750-20 UNEF	1.028 (26.11)	1.031 (26.19)	1.031 (26.19)
C	25	A (11)			1.281 (32.54)	1.156 (29.36)
C	26	B (13)	.875-20 UNEF	1.141 (28.98)	1.281 (32.54)	1.156 (29.36)
D	27	B (13)			1.531 (38.99)	1.281 (32.54)
E	28	C (15)	1.000-20 UNEF	1.263 (32.08)		

Backshell Size	Dash Number	Designator	Cable Range		E Max. Dimension	F Max. Style A	H Max. Style B
			Max.	Min.			
A	22	J (33)	1.380 (35.05)	1.000 (25.40)	2.281 (57.94)	7.852 (199.44)	6.127 (156.77)
B	23	J (33)	1.625 (41.28)	1.250 (31.75)		6.454 (163.93)	6.454 (163.93)
B	24	A (11)	.438 (11.12)	.281 (7.14)	1.156 (29.36)	5.932 (150.67)	4.252 (108.00)
C	25	A (11)	.562 (14.27)	.344 (8.74)	1.281 (32.54)	6.202 (157.53)	4.522 (114.86)
C	26	B (13)	.562 (14.27)	.344 (8.74)	1.281 (32.54)	6.202 (157.53)	4.522 (114.86)
D	27	B (13)	.625 (15.87)	.375 (9.52)	1.406 (35.71)	6.413 (162.89)	4.733 (120.22)
E	28	C (15)	.625 (15.87)	.375 (9.50)		6.413 (162.89)	4.733 (120.22)




E

Backshell Size	Dash Number	Designator	V Thread Class	X Ref. Dimension	Y Ref. Dimension
A	22	J (33)	2.000-18 UNS	1.625 (41.28)	2.343 (59.51)
B	23	J (33)	2.250-16 UNS	1.900 (48.26)	2.750 (69.85)
B	24	A (11)	.750-20 UNEF	1.281 (32.54)	1.125 (28.57)
C	25	A (11)	.875-20 UNEF		1.312 (33.32)
C	26	B (13)	.875-20 UNEF		
D	27	B (13)	1.000-20 UNEF		
E	28	C (15)	1.000-20 UNEF		

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/10 Wall Mount Receptacle Connector





Military Shell Size	Shell Size	A Thread Class 2A	V Thread Class 2A	O Ref. Mtg. Hole	R True Position ϕ to ϕ	S	T Diameter
A	11	.750-1P-.2L-D.S.	.750-20 UNEF	.812 (20.62)	.750 (19.05)	1.043 (26.49) 1.003 (25.48)	.130 (3.30) .115 (2.92)
B	13	.875-1P-.2L-D.S.	.875-20 UNEF	.937 (23.80)	.843 (21.41)	1.158 (29.41) 1.118 (28.40)	
C	15	1.062-1P-.2L-D.S.	1.000-20 UNEF	1.124 (28.55)	.968 (24.59)	1.278 (32.46) 1.238 (31.45)	
D	17	1.125-1P-.2L-D.S.	1.125-18 UNEF	1.187 (30.15)	1.015 (25.78)	1.403 (35.64) 1.363 (34.62)	
E	19	1.312-1P-.2L-D.S.	1.250-18 UNEF	1.374 (34.90)	1.140 (28.96)	1.528 (38.81) 1.488 (37.80)	
F	23	1.500-1P-.2L-D.S.	1.437-18 UNEF	1.562 (39.67)	1.281 (32.54)	1.738 (44.15) 1.698 (43.13)	
G	25	1.625-1P-.2L-D.S.	1.562-18 UNEF	1.687 (42.85)	1.392 (35.36)	1.838 (46.69) 1.798 (45.67)	.157 (3.99) .142 (3.61)
H	29	1.812-1P-.2L-D.S.	1.875-16 UN	1.874 (47.60)	1.568 (39.83)	2.158 (54.81) 2.118 (53.80)	
J	33	2.000-1P-.2L-D.S.	2.062-16 UNS	2.062 (52.37)	1.734 (44.04)	2.348 (59.64) 2.308 (58.62)	.183 (4.65) .168 (4.27)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/11 In-Line Receptacle Connector



MIL-DTL-28840
Electrical Connectors



Military Shell Size	Shell Size	A Thread Class 2A	V Thread Class 2A	R	S Diameter
A	11	.750-.1P-.2L-D.S.	.750-20 UNEF	.768 (19.51) .758 (19.25)	.963 (24.46) .943 (23.95)
B	13	.875-.1P-.2L-D.S.	.875-20 UNEF	.893 (22.68) .883 (22.43)	1.088 (27.63) 1.063 (27.13)
C	15	1.062-.1P-.2L-D.S.	1.000-20 UNEF	1.080 (27.43) 1.070 (27.18)	1.275 (32.38) 1.255 (31.88)
D	17	1.125-.1P-.2L-D.S.	1.125-18 UNEF	1.143 (29.03) 1.133 (28.78)	1.338 (33.98) 1.318 (33.48)
E	19	1.312-.1P-.2L-D.S.	1.250-18 UNEF	1.330 (33.78) 1.320 (33.53)	1.525 (38.74) 1.505 (38.23)
F	23	1.500-.1P-.2L-D.S.	1.437-18 UNEF	1.518 (38.56) 1.508 (38.30)	1.713 (43.51) 1.693 (43.00)
G	25	1.625-.1P-.2L-D.S.	1.562-18 UNEF	1.643 (41.73) 1.633 (41.48)	1.838 (46.09) 1.818 (46.18)
H	29	1.812-.1P-.2L-D.S.	1.875-16 UN	1.893 (48.08) 1.883 (47.83)	2.088 (53.04) 2.068 (52.53)
J	33	2.000-.1P-.2L-D.S.	2.062-16 UNS	2.080 (52.83) 2.070 (52.58)	2.275 (57.78) 2.255 (57.28)

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/12 Box Mount Receptacle Connector





FIGURE 1




FIGURE 2

E



Designator	N Diameter Max	O Reference Mating Hole	R True Position Centerline to Centerline	S	T	GG Diameter Max.
A (11)	.750 (19.05)	.812 (20.62)	.750 (19.05)	1.043 (26.49) 1.003 (25.48)	.130 (3.30) .115 (2.92)	.758 (19.25)
B (13)	.875 (22.22)	.937 (23.80)	.843 (21.41)	1.158 (29.41) 1.118 (28.40)		.880 (22.35)
C (15)	1.062 (26.97)	1.124 (28.55)	.968 (24.59)	1.278 (32.46) 1.238 (31.45)		1.005 (25.53)
D (17)	1.125 (28.58)	1.187 (30.15)	1.015 (25.78)	1.403 (35.64) 1.363 (34.62)		1.130 (28.70)
E (19)	1.312 (33.32)	1.374 (34.90)	1.140 (28.96)	1.528 (38.81) 1.488 (37.80)		1.255 (31.88)
F (23)	1.500 (38.10)	1.562 (39.67)	1.281 (32.54)	1.738 (44.15) 1.698 (43.13)		1.443 (36.65)
G (25)	1.625 (41.28)	1.687 (42.85)	1.392 (35.36)	1.838 (46.69) 1.798 (45.67)	.157 (3.99) .142 (3.61)	1.567 (39.80)
H (29)	1.812 (46.02)	1.874 (47.60)	1.568 (39.83)	2.158 (54.81) 2.118 (53.80)		1.880 (47.75)
J (33)	2.000 (50.80)	2.062 (52.37)	1.734 (44.04)	2.343 (59.64) 2.308 (58.62)	.183 (4.65) .168 (4.27)	2.067 (52.50)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/13 Protective Receptacle Cover



MIL-DTL-28840
Electrical Connectors



M28840/13 Receptacle Cover


Designator	E Thread Class 2A	F Max. Diameter	H ± .010 (± .25)	J Dia ± .005 (± .13)	G ± .005 (± .13)
A (11)	.750-1P-2L-D.S.	1.028 (26.21)	.890 (22.61)	.130 (3.30)	.765 (19.43)
B (13)	.875-1P-2L-D.S.	1.141 (23.98)	1.015 (25.78)		.890 (22.61)
C (15)	1.062-1P-2L-D.S.	1.263 (32.08)	1.203 (30.56)		1.015 (25.78)
D (17)	1.125-1P-2L-D.S.	1.387 (35.23)	1.265 (32.13)		1.140 (28.96)
E (19)	1.312-1P-2L-D.S.	1.513 (38.43)	1.453 (36.91)		1.265 (32.13)
F (23)	1.500-1P-2L-D.S.	1.703 (43.51)	1.640 (41.66)		1.453 (36.91)
G (25)	1.625-1P-2L-D.S.	1.825 (46.35)	1.765 (44.83)	.156 (3.96)	1.577 (40.06)
H (29)	1.812-1P-2L-D.S.	2.143 (54.43)	1.953 (49.61)		1.890 (48.01)
J (33)	2.000-1P-2L-D.S.	2.329 (59.16)	2.140 (54.36)		2.077 (52.76)

Dimensions in Inches (millimeters) are subject to change without notice.

E



M28840/14 Jam Nut Mount Receptacle Connector



Material and Finish

- A** - Class D: Aluminum, Cadmium Plate, O.D. over Electroless Nickel
- B** - Class DS: Corrosion Resistant Steel, Cadmium Plate, Black

Key Position

1, 2, 3, 4, 5 and 6

Insert Arrangement

M28840/14

Military Designator

A

Shell Size

G

1

P

1

Contact Style
P, S, F, G, D or E

E



Designator	G	K	L Across Flat	M Thread Class 2A	N Max.	P	R Max.	S Hex Nut Thickness
A (11)	1.274 (32.36) 1.254 (31.85)	1.368 (34.75) 1.348 (34.24)	.841 (21.36) .832 (21.13)	7/8-20 UNEF	.750 (19.05)	.890 (22.61) .880 (22.35)	.875 (22.22)	.125 (3.17)
B (13)	1.399 (35.53) 1.379 (35.03)	1.508 (38.30) 1.488 (37.80)	.966 (24.54) .957 (24.31)	1-20 UNEF	.875 (22.22)	1.015 (24.78) 1.005 (25.53)	1.000 (25.40)	
C (15)	1.587 (40.31) 1.567 (39.80)	1.681 (42.70) 1.661 (42.19)	1.156 (29.29) 1.144 (29.06)	1 3/16-18 UNEF	1.062 (26.97)	1.203 (30.56) 1.193 (30.30)	1.188 (30.18)	
D (17)	1.649 (41.88) 1.629 (41.38)	1.743 (44.27) 1.723 (43.76)	1.216 (30.89) 1.207 (30.66)	1 1/4-18 UNEF	1.125 (28.58)	1.265 (32.13) 1.255 (31.88)	1.250 (31.75)	
E (19)	1.837 (46.66) 1.817 (46.15)	1.931 (49.05) 1.911 (48.54)	1.403 (35.64) 1.394 (35.41)	1 7/16-18 UNEF	1.312 (33.32)	1.453 (36.91) 1.443 (36.65)	1.438 (36.52)	
F (23)	2.024 (51.41) 2.004 (50.90)	2.118 (53.80) 2.098 (53.29)	1.591 (40.41) 1.582 (40.18)	1 5/8-18 UNEF	1.500 (38.10)	1.640 (41.66) 1.630 (41.40)	1.625 (41.28)	
G (25)	2.149 (54.58) 2.129 (54.08)	2.243 (56.97) 2.223 (56.46)	1.716 (43.59) 1.707 (43.36)	1 3/4-18 UNS	1.625 (41.28)	1.765 (44.83) 1.755 (44.58)	1.750 (44.45)	.189 (4.8)
H (29)	2.337 (59.36) 2.317 (58.85)	2.435 (61.85) 2.415 (61.34)	1.903 (46.34) 1.894 (48.11)	1 15/16-16 UN	1.812 (46.02)	1.953 (49.61) 1.943 (49.35)	1.938 (49.22)	
J (33)	2.524 (64.11) 2.504 (63.60)	2.618 (66.50) 2.598 (65.99)	2.091 (53.11) 2.082 (52.88)	2 1/8-16 UN	2.000 (50.80)	2.140 (54.36) 2.130 (54.10)	2.125 (53.98)	

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/15 Protective Plug Cover



MIL-DTL-28840
Electrical Connectors





M28840/15 Plug Cover

Designator	E Thread Class 2B	F Max. Diameter
A (11)	.750-1P-.2L-DS	1.028 (26.21)
B (13)	.875-1P-.2L-DS	1.141 (28.98)
C (15)	1.062-1P-.2L-DS	1.263 (32.08)
D (17)	1.125-1P-.2L-DS	1.387 (35.23)
E (19)	1.312-1P-.2L-DS	1.108 (28.14)
F (23)	1.500-1P-.2L-DS	1.293 (32.84)
G (25)	1.625-1P-.2L-DS	1.454 (36.93)
H (29)	1.812-1P-.2L-DS	1.620 (41.15)
J (33)	2.000-1P-.2L-DS	1.812 (46.02)

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/16 Plug Connector





Designator	A Thread Class 2B	V Thread Class 2A	Ø Q Max.
A (11)	.750-1P-.2L-DS	3/4-20 UNEF	1.028 (26.11)
B (13)	.875-1P-.2L-DS	7/8-20 UNEF	1.141 (28.98)
C (15)	1.062-1P-.2L-DS	1-20 UNEF	1.263 (32.08)
D (17)	1.125-1P-.2L-DS	1 1/8-18 UNEF	1.387 (35.23)
E (19)	1.312-1P-.2L-DS	1 1/4-18 UNEF	1.513 (38.43)
F (23)	1.500-1P-.2L-DS	1 7/16-18 UNEF	1.703 (43.26)
G (25)	1.625-1P-.2L-DS	1 9/16-18 UNEF	1.825 (46.36)
H (29)	1.812-1P-.2L-DS	1 7/8-16 UN	2.143 (54.43)
J (33)	2.000-1P-.2L-DS	2 1/16-16 UNS	2.329 (59.16)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/17 Plug Connector with Straight Strain Relief



MIL-DTL-28840
Electrical Connectors





Designator	A Thread Class 2B	F Cable Entry		L Max.	Q Max.	Max. O.D. Over Rear Clamps
		Open	Closed			
A (11)	.750-1P-.2L-DS	.286	.177	2.438	1.028	.832
B (13)	.875-1P-.2L-DS	.286			1.141	
C (15)	1.062-1P-.2L-DS	.416	.250		1.263	.989
D (17)	1.125-1P-.2L-DS	.476	.291	2.688	1.387	1.094
E (19)	1.312-1P-.2L-DS	.626	.348	2.812	1.513	1.319
F (23)	1.500-1P-.2L-DS	.831	.429	2.938	1.703	1.557
G (25)	1.625-1P-.2L-DS	.956	.523	3.062	1.825	1.653
H (29)	1.812-1P-.2L-DS	1.081	.643	3.188	2.143	1.819
J (33)	2.000-1P-.2L-DS	1.187	.704	3.375	2.329	2.020

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/18 Plug Connector with 90° Strain Relief





Designator	A Thread Class 2B	F Cable Entry		L Max.	Q Max.	Z Max.	Max. O.D. Over Rear Clamps
		Open	Closed				
A (11)	.750-1P-.2L-DS	.286	.177	2.562	1.028	.929	.832
B (13)	.875-1P-.2L-DS	.286		2.562	1.141	.929	
C (15)	1.062-1P-.2L-DS	.416	.250	2.750	1.263	1.056	.989
D (17)	1.125-1P-.2L-DS	.476	.291	2.875	1.387	1.233	1.094
E (19)	1.312-1P-.2L-DS	.626	.348	3.000	1.513	1.296	1.319
F (23)	1.500-1P-.2L-DS	.831	.429	3.125	1.703	1.358	1.557
G (25)	1.625-1P-.2L-DS	.956	.523	3.250	1.825	1.420	1.653
H (29)	1.812-1P-.2L-DS	1.081	.643	3.375	2.143	1.634	1.819
J (33)	2.000-1P-.2L-DS	1.187	.704	3.438	2.329	1.859	2.020

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/19 Plug Connector with 45° Strain Relief



MIL-DTL-28840
Electrical Connectors





Designator	A Thread Class 2B	F Cable Entry		L Max.	Q Max.	Z Max.	Max. O.D. Over Rear Clamps
		Open	Closed				
A (11)	.750-1P-.2L-DS	.286	.177	3.125	1.028	.928	.832
B (13)	.875-1P-.2L-DS	.286		3.125	1.141	.928	
C (15)	1.062-1P-.2L-DS	.416	.250	3.250	1.263	.991	.989
D (17)	1.125-1P-.2L-DS	.476	.291	3.312	1.387	1.110	1.094
E (19)	1.312-1P-.2L-DS	.626	.348	3.375	1.513	1.172	1.319
F (23)	1.500-1P-.2L-DS	.831	.429	3.438	1.703	1.235	1.557
G (25)	1.625-1P-.2L-DS	.956	.523	3.500	1.825	1.297	1.653
H (29)	1.812-1P-.2L-DS	1.081	.643	3.750	2.143	1.543	1.819
J (33)	2.000-1P-.2L-DS	1.187	.704	3.875	2.329	1.668	2.020

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/20 Receptacle Connector with Straight EMI/RFI Backshell



Dimensions in Inches (millimeters) are subject to change without notice.

© 2011 Glenair, Inc. US Navy Approved Connectors U.S. CAGE Code 06324 Rev. 09.16.19 Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912
www.glenair.com E-32 E-Mail: sales@glenair.com

M28840/20 Receptacle Connector with Straight EMI/RFI Backshell



MIL-DTL-28840
Electrical Connectors



JMilitary Shell Size	Shell Size	Backshell Size Designator	A Cable Entry		A Thread Class 2B	E Max.	L Max.
			Open	Closed			
A	11	A	.312	.188	.750-1P-.2L-DS	.938	6.625
A	11	B	.438	.281		1.125	6.625
A	11	C	.562	.344		1.312	6.625
B	13	A	.312	.188	.875-1P-.2L-DS	.938	6.625
B	13	B	.438	.281		1.125	6.625
B	13	C	.562	.344		1.312	6.625
B	13	D	.652	.375		1.312	7.125
C	15	A	.438	.281	1.062-1P-.2L-DS	1.125	6.625
C	15	B	.562	.344		1.312	6.625
C	15	C	.625	.375		1.312	7.125
C	15	D	.750	.438		1.593	7.188
C	15	E	.312	.188		.938	6.625
D	17	A	.625	.375	1.125-1P-.2L-DS	1.312	7.125
D	17	B	.750	.438		1.593	7.188
D	17	C	.938	.625		1.750	7.188
E	19	A	.625	.375	1.312-1P-.2L-DS	1.312	7.125
E	19	B	.938	.625		1.750	7.250
F	23	A	.750	.438	1.500-1P-.2L-DS	1.593	7.688
F	23	B	.938	.625		1.750	7.812
F	23	C	1.188	.812		2.093	7.938
G	25	A	.938	.625	1.625-1P-.2L-DS	1.750	7.750
G	25	B	1.188	.812		2.093	8.438
G	25	C	1.250	.875		2.093	8.438
G	25	D	1.380	1.000		2.343	8.500
H	29	A	1.188	.812	1.812-1P-.2L-DS	2.093	8.438
H	29	B	1.380	1.000		2.343	8.500
J	33	A	1.380	1.000	2.000-1P-.2L-DS	2.343	8.500
J	33	B	1.625	1.250		2.750	8.750

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/21 In-Line Receptacle Connector with Straight EMI/RFI Backshell



Dimensions in Inches (millimeters) are subject to change without notice.

© 2011 Glenair, Inc. US Navy Approved Connectors U.S. CAGE Code 06324 Rev. 09.16.19 Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912
www.glenair.com E-34 E-Mail: sales@glenair.com

M28840/21
In-Line Receptacle Connector
with Straight EMI/RFI Backshell





MIL-DTL-28840
 Electrical Connectors

J Military Shell Size	Shell Size	Backshell Size Designator	A Cable Entry		A Thread Class 2B	E Max.	L Max.
			Open	Closed			
A	11	A	.312	.188	.750-1P-.2L-DS	.938	6.625
A	11	B	.438	.281		1.125	6.625
A	11	C	.562	.344		1.312	6.625
B	13	A	.312	.188	.875-1P-.2L-DS	.938	6.625
B	13	B	.438	.281		1.125	6.625
B	13	C	.562	.344		1.312	6.625
B	13	D	.652	.375		1.312	7.125
C	15	A	.438	.281	1.062-1P-.2L-DS	1.125	6.625
C	15	B	.562	.344		1.312	6.625
C	15	C	.625	.375		1.312	7.125
C	15	D	.750	.438		1.593	7.188
C	15	E	.312	.188		.938	6.625
D	17	A	.625	.375	1.125-1P-.2L-DS	1.312	7.125
D	17	B	.750	.438		1.593	7.188
D	17	C	.938	.625		1.750	7.188
E	19	A	.625	.375	1.312-1P-.2L-DS	1.312	7.125
E	19	B	.938	.625		1.750	7.250
F	23	A	.750	.438	1.500-1P-.2L-DS	1.593	7.688
F	23	B	.938	.625		1.750	7.812
F	23	C	1.188	.812		2.093	7.938
G	25	A	.938	.625	1.625-1P-.2L-DS	1.750	7.750
G	25	B	1.188	.812		2.093	8.438
G	25	C	1.250	.875		2.093	8.438
G	25	D	1.380	1.000		2.343	8.500
H	29	A	1.188	.812	1.812-1P-.2L-DS	2.093	8.438
H	29	B	1.380	1.000		2.343	8.500
J	33	A	1.380	1.000	2.000-1P-.2L-DS	2.343	8.500
J	33	B	1.625	1.250		2.750	8.750

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/22 Metal Conduit Bushing





Size	MIL- DTL-28840/04 Size Ref.	A +.020 (.50) -.000 (.000)	B +.005 (.12) -.000 (.000)	C +.000 (.000) -.005 (.12)	D +.000 (.000) -.005 (.12)
03	03	.375 (9.53)	.540 (13.71)	.625 (15.87)	.525 (13.34)
04	04	.500 (12.70)	.665 (16.89)	.750 (19.05)	.650 (16.51)
05	05	.625 (15.87)	.780 (19.81)	.875 (22.23)	.775 (19.69)
06	06	.750 (19.05)	.940 (23.88)	1.000 (25.40)	.900 (22.86)
08	08	1.000 (25.40)	1.225 (31.12)	1.375 (34.93)	1.275 (32.39)
10	10	1.250 (31.75)	1.470 (37.34)	1.625 (41.28)	1.525 (38.74)
12	12	1.500 (38.10)	1.740 (44.20)	1.875 (47.65)	1.775 (45.09)
16	16	2.000 (50.80)	2.215 (56.26)	2.375 (60.33)	2.275 (57.79)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/23 "E Nut"




MIL-DTL-28840
Electrical Connectors




Designator	A Thread Class 2B	B Max. Diameter
A (11)	.750-20 UNEF	1.028 (26.11)
B (13)	.875-20 UNEF	1.14 (26.11)
C (15)	1.000-20 UNEF	2.263 (32.08)
D (17)	1.125-18 UNEF	1.387 (35.23)
E (19)	1.250-18 UNEF	1.513 (38.43)
F (23)	1.438-18 UNEF	1.703 (43.51)
G (25)	1.562-18 UNEF	1.825 (46.35)
H (29)	1.876-16 UN	2.143 (54.43)
J (33)	2.062-16 UNS	2.329 (59.16)

Dimensions in Inches (millimeters) are subject to change without notice.


E



M28840/24
Wall Mount Receptacle Mounting Gasket
for MIL-DTL-28840 Connectors



Also for use with
M28876/180-040 connectors





Shell Size	A	B Dia.	C	D Dia.
A (11)	.760 (19.30) .740 (18.80)	.766 (19.46) .750 (19.05)	1.039 (26.39) 1.023 (25.98)	.130 (3.30) .110 (2.79)
B (13)	.853 (21.67) .833 (21.16)	.891 (22.63) .875 (22.22)	1.154 (29.31) 1.138 (28.90)	
C (15)	.978 (24.84) .958 (24.33)	1.078 (27.38) 1.062 (26.97)	1.274 (32.36) 1.258 (31.95)	
D (17)	1.025 (26.04) 1.005 (25.53)	1.141 (28.98) 1.125 (28.58)	1.399 (26.39) 1.383 (35.13)	
E (19)	1.150 (29.21) 1.130 (28.70)	1.338 (33.98) 1.312 (33.32)	1.524 (38.71) 1.508 (38.30)	
F (23)	1.291 (32.79) 1.271 (32.28)	1.516 (38.51) 1.500 (38.10)	1.734 (44.04) 1.718 (43.64)	
G (25)	1.402 (35.61) 1.382 (35.10)	1.641 (41.68) 1.625 (41.28)	1.834 (46.58) 1.818 (46.18)	.157 (3.99) .137 (3.48)
H (29)	1.578 (40.08) 1.558 (39.57)	1.891 (48.03) 1.875 (47.62)	2.154 (54.71) 2.138 (54.30)	
J (33)	1.744 (44.30) 1.724 (43.79)	2.078 (52.78) 2.062 (52.37)	2.344 (59.54) 2.328 (59.13)	

Dimensions in Inches (millimeters) are subject to change without notice.


M28840/25 90° EMI Conduit Adapter



MIL-DTL-28840
Electrical Connectors



STYLE A - EMI/Non-Environmental
(Plain Conduit)



STYLE B - EMI/Environmental
(Jacket Conduit)

Dimensions in Inches (millimeters) are subject to change without notice.

E



M28840/25

90° EMI Conduit Adapter

Dash Number	Designator	A Thread Class 2B	B Diameter Max.	C Thread Class 1	D Max Diameter	Sealing Range	
						Max.	Min.
01	A (11)	.750-20 UNEF	1.028 (26.11)	.875-20 UNEF	1.031 (26.19)	.63 (16.0)	.50 (12.7)
02	B (13)	.875-20 UNEF	1.141 (28.98)	.875-20 UNEF		.63 (16.0)	.50 (12.7)
03				1.000-20 UNEF		.75 (19.1)	.63 (16.0)
04	C (15)	1.000-20 UNEF	1.263 (32.08)	.875-20 UNEF	1.281 (32.58)	.63 (16.0)	.50 (12.7)
05				1.000-20 UNEF		.75 (19.1)	.63 (16.0)
06				1.125-18 UNEF		.88 (22.4)	.75 (19.1)
07				1.250-18 UNEF	1.531 (38.89)	1.00 (25.4)	.88 (22.4)
08	D (17)	1.125-18 UNEF	1.387 (35.23)	1.125-18 UNEF		.88 (22.4)	.75 (19.1)
09				1.250-18 UNEF		1.00 (25.4)	.88 (22.4)
10				1.625-18 UNEF		1.38 (35.1)	1.19 (30.2)
11	E (19)	1.250-18 UNEF	1.513 (38.43)	1.125-18 UNEF	1.781 (45.24)	.88 (22.4)	.75 (19.1)
12				1.250-18 UNEF		1.00 (25.4)	.88 (22.4)
13				1.625-18 UNEF		1.38 (35.1)	1.19 (30.2)
14	F (23)	1.438-18 UNEF	1.703 (45.51)	1.250-18 UNEF		1.00 (25.4)	.88 (22.4)
15				1.625-18 UNEF		1.38 (35.1)	1.18 (30.2)
16				1.875-18 UNS		1.63 (41.4)	1.44 (36.6)
17	G (25)	1.562-18 UNEF	1.825 (46.35)	1.250-18 UNEF	2.031 (51.59)	1.00 (25.4)	.88 (22.4)
18				1.625-18 UNEF		1.38 (35.1)	1.19 (30.2)
19				1.875-18 UNS		1.63 (41.4)	1.44 (36.5)
20				2.125-16 UN		1.88 (47.8)	1.63 (41.4)
21	H (29)	1.875-16 UN	2.143 (54.43)	1.875-18 UNS	2.531 (64.29)	1.63 (41.4)	1.44 (36.6)
22				2.125-16 UN		1.33 (47.8)	1.63 (41.4)
23	J (33)	2.062-16 UNS	2.329 (59.16)	2.125-16 UN	2.531 (64.29)	1.88 (47.8)	1.63 (41.4)
24				2.750-16 UN		2.38 (60.5)	2.13 (54.1)
25	A (11)	.750-20 UNEF	1.028 (26.11)	.875-20 UNEF	1.031 (25.19)	.75 (19.5)	.63 (16.0)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/25 90° EMI Conduit Adapter



MIL-DTL-28840
Electrical Connectors


Dash Number	Designator	Conduit Size M 04	E Max. Dim.	F Max. Dim.	V Thread Class 2	M Max. Dia.	Y Max. Dia.
01	A (11)	03	2.36 (59.9)	3.50 (92.8)	1.000-20 UNEF	1.12 (28.5)	1.19 (30.23)
02	B (13)	03			1.000-20 UNEF	1.12 (28.5)	1.19 (30.23)
03		04			1.188-18 UNEF	1.25 (31.8)	1.38 (35.1)
04	C (15)	03	2.56 (65.0)	3.69 (9.79)	1.000-20 UNEF	1.12 (28.5)	1.39 (35.3)
05		04			1.118-18 UNEF	1.25 (31.8)	1.38 (35.1)
06		05			1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
07		06			1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
08	D (17)	05	2.67 (67.8)	3.81 (101.0)	1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
09		06			1.750-18 UNS	1.62 (42.2)	1.94 (49.3)
10		08			2.00-18 UNS	1.81 (46.0)	2.19 (55.6)
11		05			1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
12	E (19)	06	3.05 (77.5)	4.19 (111.1)	1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
13		08			2.00-18 UNS	1.81 (46.0)	2.19 (55.6)
14		06			1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
15	F (23)	08			2.00-18 UNS	1.81 (46.0)	2.19 (55.6)
16		10			2.250-18 UN	2.18 (55.4)	2.44 (62.0)
17		06			1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
18	G (25)	08			2.00-18 UN	1.81 (46.0)	2.19 (55.6)
19		10			2.250-18 UN	2.18 (55.4)	2.44 (62.0)
20		12	3.33 (84.6)	4.50 (119.4)	2.500-16 UN	2.56 (65.0)	2.69 (68.5)
21	H (29)	10			2.250-16 UN	2.18 (55.4)	2.18 (55.4)
22		12			1.500-16 UN	2.56 (65.0)	2.44 (62.0)
23	J (33)	12	3.70 (94.0)	4.43 (128.1)	2.500-16 UN	2.56 (65.0)	2.69 (68.3)
24		16			3.00-16 UN	3.06 (77.8)	3.19 (81.0)
25	A (11)	04	2.36 (59.9)	3.50 (92.8)	1.133-18 UNF	1.25 (31.8)	1.38 (35.1)

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/26 Plug Connector with Straight EMI/RFI Backshell





Military Shell Size	Shell Size	A Thread Class 2B	Backshell Size Designator	A Cable Entry		E Max.	L Max.
				Open	Closed		
A	11	.750-1P-.2L-DS	A	.312	.188	.938	6.500
			B	.438	.281	1.125	
			C	.562	.344	1.312	
B	13	.875-1P-.2L-DS	A	.312	.188	.938	7.000
			B	.438	.281	1.125	
			C	.562	.344	1.312	
C	15	1.062-1P-.2L-DS	D	.652	.375	1.312	7.000
			A	.438	.281	1.125	
			B	.562	.344	1.312	
D	17	1.125-1P-.2L-DS	C	.625	.375	1.312	7.500
			D	.750	.438	1.593	
			E	.312	.188	.938	
E	19	1.312-1P-.2L-DS	A	.625	.375	1.312	7.625
			B	.938	.625	1.750	
			C	.938	.625	1.750	
F	23	1.500-1P-.2L-DS	A	.750	.438	1.593	8.312
			B	.938	.625	1.750	
			C	1.188	.812	2.093	
G	25	1.625-1P-.2L-DS	A	.938	.625	1.750	8.625
			B	1.188	.812	2.093	
			C	1.250	.875	2.093	
H	29	1.812-1P-.2L-DS	D	1.380	1.000	2.343	
			A	1.188	.812	2.093	
			B	1.380	1.000	2.343	
J	33	2.000-1P-.2L-DS	A	1.380	1.000	2.343	
			B	1.625	1.250	2.750	

Dimensions in inches (millimeters) are subject to change without notice.

M28840/27 45° EMI Conduit Adapter



MIL-DTL-28840
Electrical Connectors



Dimensions in Inches (millimeters) are subject to change without notice.

E



M28840/27

45° EMI Conduit Adapter

Dash No.	Designator	A Thread Class 2B	B Max Diameter	C Thread Class 2	D Max. Diameter	Sealing Range		Conduit Size M 04	E Max. Dim.
						Max.	Min.		
01	A (11)	.750-20 UNEF	1.028 (26.11)	.875-20 UNEF	1.031 (26.19)	.63 (16.0)	.50 (12.7)	03	2.36 (59.9)
02	B (13)	.875-20 UNEF	1.141 (28.98)	.875-20 UNEF		.63 (16.0)	.50 (12.7)	03	
03				1.000-20 UNEF		.75 (19.1)	.63 (16.0)	04	
04	C (15)	1.000-20 UNEF	1.263 (32.08)	.875-20 UNEF	1.281 (32.50)	.63 (16.0)	.50 (12.7)	03	2.56 (65.0)
05				1.000-20 UNEF		.75 (19.1)	.63 (16.0)	04	
06				1.125-18 UNEF		.88 (22.4)	.75 (19.1)	05	
07				1.250-18 UNEF	1.531 (38.80)	1.00 (25.4)	.88 (22.4)	06	2.67 (67.8)
08	D (17)	1.125-18 UNEF	1.387 (38.23)	1.125-18 UNEF		.88 (22.4)	.75 (19.1)	05	
09				1.250-18 UNEF		1.00 (25.4)	.88 (22.4)	06	
10				1.625-18 UNEF		1.38 (35.1)	1.19 (22)	08	
11	E (19)	1.250-18 UNEF	1.513 (38.43)	1.125-18 UNEF		.88 (22.4)	.75 (19.1)	05	
12				1.250-18 UNEF		1.00 (25.4)	.88 (22.4)	06	
13				1.625-18 UNEF	1.781 (45.24)	1.38 (35.1)	1.19 (30.2)	08	3.05 (77.5)
14	F (23)	1.438-18 UNEF	1.703 (45.51)	1.250-18 UNEF		1.000 (25.4)	.88 (22.4)	06	
15				1.625-18 UNEF		1.38 (35.1)	1.19 (30.2)	08	
16				1.875-18 UNS		1.63 (41.4)	1.44 (36.6)	10	
17	G (25)	1.562-18 UNEF	1.825 (46.35)	1.250-18 UNEF		1.00 (25.4)	.88 (22.4)	06	
18				1.625-18 UNEF		1.38 (41.4)	1.19 (30.2)	08	
19				1.875-18 UNS		1.43 (41.4)	1.44 (36.6)	10	
20				2.125-16 UN	2.031 (51.59)	1.88 (47.8)	1.63 (41.4)	12	3.33 (84.6)
21	H (29)	1.875-16 UNS	2.143 (54.43)	1.875-18 UNS		1.63 (41.4)	1.44 (36.6)	10	
22				2.125-16 UN		1.88 (47.8)	1.63 (41.4)	12	
23	J (33)	2.062-16 UNS	2.329 (50.16)	2.125-16 UN	2.531 (64.29)	1.88 (47.8)	1.63 (41.4)	12	3.70 (94.0)
24				2.750-16 UN		2.38 (60.5)	2.13 (54.1)	16	
25	A (11)	.750-20 UNEF	1.028 (16.11)	.875-20 UNEF	1.031 (26.19)	.75 (19.1)	.63 (16.0)	04	2.36 (59.9)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/27 45° EMI Conduit Adapter



MIL-DTL-28840
Electrical Connectors



Dash Number	Designator	F Max. Dim.	V Thread Class 2	M Max. Diameter	Y Max. Diameter
1	A (11)	3.50 (88.9)	1.000-20 UNEF	1.12 (28.5)	1.19 (30.23)
2	B (13)		1.000-20 UNEF	1.12 (28.5)	1.19 (30.23)
3			1.188-18 UNEF	1.25 (31.8)	1.38 (35.1)
4	C (15)	3.69 (93.7)	1.000-20 UNEF	1.12 (28.5)	1.19 (30.23)
5			1.188-18 UNEF	1.25 (31.8)	1.38 (35.1)
6			1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
7		3.81 (96.7)	1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
8	D (17)		1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
9			1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
10			2.00-18 UNS	1.81 (46.0)	2.19 (55.6)
11	E (19)	4.19 (106.4)	1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
12			1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
13			4.50 (114.3)	2.00-18 UNS	1.81 (46.0)
14	F (23)	1.750-18 UNS		1.62 (41.2)	1.94 (49.3)
15		2.00-18 UN		1.81 (46.0)	2.19 (55.6)
16		2.250-16 UN		2.18 (55.4)	2.44 (62.0)
17	G (25)	4.19 (106.4)	1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
18			2.00-18 UN	1.81 (46.0)	2.19 (55.6)
19			2.250-16 UN	2.18 (55.4)	2.44 (62.0)
20		4.50 (114.3)	2.500-16 UN	2.56 (65.0)	2.69 (68.3)
21	H (29)		2.250-16 UN	2.18 (55.4)	2.44 (62.0)
22			2.500-16 UN	2.56 (65.0)	2.69 (68.3)
23	J (33)	4.83 (122.6)	2.500-16 UN	2.56 (65.0)	2.69 (68.3)
24			3.00-16 UN	3.06 (77.8)	3.19 (81.0)
25	A (11)	3.50 (88.9)	1.188-18 UNEF	1.25 (31.8)	1.38 (35.1)

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/28 90° Adapter Assembly Plug



Dimensions in Inches (millimeters) are subject to change without notice.

M28840/28 90° Adapter Assembly Plug



MIL-DTL-28840
Electrical Connectors



J Military Shell Size	Shell Size	Backshell Size Designator	A Cable Entry		A Thread Class 2B	E Max.	H Max.	L Max.	Q Max.
			Open	Closed					
A	11	A	.312	.188	.750-1P-.2L-DS	.938	5.332	3.812	3.250
A	11	B	.438	.281		1.125	5.332	3.812	3.250
A	11	C	.562	.344		1.312	5.457	4.000	3.375
B	13	A	.438	.281	.875-1P-.2L-DS	1.125	5.332	3.812	3.250
B	13	B	.562	.344		1.312	5.457	4.000	3.375
B	13	C	.625	.375		1.312	5.682	4.250	3.500
C	15	A	.438	.281	1.062-1P-.2L-DS	1.125	5.457	4.000	3.375
C	15	B	.562	.344		1.312	5.457	4.000	3.375
C	15	C	.625	.375		1.312	5.682	4.250	3.500
C	15	D	.750	.438		1.593	5.713	4.125	3.500
D	17	A	.625	.375	1.125-1P-.2L-DS	1.312	5.682	4.250	3.500
D	17	B	.750	.438		1.593	5.713	4.250	3.500
E	19	A	.625	.375	1.312-1P-.2L-DS	1.312	5.682	4.250	3.500
E	19	B	.938	.625		1.750	5.832	4.375	3.625
F	23	A	.750	.438	1.500-1P-.2L-DS	1.593	5.738	4.500	3.625
F	23	B	.938	.625		1.750	5.832	4.500	3.625
F	23	C	1.188	.812		2.093	6.019	4.688	3.625
G	25	A	.938	.625	1.625-1P-.2L-DS	1.750	5.832	4.500	3.625
G	25	B	1.188	.812		2.093	6.019	4.688	3.625
G	25	C	1.250	.875		2.093	6.144	4.688	3.750
G	25	D	1.380	1.000		2.343	6.176	4.938	3.750
H	29	A	1.188	.812	1.812-1P-.2L-DS	2.093	6.144	4.812	3.750
H	29	B	1.380	1.000		2.343	6.176	4.938	3.750
J	33	A	1.380	1.000	2.000-1P-.2L-DS	2.343	6.426	5.188	4.000
J	33	B	1.625	1.250		2.750	6.701	5.375	4.000

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/29 Plug Connector with 45° EMI/RFI Backshell



Dimensions in Inches (millimeters) are subject to change without notice.

M28840/29
Plug Connector
with 45° EMI/RFI Backshell



MIL-DTL-28840
 Electrical Connectors




J Military Shell Size	Shell Size	Backshell Size Designator	A Cable Entry		A Thread Class 2B	E Max.	H Max.	L Max.	Q Max.
			Open	Closed					
A	11	A	.312	.188	.750-1P-.2L-DS	.938	5.432	7.404	3.250
A	11	B	.438	.281		1.125	5.432	7.457	3.250
A	11	C	.562	.344		1.312	5.557	7.727	3.375
B	13	A	.438	.281	.875-1P-.2L-DS	1.125	5.432	7.457	3.250
B	13	B	.562	.344		1.312	5.557	7.727	3.375
B	13	C	.625	.375		1.312	5.682	7.938	3.500
C	15	A	.438	.281	1.062-1P-.2L-DS	1.125	5.557	7.671	3.375
C	15	B	.562	.344		1.312	5.557	7.727	3.375
C	15	C	.625	.375		1.312	5.682	7.938	3.500
C	15	D	.750	.438		1.593	5.713	8.058	3.500
D	17	A	.625	.375	1.125-1P-.2L-DS	1.312	5.682	7.938	3.500
D	17	B	.750	.438		1.593	5.713	8.058	3.500
E	19	A	.625	.375	1.312-1P-.2L-DS	1.312	5.682	7.938	3.500
E	19	B	.938	.625		1.750	5.932	8.371	3.625
F	23	A	.750	.438	1.500-1P-.2L-DS	1.593	5.838	8.272	3.625
F	23	B	.938	.625		1.750	5.932	8.371	3.625
F	23	C	1.188	.812		2.093	6.119	8.628	3.625
G	25	A	.938	.625	1.625-1P-.2L-DS	1.750	5.932	8.371	3.625
G	25	B	1.188	.812		2.093	6.119	8.628	3.625
G	25	C	1.250	.875		2.093	6.244	8.841	3.750
G	25	D	1.380	1.000		2.343	6.276	8.950	3.750
H	29	A	1.188	.812	1.812-1P-.2L-DS	2.093	6.244	8.841	3.750
H	29	B	1.380	1.000		2.343	6.276	8.950	3.750
J	33	A	1.380	1.000	2.000-1P-.2L-DS	2.343	6.526	9.377	4.000
J	33	B	1.625	1.250		2.750	6.801	9.659	4.000

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/30 Metal Conduit Coupler Styles A and B





Dash Number	Conduit Size	Sealing Range		C Thread	M Max Diameter	V Thread Class 2	Y Max Diameter
		Max.	Min.				
03	03	.63 (16.0)	.50 (12.7)	.875-20 UNEF	1.12 (28.5)	1.00-20 UNEF	1.19 (30.23)
04	04	.75 (19.1)	.63 (16.0)	1.000-20 UNEF	1.25 (31.8)	1.188-18 UNEF	1.38 (35.1)
05	05	.88 (22.4)	.75 (18.1)	1.125-18 UNEF	1.43 (36.3)	1.438-18 UNEF	1.63 (41.4)
06	06	1.00 (25.4)	.88 (22.4)	1.250-18 UNEF	1.62 (41.2)	1.750-18 UNS	1.94 (49.3)
08	08	1.38 (35.1)	1.19 (30.2)	1.625-18 UNEF	1.81 (46.0)	2.00-18 UNS	2.19 (55.6)
10	10	1.63 (41.4)	1.44 (36.6)	1.875-18 UNS	2.18 (55.4)	2.250-16 UN	2.44 (62.0)
12	12	1.88 (47.8)	1.63 (41.4)	2.125-16 UN	2.56 (65.0)	2.50-16 UN	2.69 (68.3)
16	16	2.38 (60.5)	2.13 (54.1)	2.750-16 UN	3.06 (77.8)	3.00-16 UN	3.19 (81.0)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/19 Plug Connector with 45° Strain Relief



MIL-DTL-28840
Electrical Connectors





Designator	A Thread Class 2B	F Cable Entry		L Max.	Q Max.	Z Max.	Max. O.D. Over Rear Clamps
		Open	Closed				
A (11)	.750-1P-.2L-DS	.286	.177	3.125	1.028	.928	.832
B (13)	.875-1P-.2L-DS	.286		3.125	1.141	.928	
C (15)	1.062-1P-.2L-DS	.416	.250	3.250	1.263	.991	.989
D (17)	1.125-1P-.2L-DS	.476	.291	3.312	1.387	1.110	1.094
E (19)	1.312-1P-.2L-DS	.626	.348	3.375	1.513	1.172	1.319
F (23)	1.500-1P-.2L-DS	.831	.429	3.438	1.703	1.235	1.557
G (25)	1.625-1P-.2L-DS	.956	.523	3.500	1.825	1.297	1.653
H (29)	1.812-1P-.2L-DS	1.081	.643	3.750	2.143	1.543	1.819
J (33)	2.000-1P-.2L-DS	1.187	.704	3.875	2.329	1.668	2.020

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/20 Receptacle Connector with Straight EMI/RFI Backshell



Dimensions in Inches (millimeters) are subject to change without notice.

M28840/20 Receptacle Connector with Straight EMI/RFI Backshell



MIL-DTL-28840
Electrical Connectors



J Military Shell Size	Shell Size	Backshell Size Designator	A Cable Entry		A Thread Class 2B	E Max.	L Max.
			Open	Closed			
A	11	A	.312	.188	.750-1P-.2L-DS	.938	6.625
A	11	B	.438	.281		1.125	6.625
A	11	C	.562	.344		1.312	6.625
B	13	A	.312	.188	.875-1P-.2L-DS	.938	6.625
B	13	B	.438	.281		1.125	6.625
B	13	C	.562	.344		1.312	6.625
B	13	D	.652	.375		1.312	7.125
C	15	A	.438	.281	1.062-1P-.2L-DS	1.125	6.625
C	15	B	.562	.344		1.312	6.625
C	15	C	.625	.375		1.312	7.125
C	15	D	.750	.438		1.593	7.188
C	15	E	.312	.188		.938	6.625
D	17	A	.625	.375	1.125-1P-.2L-DS	1.312	7.125
D	17	B	.750	.438		1.593	7.188
D	17	C	.938	.625		1.750	7.188
E	19	A	.625	.375	1.312-1P-.2L-DS	1.312	7.125
E	19	B	.938	.625		1.750	7.250
F	23	A	.750	.438	1.500-1P-.2L-DS	1.593	7.688
F	23	B	.938	.625		1.750	7.812
F	23	C	1.188	.812		2.093	7.938
G	25	A	.938	.625	1.625-1P-.2L-DS	1.750	7.750
G	25	B	1.188	.812		2.093	8.438
G	25	C	1.250	.875		2.093	8.438
G	25	D	1.380	1.000		2.343	8.500
H	29	A	1.188	.812	1.812-1P-.2L-DS	2.093	8.438
H	29	B	1.380	1.000		2.343	8.500
J	33	A	1.380	1.000	2.000-1P-.2L-DS	2.343	8.500
J	33	B	1.625	1.250		2.750	8.750

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/21 In-Line Receptacle Connector with Straight EMI/RFI Backshell



Dimensions in Inches (millimeters) are subject to change without notice.

M28840/21

In-Line Receptacle Connector with Straight EMI/RFI Backshell



MIL-DTL-28840
Electrical Connectors



J Military Shell Size	Shell Size	Backshell Size Designator	A Cable Entry		A Thread Class 2B	E Max.	L Max.
			Open	Closed			
A	11	A	.312	.188	.750-1P-.2L-DS	.938	6.625
A	11	B	.438	.281		1.125	6.625
A	11	C	.562	.344		1.312	6.625
B	13	A	.312	.188	.875-1P-.2L-DS	.938	6.625
B	13	B	.438	.281		1.125	6.625
B	13	C	.562	.344		1.312	6.625
B	13	D	.652	.375		1.312	7.125
C	15	A	.438	.281	1.062-1P-.2L-DS	1.125	6.625
C	15	B	.562	.344		1.312	6.625
C	15	C	.625	.375		1.312	7.125
C	15	D	.750	.438		1.593	7.188
C	15	E	.312	.188		.938	6.625
D	17	A	.625	.375	1.125-1P-.2L-DS	1.312	7.125
D	17	B	.750	.438		1.593	7.188
D	17	C	.938	.625		1.750	7.188
E	19	A	.625	.375	1.312-1P-.2L-DS	1.312	7.125
E	19	B	.938	.625		1.750	7.250
F	23	A	.750	.438	1.500-1P-.2L-DS	1.593	7.688
F	23	B	.938	.625		1.750	7.812
F	23	C	1.188	.812		2.093	7.938
G	25	A	.938	.625	1.625-1P-.2L-DS	1.750	7.750
G	25	B	1.188	.812		2.093	8.438
G	25	C	1.250	.875		2.093	8.438
G	25	D	1.380	1.000		2.343	8.500
H	29	A	1.188	.812	1.812-1P-.2L-DS	2.093	8.438
H	29	B	1.380	1.000		2.343	8.500
J	33	A	1.380	1.000	2.000-1P-.2L-DS	2.343	8.500
J	33	B	1.625	1.250		2.750	8.750

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/22 Metal Conduit Bushing





Size	MIL- DTL-28840/04 Size Ref.	A +.020 (.50) -.000 (.000)	B +.005 (.12) -.000 (.000)	C +.000 (.000) -.005 (.12)	D +.000 (.000) -.005 (.12)
03	03	.375 (9.53)	.540 (13.71)	.625 (15.87)	.525 (13.34)
04	04	.500 (12.70)	.665 (16.89)	.750 (19.05)	.650 (16.51)
05	05	.625 (15.87)	.780 (19.81)	.875 (22.23)	.775 (19.69)
06	06	.750 (19.05)	.940 (23.88)	1.000 (25.40)	.900 (22.86)
08	08	1.000 (25.40)	1.225 (31.12)	1.375 (34.93)	1.275 (32.39)
10	10	1.250 (31.75)	1.470 (37.34)	1.625 (41.28)	1.525 (38.74)
12	12	1.500 (38.10)	1.740 (44.20)	1.875 (47.65)	1.775 (45.09)
16	16	2.000 (50.80)	2.215 (56.26)	2.375 (60.33)	2.275 (57.79)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/23 "E Nut"



MIL-DTL-28840
Electrical Connectors



Designator	A Thread Class 2B	B Max. Diameter
A (11)	.750-20 UNEF	1.028 (26.11)
B (13)	.875-20 UNEF	1.14 (26.11)
C (15)	1.000-20 UNEF	2.263 (32.08)
D (17)	1.125-18 UNEF	1.387 (35.23)
E (19)	1.250-18 UNEF	1.513 (38.43)
F (23)	1.438-18 UNEF	1.703 (43.51)
G (25)	1.562-18 UNEF	1.825 (46.35)
H (29)	1.876-16 UN	2.143 (54.43)
J (33)	2.062-16 UNS	2.329 (59.16)


Dimensions in Inches (millimeters) are subject to change without notice.

E




M28840/24

Wall Mount Receptacle Mounting Gasket for MIL-DTL-28840 Connectors



Also for use with
M28876/180-040 connectors



E



Shell Size	A	B Dia.	C	D Dia.
A (11)	.760 (19.30) .740 (18.80)	.766 (19.46) .750 (19.05)	1.039 (26.39) 1.023 (25.98)	.130 (3.30) .110 (2.79)
B (13)	.853 (21.67) .833 (21.16)	.891 (22.63) .875 (22.22)	1.154 (29.31) 1.138 (28.90)	
C (15)	.978 (24.84) .958 (24.33)	1.078 (27.38) 1.062 (26.97)	1.274 (32.36) 1.258 (31.95)	
D (17)	1.025 (26.04) 1.005 (25.53)	1.141 (28.98) 1.125 (28.58)	1.399 (26.39) 1.383 (35.13)	
E (19)	1.150 (29.21) 1.130 (28.70)	1.338 (33.98) 1.312 (33.32)	1.524 (38.71) 1.508 (38.30)	
F (23)	1.291 (32.79) 1.271 (32.28)	1.516 (38.51) 1.500 (38.10)	1.734 (44.04) 1.718 (43.64)	
G (25)	1.402 (35.61) 1.382 (35.10)	1.641 (41.68) 1.625 (41.28)	1.834 (46.58) 1.818 (46.18)	.157 (3.99) .137 (3.48)
H (29)	1.578 (40.08) 1.558 (39.57)	1.891 (48.03) 1.875 (47.62)	2.154 (54.71) 2.138 (54.30)	
J (33)	1.744 (44.30) 1.724 (43.79)	2.078 (52.78) 2.062 (52.37)	2.344 (59.54) 2.328 (59.13)	

Dimensions in Inches (millimeters) are subject to change without notice.


M28840/25 90° EMI Conduit Adapter



MIL-DTL-28840
Electrical Connectors



STYLE A - EMI/Non-Environmental
(Plain Conduit)



STYLE B - EMI/Environmental
(Jacket Conduit)

Dimensions in Inches (millimeters) are subject to change without notice.

E



M28840/25

90° EMI Conduit Adapter

Dash Number	Designator	A Thread Class 2B	B Diameter Max.	C Thread Class 1	D Max Diameter	Sealing Range	
						Max.	Min.
01	A (11)	.750-20 UNEF	1.028 (26.11)	.875-20 UNEF	1.031 (26.19)	.63 (16.0)	.50 (12.7)
02	B (13)	.875-20 UNEF	1.141 (28.98)	.875-20 UNEF		.63 (16.0)	.50 (12.7)
03				1.000-20 UNEF		.75 (19.1)	.63 (16.0)
04	C (15)	1.000-20 UNEF	1.263 (32.08)	.875-20 UNEF	1.281 (32.58)	.63 (16.0)	.50 (12.7)
05				1.000-20 UNEF		.75 (19.1)	.63 (16.0)
06				1.125-18 UNEF		.88 (22.4)	.75 (19.1)
07				1.250-18 UNEF	1.531 (38.89)	1.00 (25.4)	.88 (22.4)
08	D (17)	1.125-18 UNEF	1.387 (35.23)	1.125-18 UNEF		.88 (22.4)	.75 (19.1)
09				1.250-18 UNEF		1.00 (25.4)	.88 (22.4)
10				1.625-18 UNEF		1.38 (35.1)	1.19 (30.2)
11	E (19)	1.250-18 UNEF	1.513 (38.43)	1.125-18 UNEF	1.781 (45.24)	.88 (22.4)	.75 (19.1)
12				1.250-18 UNEF		1.00 (25.4)	.88 (22.4)
13				1.625-18 UNEF		1.38 (35.1)	1.19 (30.2)
14	F (23)	1.438-18 UNEF	1.703 (45.51)	1.250-18 UNEF		1.00 (25.4)	.88 (22.4)
15				1.625-18 UNEF		1.38 (35.1)	1.18 (30.2)
16				1.875-18 UNS		1.63 (41.4)	1.44 (36.6)
17	G (25)	1.562-18 UNEF	1.825 (46.35)	1.250-18 UNEF	2.031 (51.59)	1.00 (25.4)	.88 (22.4)
18				1.625-18 UNEF		1.38 (35.1)	1.19 (30.2)
19				1.875-18 UNS		1.63 (41.4)	1.44 (36.5)
20				2.125-16 UN		1.88 (47.8)	1.63 (41.4)
21	H (29)	1.875-16 UN	2.143 (54.43)	1.875-18 UNS	2.531 (64.29)	1.63 (41.4)	1.44 (36.6)
22				2.125-16 UN		1.33 (47.8)	1.63 (41.4)
23	J (33)	2.062-16 UNS	2.329 (59.16)	2.125-16 UN	2.531 (64.29)	1.88 (47.8)	1.63 (41.4)
24				2.750-16 UN		2.38 (60.5)	2.13 (54.1)
25	A (11)	.750-20 UNEF	1.028 (26.11)	.875-20 UNEF	1.031 (25.19)	.75 (19.5)	.63 (16.0)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/25 90° EMI Conduit Adapter



MIL-DTL-28840
Electrical Connectors


Dash Number	Designator	Conduit Size M 04	E Max. Dim.	F Max. Dim.	V Thread Class 2	M Max. Dia.	Y Max. Dia.
01	A (11)	03	2.36 (59.9)	3.50 (92.8)	1.000-20 UNEF	1.12 (28.5)	1.19 (30.23)
02	B (13)	03			1.000-20 UNEF	1.12 (28.5)	1.19 (30.23)
03		04			1.188-18 UNEF	1.25 (31.8)	1.38 (35.1)
04	C (15)	03	2.56 (65.0)	3.69 (9.79)	1.000-20 UNEF	1.12 (28.5)	1.39 (35.3)
05		04			1.118-18 UNEF	1.25 (31.8)	1.38 (35.1)
06		05			1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
07		06			1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
08	D (17)	05	2.67 (67.8)	3.81 (101.0)	1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
09		06			1.750-18 UNS	1.62 (42.2)	1.94 (49.3)
10		08			2.00-18 UNS	1.81 (46.0)	2.19 (55.6)
11		05			1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
12	E (19)	06	3.05 (77.5)	4.19 (111.1)	1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
13		08			2.00-18 UNS	1.81 (46.0)	2.19 (55.6)
14		06			1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
15	F (23)	08			2.00-18 UNS	1.81 (46.0)	2.19 (55.6)
16		10			2.250-18 UN	2.18 (55.4)	2.44 (62.0)
17		06			1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
18	G (25)	08			2.00-18 UN	1.81 (46.0)	2.19 (55.6)
19		10			2.250-18 UN	2.18 (55.4)	2.44 (62.0)
20		12	3.33 (84.6)	4.50 (119.4)	2.500-16 UN	2.56 (65.0)	2.69 (68.5)
21	H (29)	10			2.250-16 UN	2.18 (55.4)	2.18 (55.4)
22		12			1.500-16 UN	2.56 (65.0)	2.44 (62.0)
23	J (33)	12	3.70 (94.0)	4.43 (128.1)	2.500-16 UN	2.56 (65.0)	2.69 (68.3)
24		16			3.00-16 UN	3.06 (77.8)	3.19 (81.0)
25	A (11)	04	2.36 (59.9)	3.50 (92.8)	1.133-18 UNF	1.25 (31.8)	1.38 (35.1)

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/26 Plug Connector with Straight EMI/RFI Backshell





Military Shell Size	Shell Size	A Thread Class 2B	Backshell Size Designator	A Cable Entry		E Max.	L Max.
				Open	Closed		
A	11	.750-1P-.2L-DS	A	.312	.188	.938	6.500
			B	.438	.281	1.125	
			C	.562	.344	1.312	
B	13	.875-1P-.2L-DS	A	.312	.188	.938	7.000
			B	.438	.281	1.125	
			C	.562	.344	1.312	
C	15	1.062-1P-.2L-DS	D	.652	.375	1.312	7.000
			A	.438	.281	1.125	
			B	.562	.344	1.312	
D	17	1.125-1P-.2L-DS	C	.625	.375	1.312	7.000
			D	.750	.438	1.593	
			E	.938	.625	1.750	
E	19	1.312-1P-.2L-DS	A	.625	.375	1.312	7.500
			B	.938	.625	1.750	7.625
			C	.750	.438	1.593	7.812
F	23	1.500-1P-.2L-DS	A	.938	.625	1.750	7.625
			B	1.188	.812	2.093	8.312
			C	.938	.625	1.750	
G	25	1.625-1P-.2L-DS	A	1.188	.812	2.093	
			B	1.380	1.000	2.343	
			C	1.250	.875	2.093	
H	29	1.812-1P-.2L-DS	D	1.380	1.000	2.343	8.625
			A	1.188	.812	2.093	
			B	1.380	1.000	2.343	
J	33	2.000-1P-.2L-DS	A	1.380	1.000	2.343	8.625
			B	1.625	1.250	2.750	

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/27 45° EMI Conduit Adapter



MIL-DTL-28840
Electrical Connectors



Dimensions in Inches (millimeters) are subject to change without notice.



M28840/27

45° EMI Conduit Adapter

Dash No.	Designator	A Thread Class 2B	B Max Diameter	C Thread Class 2	D Max. Diameter	Sealing Range		Conduit Size M 04	E Max. Dim.
						Max.	Min.		
01	A (11)	.750-20 UNEF	1.028 (26.11)	.875-20 UNEF	1.031 (26.19)	.63 (16.0)	.50 (12.7)	03	2.36 (59.9)
02	B (13)	.875-20 UNEF	1.141 (28.98)	.875-20 UNEF		.63 (16.0)	.50 (12.7)	03	
03				1.000-20 UNEF		.75 (19.1)	.63 (16.0)	04	
04	C (15)	1.000-20 UNEF	1.263 (32.08)	.875-20 UNEF	1.281 (32.50)	.63 (16.0)	.50 (12.7)	03	2.56 (65.0)
05				1.000-20 UNEF		.75 (19.1)	.63 (16.0)	04	
06				1.125-18 UNEF		.88 (22.4)	.75 (19.1)	05	
07				1.250-18 UNEF	1.531 (38.80)	1.00 (25.4)	.88 (22.4)	06	2.67 (67.8)
08	D (17)	1.125-18 UNEF	1.387 (38.23)	1.125-18 UNEF		.88 (22.4)	.75 (19.1)	05	
09				1.250-18 UNEF		1.00 (25.4)	.88 (22.4)	06	
10				1.625-18 UNEF		1.38 (35.1)	1.19 (22)	08	
11				1.125-18 UNEF		.88 (22.4)	.75 (19.1)	05	
12	E (19)	1.250-18 UNEF	1.513 (38.43)	1.250-18 UNEF	1.781 (45.24)	1.00 (25.4)	.88 (22.4)	06	3.05 (77.5)
13				1.625-18 UNEF		1.38 (35.1)	1.19 (30.2)	08	
14	F (23)	1.438-18 UNEF	1.703 (45.51)	1.250-18 UNEF		1.000 (25.4)	.88 (22.4)	06	
15				1.625-18 UNEF		1.38 (35.1)	1.19 (30.2)	08	
16				1.875-18 UNS		1.63 (41.4)	1.44 (36.6)	10	
17				1.250-18 UNEF		1.00 (25.4)	.88 (22.4)	06	
18	G (25)	1.562-18 UNEF	1.825 (46.35)	1.625-18 UNEF	2.031 (51.59)	1.38 (41.4)	1.19 (30.2)	08	3.33 (84.6)
19				1.875-18 UNS		1.43 (41.4)	1.44 (36.6)	10	
20				2.125-16 UN		1.88 (47.8)	1.63 (41.4)	12	
21				1.875-18 UNS		1.63 (41.4)	1.44 (36.6)	10	
22	H (29)	1.875-16 UNS	2.143 (54.43)	2.125-16 UN		1.88 (47.8)	1.63 (41.4)	12	
23	J (33)	2.062-16 UNS	2.329 (50.16)	2.125-16 UN	2.531 (64.29)	1.88 (47.8)	1.63 (41.4)	12	3.70 (94.0)
24				2.750-16 UN		2.38 (60.5)	2.13 (54.1)	16	
25	A (11)	.750-20 UNEF	1.028 (16.11)	.875-20 UNEF	1.031 (26.19)	.75 (19.1)	.63 (16.0)	04	2.36 (59.9)

Dimensions in Inches (millimeters) are subject to change without notice.

M28840/27 45° EMI Conduit Adapter



MIL-DTL-28840
Electrical Connectors



Dash Number	Designator	F Max. Dim.	V Thread Class 2	M Max. Diameter	Y Max. Diameter
1	A (11)	3.50 (88.9)	1.000-20 UNEF	1.12 (28.5)	1.19 (30.23)
2	B (13)		1.000-20 UNEF	1.12 (28.5)	1.19 (30.23)
3			1.188-18 UNEF	1.25 (31.8)	1.38 (35.1)
4	C (15)	3.69 (93.7)	1.000-20 UNEF	1.12 (28.5)	1.19 (30.23)
5			1.188-18 UNEF	1.25 (31.8)	1.38 (35.1)
6			1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
7	D (17)	3.81 (96.7)	1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
8			1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
9			1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
10			2.00-18 UNS	1.81 (46.0)	2.19 (55.6)
11	E (19)	4.19 (106.4)	1.438-18 UNEF	1.43 (36.3)	1.63 (41.4)
12			1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
13			2.00-18 UNS	1.81 (46.0)	2.19 (55.6)
14	F (23)	4.19 (106.4)	1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
15			2.00-18 UN	1.81 (46.0)	2.19 (55.6)
16			2.250-16 UN	2.18 (55.4)	2.44 (62.0)
17	G (25)	4.19 (106.4)	1.750-18 UNS	1.62 (41.2)	1.94 (49.3)
18			2.00-18 UN	1.81 (46.0)	2.19 (55.6)
19			2.250-16 UN	2.18 (55.4)	2.44 (62.0)
20	H (29)	4.50 (114.3)	2.500-16 UN	2.56 (65.0)	2.69 (68.3)
21			2.250-16 UN	2.18 (55.4)	2.44 (62.0)
22			2.500-16 UN	2.56 (65.0)	2.69 (68.3)
23	J (33)	4.83 (122.6)	2.500-16 UN	2.56 (65.0)	2.69 (68.3)
24			3.00-16 UN	3.06 (77.8)	3.19 (81.0)
25	A (11)	3.50 (88.9)	1.188-18 UNEF	1.25 (31.8)	1.38 (35.1)

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/28 90° Adapter Assembly Plug



Dimensions in Inches (millimeters) are subject to change without notice.

M28840/28 90° Adapter Assembly Plug



MIL-DTL-28840
Electrical Connectors



J Military Shell Size	Shell Size	Backshell Size Designator	A Cable Entry		A Thread Class 2B	E Max.	H Max.	L Max.	Q Max.
			Open	Closed					
A	11	A	.312	.188	.750-1P-.2L-DS	.938	5.332	3.812	3.250
A	11	B	.438	.281		1.125	5.332	3.812	3.250
A	11	C	.562	.344		1.312	5.457	4.000	3.375
B	13	A	.438	.281	.875-1P-.2L-DS	1.125	5.332	3.812	3.250
B	13	B	.562	.344		1.312	5.457	4.000	3.375
B	13	C	.625	.375		1.312	5.682	4.250	3.500
C	15	A	.438	.281	1.062-1P-.2L-DS	1.125	5.457	4.000	3.375
C	15	B	.562	.344		1.312	5.457	4.000	3.375
C	15	C	.625	.375		1.312	5.682	4.250	3.500
C	15	D	.750	.438		1.593	5.713	4.125	3.500
D	17	A	.625	.375	1.125-1P-.2L-DS	1.312	5.682	4.250	3.500
D	17	B	.750	.438		1.593	5.713	4.250	3.500
E	19	A	.625	.375	1.312-1P-.2L-DS	1.312	5.682	4.250	3.500
E	19	B	.938	.625		1.750	5.832	4.375	3.625
F	23	A	.750	.438	1.500-1P-.2L-DS	1.593	5.738	4.500	3.625
F	23	B	.938	.625		1.750	5.832	4.500	3.625
F	23	C	1.188	.812		2.093	6.019	4.688	3.625
G	25	A	.938	.625	1.625-1P-.2L-DS	1.750	5.832	4.500	3.625
G	25	B	1.188	.812		2.093	6.019	4.688	3.625
G	25	C	1.250	.875		2.093	6.144	4.688	3.750
G	25	D	1.380	1.000		2.343	6.176	4.938	3.750
H	29	A	1.188	.812	1.812-1P-.2L-DS	2.093	6.144	4.812	3.750
H	29	B	1.380	1.000		2.343	6.176	4.938	3.750
J	33	A	1.380	1.000	2.000-1P-.2L-DS	2.343	6.426	5.188	4.000
J	33	B	1.625	1.250		2.750	6.701	5.375	4.000

E

Dimensions in Inches (millimeters) are subject to change without notice.



M28840/29 Plug Connector with 45° EMI/RFI Backshell



Dimensions in Inches (millimeters) are subject to change without notice.

M28840/29
Plug Connector
with 45° EMI/RFI Backshell



MIL-DTL-28840
 Electrical Connectors




J Military Shell Size	Shell Size	Backshell Size Designator	A Cable Entry		A Thread Class 2B	E Max.	H Max.	L Max.	Q Max.
			Open	Closed					
A	11	A	.312	.188	.750-1P-.2L-DS	.938	5.432	7.404	3.250
A	11	B	.438	.281		1.125	5.432	7.457	3.250
A	11	C	.562	.344		1.312	5.557	7.727	3.375
B	13	A	.438	.281	.875-1P-.2L-DS	1.125	5.432	7.457	3.250
B	13	B	.562	.344		1.312	5.557	7.727	3.375
B	13	C	.625	.375		1.312	5.682	7.938	3.500
C	15	A	.438	.281	1.062-1P-.2L-DS	1.125	5.557	7.671	3.375
C	15	B	.562	.344		1.312	5.557	7.727	3.375
C	15	C	.625	.375		1.312	5.682	7.938	3.500
C	15	D	.750	.438		1.593	5.713	8.058	3.500
D	17	A	.625	.375	1.125-1P-.2L-DS	1.312	5.682	7.938	3.500
D	17	B	.750	.438		1.593	5.713	8.058	3.500
E	19	A	.625	.375	1.312-1P-.2L-DS	1.312	5.682	7.938	3.500
E	19	B	.938	.625		1.750	5.932	8.371	3.625
F	23	A	.750	.438	1.500-1P-.2L-DS	1.593	5.838	8.272	3.625
F	23	B	.938	.625		1.750	5.932	8.371	3.625
F	23	C	1.188	.812		2.093	6.119	8.628	3.625
G	25	A	.938	.625	1.625-1P-.2L-DS	1.750	5.932	8.371	3.625
G	25	B	1.188	.812		2.093	6.119	8.628	3.625
G	25	C	1.250	.875		2.093	6.244	8.841	3.750
G	25	D	1.380	1.000		2.343	6.276	8.950	3.750
H	29	A	1.188	.812	1.812-1P-.2L-DS	2.093	6.244	8.841	3.750
H	29	B	1.380	1.000		2.343	6.276	8.950	3.750
J	33	A	1.380	1.000	2.000-1P-.2L-DS	2.343	6.526	9.377	4.000
J	33	B	1.625	1.250		2.750	6.801	9.659	4.000

E

Dimensions in Inches (millimeters) are subject to change without notice.




M28840/30 Metal Conduit Coupler Styles A and B



Dash Number	Conduit Size	Sealing Range		C Thread	M Max Diameter	V Thread Class 2	Y Max Diameter
		Max.	Min.				
03	03	.63 (16.0)	.50 (12.7)	.875-20 UNEF	1.12 (28.5)	1.00-20 UNEF	1.19 (30.23)
04	04	.75 (19.1)	.63 (16.0)	1.000-20 UNEF	1.25 (31.8)	1.188-18 UNEF	1.38 (35.1)
05	05	.88 (22.4)	.75 (18.1)	1.125-18 UNEF	1.43 (36.3)	1.438-18 UNEF	1.63 (41.4)
06	06	1.00 (25.4)	.88 (22.4)	1.250-18 UNEF	1.62 (41.2)	1.750-18 UNS	1.94 (49.3)
08	08	1.38 (35.1)	1.19 (30.2)	1.625-18 UNEF	1.81 (46.0)	2.00-18 UNS	2.19 (55.6)
10	10	1.63 (41.4)	1.44 (36.6)	1.875-18 UNS	2.18 (55.4)	2.250-16 UN	2.44 (62.0)
12	12	1.88 (47.8)	1.63 (41.4)	2.125-16 UN	2.56 (65.0)	2.50-16 UN	2.69 (68.3)
16	16	2.38 (60.5)	2.13 (54.1)	2.750-16 UN	3.06 (77.8)	3.00-16 UN	3.19 (81.0)

Dimensions in Inches (millimeters) are subject to change without notice.

907-003 Glenair MIL-DTL-28840 Commercial Equivalent Box Mount Receptacle with PC Tail Contacts



Symbol	Material	Finish Description
NF	Aluminum	Cadmium O.D. over Electroless Nickel
ZN		Zinc Nickel
MT		Nickel-PTFE, 1000 Hour Grey™
Z1	316 Type Stainless Steel	Passivate
ZU		Black Cadmium Olive Drab over Nickel


Military Shell Size	Shell Size	A Thread Class 2A	O Ref. Mtg. Max.	R True Position ϕ to ϕ	S	T	GG Diameter Max.
A	11	.750-.1P-.2L-D.S.	.812	.750	1.043 1.003	.130 .115	.758
B	13	.875-.1P-.2L-D.S.	.937	.843	1.158 1.118		.880
C	15	1.062-.1P-.2L-D.S.	1.124	.968	1.278 1.238		1.005
D	17	1.125-.1P-.2L-D.S.	1.187	1.015	1.403 1.363		1.130
E	19	1.312-.1P-.2L-D.S.	1.374	1.140	1.528 1.488		1.255
F	23	1.500-.1P-.2L-D.S.	1.562	1.281	1.738 1.698		1.443
G	25	1.625-.1P-.2L-D.S.	1.687	1.392	1.838 1.798	.157 .142	1.567
H	29	1.812-.1P-.2L-D.S.	1.937	1.568	2.158 2.118		1.880
J	33	2.000-.1P-.2L-D.S.	2.124	1.734	2.348 2.308		2.067

Dimensions in Inches (millimeters) are subject to change without notice.



907-037 Glenair MIL-DTL-28840 Commercial Equivalent Box Mount Receptacle with PC Tail Contacts

Basic Part Number	Shell Size (See Table)	Key Position
907-037	NF 25	S 1
Finish <i>NF - Olive Drab Cadmium / Nickel</i>		Contact Style <i>S - Socket Contacts / PC Tail</i>



Dimensions in Inches (millimeters) are subject to change without notice.

907-037
Glenair MIL-DTL-28840 Commercial Equivalent
Box Mount Receptacle with PC Tail Contacts



Comm Equiv 28840
Connectors/Accessories



Symbol	Material	Finish Description
NF	Aluminum	Cadmium O.D. over Electroless Nickel
ZN		Zinc Nickel
MT		Nickel-PTFE, 1000 Hour Grey™
Z1	316 Type Stainless Steel	Passivate
ZU		Black Cadmium Olive Drab over Nickel

Military Shell Size	Shell Size	A Thread Class 2A	O Ref. Mtg. Max.	R True Position ⌀ to ⌀	S	T	GG Diameter Max.
A	11	.750-.1P-.2L-D.S.	.812	.750	1.043 1.003	#4-40	.758
B	13	.875-.1P-.2L-D.S.	.937	.843	1.158 1.118	#4-40	.880
C	15	1.062-.1P-.2L-D.S.	1.124	.968	1.278 1.238	#4-40	1.005
D	17	1.125-.1P-.2L-D.S.	1.187	1.015	1.403 1.363	#4-40	1.130
E	19	1.312-.1P-.2L-D.S.	1.374	1.140	1.528 1.488	#4-40	1.255
F	23	1.500-.1P-.2L-D.S.	1.562	1.281	1.738 1.698	#4-40	1.443
G	25	1.625-.1P-.2L-D.S.	1.687	1.392	1.838 1.798	#6-32	1.567
H	29	1.812-.1P-.2L-D.S.	1.937	1.568	2.158 2.118	#6-32	1.880
J	33	2.000-.1P-.2L-D.S.	2.124	1.734	2.348 2.308	#6-32	2.067

Dimensions in Inches (millimeters) are subject to change without notice.



240-288A Sav-Con® Filtered Connector Saver for MIL-DTL-28840 Connectors



Military Shell Size	Shell Size	A Thread Class 2A	B Thread Class 2B	Ø C Max
A	11	.750-.1P-.2L-D.S.	.750-.1P-.2L-D.S.	1.028
B	13	.875-.1P-.2L-D.S.	.875-.1P-.2L-D.S.	1.141
C	15	1.062-.1P-.2L-D.S.	1.062-.1P-.2L-D.S.	1.263
D	17	1.125-.1P-.2L-D.S.	1.125-.1P-.2L-D.S.	1.387
E	19	1.312-.1P-.2L-D.S.	1.312-.1P-.2L-D.S.	1.513
F	23	1.500-.1P-.2L-D.S.	1.500-.1P-.2L-D.S.	1.703
G	25	1.625-.1P-.2L-D.S.	1.625-.1P-.2L-D.S.	1.825
H	29	1.812-.1P-.2L-D.S.	1.812-.1P-.2L-D.S.	2.143
J	33	2.000-.1P-.2L-D.S.	2.000-.1P-.2L-D.S.	2.329

Dimensions in Inches (millimeters) are subject to change without notice.

240-288A
Sav-Con® Filtered Connector Saver
for MIL-DTL-28840 Connectors



Symbol	Material	Finish Description
M	Aluminum	Electroless Nickel
MT	Aluminum	Nickel-PTFE, 1000 Hour Grey™
NF	Aluminum	Cadmium O.D. over Electroless Nickel
P	Stainless Steel	Electrodeposited Nickel




Filter Type	
P	PI-Section
C	C-Section

Class	PI-Section (pF)	C-Section (pF)
X	160,000 - 240,000	80,000 - 120,000
Y	80,000 - 120,000	40,000 - 60,000
Z	60,000 - 91,000	30,000 - 45,000
A	38,000 - 56,000	19,000 - 28,000
B	32,000 - 45,000	16,000 - 22,500
C	18,000 - 33,000	9,000 - 16,500
D	8,000 - 12,000	4,000 - 6,000
E	3,300 - 5,000	1,650 - 2,500
F	800 - 1,300	400 - 650
G	400 - 600	200 - 300

Dimensions in Inches (millimeters) are subject to change without notice.



240-288W Filtered Wall Mount Receptacle MIL-DTL-28840 Type



Symbol	Material	Finish Description
M	Aluminum	Electroless Nickel
MT	Aluminum	Nickel-PTFE, 1000 Hour Grey™
NF	Aluminum	Cadmium O.D. over Electroless Nickel
P	Stainless Steel	Electrodeposited Nickel


Dimensions in Inches (millimeters) are subject to change without notice.

240-288W Filtered Wall Mount Receptacle MIL-DTL-28840 Type



Comm Equiv 28840
Connectors/Accessories

Class	PI-Section (pF)	C-Section (pF)
X	160,000 - 240,000	80,000 - 120,000
Y	80,000 - 120,000	40,000 - 60,000
Z	60,000 - 91,000	30,000 - 45,000
A	38,000 - 56,000	19,000 - 28,000
B	32,000 - 45,000	16,000 - 22,500
C	18,000 - 33,000	9,000 - 16,500
D	8,000 - 12,000	4,000 - 6,000
E	3,300 - 5,000	1,650 - 2,500
F	800 - 1,300	400 - 650
G	400 - 600	200 - 300



RECOMMENDED PANEL CUT OUT





Filter Type	
P	PI-Section
C	C-Section

Military Shell Size	Shell Size	A Thread Class 2A	V Thread Class 2A	O Ref. Mtg. Hole	R True Position ϕ to ϕ	S	T Diameter
A	11	.750-.1P-.2L-D.S.	.750-20 UNEF	.812	.750	1.043 1.003	.130 .115
B	13	.875-.1P-.2L-D.S.	.875-20 UNEF	.937	.843	1.158 1.118	
C	15	1.062-.1P-.2L-D.S.	1.000-20 UNEF	1.124	.968	1.278 1.238	
D	17	1.125-.1P-.2L-D.S.	1.125-18 UNEF	1.187	1.015	1.403 1.363	
E	19	1.312-.1P-.2L-D.S.	1.250-18 UNEF	1.374	1.140	1.528 1.488	
F	23	1.500-.1P-.2L-D.S.	1.437-18 UNEF	1.562	1.281	1.738 1.698	
G	25	1.625-.1P-.2L-D.S.	1.562-18 UNEF	1.687	1.392	1.838 1.798	.157 .142
H	29	1.812-.1P-.2L-D.S.	1.875-16 UN	1.874	1.568	2.158 2.118	
J	33	2.000-.1P-.2L-D.S.	2.062-16 UNS	2.062	1.734	2.348 2.308	

Dimensions in Inches (millimeters) are subject to change without notice.



240-288J Filtered Jam Nut Mount Receptacle MIL-DTL-28840 Type



Filter Type	
P	PI-Section
C	C-Section

Class	PI-Section (pF)	C-Section (pF)
X	160,000 - 240,000	80,000 - 120,000
Y	80,000 - 120,000	40,000 - 60,000
Z	60,000 - 91,000	30,000 - 45,000
A	38,000 - 56,000	19,000 - 28,000
B	32,000 - 45,000	16,000 - 22,500
C	18,000 - 33,000	9,000 - 16,500
D	8,000 - 12,000	4,000 - 6,000
E	3,300 - 5,000	1,650 - 2,500
F	800 - 1,300	400 - 650
G	400 - 600	200 - 300

Symbol	Material	Finish Description
M	Aluminum	Electroless Nickel
MT	Aluminum	Nickel-PTFE, 1000 Hour Grey™
NF	Aluminum	Cadmium O.D. over Electroless Nickel
P	Stainless Steel	Electrodeposited Nickel

Dimensions in Inches (millimeters) are subject to change without notice.

240-288J
Filtered Jam Nut Mount Receptacle
MIL-DTL-28840 Type



Comm Equiv 28840
Connectors/Accessories




Military Shell Size	Shell Size	A Thread Class 2A	G	K Dia.	L Across Flat	M Thread Class 2A
A	11	.750-.1P-.2L-D.S.	1.274 1.254	1.368 1.348	.841 .832	.875-20 UNEF
B	13	.875-.1P-.2L-D.S.	1.399 1.379	1.508 1.488	.966 .957	1.000-20 UNEF
C	15	1.062-.1P-.2L-D.S.	1.587 1.567	1.681 1.661	1.153 1.144	1.187-18 UNEF
D	17	1.125-.1P-.2L-D.S.	1.649 1.629	1.743 1.723	1.216 1.207	1.250-18 UNEF
E	19	1.312-.1P-.2L-D.S.	1.837 1.817	1.931 1.911	1.403 1.394	1.437-18 UNEF
F	23	1.500-.1P-.2L-D.S.	2.024 2.004	2.118 2.098	1.591 1.582	1.625-18 UNEF
G	25	1.625-.1P-.2L-D.S.	2.149 2.129	2.243 2.223	1.716 1.707	1.750-18 UNS
H	29	1.812-.1P-.2L-D.S.	2.337 2.317	2.435 2.415	1.903 1.894	1.937-16 UN
J	33	2.000-.1P-.2L-D.S.	2.524 2.504	2.618 2.598	2.091 2.082	2.125-16 UN

Military Shell Size	Shell Size	V Thread Class 2A	BB Dia.	S Nominal	T ± .017	P Dia.	LL Flat
A	11	.750-20 UNEF	.979 .969	.125	1.062	.890 .880	.853 .843
B	13	.875-20 UNEF	1.104 1.094		1.188	1.015 1.005	.978 .968
C	15	1.000-20 UNEF	1.292 1.282		1.375	1.203 1.193	1.165 1.155
D	17	1.125-18 UNEF	1.354 1.344		1.438	1.265 1.255	1.228 1.218
E	19	1.250-18 UNEF	1.542 1.532		1.625	1.453 1.443	1.415 1.405
F	23	1.437-18 UNEF	1.729 1.719		1.812	1.640 1.630	1.603 1.593
G	25	1.562-18 UNEF	1.854 1.844	.189	2.000	1.765 1.755	1.728 1.718
H	29	1.875-16 UN	2.042 2.032		2.188	1.953 1.943	1.915 1.905
J	33	2.062-16 UNS	2.229 2.219		2.375	2.140 2.130	1.103 2.093

Dimensions in Inches (millimeters) are subject to change without notice.



947-128 Bulkhead Feedthrough Receptacle Wall Mount MIL-DTL-28840 Type



Dimensions in Inches (millimeters) are subject to change without notice.

947-128
Bulkhead Feedthrough Receptacle
Wall Mount
MIL-DTL-28840 Type






Symbol	Material	Finish Description
NF	Aluminum	Cadmium O.D. over Electroless Nickel
ZN		Zinc Nickel
MT		Nickel-PTFE, 1000 Hour Grey™
Z1	316 Type Stainless Steel	Passivate
ZU		Black Cadmium Olive Drab over Nickel

Military Shell Size	Shell Size	Insert Arrangement Dash Number	A Thread Class 2A	E BSC	F Max.	G Dia. Max.
A	11	A-1	.750-.1P-.2L-D.S.	.750	1.039	.130
B	13	B-1	.875-.1P-.2L-D.S.	.843	1.154	
C	15	C-1	1.062-.1P-.2L-D.S.	.968	1.274	
D	17	D-1	1.125-.1P-.2L-D.S.	1.015	1.399	
E	19	E-1	1.312-.1P-.2L-D.S.	1.140	1.524	
F	23	F-1	1.500-.1P-.2L-D.S.	1.281	1.734	
G	25	G-1	1.625-.1P-.2L-D.S.	1.392	1.834	.157
H	29	H-1	1.812-.1P-.2L-D.S.	1.568	2.154	
J	33	J-1	2.000-.1P-.2L-D.S.	1.734	2.344	.183

Dimensions in Inches (millimeters) are subject to change without notice.



947-229 Bulkhead Feedthrough Receptacle Jam Nut Mount MIL-DTL-28840 Type



Dimensions in Inches (millimeters) are subject to change without notice.

947-229
Bulkhead Feedthrough Receptacle
Jam Nut Mount
MIL-DTL-28840 Type



Symbol	Material	Finish Description
NF	Aluminum	Cadmium O.D. over Electroless Nickel
ZN		Zinc Nickel
MT		Nickel-PTFE, 1000 Hour Grey™
ZI	316 Type Stainless Steel	Passivate
ZU		Black Cadmium Olive Drab over Nickel


Military Shell Size	Shell Size	Insert Arrangement Dash Number	A Thread Class 2A	B Thread Class 2A	C Flats	D Dia.	E Hex	F Thread Flat
A	11	A-1	.750-.1P-.2L-D.S.	.875-20 UNEF	1.264	1.358	1.062	.836
B	13	B-1	.875-.1P-.2L-D.S.	1.000-20 UNEF	1.389	1.498	1.188	.962
C	15	C-1	1.062-.1P-.2L-D.S.	1.187-18 UNEF	1.577	1.671	1.375	1.149
D	17	D-1	1.125-.1P-.2L-D.S.	1.250-18 UNEF	1.639	1.733	1.438	1.212
E	19	E-1	1.312-.1P-.2L-D.S.	1.437-18 UNEF	1.827	1.921	1.625	1.399
F	23	F-1	1.500-.1P-.2L-D.S.	1.625-18 UNF	2.014	2.108	1.812	1.587
G	25	G-1	1.625-.1P-.2L-D.S.	1.750-18 UNS	2.139	2.233	2.000	1.708
H	29	H-1	1.812-.1P-.2L-D.S.	1.937-16 UN	2.327	2.425	2.188	1.898
J	33	J-1	2.000-.1P-.2L-D.S.	2.125-16 UN	2.514	2.608	2.375	2.086

F


Dimensions in Inches (millimeters) are subject to change without notice.



930-006 Wall Mount Receptacle Mounting Gasket for MIL-DTL-28840 Connectors



Also for use with
M28876/180-040 connectors



F

Table I: Material



Symbol	Material Description
F	Fluorosilicone
M	Silver Plated Glass Filled Silicone
N	Neoprene

Table II: Material

Shell Size	A ± .010	Ø B +.016 -.000	C .016 -.000	Ø D ± .010	F Radius ± .010
11	.750	.750	1.023	.120	.141
13	.843	.875	1.138		
15	.968	1.062	1.258		
17	1.015	1.125	1.383		
19	1.140	1.312	1.508		
23	1.281	1.500	1.718	.147	.188
25	1.392	1.625	1.818		
29	1.568	1.875	2.138		
33	1.734	2.062	2.328		
				.173	.219

Dimensions in Inches (millimeters) are subject to change without notice.

941-002
Sav-Con® Environmental Connector Saver
for MIL-DTL-28840 Connectors




Insert Arrangement Dash Number	Shell Size	A Thread Class 2*	B Max	Contact Size 20 Quantity
A-1	11	.750-.1P-.2L-D.S.	1.028 (26.1)	7
B-1	13	.875-.1P-.2L-D.S.	1.141 (29.0)	12
C-1	15	1.062-.1P-.2L-D.S.	1.263 (32.1)	21
D-1	17	1.125-.1P-.2L-D.S.	1.387 (35.2)	31
E-1	19	1.312-.1P-.2L-D.S.	1.513 (38.4)	42
F-1	23	1.500-.1P-.2L-D.S.	1.703 (43.3)	64
G-1	25	1.625-.1P-.2L-D.S.	1.825 (46.4)	92
H-1	29	1.812-.1P-.2L-D.S.	2.143 (54.4)	121
J-1	33	2.000-.1P-.2L-D.S.	2.329 (59.2)	155

Dimensions in Inches (millimeters) are subject to change without notice.



TG70 Strap Wrench Assembly Tool for Use with MIL-DTL-28840 Connectors



Basic Part Number

Torque Wrench (Omit for None)

TG70 - 1 - 18

Strap Length in Inches (See Notes 2 and 4)
Lengths Available: 12, 18, 24 and 36-Inch Only
Standard length is 12 Inches,
Omit Dash Number for Standard

- ### APPLICATION NOTES
1. These wrenches are made of the following materials:
Wrench Handle - Aluminum Alloy/Nickel Plate.
Wedge - Stainless Steel/Passivated.
Strap - Impregnated Fabric. Straps are 1/2 inch (12.7) in width.
 2. Replacement straps are available. Specify part number G70515-xx for 12, 18, 24 or 36-inch strap. 24 and 36 inch for double wrap.
 3. Metric dimensions (mm) are indicated in parentheses.
 4. Double wrap as shown for heavy duty range.
 5. Not recommended for composite coupling nuts (use 600-091 or 600-157).

F

VARIANCE CHART				
TG-70 Strap Wrench Used with Glenair Torque Wrenches				
Accessory Shell Size	Recommended Installation Torque			
	Light/Medium Duty ± 5 Inch Pounds		Heavy Duty ± 5 Inch Pounds	
	TG70 Torque	Part Torque	TG70 Torque	Part Torque
08/09	28	35	45	60
10/11	28	35	70	80
12/13	30	40	75	110 [80]
14/15	30	40	75	120 [80]
16/17	30	40	75	120 [80]
18/19	30	40	75	120 [80]
20/21	75	80	95	140 [100]
22/23	75	80	120*	140
24/25	75	80	120*	140
28			135*	150
32			150*	150
36			150*	150

* TG70 Not Recommended For Values of 120 Inch Lbs. or Greater.

- ### VARIANCE CHART NOTES
1. Recommended installation torque is approximately 80% of MIL-C-85049 accessory thread strength values.
 2. Heavy duty installation torque values may be difficult to attain with the TG70 Strap Wrench; the values shown in brackets [] are the maximum attainable with the TG70 Strap Wrench using a single wrap.
 3. Glenair recommends using 600 series torque tools whenever possible. When torque loading exceeds 75 inch pounds, or to attain the heavy duty torque values shown, a double wrap strap provides suitable friction to achieve torque values.
 4. Glenair recommends that heavy duty torque values be directly read through the connector shell body with the use of 600-005 connectors holding tools.

Dimensions in Inches (millimeters) are subject to change without notice.


TG69 and TG82
Soft Jaw Pliers and Strap Wrench Assembly Tool
for Use with MIL-DTL-28840 Connectors



TG69

Basic
Number

Nylon Replacement
Inserts P/N G77015




Basic
Number

TG82

7.0 (177.8) Approx.

7/16 (11.1)



Notes

2.50 (63.5) Max Capacity; Not recommended for composite coupling nuts (use 600-091 or 600-157)
1/4 Inch Drive
The replacement strap part number is G62748-11. Consult Factory for other lengths.

Dimensions in Inches (millimeters) are subject to change without notice.

MIL-QPL'D AND COMMERCIAL EQUIVALENT

NAVY CONNECTORS, TERMINI, ACCESSORIES AND TOOLS

RUGGEDIZED, ENVIRONMENTAL INTERCONNECT SOLUTIONS



Glenair offers a complete line of Navy connector solutions: From QPL'd MIL-PRF-28876 fiber optic connectors for today's high-speed ship-to-shore communications, to qualified MIL-DTL-28840 shipboard electrical connectors and accessories for ruggedized environmental shipboard interconnect systems, to precision tools for crimping and termination. The products are fully tooled and many are ready for immediate, same-day shipment.



U.S. Navy Approved Connectors and Accessories Index



Part/Config. Number	Page
180-040-03	C-6
180-040-04	C-8
180-040-06	C-10
180-040-13	C-6
180-040-14	C-8
180-040-16	C-10
180-040-23	C-7
180-040-24	C-9
180-040-26	C-11
180-040-33	C-7
180-040-34	C-9
180-040-36	C-11
181-039-1250C	B-1
181-039-1255C	B-1
181-039-1260C	B-1
181-039-1270C	B-1
181-039-1420C	B-1
181-040-1250C	B-2
181-040-1255C	B-2
181-040-1260C	B-2
181-040-1270C	B-2
181-040-1420C	B-2
181-051	B-3
181-057-125	B-14
181-057-126	B-14
181-075-125	B-14
181-075-126	B-14
182-012	B-4
182-013	B-5
182-014	B-6
182-015	B-7
182-035	B-8
240-288A	F-4
240-288J	F-8

Part/Config. Number	Page
240-288W	F-6
660-072	C-14
660-073	C-14
850-004	D-8
850-004-20-450	D-8
850-004-20-451	D-8
850-004-20-508	D-8
850-005	D-10
850-005-20-452	D-10
850-005-20-453	D-10
850-005-20-509	D-10
907-003	F-1
907-037	F-2
930-006	F-14, C-13
941-002	F-15
947-128	F-10
947-229	F-12
GAP-036	B-9
GCLT-H200	B-17
GCLT-HC250	B-17
GCLT-H160	B-17
GCLT-H125	B-17
GCLT-C125	B-17
GCLT-C250	B-17
GCLT-MPO	B-17
GCLT-MTC	B-17
GCLT-MTC-RE	B-17
M22520/34-01	D-3
M22520/34-02	D-3
M22520/35	D-3
M28840/1	E-1
M28840/2	E-2
M28840/3	E-3
M28840/4	E-4

Dimensions in Inches (millimeters) are subject to change without notice.



U.S. Navy Approved Connectors and Accessories Index

Part/Config. Number	Page
M28840/5	E-5
M28840/6	E-8
M28840/7	E-11
M28840/8	E-12
M28840/9	E-17
M28840/10	E-22
M28840/11	E-23
M28840/12	E-24
M28840/13	E-25
M28840/14	E-26
M28840/15	E-27
M28840/16	E-28
M28840/17	E-29
M28840/18	E-30
M28840/19	E-31
M28840/20	E-32
M28840/21	E-34
M28840/22	E-36
M28840/23	E-37
M28840/24	E-38, C-13
M28840/25	E-39
M28840/26	E-42
M28840/27	E-43
M28840/28	E-46
M28840/29	E-48
M28840/30	E-50
M28876/1	C-6
M28876/2	C-6
M28876/3	C-7
M28876/4	C-7
M28876/5	C-12
M28876/6	C-10
M28876/7	C-10
M28876/8	C-11

Part/Config. Number	Page
M28876/9	C-11
M28876/10	C-14
M28876/11	C-8
M28876/12	C-8
M28876/13	C-9
M28876/14	C-9
M28876/15	C-14
M29504/3-4038	B-3
M29504/14-4131C	B-1
M29504/14-4132C	B-1
M29504/14-4135C	B-1
M29504/14-4140C	B-1
M29504/14-4141C	B-1
M29504/15-4171C	B-2
M29504/15-4172C	B-2
M29504/15-4175C	B-2
M29504/15-4180C	B-2
M29504/15-4181C	B-2
M39029/83	D-8
M39029/83-450	D-8
M39029/83-451	D-8
M39029/83-508	D-8
M39029/84	D-10
M39029/84-452	D-10
M39029/84-453	D-10
M39029/84-509	D-10
M81969/33-01	D-3
M81969/33-02	D-3
M81969/34-01	D-3
TG69	F-17
TG70	F-16
TG82	F-17

Dimensions in Inches (millimeters) are subject to change without notice.

The world's broadest selection of interconnect products—in stock and ready for immediate same-day shipment

Glenair's World of Interconnect Solutions

A complete overview of Glenair's innovative range of interconnect products and services, including Military Standard and commercial equivalent connectors and accessories.




High-Performance Micro-D Connectors and Cables

Glenair offers both Military Standard 83513 Micro-D connectors as well as COTS selections, backshells, mounting hardware and more. Our TwistPin contact provides superior performance.



EMI/EMP Filter Connectors

MIL-DTL-38999 type EMI/EMP filter connectors, as well as other Military Standard and commercial electromagnetic shielding technologies. Also includes Glenair Series 80 "Mighty Mouse" filter products.



Fiber Optic Interconnect Solutions

Tactical fiber optic connectors, cables, and termini for airframe, shipboard, and military ground vehicles. Catalog features Glenair's innovative high-density (GHD) connector system for reduced size and weight applications.



Available now:
Glenair's Interconnect Product Guide CD,
featuring our
entire library of
Glenair catalogs
and data sheets.



In addition to over a dozen product line catalogs, the CD includes a powerful part number development program that takes all the pain and confusion out of ordering interconnect components. An easy-to-use inventory search program provides ready access to 60,000 MIL-STD and commercial part numbers.


Composite Thermoplastic Interconnect Solutions

Glenair is the world's leading manufacturer of composite interconnect solutions. We are the 'go-to' supplier for advanced composite technologies for commercial and military interconnect applications.



Military Standard Connector Accessories

If the MS connector accessory you need isn't in here – it doesn't exist. Search this easy-to-use catalog by accessory type or Mil-Spec slash number, then place your order against Glenair's 60,000 part number same-day inventory.



Series 80 "Mighty Mouse" Connectors and Cables

Glenair's revolutionary connector series that reduces interconnect system size and weight by 50% compared to MIL-DTL-38999 connectors. Now used on hundreds of mission-critical military and commercial applications.



Visit us at www.glenair.com and use the literature order form for immediate catalog fulfillment



A World of Interconnect Solutions

Glenair, Inc.

1211 Air Way • Glendale, California • 91201-2497

Telephone: 818-247-6000 • Fax: 818-500-9912 • sales@glenair.com

www.glenair.com

Glenair Power Products Group

860 N. Main Street Extension
Wallingford, CT
06492

Telephone:
203-741-1115
Facsimile:
203-741-0053
sales@glenair.com

Glenair UK Ltd

40 Lower Oakham Way
Oakham Business Park
P.O. Box 37, Mansfield
Notts, NG18 5BY England

Telephone:
+44-1623-638100
Facsimile:
+44-1623-638111
sales@glenair.co.uk

Glenair Microway Systems

7000 North Lawndale Avenue
Lincolnwood, IL
60712

Telephone:
847-679-8833
Facsimile:
847-679-8849

Glenair Nordic AB

Gustav III : S Boulevard 46
S - 169 27 Solna
Sweden

Telephone:
+46-8-50550000
Facsimile:
+46-8-50550001
sales@glenair.se

Glenair Electric GmbH

Siemensstrasse 9
D-61449 Steinbach
Germany

Telephone:
49-6171-5905-0
Facsimile:
49-6171-5905-90
germany@glenair.com

Glenair Iberica

C/ La Vega, 16
45612 Velada
Spain

Telephone:
+34-925-89-29-88
Facsimile:
+34-925-89-29-87
sales@glenair.es

Glenair Italia S.p.A.

Via Cà dell'Orbo Nord, 22
40055 Villanova di Castenaso
Bologna, Italy

Telephone:
+39-051-780098
Facsimile:
+39-051-782259
info@glenair.it

Glenair France SARL

7, Avenue Parmentier
Immeuble Central Parc #2
31200 Toulouse
France

Telephone:
+33-5-34-40-97-40
Facsimile:
+33-5-61-47-86-10
sales@glenair.fr

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Glenair:](#)

[182-012](#)