

Amphenol Star-line EX® Series Connectors



HARD ANODIC COATING ALLOWS FOR HEAT RESISTANCE UP TO 750°F (399°C)

Amphenol Explosion-proof Connectors ATEX certified for Zone 1-Ilc hazardous environment, Cenelec IP68-8 rated, and IECex certified (IECex 60079). With a broad range of reversible inserts; solder, crimp and pressure terminals; and flexible cable options, Star-Line EX will meet application demands in petrochemical refineries, land and offshore drilling systems. RoHS compliant products available.

FEATURES

ATEX CERTIFIED

For Zone 1-Ilc hazardous environment. For certificate, contact factory.

IECEX CERTIFIED

For certificate, contact factory.

CENELEC IP68 RATED

Cable connectors listed under Ex d Ilc T6. Panel mount receptacles listed under Ex de Ilc T6.

HARD ANODIC COATING

All machined aluminum parts finished with a hard, scratch-resistant coating per MIL-A-8625, Type III. Dielectric strength 1800 volts. Heat resistance of 750°F.

REVERSIBLE INSERTS

A full range of contact inserts for power, signal and mixed applications are available. All are interchangeable and reversible to suit specific needs.

EASILY ACCESSIBLE WIRE TERMINALS

Conductors are readily terminated to contacts. Cable housings are slipped over conductors or leads after terminating. Cumbersome handling and seating of inserts with conductors attached is eliminated.

HIGH TENSILE STRENGTH ALUMINUM

Bar Stock Components precision machined. Points of impact designed for extra strength.

CABLE OPTIONS

Starline EX Series can be terminated onto unarmored or armored and sheathed cables built to IEEE-45 / UL1309, IEC, BS, DIN and JIC standards. Flexible cables like SOOW-A, W, G-GC and DLO constructions can also be used with this Series.

EX CABLE GLANDS

Wide variety of glands are available for Star-Line EX connectors.

INSERT VARIETY

1 to 143 contacts. High amperage up to 1135 amps at 1000V / AC or DC. Contacts are high quality copper with silver plating. (Gold plating available as an option) Composite inserts for power, control and instrumentation service available.

RADSOK® HIGH AMPERAGE CONTACTS

Special arrangements are available with RADSOK high amperage contacts. Standard Star-line EX inserts are not interchangeable with new RADSOK contact insert arrangements.

ROHS COMPLIANT PRODUCT AVAILABLE

TECHNICAL
SPECIFICATIONS**MATERIALS AND FINISHES**

Shell	Aluminium Alloy or Stainless Steel
Shell Plating	Hard Anodic
Contacts	Copper Alloy
Contact Platings	Silver or Gold Plated
Seals	Buna Rubber

ELECTRICAL DATA

Wire Range Sizes	18 to 777MCM
------------------	--------------

Current Rating

CONTACT SIZE	MAX. CURRENT RATING PER CONTACT AMPS
18	3
16	16
12	30
10	40
8	50
4	90
1/0	155
4/0	225
313MCM	325
350MCM	325
373MCM	Contact us
444MCM	Contact us
500MCM	750
535MCM	Contact us
646MCM	940
777MCM	1,135

TECHNICAL SPECIFICATIONS

MECHANICAL

Operating Temperature -67°F to +257°F (-55°C to +125°C)

Insulation Strip Length

CONTACT SIZE	STRIP LENGTH - SOLDER		STRIP LENGTH - CRIMP	
	INCHES	MM	INCHES	MM
18	0.284	7.2	0.453	11.5
16	0.284	7.2	0.575	14.6
12	0.343	8.7	0.611	15.5
10	0.469	11.9	0.674	17.1
8	0.595	15.1	0.827	21.0
4	0.658	16.7	0.906	23.0
1/0	0.721	18.3	1.221	31.0
4/0	0.721	18.3	1.221	31.0
313MCM	0.843	21.4	1.319	33.5
350MCM	0.843	21.4	1.319	33.5
373MCM	0.843	21.4	1.319	33.5
444MCM	1.969	50.0	1.969	50.0
500MCM	1.969	50.0	1.969	50.0
535MCM	1.969	50.0	1.969	50.0
646-777MCM	1.969	50.0	1.969	50.0

Mating Life 500 cycles

Salt Spray 300 days

Vibration 10g

Shock 60g

Sealed IP68

Contact Type Solder, Crimp, Power, and Signal

Number of Circuits 1 to 143

Polarization Keyway with optional insert orientation

Approvals CSA, ATEX, and IECEx

CREATE YOUR PART NUMBER

	1	2	3	4	5	6	7	8	9
EX	S-	13-3	-C	-20-332	P	N	K	-01	-BS
SERIES PREFIX	SHELL MATERIAL	SHELL & HARDWARE TYPE	EEX D GLAND/ CABLE GRIP SIZE	LAYOUT	CONTACT TYPE	CONTACT TERMINATION	CONTACT PLATING	KEYING	CABLE TYPE

STEP 1: SELECT SHELL MATERIAL

Blank = Aluminum

S = Stainless Steel

STEP 2: SELECT SHELL & HARDWARE TYPE

RECEPTACLES

Mates with

PLUGS



15-2

In-Line Receptacle with
Mechanical Clamp


15-3

In-Line Receptacle with
EEx d Gland


13-2

Plug with Mechanical
Clamp


13-3

Plug with EEx d Gland



15-4

In-Line Receptacle with
Basketweave Cable Grip


17-1

Panel Mount Receptacle



13-4

Plug with Basketweave
Cable Grip


17-2

Fixed In-Line Receptacle with
Mechanical Clamp


17-3

Fixed In-Line
Receptacle with
EEx d Gland


17-4

Fixed In-Line Receptacle with
Basketweave Cable Grip

STEP 3: SELECT EEX D GLAND / CORD GRIP SIZE**For Shell and hardware styles 13-3, 15-3 or 17-3**

SHELL SIZE	ENTRY THREAD	GLAND SIZES AVAILABLE												BLANK - NO GLAND FITTED
		A1 16	A2 20S	A 20	B 25	C 32	C2 40	D 50S	D2 50	E 63S	E2 63	F 75S	F2 75	
12	M25	x	x	x	x									x
16	M40			x	x	x	x							x
20	M50				x	x	x	x	x					x
24	M63					x	x	x	x	x	x			x
28	M75							x	x	x	x	x	x	x

SHELL SIZE	GLAND CODE THREAD	UNARMORED CABLE OD				ARMORED CABLE											
						INNER SHEATH DIAMETER				STANDARD OD ("BS")				REDUCED BORE OD ("BSR")			
		MIN		MAX		MIN		MAX		MIN		MAX		MIN		MAX	
		IN	MM	IN	MM	IN	MM	IN	MM	IN	MM	IN	MM	IN	MM	IN	MM
12	A1	0.1575	4.0	0.3307	8.4	0.1339	3.4	0.3307	8.4	0.3543	9.0	0.5315	13.5	0.2638	6.7	0.4055	10.3
	A2	0.2835	7.2	0.4606	11.7	0.2835	7.2	0.4606	11.7	0.4528	11.5	0.6299	16.0	0.3701	9.4	0.4921	12.5
12 & 16	A	0.3780	9.6	0.5512	14.0	0.3701	9.4	0.5512	14.0	0.6102	15.5	0.8307	21.1	0.4724	12.0	0.6929	17.6
12, 16, & 20	B	0.5315	13.5	0.7874	20.0	0.5315	13.5	0.7874	20.0	0.7992	20.3	1.0790	27.4	0.6614	16.8	0.9409	23.9
16, 20, & 24	C	0.7677	19.5	1.0350	26.3	0.7677	19.5	1.0350	26.3	1.0510	26.7	1.3390	34.0	0.9134	23.2	1.2010	30.5
	C2	0.9055	23.0	1.2680	32.2	0.9055	23.0	1.2680	32.2	1.2990	33.0	1.5980	40.6	1.1260	28.6	1.4250	36.2
20, 24, & 28	D	1.1100	28.2	1.5040	38.2	1.1060	28.1	1.5040	38.2	1.5510	39.4	1.8390	46.7	1.3700	34.8	1.6690	42.4
	D2	1.3070	33.2	1.7360	44.1	1.3030	33.1	1.7360	44.1	1.7990	45.7	2.0940	53.2	1.6180	41.1	1.9090	48.5
24 & 28	E	1.5470	39.3	1.9720	50.1	1.5430	39.2	1.9690	50.0	2.0510	52.1	2.3430	59.5	1.8700	47.5	2.1570	54.8
	E2	1.8390	46.7	2.2050	56.0	1.8390	46.7	2.2050	56.0	2.2990	58.4	2.5910	65.8	2.1180	53.8	2.4090	61.2
28	F	2.0590	52.3	2.4410	62.0	2.0510	52.1	2.4410	62.0	2.5510	64.8	2.8430	72.2	2.3700	60.2	2.6770	68.0
	F2	2.2870	58.1	2.6770	68.0	2.2830	58.0	2.6770	68.0	2.7990	71.1	3.0710	78.0	2.6180	66.5	2.8900	73.4

For Shell and hardware styles 13-2, 13-4, 15-2, 15-4, 17-2 or 17-4

SHELL#	CABLE GRIP CODE	CABLE OD			
		MIN. IN.	MAX. IN.	MIN. MM.	MAX. MM.
12	02	0.062	0.125	1.6	3.2
	04	0.125	0.250	3.2	6.4
	06	0.250	0.375	6.4	9.5
	08	0.375	0.500	9.5	12.7
	10	0.500	0.625	12.7	15.9
	12	0.625	0.750	15.9	19.1
	14	0.750	0.875	19.1	22.2
	15	0.875	0.937	22.2	23.8
	06	0.250	0.375	6.4	9.5
	08	0.375	0.500	9.5	12.7
16	10	0.500	0.625	12.7	15.9
	12	0.625	0.750	15.9	19.1
	14	0.750	0.875	19.1	22.2
	16	0.875	1.000	22.2	25.4
	18	1.000	1.125	25.4	28.6
	20	1.125	1.250	28.6	31.8
	22	1.250	1.375	31.8	34.9
	23	1.375	1.437	34.9	36.5
	10	0.500	0.625	12.7	15.9
	12	0.625	0.750	15.9	19.1
20/C20	14	0.750	0.875	19.1	22.2
	16	0.875	1.000	22.2	25.4
	18	1.000	1.125	25.4	28.6
	20	1.125	1.250	28.6	31.8
	22	1.250	1.375	31.8	34.9
	24	1.375	1.500	34.9	38.1
	26	1.500	1.625	38.1	41.3
	28	1.625	1.750	41.3	44.5
	30	1.750	1.875	44.5	47.6
	31	1.875	1.937	47.6	49.2
24/C24	16	0.875	1.000	22.2	25.4
	18	1.000	1.125	25.4	28.6
	20	1.125	1.250	28.6	31.8
	22	1.250	1.375	31.8	34.9
	24	1.375	1.500	34.9	38.1
	26	1.500	1.625	38.1	41.3
	28	1.625	1.750	41.3	44.5
	30	1.750	1.875	44.5	47.6
	32	1.875	2.000	47.6	50.8
	34	2.000	2.125	50.8	54.0
28/C28	36	2.125	2.250	54.0	57.2
	38	2.250	2.375	57.2	60.3
	39	2.375	2.437	60.3	61.9
	24	1.375	1.500	34.9	38.1
	26	1.500	1.625	38.1	41.3
	28	1.625	1.750	41.3	44.5
	30	1.750	1.875	44.5	47.6
	32	1.875	2.000	47.6	50.8
	34	2.000	2.125	50.8	54.0
	36	2.125	2.250	54.0	57.2
	38	2.250	2.375	57.2	60.3
	40	2.375	2.500	60.3	63.5
	42	2.500	2.625	63.5	66.7
	44	2.625	2.750	66.7	69.9
	46	2.750	2.875	69.9	73.0

STEP 4: SELECT LAYOUT

Layout	ATEX / IECEx Certified	ANSI / CSA Certified	Shell Size	Crimp Mod	Number of Contacts	Keying Available	Layout Description	Solder	Crimp	Pressured	Radsok	AWG/MCM	18	16	12	10	8	4	Coax	1/0	4/0	313 MCM	350 MCM	373 MCM	444 MCM	500 MCM	535 MCM	646-777 MCM
												mm ²	0.75	1.5	4	6	10	25		50	120	150	185	185	225	240	240	300 - 400
12-10	•		12	-	7	Δ	7#12	X							7													
12-11	•		12	-	7	Δ	7#12	X							7													
12-14	•	†	12	-	4	Δ	4#10	X		X						4												
12-15	•	†	12	-	4	Δ	4#10	X	X							4												
12-16	•	†	12	-	4	Δ	4#10	X	X							4												
12-17	•	†	12	-	10	Δ	10#16	X						10														
12-21	•	†	12	-	5	Δ	5#12	X							5													
12-22	•	†	12	-	4	Δ	4#10	X		X						4												
12-23	•	†	12	-	17	Δ	17#18	X				17																
12-24	•	†	12	-	5	Δ	5#12	X							5													
12-27	•	†	12	-	3	Δ	3#12	X							3													
12-310	•	†	12	II	7	Δ	7#12		X						7													
12-311	•		12	II	7	Δ	7#12		X						7													
12-314	•	†	12	II	4	Δ	4#10		X							4												
12-316	•	†	12	II	4	Δ	4#10		X							4												
12-317	•		12	II	10	Δ	10#16		X					10														
12-322	•	†	12	II	4	Δ	4#10		X							4												
12-323	•	†	12	II	17	Δ	17#18	X				17																
12-324	•	†	12	II	5	Δ	5#12		X						5													
12-326	•	†	12	II	5	Δ	3#16,2#8		X					3			2											
12-327	•	†	12	II	3	Δ	3#12		X						3													
12-33	•	†	12	-	4	Δ	4#16	X						4														
12-330	•		12	II	3	Δ	3#12		X						3													
12-333	•	†	12	II	4	Δ	4#16		X					4														
12-334	•	†	12	II	10	Δ	10#16		X					10														
12-346	•	†	12	II	4	Δ	4#10		X							4												
12-348	•		12	II	7	Δ	7#16		X					7														
12-354	•	†	12	II	7	Δ	7#12		X						7													
12-355	•	†	12	II	10	Δ	10#16		X					10														
12-45	•		12	-	3	Δ	3#8	X								3												
12-46	•	†	12	-	4	Δ	4#10		X							4												
12-53	•	†	12	-	5		5#12	X							5													
12-56	•		12	-	3	Δ	3#8	X								3												
12-614	•	†	12	III	4	Δ	4#10		X							4												
12-616	•	†	12	III	4	Δ	4#10		X							4												
12-617	•		12	III	10	Δ	10#16		X					10														
12-624	•	†	12	III	5	Δ	5#12		X						5													
12-637	•		12	III	3	Δ	3#10		X							3												
12-648	•	†	12	III	7	Δ	7#16		X					7														
12-649	•	†	12	III	3	Δ	3#10		X							3												
12-651	•	†	12	III	3	Δ	3#10		X							3												
12-653	•	†	12	III	5		5#12		X						5													
12-654	•	†	12	III	7	Δ	7#12		X						7													
12-655	•	†	12	III	10	Δ	10#16		X					10														
16-11	•		16	-	19	Δ	19#12	X							19													
16-12	•	†	16	-	19	Δ	19#12	X							19													
16-16	•	†	16	-	5	Δ	5#8	X								5												
16-21	•	†	16	-	37	Δ	37#16	X						37														
16-22	•	†	16	-	4	Δ	4#4	X		X							4											
16-23	•	†	16	-	4	Δ	4#4	X		X							4											
16-24	•	†	16	-	18	Δ	16#16,2#10	X						16		2												
16-25	•		16	-	16	Δ	16#16	X						16														
16-26	•	†	16	-	4	Δ	4#8	X								4												
16-27	•	†	16	-	5	Δ	5#8	X								5												
16-28	•	†	16	-	4	Δ	4#8	X								4												
16-29	•	†	16	-	9	Δ	8#16,1#4	X						8			1											
16-31	•		16	-	5	Δ	5#8	X								5												
16-311	•		16	II	19	Δ	19#12		X						19													
16-312	•	†	16	II	19	Δ	19#12		X						19													
16-316	•	†	16	II	5	Δ	5#8		X							5												
16-321	•	†	16	II	37	Δ	37#16		X					37														
16-322	•	†	16	II	4	Δ	4#4		X								4											
16-324	•	†	16	II	18	Δ	16#16,2#10		X					16		2												

STEP 4: SELECT LAYOUT

Layout	ATEX / IECX Certified	ANSI / CSA Certified	Shell Size	Crimp Mod	Number of Contacts	Keying Available	Layout Description	Solder	Crimp	Pressured	Radsok	AWG/MCM	18	16	12	10	8	4	Coax	1/0	4/0	313 MCM	350 MCM	373 MCM	444 MCM	500 MCM	535 MCM	646-777 MCM
												mm ²	0.75	1.5	4	6	10	25		50	120	150	185	185	225	240	240	300 - 400
16-325	•	†	16	II	16	Δ	16#16		X					16														
16-328	•	†	16	II	4	Δ	4#8		X								4											
16-33	•	†	16	-	61	Δ	61#18	X				61																
16-333	•	†	16	II	61	Δ	61#18		X			61																
16-335	•	†	16	II	27	Δ	24#16,3#12		X				24	3														
16-344	•	†	16	II	21	Δ	11#16,10#12		X				11	10														
16-345	•	†	16	II	5	Δ	5#8		X								5											
16-346	•	†	16	II	9	Δ	6#12,3#8		X					6		3												
16-349	•	†	16	II	14	Δ	12#16,2#4		X				12					2										
16-355	•	†	16	II	19	Δ	19#16		X				19															
16-37	•	†	16	-	26	Δ	18#18, 4#16,4#12	X				18	4	4														
16-371	•	†	16	II	46		45#18,1#8		X			45					1											
16-373	•		16	II	27	Δ	24#16,3#12		X				24	3														
16-376	•		16	II	10	Δ	6#12,4#10		X					6	4													
16-377	•	†	16	II	19	Δ	19#12		X					19														
16-378	•	†	16	II	7	Δ	7#12		X					7														
16-38	•	†	16	-	4	Δ	4#4	X		X								4										
16-381	•		16	II	10	Δ	6#12,4#10		X					6	4													
16-40	•	†	16	-	55	Δ	55#18	X				55																
16-47	•	†	16	-	4	Δ	4#10	X							4													
16-51	•		16	-	3	Δ	3#4	X		X								3										
16-611	•		16	III	19	Δ	19#12		X					19														
16-616	•	†	16	III	5	Δ	5#8		X								5											
16-621	•	†	16	III	37	Δ	37#16		X				37															
16-622	•	†	16	III	4	Δ	4#4		X									4										
16-624	•	†	16	III	18	Δ	16#16,2#10		X				16		2													
16-628	•	†	16	III	4	Δ	4#8		X							4												
16-633	•	†	16	III	61	Δ	61#18		X			61																
16-635	•	†	16	III	27	Δ	24#16,3#12		X				24	3														
16-638	•	†	16	III	4	Δ	4#4		X									4										
16-640	•	†	16	III	55	Δ	55#18		X			55																
16-655	•	†	16	III	19	Δ	19#16		X				19															
16-673	•	†	16	III	27	Δ	24#16,3#12		X				24	3														
16-676	•	†	16	III	10	Δ	6#12,4#10		X					6	4													
16-677	•	†	16	III	19	Δ	19#12		X					19														
16-68	•		16	-	5	Δ	5#Coax	X										5										
16-681	•	†	16	III	10	Δ	6#12,4#10		X					6	4													
16-70	•	†	16	-	3	Δ	3#4	X		X								3										
16-74	•	†	16	-	3	Δ	3#4	X		X								3										
16-75	•	†	16	-	5		5#8	X									5											
20-10	•		20	-	37	Δ	37#12	X						37														
20-13	•		20	-	68	Δ	68#16	X					68															
20-23	•	†	20	-	38	Δ	35#16,3#10	X					35		3													
20-29	•	†	20	-	64	Δ	62#16,2#10	X					62		2													
20-31	•		20	-	22	Δ	20#16,2#8	X					20			2												
20-310	•	†	20	II	37	Δ	37#12		X					37														
20-313	•	†	20	II	68	Δ	68#16		X				68															
20-32	•	†	20	-	20	Δ	20#12	X						20														
20-323	•	†	20	II	38	Δ	35#16,3#10		X				35		3													
20-329	•	†	20	II	64	Δ	62#16,2#10		X				62		2													
20-331	•	†	20	II	22	Δ	20#16,2#8		X				20			2												
20-332	•	†	20	II	20	Δ	20#12		X					20														
20-334	•	†	20	II	20	Δ	16#16,4#8		X				16			4												
20-337	•		20	II	5	Δ	5#4		X									5										
20-34	•		20	-	20	Δ	16#16,4#8	X					16			4												
20-344	•	†	20	II	81	Δ	69#18,12#12		X			69		12														
20-345	•	†	20	II	90	Δ	90#18		X			90																
20-35	•	†	20	-	60	Δ	60#16	X					60															
20-350	•	†	20	II	37	Δ	37#12		X					37														
20-354	•	†	20	II	47	Δ	45#16,2#8		X				45			2												
20-357	•		20	II	22	Δ	20#16, 2#Coax		X				20					2										
20-358	•	†	20	II	16	Δ	16#8		X								16											

STEP 4: SELECT LAYOUT

								AWG/MCM				18	16	12	10	8	4	Coax	1/0	4/0	313 MCM	350 MCM	373 MCM	444 MCM	500 MCM	535 MCM	646-777 MCM
								mm²				0.75	1.5	4	6	10	25		50	120	150	185	185	225	240	240	300 - 400
Layout	ATEX / IECEx Certified	ANSI / CSA Certified	Shell Size	Crimp Mod	Number of Contacts	Keying Available	Layout Description	Solder	Crimp	Pressured	Radsok																
20-359	•		20	II	7	Δ	7#8		X						7												
20-36	•	†	20	-	5	Δ	5#4	X		X						5											
20-37	•	†	20	-	5	Δ	5#4	X		X						5											
20-374	•	†	20	II	27	Δ	25#12,2#4		X				25			2											
20-375	•	†	20	II	12	Δ	12#10		X					12													
20-376	•		20	II	19		19#12		X					19													
20-38	•	†	20	-	5	Δ	5#4	X		X						5											
20-384	•	†	20	II	5		5#4		X							5											
20-386	•	†	20	II	37		37#12		X					37													
20-387	•	†	20	II	20	Δ	20#12		X					20													
20-388	•		20	II	19		19#12		X					19													
20-39	•		20	-	4	Δ	4#1/0	X									4										
20-390	•		20	II	21	Δ	21#12		X					21													
20-41	•		20	-	4	Δ	4#1/0	X									4										
20-43	•	†	20	-	6	Δ	2#10,4#4	X		X					2		4										
20-44	•		20	-	81	Δ	69#18,12#12	X				69		12													
20-45	•		20	-	90	Δ	90#18	X				90															
20-46	•	†	20	-	6	Δ	4#4,2#1/0	X								4		2									
20-48	•	†	20	-	6	Δ	3#12,3#1/0	X						3				3									
20-49	•	†	20	-	5	Δ	3#12,2#1/0	X		X				3				2									
20-55	•	†	20	-	10	Δ	8#12,2#1/0	X						8				2									
20-56	•		20	-	7	Δ	7#Coax	X								7											
20-613	•	†	20	III	68	Δ	68#16		X				68														
20-623	•	†	20	III	38	Δ	35#16,3#10	X					35		3												
20-632	•	†	20	III	20	Δ	20#12	X						20													
20-639	•		20	III	4	Δ	4#1/0	X									4										
20-643	•	†	20	III	6	Δ	2#10,4#4	X							2			4									
20-646	•	†	20	III	6	Δ	4#4,2#1/0	X								4		2									
20-648	•	†	20	III	6	Δ	3#12,3#1/0	X						3				3									
20-649	•	†	20	III	5	Δ	3#12,2#1/0	X						3				2									
20-659	•	†	20	III	7	Δ	7#8	X								7											
20-672	•	†	20	III	6	Δ	4#12,2#4	X						4			2										
20-673	•	†	20	III	50	Δ	46#16,4#8	X					46			4											
20-674	•	†	20	III	27	Δ	25#12,2#4	X						25			2										
20-676	•	†	20	III	19		19#12	X						19													
20-680	•	†	20	III	10	Δ	6#12,4#4	X						6			4										
20-685	•	†	20	III	10	Δ	6#12,4#4	X						6			4										
20-686	•	†	20	III	37		37#12		X					37													
20-688	•		20	III	19		19#12	X						19													
20-84	•	†	20	-	5		5#4	X		X						5											
24-11	•		24	-	58	Δ	58#12	X						58													
24-13	•		24	-	100	Δ	100#16	X					100														
24-16	•	†	24	-	66	Δ	58#16, 5#12, 3#Coax	X					58	5			3										
24-31	•		24	-	60	Δ	53#16,7#12	X					53	7													
24-311	•		24	II	58	Δ	58#12		X					58													
24-313	•	†	24	II	100		100#16		X				100														
24-331	•	†	24	II	60	Δ	53#16, 7#12		X				53	7													
24-352	•	†	24	II	58	Δ	58#12	X						58													
24-354	•	†	24	II	75	Δ	61#16, 11#12,3#8		X				61	11		3											
24-362	•		24	II	62	Δ	62#16	X					62														
24-371	•	†	24	II	37	Δ	37#16	X					37														
24-384	•	†	24	II	58	Δ	58#12	X						58													
24-385	•	†	24	II	100		100#16	X					100														
24-388	•		24	II	72	Δ	72#16	X					72														
24-389	•		24	II	60	Δ	60#16	X					60														
24-40	•	†	24	-	15	Δ	10#16,5#1/0	X					10					5									
24-55	•	†	24	-	8	Δ	4#4,4#1/0	X								4		4									
24-57	•		24	-	8	Δ	8#Coax	X									8										
24-613	•	†	24	III	100	Δ	100#16		X				100														
24-655	•	†	24	III	8	Δ	4#4,4#1/0		X							4		4									
24-658	•	†	24	III	7	Δ	7#4	X								7											
24-673	•	†	24	III	10	Δ	8#8,2#4	X							8	2											

STEP 4: SELECT LAYOUT

Layout	ATEX / IECEx Certified	ANSI / CSA Certified	Shell Size	Crimp Mod	Number of Contacts	Keying Available	Layout Description	Solder	Crimp	Pressured	Radsok	AWG/MCM	18	16	12	10	8	4	Coax	1/0	4/0	313 MCM	350 MCM	373 MCM	444 MCM	500 MCM	535 MCM	646-777 MCM
												mm²	0.75	1.5	4	6	10	25		50	120	150	185	185	225	240	240	300 - 400
24-83	•	†	24	-	4	Δ	4#4/0	X													4							
24-84	•	†	24	-	58	Δ	58#12	X								58												
28-14	•	†	28	-	100	Δ	83#16,17#12	X					83	17														
28-22	•	†	28	-	143	Δ	143#16	X					143															
28-314	•	†	28	II	100	Δ	83#16,17#12		X				83	17														
28-322	•	†	28	II	143	Δ	143#16		X				143															
28-324	•	†	28	II	55	Δ	41#16,5#12,3#8,6#4		X				41	5		3	6											
28-339	•	†	28	II	42	Δ	42#12		X					42														
C20-342	•	†	C20	II	4	Δ	4#1/0		X											4								
C20-379	•	†	C20	II	1		1#500MCM		X																1			
C20-40	•	†	C20	-	4	Δ	4#1/0	X		X										4								
C20-42	•	†	C20	-	4	Δ	4#1/0	X		X										4								
C20-640	•	†	C20	III	4	Δ	4#1/0		X											4								
C20-642	•	†	C20	III	4	Δ	4#1/0		X											4								
C24-26	•	†	C24	-	4	Δ	4#4/0	X		X										4								
C24-29	•	†	C24	-	5	Δ	5#1/0	X		X										5								
C24-313	•	†	C24	II	1		1#313MCM		X													1						
C24-353	•	†	C24	II	8	Δ	4#12,4#1/0		X					4						4								
C24-36	•	†	C24	-	37	Δ	35#12,2#1/0	X					35							2								
C24-373	•		C24	II	1		1#373MCM		X														1					
C24-38	•	†	C24	-	4	Δ	4#4/0	X		X										4								
C24-386	•	†	C24	II	1		1#777MCM		X																			1
C24-39	•		C24	-	4	Δ	4#4/0	X												4								
C24-42	•	†	C24	-	4	Δ	4#1/0	X												4								
C24-43	•	†	C24	-	4	Δ	4#1/0	X												4								
C24-44	•		C24	-	5	Δ	5#1/0	X		X										5								
C24-47	•	†	C24	-	15	Δ	10#12,5#1/0	X						10						5								
C24-48	•	†	C24	-	5	Δ	2#12,3#4/0	X						2							3							
C24-49	•	†	C24	-	5	Δ	5#1/0	X		X										5								
C24-50	•	†	C24	-	6	Δ	2#10,1#4,3#1/0	X							2		1			3								
C24-535	•	†	C24	II	1		1#535MCM		X																	1		
C24-59	•	†	C24	-	7	Δ	7#1/0	X												7								
C24-659	•	†	C24	III	7	Δ	7#1/0		X											7								
C24-675	•	†	C24	III	10	Δ	6#12,4#1/0	X						6						4								
C24-680	•	†	C24	III	10	Δ	6#12,4#1/0	X						6						4								
C24-687	•		C24	III	9	Δ	2#12,4#4,3#1/0		X					2			4			3								
C24-72	•	†	C24	-	6	Δ	3#12,3#4/0	X						3							3							
C24-79	•	†	C24	-	5	Δ	5#1/0	X		X										5								
C24-81	•	†	C24	-	15		10#12,5#1/0	X						10						5								
C24-R313	•	†	C24	II	1		1#313MCM		X		X											1						
C24-R373	•		C24	II	1		1#373MCM		X		X												1					
C24-R386	•	†	C24	II	1		1#777MCM		X	X	X																	1
C24-R44	•		C24	-	7		1#10,3#8,3#1/0	X		X	X				1	3				3								
C24-R535	•	†	C24	II	1		1#535MCM		X		X															1		
C28-12	•	†	C28	-	39	Δ	31#12,5#10,1#8,2#1/0	X						31	5	1				2								
C28-15	•	†	C28	-	47	Δ	43#12,3#4,1#1/0	X						43			3			1								
C28-17	•	†	C28	-	6	Δ	2#12,4#4/0	X						2						4								
C28-18	•	†	C28	-	6	Δ	2#12,4#350MCM	X						2									4					
C28-19	•		C28	-	5	Δ	5#4/0	X		X										5								
C28-20	•	†	C28	-	5	Δ	5#4/0	X		X										5								
C28-21	•	†	C28	-	8	Δ	4#12,4#350MCM	X						4									4					
C28-23	•	†	C28	-	5	Δ	5#4/0	X		X										5								
C28-327	•	†	C28	II	6	Δ	6#1/0		X											6								
C28-328	•	†	C28	II	29	Δ	23#12,2#8,4#1/0		X					23		2				4								
C28-42	•	†	C28	-	6	Δ	2#10,4#4/0	X		X					2					4								
C28-43	•	†	C28	-	8	Δ	4#12,4#350MCM	X						4									4					
C28-627	•	†	C28	III	6	Δ	6#1/0		X											6								
C28-628	•	†	C28	III	29	Δ	23#12,2#8,4#1/0		X					23		2				4								
C28-R18	•	†	C28	-	6	Δ	2#12,4#350MCM	X			X			2									4					
C28-R42	•	†	C28	-	6	Δ	2#10,4#4/0	X		X	X				2					4								
C28-R44	•		C28	-	7	Δ	1#10,3#8,3#4/0	X		X	X				1	3				3								

Arrangements with RADSOK contacts are designated with an 'R' in front of the dash number. Example ZP-16-R322

CREATE YOUR PART NUMBER

STEP 5: SELECT CONTACT TYPE



P = Pin

S = Socket

STEP 6: SELECT CONTACT TERMINATION



Blank = Solder

N = Crimp

R = Pressure

See Layout Table for valid Termination Type

STEP 7: SELECT CONTACT PLATING



Blank = Silver

K = Gold

STEP 8: SELECT KEYING



Blank = Normal

See Layout Table for valid Keying by Insert Layout

STEP 9: CABLE TYPE



Blank = Unarmored

BS = Armored & Sheathed Cable

BSR = Armored & Sheathed
with Reduced Bore Cable

CREATE YOUR PART NUMBER

Grounding Contact Termination Symbol

 Solder Well

 Pressure

 Crimp

○
18

●
16

⊕
12

○
10

⊙
8

●
4

⊕
1/0

⊕
4/0







⊕
350 MCM

⊕
500 MCM

⊕
646-777

CONTACTS

1



LAYOUT
OF CONTACTS

C24-386
1#777MCM

C24-R386
1#777MCM

C24-535
1#535MCM







C24-R535
1#535MCM

C24-313
1#313MCM

C24-R313
1#313MCM

CONTACTS

1



LAYOUT
OF CONTACTS

C24-373
1#373MCM

C24-R373
1#373MCM

C20-379
1#500MCM







12-27
3#12

12-327
3#12

12-330
3#12

CONTACTS

3



LAYOUT
OF CONTACTS

12-637
3#10

12-45
3#8

12-649
3#10







12-651
3#10

12-56
3#8

16-51
3#4

CONTACTS

3



LAYOUT
OF CONTACTS

16-70
3#4

16-74
3#4

12-14
4#10

12-314
4#10

12-614
4#10

12-15
4#10

LAYOUT BY NUMBER OF CONTACTS

Grounding Contact Termination Symbol



Solder Well



Pressure



Crimp



18



16



12



10



8



4



1/0



4/0



350 MCM




500 MCM



646-777

CONTACTS

4


LAYOUT
OF CONTACTS

12-16
4#10

12-316
4#10

12-616
4#10


12-22
4#10

12-322
4#10

12-33
4#16

CONTACTS

4


LAYOUT
OF CONTACTS

12-333
4#16

12-46
4#10

12-346
4#10


16-22
4#4

16-322
4#4

16-622
4#4

CONTACTS

4


LAYOUT
OF CONTACTS

16-23
4#4

16-26
4#8

16-28
4#8


16-328
4#8

16-628
4#8

16-38
4#4

CONTACTS

4


LAYOUT
OF CONTACTS

16-638
4#4

16-47
4#10

20-39
4#1/0

20-639
4#1/0

C20-40
4#1/0

C20-640
4#1/0

Grounding Contact Termination Symbol

 Solder Well

 Pressure

 Crimp

 18

 16

 12

 10

 8

 4

 1/0

 4/0


 350 MCM

 500 MCM

 646-777


CONTACTS

4




LAYOUT
OF CONTACTS


20-41
4#1/0




C20-42
4#1/0




C20-342
4#1/0



C20-642
4#1/0




C24-26
4#4/0



C24-38
4#4/0


CONTACTS

4




LAYOUT
OF CONTACTS


C24-39
4#4/0




C24-42
4#1/0




C24-43
4#1/0



24-83
4#4/0




12-21
5#12



12-24
5#12


CONTACTS

5




LAYOUT
OF CONTACTS


12-324
5#12




12-624
5#12




12-326
3#16,2#8



12-53
5#12




12-653
5#12



16-16
5#8


CONTACTS

5




LAYOUT
OF CONTACTS


16-316
5#8




16-27
5#8



16-31
5#8




16-345
5#8



16-616
5#8

image not
available



16-75
5#8

LAYOUT BY NUMBER OF CONTACTS

Grounding Contact Termination Symbol



Solder Well



Pressure



Crimp



18



16



12



10



8



4



1/0



4/0



350 MCM




500 MCM








646-777

CONTACTS


5







LAYOUT
OF CONTACTS

20-36
5#4

20-37
5#4

20-337
5#4

20-38
5#4

20-49
3#12,2#1/0

20-649
3#12,2#1/0

CONTACTS

5



LAYOUT
OF CONTACTS






20-84
5#4

20-384
5#4

C24-29
5#1/0

C24-44
5#1/0

C24-48
2#12,3#4/0

C24-49
5#1/0

CONTACTS

5


6







LAYOUT
OF CONTACTS

C24-79
5#1/0

C28-19
5#4/0

C28-20
5#4/0

C28-23
5#4/0

20-43
2#10,4#4

20-643
2#10,4#4

CONTACTS

6


LAYOUT
OF CONTACTS

20-46
4#4,2#1/0

20-646
4#4,2#1/0

20-48
3#12,3#1/0

20-648
3#12,3#1/0

20-672
4#12,2#4

C24-50
2#10,1#4,3#1/0

CREATE YOUR PART NUMBER

Grounding Contact Termination Symbol

 Solder Well

 Pressure

 Crimp

 18

 16

 12

 10

 8

 4

 1/0

 4/0


 350 MCM

 500 MCM

 646-777

CONTACTS

6




LAYOUT
OF CONTACTS


C24-72
3#12,3#4/0




C28-17
2#12,4#4/0




C28-18
2#12,4#350MCM



C28-R18
2#12,4#350MCM



C28-327
6#1/0




C28-627
6#1/0

CONTACTS


6

7




LAYOUT
OF CONTACTS


C28-42
2#10,4#4/0




C28-R42
2#10,4#4/0




12-10
7#12



12-310
7#12




12-11
7#12



12-311
7#12


CONTACTS

7




LAYOUT
OF CONTACTS


12-348
7#16




12-648
7#16




12-354
7#12



12-654
7#12




16-378
7#12



20-56
7#COAX


CONTACTS

7




LAYOUT
OF CONTACTS


20-359
7#8




20-659
7#8




C24-R44
3#1/0,3#8,1#10



24-658
7#4



C24-59
7#1/0



C24-659
7#1/0

LAYOUT BY NUMBER OF CONTACTS

Grounding Contact Termination Symbol



Solder Well



Pressure



Crimp



18



16



12



10



8



4



1/0



4/0



350 MCM




500 MCM








646-777

CONTACTS


7







LAYOUT
OF CONTACTS

C28-R44
1#10,3#8,3#4/0

C24-353
4#12,4#1/0

24-55
4#4,4#1/0

24-655
4#4,4#1/0

24-57
8#COAX

C28-21
4#12,4#350MCM

CONTACTS


8







LAYOUT
OF CONTACTS

C28-43
4#12,4#350MCM

16-29
8#16,1#4

16-346
6#12,3#8

C24-687
2#12,4#4,3#1/0

12-17
10#16

12-317
10#16

CONTACTS


10







LAYOUT
OF CONTACTS

12-617
10#16

12-334
10#16

12-355
10#16

12-655
10#16

16-376
6#12,4#10

16-676
6#12,4#10

CONTACTS


10







LAYOUT
OF CONTACTS

16-381
6#12,4#10

16-681
6#12,4#10

20-55
8#12,2#1/0

20-680
6#12,4#4

20-685
6#12,4#4

24-673
8#8,2#4

CONTACTS

10


LAYOUT
OF CONTACTS

C24-675
6#12,4#1/0

C24-680
6#12,4#1/0

20-375
12#10

16-349
12#16,2#4

24-40
10#16,5#1/0

C24-47
10#12,5#1/0

CREATE YOUR PART NUMBER

Grounding Contact Termination Symbol

 Solder Well

 Pressure

 Crimp

 18

 16

 12

 10

 8

 4

 1/0

 4/0

 350 MCM

 500 MCM







 646-777

CONTACTS

15

16

17



LAYOUT
OF CONTACTS

C24-81
10#12,5#1/0

16-25
16#16

16-325
16#16

20-358
16#8







12-23
17#18

12-323
17#18

CONTACTS

18

19



LAYOUT
OF CONTACTS

16-24
16#16,2#10

16-324
16#16,2#10

16-624
16#16,2#10







16-11
19#12

16-311
19#12

16-611
19#12

CONTACTS

19



LAYOUT
OF CONTACTS

16-12
19#12

16-312
19#12

16-355
19#16

16-655
19#16







16-377
19#12

16-677
19#12

CONTACTS

19

20



LAYOUT
OF CONTACTS

20-376
19#12

20-676
19#12

20-388
19#12

20-688
19#12

20-32
20#12

20-332
20#12

LAYOUT BY NUMBER OF CONTACTS

Grounding Contact Termination Symbol



Solder Well



Pressure



Crimp



18



16



12



10



8



4



1/0



4/0



350 MCM



500 MCM








646-777

CONTACTS

20

21


image not
available

LAYOUT
OF CONTACTS

20-632
20#12

20-34
16#16,4#8

20-334
16#16,4#8

20-387
20#12

16-344
11#16,10#12







20-390
21#12

CONTACTS

22

26

27


LAYOUT
OF CONTACTS

20-31
20#16,2#8

20-331
20#16,2#8

20-357
20#16,2#COAX

16-37
18#18,4#16,4#12







16-335
24#16,3#12

16-635
24#16,3#12

CONTACTS

27

29


LAYOUT
OF CONTACTS

16-373
24#16,3#12

16-673
24#16,3#12

20-374
25#12,2#4







20-674
25#12,2#4

C28-328
23#12,2#8,4#1/0

C28-628
23#12,2#8,4#1/0

CONTACTS

37


LAYOUT
OF CONTACTS

16-21
37#16

16-321
37#16

16-621
37#16

20-10
37#12

20-310
37#12

20-350
37#12

CREATE YOUR PART NUMBER

Grounding Contact Termination Symbol

 Solder Well

 Pressure

 Crimp

 18

 16

 12

 10

 8

 4

 1/0

 4/0

 350 MCM







 500 MCM

 646-777

CONTACTS

37

38



LAYOUT
OF CONTACTS

20-386
37#12

20-686
37#12

C24-36
35#12,2#1/0

24-371
37#16

20-23
35#16,3#10

20-323
35#16,3#10

CONTACTS

38








39

42

46

47

50



LAYOUT
OF CONTACTS

20-623
35#16,3#10

C28-12
31#12,5#10,1#8,2#1/0

28-339
42#12

16-371
45#18,1#8

20-354
45#16,2#8







C28-15
43#12,3#4,1#1/0

20-673
46#16,4#8

CONTACTS

55

58



LAYOUT
OF CONTACTS

16-40
55#18

16-640
55#18

28-324
41#16,5#12,3#8,6#4

24-11
58#12







24-311
58#12

24-352
58#12

CONTACTS

58

60



LAYOUT
OF CONTACTS

24-84
58#12

24-384
58#12

20-35
60#16

24-31
53#16,7#12

24-331
53#16,7#12

24-389
60#16

LAYOUT BY NUMBER OF CONTACTS

Grounding Contact Termination Symbol



Solder Well



Pressure



Crimp



18



16



12



10



8



4



1/0



4/0



350 MCM



500 MCM









646-777

CONTACTS

61

62

64


LAYOUT
OF CONTACTS

16-33
61#18

16-333
61#18

16-633
61#18

24-362
62#16

20-29
62#16, 2#10

20-329
62#16, 2#10

CONTACTS







66

68

72

75

81


LAYOUT
OF CONTACTS

24-16
58#16, 5#12, 3 COAX

20-13
68#16

20-313
68#16

24-388
72#16

24-354
61#16, 11#12, 3#8







20-44
69#18, 12#12

CONTACTS

81

90

100


LAYOUT
OF CONTACTS

20-344
69#18, 12#12

20-45
90#18

20-345
90#18

24-13
100#16






24-313
100#16

24-613
100#16

CONTACTS

100

143


LAYOUT
OF CONTACTS

24-385
100#16

28-14
83#16, 17#12

28-314
83#16, 17#12


28-22
143#16

28-322
143#16

DIMENSIONS

PLUGS


EX-13-2 STYLE PLUG WITH MECHANICAL CLAMP (POTTING REQUIRED)



SHELL SIZE	A*	B*	C	D	E	F
12	7-7/16 (189)	3-9/16 (91)	2-1/8 (54)	2 (51)	15/16 (24)	2-3/8 (60)
16	9-1/2 (241)	3-9/16 (91)	2-5/8 (67)	2-1/16 (52)	1-7/16 (37)	3 (76)
20	9-9/16 (243)	3-9/16 (91)	3-1/8 (79)	2-1/8 (54)	1-15/16 (49)	3-3/4 (95)
24	9-5/8 (245)	3-9/16 (91)	3-5/8 (92)	2-3/16 (56)	2-7/16 (62)	4-1/2 (114)
28	9-11/16 (246)	3-9/16 (91)	4-1/8 (105)	2-1/4 (57)	2-7/8 (73)	5-1/8 (130)

*Note: For "C" length inserts, add 1/2" to both dimensions "A" & "B".

EX-13-3 STYLE PLUG WITH EEX D GLAND




SHELL SIZE	A*	B*	C	GLAND THREAD
12	6-1/16 (154)	3-9/16 (91)	2-1/8 (54)	M25
16	8-1/16 (205)	3-9/16 (91)	2-5/8 (67)	M40
20	8-1/16 (205)	3-9/16 (91)	3-1/8 (79)	M50
24	8-1/16 (205)	3-9/16 (91)	3-5/8 (92)	M63
28	8-1/16 (205)	3-9/16 (91)	4-1/8 (105)	M75

*Notes: For "C" length inserts, add 1/2" to both dimensions "A" & "B".

'D' Dimension varies according to cable gland. Detailed cable dimensions and type required.

Gland is included with the connector.

EX-13-4 STYLE PLUG WITH BASKETWEAVE CABLE GRIP W (POTTING REQUIRED)



SHELL SIZE	A*	B*	C	D	E	F	G
12	6-1/16 (154)	3-9/16 (91)	2-1/8 (54)	1-1/4 (32)	15/16 (24)	1-9/32 (33)	8 (203)
16	8-1/16 (205)	3-9/16 (91)	2-5/8 (67)	1-1/4 (32)	1-7/16 (37)	1-25/32 (45)	10-1/2 (267)
20	8-1/16 (205)	3-9/16 (91)	3-1/8 (79)	1-1/4 (32)	1-15/16 (49)	2-9/32 (58)	14-1/2 (368)
24	8-1/16 (205)	3-9/16 (91)	3-5/8 (92)	1-1/4 (32)	2-7/16 (62)	2-25/32 (71)	17-1/2 (445)
28	8-1/16 (205)	3-9/16 (91)	4-1/8 (105)	1-1/4 (32)	2-7/8 (73)	3-9/32 (83)	19 (483)

*Note: For "C" length inserts, add 1/2" to both dimensions "A" & "B".


Dimensions are shown in Inches (mm) unless otherwise indicated.

RECEPTACLES

EX-15-2 STYLE IN-LINE RECEPTACLE WITH MECHANICAL CLAMP (POTTING REQUIRED)

SHELL SIZE	A*	B*	C	D	E	F
12	7 (178)	1-7/16 (37)	1-1/2 (38)	2 (51)	15/16 (24)	2-3/8 (60)
16	9-1/16 (230)	1-7/16 (37)	2 (51)	2-1/16 (52)	1-7/16 (37)	3 (76)
20	9-1/8 (232)	1-7/16 (37)	2-1/2 (64)	2-1/8 (54)	1-15/16 (49)	3-3/4 (95)
24	9-3/16 (233)	1-7/16 (37)	3 (76)	2-3/16 (56)	2-7/16 (62)	4-1/2 (114)
28	9-1/4 (235)	1-7/16 (37)	3-1/2 (89)	2-1/4 (57)	2-7/8 (73)	5-1/8 (130)

*Note: For "C" length inserts, add 1/2" to both dimensions "A" & "B".




EX-15-3 STYLE IN-LINE RECEPTACLE WITH EEX D GLAND

SHELL SIZE	A*	B*	C	GLAND THREAD
12	5-5/8 (143)	1-7/16 (37)	1-1/2 (38)	M25
16	7-5/8 (194)	1-7/16 (37)	2 (51)	M40
20	7-5/8 (194)	1-7/16 (37)	2-1/2 (64)	M50
24	7-5/8 (194)	1-7/16 (37)	3 (76)	M63
28	7-5/8 (194)	1-7/16 (37)	3-1/2 (89)	M75

*Notes: For "C" length inserts, add 1/2" to both dimensions "A" & "B".

'D' Dimension varies according to cable gland. Detailed cable dimensions and type required. Gland is included with the connector.




EX-15-4 STYLE IN-LINE RECEPTACLE WITH BASKETWEAVE CABLE GRIP (POTTING REQUIRED)

SHELL SIZE	A*	B*	C	D	E	F	G
12	6-1/4 (159)	1-7/16 (37)	1-1/2 (38)	1-1/4 (32)	15/16 (24)	1-9/32 (33)	8 (203)
16	8-1/4 (210)	1-7/16 (37)	2 (51)	1-1/4 (32)	1-7/16 (37)	1-25/32 (45)	10-1/2 (267)
20	8-1/4 (210)	1-7/16 (37)	2-1/2 (64)	1-1/4 (32)	1-15/16 (49)	2-9/32 (58)	14-1/2 (368)
24	8-1/4 (210)	1-7/16 (37)	3 (76)	1-1/4 (32)	2-7/16 (62)	2-25/32 (71)	17-1/2 (445)
28	8-1/4 (210)	1-7/16 (37)	3-1/2 (89)	1-1/4 (32)	2-7/8 (73)	3-9/32 (83)	19 (483)

*Note: For "C" length inserts, add 1/2" to both dimensions "A" & "B".


Dimensions are shown in Inches (mm) unless otherwise indicated.



EX-17-1 STYLE PANEL MOUNT RECEPTACLE

SHELL SIZE	A*	B*	C	D	E	F
12	4-7/16 (113)	1.765 (45)	1-1/2 (38)	1.654 (42)	2-1/4 (57)	M40
16	4-7/16 (113)	1.765 (45)	2 (51)	2.047 (52)	2-5/8 (67)	M50
20	4-7/16 (113)	1.765 (45)	2-1/2 (64)	2.441 (62)	3 (76)	M63
24	4-7/16 (113)	1.765 (45)	3 (76)	2.835 (72)	3-1/2 (89)	M75
28	4-7/16 (113)	1.765 (45)	3-1/2 (89)	3.228 (82)	4 (102)	M90


*Note: For "C" length inserts, add 1/2" to both dimensions "A" & "B".



EX-17-2 STYLE FIXED IN-LINE RECEPTACLE WITH MECHANICAL CLAMP (POTTING REQUIRED)

SHELL SIZE	A*	B*	C	D	E	F
12	7 (178)	1-7/16 (37)	1-1/2 (38)	2 (51)	5/16 (24)	2-3/8 (60)
16	9-1/16 (230)	1-7/16 (37)	2 (51)	2-1/16 (52)	1-7/16 (37)	3 (76)
20	9-1/8 (229)	1-7/16 (37)	2-1/2 (64)	2-1/8 (54)	1-15/16 (49)	3-3/4 (95)
24	9-3/16 (233)	1-7/16 (37)	3 (76)	2-3/16 (56)	2-7/16 (62)	4-1/2 (114)
28	9-1/4 (235)	1-7/16 (37)	3-1/2 (89)	2-1/4 (57)	2-7/8 (73)	5-1/8 (130)


*Note: For "C" length inserts, add 1/2" to both dimensions "A" & "B".



EX-17-3 STYLE FIXED IN-LINE RECEPTACLE WITH EEX D GLAND

SHELL SIZE	A*	B*	C	D
12	5-5/8 (143)	1-7/16 (37)	1-1/2 (38)	M25
16	7-7/8 (194)	1-7/16 (37)	2 (51)	M40
20	7-7/8 (194)	1-7/16 (37)	2-1/2 (64)	M50
24	7-7/8 (194)	1-7/16 (37)	3 (76)	M63
28	7-7/8 (194)	1-7/16 (37)	3-1/2 (89)	M75


*Note: For "C" length inserts, add 1/2" to both dimensions "A" & "B".



EX-17-4 STYLE FIXED IN-LINE RECEPTACLE WITH BASKETWEAVE CABLE GRIP (POTTING REQUIRED)

SHELL SIZE	A*	B*	C	D	E	F	G
12	6-1/4 (159)	1-7/16 (37)	1-1/2 (38)	1-1/4 (32)	5/16 (24)	1-9/32 (33)	8 (203)
16	8-1/4 (210)	1-7/16 (37)	2 (51)	1-1/4 (32)	1-7/16 (37)	1-25/32 (45)	10-1/2 (267)
20	8-1/4 (210)	1-7/16 (37)	2-1/2 (64)	1-1/4 (32)	1-15/16 (49)	2-9/32 (58)	14-1/2 (368)
24	8-1/4 (210)	1-7/16 (37)	3 (76)	1-1/4 (32)	2-7/16 (62)	2-25/32 (71)	17-1/2 (445)
28	8-1/4 (210)	1-7/16 (37)	3-1/2 (89)	1-1/4 (32)	2-7/8 (73)	3-9/32 (83)	19 (483)

*Note: For "C" length inserts, add 1/2" to both dimensions "A" & "B".



MOD II CRIMP CONTACTS & TOOLING

CONTACT SIZE	CRIMP WIRE RANGE	PIN	"C" PIN*	GROUND PIN	SOCKET	WIRE STRIP LENGTH	HAND CRIMP TOOL	LOCATOR	POWER CRIMP TOOL	POWER CRIMP DIE	POWER CRIMP LOCATOR	"C" PIN LOCATOR	INSERTION TOOL	EXTRACTION TOOL
18	18-22 AWG	ZP-4018-36L	-	-	ZP-4118-36L	11.5mm	M300-25A	TP682-1	-	-	-	-	TP-201047-1	TP-201459 (pin) TP-201011-3 (skt)
16	16-20 AWG	ZP-4016-36L	-	ZP-4016-37L	ZP-4116-36L	14.6mm	M300-25A	TP682-1	-	-	-	-	TP-201048-1	TP-201459 (pin) TP-201010-3 (skt)
12	12-16 AWG	ZP-4012-36L	ZP-4012-36LB	ZP-4012-37L3	ZP-4112-36L	15.5mm	M300-25A	TP683-1 (pin) TP684-1 (skt)*	400-B-1	414DA-12N	4150	4151	TP-201049-1	TP-201459 (pin) TP-201009-3 (skt)
10	10-14 AWG	ZP-4010-36L	-	ZP-4010-37L2	ZP-4110-36L	17.1mm	M300-25A	TP684-1	400-B-1	414DA-10N	4152	-	TP-201046-1	TP-201459 (pin) TP-201008-3 (skt)
8	8-10 AWG	ZP-4008-36L	-	-	ZP-4108-36L	21.0mm	-	-	400-B-1	414DA-8N	4154	-	TP-201007-A TP-201007-B	Contact us
4	4-6 AWG	ZP-4004-36L	-	-	ZP-4104-36L	23.0mm	-	-	400-B-1	414DA-4N	4156	-	TP-201033-A TP-201033-B	Contact us
1/0	1/0-2 AWG	-	ZP-4000-66LB	-	ZP-4100-66L	31.0mm	-	-	400-B-1	414DA-1/0PN 414DA-2PN	-	4158	-	Contact us
4/0	4/0-2/0 AWG	-	ZP-4041-76LB	-	ZP-4141-76L	31.6mm	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us
313 MCM	313 MCM	-	RIG-C24-313PN	-	RIG-C24-313SN	33.5mm	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us
373 MCM	373 MCM	-	RIG-C24-373PN	-	RIG-C24-373SN	33.5mm	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us
500 MCM	500-535 MCM	-	P-206053-CP	-	P-206053-CS	33.5mm	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us
535 MCM	535 MCM	-	RIG-C24-535PN	-	RIG-C24-535SN	33.5mm	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us
646 MCM	646-777 MCM	-	RIG-C24-386PN	-	RIG-C24-386SN	33.5mm	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us	Contact us

MOD III CRIMP CONTACTS & TOOLING

CONTACT SIZE	CRIMP WIRE RANGE	PIN	"C" PIN*	GROUND PIN	SOCKET	WIRE STRIP LENGTH	HAND CRIMP TOOL	LOCATOR	POWER CRIMP TOOL	POWER CRIMP DIE	POWER CRIMP LOCATOR	"C" PIN LOCATOR	INSERTION TOOL	EXTRACTION TOOL
18	18-22 AWG	ZP-4018-50L	-	-	ZP-4108-50L	11.5mm	M300-25A	TP682-1	-	-	-	-	Not required	TP-201315-18
16	16-20 AWG	ZP-4016-50L	-	-	ZP-4106-50L	14.6mm	M300-25A	TP682-1	-	-	-	-	Not required	TP-201315-16
12	12-16 AWG	ZP-4012-50L	ZP-4012-50LB	ZP-4012-52LK	ZP-4102-50L	15.5mm	M300-25A	TP684-1 (skt) TP683-1 (pin)	400-B-1	414DA-12N	4002-3	4002-3	Not required	TP-201315-12
10	10-14 AWG	ZP-4010-50L		ZP-4010-52LK	ZP-4100-50L	17.1mm	M300-25A	TP684-1	400-B-1	414DA-10N	4003-3	4003-3	Not required	TP-201315-10
8	8-10 AWG	ZP-4008-50L	ZP-4008-50LB		ZP-4108-50L	21.0mm	-	-	400-B-1	414DA-8N	4004-3	4004-3	Not required	TP-201315-08
4	4-6 AWG	ZP-4004-50L		ZP-4004-52LK	ZP-4104-50L	23.0mm	-	-	400-B-1	414DA-4N	4005-3	4005-3	Not required	TP-201315-04
1/0	1/0-2 AWG	-	ZP-4000-50LB	ZP-4800-52LK	ZP-4100-50L	31.0mm	-	-	400-B-1	414DA-1/0PN 414DA-2PN	-	4006-3	Not required	TP-201260-00

* "C" pins are used in C length inserts and are 1/2 in. longer than standard Thermocouple contacts for Mod II size 16 (crimp) - contact us.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[EX-15-3-C2-16-321PN-BS](#) [EX-13-3-A-12-333PN-BS](#) [EX-13-3-A1-12-333SN-BS](#) [EX-17-3-A1-12-333PN-BS](#) [EXS-17-1-12-355PNK](#) [EXS-17-1-12-648SNK](#)