



Experience the difference in power:
CoolMOS™ 7 - CoolSiC™ - CoolGaN™
and complementing EiceDRIVER™ ICs

www.infineon.com/coolmos
www.infineon.com/coolsic
www.infineon.com/coolgan
www.infineon.com/eicedriver

EN





Content

| | |
|---|-----------|
| Experience the difference in power: CoolMOS™ 7 – CoolSiC™ - CoolGaN™ | 4 |
| Application overview | 5 |
| Automotive applications | 6 |
| On-board charger | 6 |
| DC-DC converter | 7 |
| Industrial applications | 8 |
| EV charging | 8 |
| Battery powered applications | 10 |
| Telecom power supply | 11 |
| Server power supply | 13 |
| Industrial SMPS | 15 |
| Solar | 16 |
| Consumer applications | 19 |
| TV power supply | 19 |
| Adapter and charger power supply | 20 |
| LED lighting | 21 |
| Audio power supply and class D amplifiers | 22 |
| PC power supply | 23 |
| Smart meter | 24 |
| Major home appliances | 25 |
| CoolMOS™ package innovations | 27 |
| Product portfolio | 28 |

Infiniteon masters it all – for you

Experience the difference in power with CoolMOS™, CoolSiC™, and CoolGaN™

Infiniteon is the leader in the power semiconductor market and currently the only manufacturer mastering all power technologies while offering the broadest product and technology portfolio of silicon (such as SJ MOSFETs, IGBTs), silicon carbide (such as Schottky diodes and MOSFETs) and gallium-nitride-based (e-mode HEMTs) devices, covering bare die, discretes, and modules.

Equipped with a 300-millimeter wafer fab for power semiconductors, Infiniteon is best positioned to fully seize the growth opportunities in the power semiconductor industry.

With its high-quality and highly efficient products, Infiniteon is setting new standards for energy efficiency, power density and ease of use.

CoolMOS™ SJ MOSFET products boast outstanding figures of merit in terms of conduction, switching and driving losses. CoolSiC™ and CoolGaN™ enable extremely efficient and compact system designs that meet future demands for greener and better performing products. Additionally, a comprehensive portfolio of gate-driver ICs for silicon and wide bandgap technologies unlock the full potential of the switches.

The 600 V/650 V class of power products is the area where CoolMOS™, CoolSiC™ and CoolGaN™ will coexist, delivering a specific value proposition depending on application requirements.

CoolMOS™ Superjunction MOSFETs



- › Best price/performance ratio
- › Largest SJ MOSFET portfolio on the market
- › Mature, stable, well-established

CoolSiC™ MOSFETs




- › High performance, robustness and ease of use
- › High reliability especially with high temperature and in harsh environments
- › Smaller system size

CoolGaN™ HEMTs



- › Highest efficiency at the highest frequency
- › Smallest system size
- › Enables system integration

Technology comparison



www.infineon.com/coolmos

www.infineon.com/coolsic

www.infineon.com/coolgan

Application to product matrix

| Application | CoolMOS™ 7 | | | | | | | | | | | | CoolMOS™ Automotive | | | | CoolSiC™ | | CoolGaN™ | |
|---|-------------|---------------|---------------|-------------|-------------|-------------|-------------|-------------|--------------|--------------|--------------|--------------|---------------------|---------------|--------------|--------------|--------------|------------------|----------|-------|
| | S7 600 V | CFD7 600 V | PFD7 600 V | C7 650 V | C7 600 V | G7 650 V | G7 600 V | P7 600 V | P7S 600 V | P7S 700 V | P7S 800 V | P7S 950 V | CFD7A 650 V | CFDA 650 V | C3A 800 V | CPA 600 V | SiC Diode | SiC MOS 650 V | 600 V | 400 V |
| Automotive | | | | | | | | | | | | | | | | | | | | |
| On-board charger (OBC) | | | | | | | | | | | | | ✓ | ✓ | | ✓ | | | | |
| HV-LV DC-DC converter | | | | | | | | | | | | | ✓ | ✓ | ✓ | | | | | |
| Industrial | | | | | | | | | | | | | | | | | | | | |
| EV Charging | | ✓ | | ✓ | | ✓ | | ✓ | | | | | | | | | | ✓ | | |
| Server | ✓ | ✓ | | ✓ | ✓ | ✓ | ✓ | ✓ | | | ✓ | | | | | | ✓ | ✓ | ✓ | |
| Telecom | ✓ | ✓ | | ✓ | ✓ | ✓ | ✓ | ✓ | | | ✓ | | | | | | ✓ | ✓ | ✓ | |
| Industrial SMPS | ✓ | ✓ | | ✓ | ✓ | ✓ | ✓ | ✓ | | | ✓ | | | | | | ✓ | ✓ | ✓ | |
| Solar/UPS | ✓ | | | ✓ | | ✓ | | ✓ | | | ✓ | | | | | | ✓ | ✓ | | |
| LSEV (industrial battery charger) | | ✓ | | ✓ | | ✓ | | ✓ | | | | | | | | | ✓ | ✓ | | |
| Solid state relays and circuit breakers | ✓ | | | | | | | ✓ | | ✓ | ✓ | | | | | | | | | |
| Battery formation | ✓ | ✓ | | ✓ | ✓ | ✓ | ✓ | ✓ | | | ✓ | | | | | | ✓ | ✓ | | |
| Consumer | | | | | | | | | | | | | | | | | | | | |
| TV/PC/Gaming | | | | | | | | | ✓ | ✓ | ✓ | | | | | | | | | |
| Charger/adapters | | | ✓ | | | | | | ✓ | ✓ | ✓ | ✓ | | | | | | | ✓ | |
| Lighting | | | | | | | | | ✓ | ✓ | ✓ | ✓ | | | | | | | | |
| Audio | | | | | | | | | ✓ | ✓ | ✓ | | | | | | | | | ✓ |
| Smart meter | | | | | | | | | | ✓ | ✓ | ✓ | | | | | | | | |
| Major home appliances | | | ✓ | | | | | | | | | | | | | | | | | |

Automotive portfolio

| CoolMOS™ C3A – 800 V | CoolMOS™ CPA – 600 V | CoolMOS™ CFDA – 650 V | | CoolMOS™ CFD7A – 650 V | |
|---------------------------|-------------------------|--------------------------|-----|---------------------------|-----|
| Bias supply | PFC | PFC | LLC | PFC | LLC |
| $R_{DS(on)}$: 22-2700 mΩ | | | | | |

Industrial portfolio

| CoolMOS™ S7 – 600 | CoolMOS™ C7 – 600 V C7 – 650 V G7 – 600 V G7 – 650 V CFD7 – 600 V | CoolMOS™ C7 – 600 V G7 – 600 V CFD7 – 600 V | CoolMOS™ CFD7 – 600 V | CoolMOS™ P7 – 600 V | CoolMOS™ P7 – 600 V CFD7 – 600 V | CoolMOS™ CFD7 – 600 V | CoolSiC™ diode 600 V/650 V | CoolGaN™ 600 V |
|----------------------------|--|--|--------------------------|------------------------|--|--------------------------|----------------------------------|--------------------------|
| Synchronous Rectification | PFC | LLC | ZVS PS FB | PFC | LLC | ZVS PS | PFC | PFC |
| $R_{DS(on)}$: 17 – 190 mΩ | | | | | | | I_F : 4-20 A | $R_{DS(on)}$: 70-190 mΩ |

Consumer portfolio

| CoolMOS™ PFD7 – 600 V | | CoolMOS™ P7 – 600 V | | CoolMOS™ P7 – 700 V | | CoolMOS™ P7 – 800 V | | CoolMOS™ P7 – 950 V | | CoolGaN™ 400 V and 600 V | |
|-------------------------------------|--|-------------------------------------|-----|-------------------------------------|---------|-------------------------------------|---------|-------------------------------------|---------|----------------------------------|--|
| PFC/Flyback/Inverter | | Flyback | LLC | PFC | Flyback | PFC | Flyback | PFC | Flyback | Flyback | |
| R _{DS(on)} 125 mΩ - 2 Ω | | R _{DS(on)} 0.18 – 0.6 Ω | | R _{DS(on)} 0.36 – 2.0 Ω | | R _{DS(on)} 0.28 – 4.5 Ω | | R _{DS(on)} 0.45 – 3.7 Ω | | R _{DS(on)} 70-190 mΩ | |

www.infineon.com/coolmos

www.infineon.com/coolsic

www.infineon.com/coolgan



On-board charger

Automotive-qualified products have a long track record at Infineon. With a proven experience in serving major market players with high quality and reliable devices, Infineon offerings balance highest performance at attractive costs combined with high delivery reliability. While further improving performance of new products, Infineon continuously invests in capacity expansion to support the upcoming demand. The mainstream applications use high voltage battery systems up to 475 V_{DC} supporting system cost optimization.


On-board charger

In cars with on-board chargers (OBC), the batteries can be recharged from any standard AC power outlet (single or three phase), which provides power typically from 3.6 kW up to 11 kW. Charging cases can be clustered in:

- > Harbor charging at home or at the office (low power AC)
- > Destination charging at while parking e.g. supermarkets, cinemas and restaurants (low power AC or low power DC)
- > Range extension charging at highways and travel routes (high power DC)

The main requirements for OBC beside meeting automotive reliability standards are high power density and low cost at moderate efficiency levels (> 94%). Bidirectional OBCs are emerging and will become an even more important additional feature in future.

The typical OBC structure contains a PFC stage and an isolated high-voltage DC to DC conversion stage. Filter stages are required to comply with EMI standards and to protect the board net form undesired disturbances.






High-voltage to low-voltage DC-DC converter

While DC-DC converters within the onboard charger take care about charging the battery, the high-voltage to low-voltage DC-DC converter ensures energy flow towards the low voltage battery in a hybrid or electric vehicle. In some cases the DC-DC converter will be bidirectional.

The systems are optimized for light load conditions. The power requirements are in the range of 3500 W. Typical requirements besides high power density and low cost are low ripple current, excellent EMI behavior, as well as bidirectional power flow capabilities.



Automotive products for onboard units

| Functional block | Product category | Description |
|----------------------------------|-------------------------------|---|
| Power | Automotive CoolMOS™ CFD7A | 650 V MOSFET with integrated fast body diode, $R_{DS(on)}$: 22 to 230 mΩ |
| | Automotive CoolMOS™ CFDA | 650 V MOSFET with integrated fast body diode, $R_{DS(on)}$: 48 to 660 mΩ |
| | Automotive CoolMOS™ C3A | 800 V MOSFET, $R_{DS(on)}$: 290 and 2700 mΩ |
| | Automotive CoolMOS™ CPA | 600 V MOSFET, $R_{DS(on)}$: 45 to 299 mΩ |
| | Automotive TRENCHSTOP™ 5 IGBT | 600 V/650 V IGBT with and wo co-packed SiC or fast body diode, 15-50 A |
| | Automotive CoolSiC™ - diode | 650 V SiC diode, 8-50 A |
| | Automotive CoolSiC™ - MOSFET | 1200 V, 20-120 mΩ |
| Gate driver | Automotive EiceDRIVER™ | Single- and dual-channel isolated driver |
| Supply and control | OPTIREG™ | System supply optimized for AURIX™ |
| | CAN FD Transceiver | High-speed automotive CAN transceiver |
| Control and communication | AURIX™ microcontroller | 32-bit lockstep microcontroller |



Off-board DC EV charging stations

What speaks for off-board DC EV charging?

The automotive market is facing growth trend towards electric vehicles (EV), especially in China, where EVs have gained traction. To truly welcome EVs on a large scale, these markets need to provide widespread availability of DC charging infrastructure. DC charging systems are an attractive choice because they offer much faster charging than a standard AC EV charger which many EV drivers possess. Today a DC charger with e.g. 150 kW can put a 200 km charge on an EV battery in just 15 minutes. The improvement of charging technologies is expected to even further lower the charging time.




Consequently, off-board charging is becoming more and more attractive.

Reaching the next level in designing DC EV chargers confronts engineers with many new challenges.



For a DC charging design to be a long term success, you must:

- › Enhance output power to shorten the charging time
- › Improve power density within the set dimensions of the charging station
- › Increase efficiency by boosting the load and decreasing power dissipation
- › Reduce design cost per watt

Overcoming all of the mentioned issues is possible – with the right partner.

| Best-fit performance for target applications  | Adequate ease of use  | High quality and price/performance  |
|---|--|---|
| <ul style="list-style-type: none"> › Ultrafast body diode and best-in-class Q_{rr} level of all CoolMOS™ families › Highest reliability and robustness › Highest efficiency within CoolMOS™ fast body diode series › Enabling highest power density levels thanks to best-in-class $R_{DS(on)}$ in THD and SMD packages | <ul style="list-style-type: none"> › 600 V CoolMOS™ P7 offers <ul style="list-style-type: none"> – Excellent ESD robustness >2 kV (HBM) – Smooth switching waveforms › 600 V CoolMOS™ CFD7 offers <ul style="list-style-type: none"> – Best-in-class body diode robustness – Early channel shutdown allows increase of $R_{Gon, ext.}$ without negative impact on efficiency | <ul style="list-style-type: none"> › Best-in-class price/performance ratio <ul style="list-style-type: none"> – Attractive price position for high performance technology › Granular portfolio - $R_{DS(on)}$ range from 70 mΩ down to 18 mΩ in the common TO-247 package › High Infineon quality |

System diagram DC EV charger



www.infineon.com/ev-charging

PFC stage (three-phase input)

| Product category | Product family | Product | Additional information |
|--|-----------------------------------|---------------------------|---|
| High voltage MOSFET / SiC MOSFET/IGBT | 600 V CoolMOS™ C7 | IPW60R017C7 | 600 V, 17 mΩ, TO-247 |
| | 600 V CoolMOS™ P7 | IPW60R024P7 | 600 V, 24 mΩ, TO-247 |
| | | IPW60R037P7 | 600 V, 37 mΩ, TO-247 |
| | | IPW60R060P7 | 600 V, 60 mΩ, TO-247 |
| | 650 V CoolMOS™ C7 | IPW65R019C7 | 650 V, 19 mΩ, TO-247 |
| | CoolSiC™ MOSFET 650 V | IMZA65R027M1H | 650 V, 35 mΩ, TO-247-4 |
| | | IMW65R027M1H | 650 V, 35 mΩ, TO-247-3 |
| | | IMZA65R048M1H | 650 V, 65 mΩ, TO-247-4 |
| | | IMW65R048M1H | 650 V, 65 mΩ, TO-247-3 |
| | TRENCHSTOP™ 5 IGBT 650 V H5 | IKW50N65EH5/IKZ50N65EH5 | 650 V, 50 A, TO-247-3/4 |
| | | IKW75N65EH5/IKZ75N65EH5 | 650 V, 75 A, TO-247-3/4 |
| | CoolSiC™ MOSFET 1200 V | IMW120R045M1/IMZ120R045M1 | 1200 V, 45 mΩ, TO-247-3/4 |
| | CoolSiC™ Easy modules 1200 V | F3L15MR12W2M1_B69 | 1200 V, 15 mΩ, Easy 2B, Vienna rectifier phase leg |
| | | FS45MR12W1M1_B11 | 1200 V, 45 mΩ, Easy 1B, sixpack |
| SiC diodes | CoolSiC™ Schottky diode 1200 V G5 | IDW15G120C5B/IDWD15G120C5 | 1200 V, 15 A, TO-247-3/2 |
| | | IDW20G120C5B/IDWD20G120C5 | 1200 V, 20 A, TO-247-3/2 |
| | | IDW30G120C5B/IDWD30G120C5 | 1200 V, 30 A, TO-247-3/2 |
| Gate driver ICs for high voltage MOSFETs and SiC MOSFETs | EiceDRIVER™ 2EDi | 2EDF7175F | Dual-channel, functional, 1 A/2 A output, 4 V UVLO |
| | | 2EDF7275F | Dual-channel, functional, 4 A/8 A output, 4 V UVLO |
| | | 2EDF7975F | Dual-channel, functional, 2 A/4 A output, 4 V UVLO |
| | EiceDRIVER™ 1EDB* | 1EDB7275F | Single-channel, functional, 4 A/8 A output, 4 V UVLO |
| | | 1EDB8275F | Single-channel, functional, 4 A/8 A output, 8 V UVLO |
| | | 1EDB9275F | Single-channel, functional, 4 A/8 A output, 14 V UVLO |
| | EiceDRIVER™ 1EDN-TDI | 1EDN8550B | Single-channel, low-side gate driver with truly differential inputs |

HV DC-DC main stage




| Product category | Product family | Product | Additional information |
|--|-----------------------------------|---------------------------|---|
| High voltage MOSFET/ SiC MOSFET | 600 V CoolMOS™ CFD7/CSFD | IPW60R024CFD7 | 600 V, 24 mΩ, TO-247 |
| | | IPW60R037CSFD | 600 V, 37 mΩ, TO-247 |
| | | IPW60R040CFD7 | 600 V, 40 mΩ, TO-247 |
| | | IPW60R055CFD7 | 600 V, 55 mΩ, TO-247 |
| | | IPW60R070CFD7 | 600 V, 70 mΩ, TO-247 |
| | | IMW120R045M1/IMZ120R045M1 | 1200 V, 45 mΩ, TO-247-3/4 |
| | CoolSiC™ MOSFET 1200 V | | |
| | CoolSiC™ Easy module 1200 V | FF6MR12W2M1_B11 | 1200 V, 6 mΩ, Easy 2B, half-bridge |
| | | FF8MR12W2M1_B11 | 1200 V, 8 mΩ, Easy 2B, half-bridge |
| | | FF11MR12W1M1_B11 | 1200 V, 11 mΩ, Easy 1B, half-bridge |
| | | FF23MR12W1M1_B11 | 1200 V, 23 mΩ, Easy 1B, half-bridge |
| | | F4-23MR12W1M1_B11 | 1200 V, 23 mΩ, Easy 1B, fourpack |
| | | FS45MR12W1M1_B11 | 1200 V, 45 mΩ, Easy 1B, sixpack |
| Gate driver ICs for high voltage MOSFETs and SiC MOSFETs | EiceDRIVER™ 2EDi | 2EDS8165H | Dual-channel, reinforced, 1 A/2 A output, 8 V UVLO |
| | | 2EDS8265H | Dual-channel, reinforced, 4 A/8 A output, 8 V UVLO |
| | | 2EDS9265H | Dual-channel, reinforced, 4 A/8 A output, 14 V UVLO |
| SiC diodes / output rectification diodes | CoolSiC™ Schottky diode 1200 V G5 | IDW15G120C5B/IDWD15G120C5 | 1200 V, 15 A, TO-247-3/2 |
| | | IDW20G120C5B/IDWD20G120C5 | 1200 V, 20 A, TO-247-3/2 |
| | | IDW30G120C5B/IDWD30G120C5 | 1200 V, 30 A, TO-247-3/2 |
| | CoolSiC™ Schottky diode 650 V G5 | IDW12G65C5 | 650 V, 12 A, TO-247 |
| | | IDW16G65C5 | 650 V, 16 A, TO-247 |
| | | IDW20G65C5 | 650 V, 20 A, TO-247 |
| | | IDW30G65C5 | 650 V, 30 A, TO-247 |
| | | IDW40G65C5 | 650 V, 40 A, TO-247 |
| | CoolSiC™ Schottky diode 650 V G6 | IDH12G65C6 | 650 V, 12 A, TO-220 |
| | | IDH16G65C6 | 650 V, 16 A, TO-220 |
| | | IDH20G65C6 | 650 V, 20 A, TO-220 |



Battery powered applications

We live in a mobile world filled with electrical devices - consumer-grade robots, light electric vehicles, multicopters and other end-products driven by highly efficient electric motors. As these products evolve and improve, there is an increasing need for designers and engineers to find solutions that are more efficient, smaller, and less costly. Based on the industry-leading technology, highest quality, and manufacturing expertise, Infineon provides a variety of innovative power semiconductors addressing a broad range of battery powered motor control applications, such as power tools, forklifts, all kinds of light electric vehicles including e-skateboards, e-scooters, pedelecs, low speed cars, and many others. Through an excellent selection of devices for power management, consumption and voltage regulation – such as power MOSFETs (e.g. CoolMOS™, OptiMOS™, and HEXFET™/StrongIRFET™), XMC™ microcontrollers, EiceDRIVER™ gate drivers and more, Infineon offers all components that are needed for the compact, cost-effective designs of today, and for the innovative designs of tomorrow.

Key enabling products for battery powered applications

| | Consumer robotics  | Home and professional applications  | Light electric vehicles  |
|-----------------------------------|---|--|---|
| MOSFETs | HEXFET™/StrongIRFET™ 20-300 V | | |
| | OptiMOS™ 25-100 V | | OptiMOS™ 80-300 V |
| | CoolMOS™ 7 | | CoolMOS™ 7 |
| Gate driver ICs | EiceDRIVER™ | | |
| | 200 V and 600 V gate driver ICs | | |
| IPM | CIPOS™ Nano | | |
| Microcontrollers | XMC1100 | XMC1300/XMC1400 | |
| | XMC1000/XMC4000 | XMC4500/XMC4400 | |
| | iMOTION™ and embedded power ICs | | |
| Microcontroller and driver supply | Linear voltage and DC-DC switching regulators | | |
| CAN transceivers | IFX1050, IFX1051 | | |
| Magnetic sensors | Hall and xMR sensors | | |
| Authentication | OPTIGA™ Trust B/X, OPTIGA™ TPM | OPTIGA™ Trust B | |

A complete set of components that ensure system-cost competitiveness and high performance solution

| Infineon product offering | | Consumer robotics | Home and professional applications | Light electric vehicles |
|---|---------|---|---|--|
| Supply voltage | | 12-48 V | 10.8-56 V | 24-144 V |
| OptiMOS™ and HEXFET™/StrongIRFET™ power MOSFETs | Voltage | 25-200 V | 20-100 V | 60-300 V |
| | Package | SuperS08, PQFN 3x3, DirectFET™ S/M/L-Can, TOLL, TO-220, DPAK, D ² PAK | SuperS08, PQFN 3x3, DirectFET™ S/M/L-Can, TOLL, TO-220, TO-247, DPAK, D ² PAK, D ² PAK 7-pin | SuperS08, PQFN 3x3, TO-220, DPAK, D ² PAK, D ² PAK 7-pin, D2PAK 7-pin+, TOLL, DirectFET™ L-Can |
| HV MOSFETs CoolMOS™ 7 | Voltage | 600-950 V CoolMOS™ P7 | 600-950 V CoolMOS™ P7 | 600 V CoolMOS™ P7 600 V CoolMOS™ CFD7/CSFD |
| Gate driver ICs | | 1EDN, 2EDN, 1EDN7550, 1EDN7550B, 1EDN8550B, 2EDL811x, 2EDF7275K, 2EDF7235K, 6ED003L02-F2, 6ED003L06-F2, 6EDL04N02PR, 6EDL04N06PT, 2EDL05N06PF, Integrated gate driver ICs: IFX9201/2, NovalithIC™ BTN8982, Trilith IC BTM7752 | 1EDN/2EDN/6EDL04N02PR, 6ED003L02-F2, 2EDL05N06PF, 2ED2304S06F, 2EDF7275K, 2EDF7235K, 1EDN7550B, 1EDN8550B Integrated: IFX9201SG/ BTN8982 | 1EDN/2EDN/ 2EDL/ 6EDL04N02PR, 6ED003L02-F2, 2EDL05N06PF, 2ED2304S06F |
| IPM – CIPOS™ Nano | | IRSM836-0x4MA (x=2,4,8), IRSM808-204MH | IRSM005-800MH, IRSM005-301MH | |
| Authentication IC, security | | OPTIGA™ Trust B/X, OPTIGA™ TPM | OPTIGA™ Trust B | OPTIGA™ Trust B |
| XMC™ microcontrollers iMotion™ ePower | | XMC1100 XMC1000/XMC4000 iMOTION™: IRMCK099M ePower: TLE987X (BLDC), TLE986X (BDC) | XMC1300 XMC4400/XMC4500 iMOTION™ IRMCK099M ePower: TLE987X (BLDC) | XMC1300 XMC 4400/XMC4500 |
| Microcontroller and driver supply: linear voltage and DC-DC switching regulators | | IFX1763/IFX54441/IFX54211/IFX30081/IFX90121/IFX91041 | | |
| CAN transceivers | | IFX1050, IFX1051 | | |
| Sensors | | Hall switches (TLE 496X), angle sensor (TLI5012B, TLE5501), 3D magnetic sensor (TLV493D), current sensor (TLI4970) | Hall switches (TLE496X), angle sensor (TLI5012B), 3D magnetic sensor (TLV493D) | Hall switches (TLE496X), angle sensor (TLI5012B), 3D magnetic sensor (TLV493D) |



www.infineon.com/motorcontrol



Telecom power supply

The telecommunication industry providing data, voice, and video services is continuously growing supported by the expansion into new markets and accelerated by the spread of wireless and broadband technologies. The outstanding improvements in telecom SMPS performance made in the past 10 years have been primarily brought about by the dramatic reduction of the on-resistance achieved in high voltage MOSFETs, using the revolutionary superjunction principle. This principle was introduced by Infineon at the end of the nineties with the CoolMOS™ series.

Equally impressive improvements in reverse-recovery characteristics have been achieved for high voltage CoolSiC™ (silicon carbide) diodes. Infineon's high voltage (HV) offerings are complemented by the newly introduced HV GaN and SiC switches – the CoolGaN™ and CoolSiC™™ families, which enable highest electrical conversion efficiency at attractive system costs. In order to meet the new challenging efficiency targets, the synchronous rectification utilizing the unique performance of OptiMOS™ low voltage MOSFETs has become increasingly popular even in the typically high output voltage of telecom rectifiers.



| Functional block | Product category | Topology | Product family | Benefits |
|------------------|--|--------------------------|---|---|
| PFC | High voltage MOSFETs | CCM/interleaved PFC; TTF | 600 V/650 V CoolMOS™ C7/ G7 | <ul style="list-style-type: none"> Best FOM $R_{DS(on)} \cdot Q_G$ and $R_{DS(on)} \cdot E_{oss}$ Lowest $R_{DS(on)}$ per package Low dependency of switching losses from $R_{g,ext}$ |
| | | | 600 V CoolMOS™ P7 | <ul style="list-style-type: none"> Low turn-off losses Low Q_{oss} Low Q_G |
| | High voltage GaN | CCM totem pole | CoolGaN™ 600 V | <ul style="list-style-type: none"> Switching at high frequencies (> Si) Enables high power density |
| | SiC MOSFETs | CCM totem pole | CoolSiC™ MOSFET 650 V | <ul style="list-style-type: none"> Increase efficiency Increase power density Supports harsh and high temperature operations |
| | SiC diodes | CCM/interleaved PFC | CoolSiC™ Schottky diode 650 V G6 | <ul style="list-style-type: none"> Low FOM $V_F \cdot Q_C$ |
| | Control ICs | CCM PFC ICs | 800 V – ICE3PCS0xG | <ul style="list-style-type: none"> High PFC and low THD |
| | Gate Driver ICs for SiC and GaN | CCM/interleaved PFC TTF | EiceDRIVER™ 2EDi (2EDF7275F, 2EDF7175F) EiceDRIVER™ 1EDB* (1EDB7275F, 1EDB8275F) | <ul style="list-style-type: none"> EiceDRIVER™ 1EDB, 2EDi Functional isolation up to 1500 V_{DC} channel-to-channel isolation Strong driving for increased switching speed Low part-to-part skew and low channel-to-channel mismatch for dead-time optimization |
| | Gate Driver ICs for high voltage MOSFETs | | EiceDRIVER™ 1EDN-TDi (1EDN8550B) | <ul style="list-style-type: none"> EiceDRIVER™ 1EDN-TDi Best suited for use as low-side gate driver in combination with EiceDRIVER™ 1EDBx for half-bridge driving Recommended solution in case for high-power PFCs, to reduce the gate drive loop using single-channel drivers |
| | GaN driver ICs for high voltage SiC | CCM totem pole | EiceDRIVER™ 2EDi, 1EDB* (2EDF9275F, 1EDB9275F) | <ul style="list-style-type: none"> Functional isolation up to 1500 V_{DC} channel-to-channel isolation Single-channel (1EDB) and dual-channel (2EDF) versions available 14 V UVLO version for SiC MOSFETs driving |
| | GaN driver ICs for high voltage GaN | CCM totem pole | EiceDRIVER™ 1EDi-GaN (1EDF5673F, 1EDF5673K) | <ul style="list-style-type: none"> Functional isolation up to 1500 V_{DC} channel-to-channel isolation Robust driving against switching induced gate overshoots Reduced reverse conduction losses compared to bipolar driving |

www.infineon.com/telecom

* Coming soon

| Functional block | Product category | Topology | Product family | Benefits |
|---------------------------|--|---|--|--|
| DC-DC main stage | High voltage MOSFETs | CCM/interleaved PFC; TTF HB LLC | 600 V CoolMOS™ C7/P7/G7 | <ul style="list-style-type: none"> › Fast-switching speed for improved efficiency and thermals › Low gate charge for enhanced light load efficiency and low power consumption at no load condition › Optimized V_{GS} threshold for lower turn-off losses › Rugged body diode which prevents device failure during hard commutation |
| | | LLC | 600 V CoolMOS™ C7/G7 | <ul style="list-style-type: none"> › Low turn-off losses › Low Q_{OSS} › Low Q_G |
| | | CCM/interleaved PFC; TTF HB LLC | 600 V CoolMOS™ CFD7 | <ul style="list-style-type: none"> › Best-in-class Q_{rr} and t_{rr} level › Significantly reduced Q_G › Improved efficiency over previous CoolMOS™ fast body diode series |
| | SiC MOSFET | CMM totem pole | CoolSiC™ MOSFET 650 V | <ul style="list-style-type: none"> › Increased efficiency › Ease of use |
| | Control ICs | HB LLC ICs | ICE1HS01G-1, ICE2HS01G | › High efficiency and low EMI |
| | GaN driver ICs | LLC, ZVS phase shift full-bridge | EiceDRIVER™ 1EDi-GaN (1EDS5663H) | <ul style="list-style-type: none"> › Low driving impedance (on-resistance 0.85 Ω source, 0.35 Ω sink) › Input-output propagation delay accuracy: ± 5 ns › Functional and reinforced isolation available |
| | GaN e-mode HEMTs | LLC, ZVS phase shift full-bridge | CoolGaN™ 600 V | › Enable the highest efficiency and highest power density |
| | Gate driver ICs for high voltage MOSFETs | LLC, ZVS phase shift full-bridge | EiceDRIVER™ 2EDi (2EDS8265H 2EDS8165H) | <ul style="list-style-type: none"> › Reinforced isolation up to 1000 RMS input-to-output working voltage › Low part-to-part skew and low channel-to-channel mismatch for dead-time optimization |
| | Gate driver ICs for high voltage GaN | LLC, ZVS phase shift full-bridge | EiceDRIVER™ 1EDi (1EDS5663H) | <ul style="list-style-type: none"> › Functional isolation up to 1500 V_{DC} channel-to-channel isolation › Robust driving against switching induced gate overshoots › Reduced reverse conduction losses compared to bipolar driving |
| Synchronous rectification | Low voltage MOSFETs | Synchronous rectification MOSFET (Secondary side) | OptiMOS™ 80-150 V | <ul style="list-style-type: none"> › Industry's lowest FOM ($R_{DS(on)} \cdot Q_G$) leading to high efficiency at good price/performance › Low voltage overshoots enabling easy design-in › Industry's lowest $R_{DS(on)}$ › Highest system efficiency and power density › Outstanding quality and reliability › Reduces the need for a snubber circuit |
| | High voltage MOSFETs | Synchronous rectification MOSFET (primary side) | 600 V ColMOS™ S7 | <ul style="list-style-type: none"> › Eliminated or reduced heat sink in solid state design › Increased energy efficiency |
| | Gate driver ICs for low and high voltage MOSFETs | Standard synchronous rectification | EiceDRIVER™ 2EDi EiceDRIVER™ 2EDL8 (2EDL811x) | EiceDRIVER™ 2EDi <ul style="list-style-type: none"> › Functional isolation up to 650 V_{DC} channel-to-channel isolation › Compact solution available in IGA-13 5x5 mm package EiceDRIVER™ 2EDL8 <ul style="list-style-type: none"> › Level-shift half-bridge gate driver up to 120 V isolation |
| | | Full-bridge synchronous rectification | EiceDRIVER™ 1EDN (1EDN751x) EiceDRIVER™ 2EDN | <ul style="list-style-type: none"> › Low-side gate drivers › 4 V and 8 V UVLO output supply UVLO versions for logic level and normal level OptiMOS™ driving |
| Auxiliary power supply | Control ICs | 5 th generation QR/FF flyback CoolSET™ | QR 800 V - ICE5QRxx80Ax FF 800 V - ICE5xRxx80AG | <ul style="list-style-type: none"> › Quasi-resonant switching operation for high efficiency and low EMI signature › Fixed frequency switching operation for ease of design – 100 KHz and 125 KHz › Fast and robust start-up with cascode configuration › Robust protection with adjustable line input over-voltage protection, V_{CC} and CS pin short-to-ground protection › Frequency reduction for mid- and light-load condition to reduce switching losses and increase efficiency › High power delivery of up to 42 W with 800 V CoolSET™ in heatsink-free SMD package |
| Housekeeping | Microcontrollers | - | XMC1xxx | <ul style="list-style-type: none"> › Flexibility, HR PWM, digital communication › ARM® based standard MCU family and wide family |
| Conversion | Microcontrollers | - | XMC4xxx | <ul style="list-style-type: none"> › Flexibility, HR PWM, digital communication › ARM® based standard MCU family and wide family |
| Or-ing | Low voltage MOSFETs | Or-ing MOSFET | OptiMOS™ 60-200 V | <ul style="list-style-type: none"> › Industry's lowest FOM ($R_{DS(on)} \cdot Q_G$) leading to high efficiency at good price/performance › Low voltage overshoots enabling easy design-in |
| Battery protection | Low voltage MOSFETs | MOSFET | OptiMOS™ 60-150 V | |
| Isolated DC-DC | Low voltage MOSFETs | Primary side PWM MOSFET | OptiMOS™ 60-200 V | <ul style="list-style-type: none"> › Industry's lowest $R_{DS(on)}$ › Highest system efficiency and power density › Outstanding quality and reliability › Reduces the need for a snubber circuit |
| | | | StrongIRFET™ 60-200 V | |
| | | | Small signal MOSFETs 60-200 V | |
| | Synchronous rectification MOSFET | Synchronous rectification MOSFET | OptiMOS™ 40-100 V | |
| | | | StrongIRFET™ 40-100 V | |
| | | | OptiMOS™ 25-30 V | |
| | | Or-ing MOSFET | StrongIRFET™ 25-30 V | |




Server power supply

Efficiency optimization is the key requirement across the entire load range for server and data center design. The requirement for higher power, increased power density and cost effective design in server is the driving trend in the market. Infineon recommends the 600 V CoolMOS™ C7 family with the lowest FOM $R_{DS(on)} * Q_G$ and $R_{DS(on)} * E_{oss}$ for the PFC stage. This results in the lowest switching losses, enabling fast switching in high-end server SMPS, thus optimizing the efficiency starting from very light load operation. The very compact SMD packages such as ThinPAK, offer benefits in space and power density, and are used with Infineon's new industry standard non-isolated driver family 2EDN752x. Complementary to 600 V CoolMOS™ C7 in high efficiency PFC are the CoolSiC™ Schottky diodes G6 and G5. The 600 V CoolMOS™ P7 family offers a good compromise between price and performance. In applications with a low output voltage and high output current, further efficiency improvement is enabled by the continuous reduction of on-resistance by Infineon's low voltage OptiMOS™ MOSFET series used in the synchronous rectification stage. Infineon's low voltage families are complemented by StrongIRFET™ which is optimized for lower switching frequencies and highest system robustness.

The new CoolMOS™ S7 is the optimal price/performance fit for sockets switching at low frequency and for mechanical relay replacement. If it is used in the rectification bridges, in parallel or in place of diodes, it can boost efficiency with little design effort. It is used to replace inrush mechanical relays, the CoolMOS™ S7 can free up space and offer power density opportunities.

The new GaN and SiC based switches enable system with efficiency close to the theoretical limit and very high density. This is a step forward to fulfill the increasing demand for higher energy efficiency that large hyperscale datacenters are bringing in the industry.

Block diagram



| Functional block | Product category | Topology | Product family | Benefits |
|------------------|----------------------|--------------------------|--|--|
| PFC | High voltage MOSFETs | CCM/interleaved PFC; TTF | 600 V/650 V CoolMOS™ C7 600 V/650 V CoolMOS™ G7 | <ul style="list-style-type: none"> Best FOM $R_{DS(on)} * Q_G$ and $R_{DS(on)} * E_{oss}$ Lowest $R_{DS(on)}$ per package Low dependency of switching losses from $R_{g,ext}$ |
| | SiC MOSFETs | CMM totem pole | CoolSiC™ MOSFET 650 V | <ul style="list-style-type: none"> Increased efficiency Increased power density Supports harsh and high temperature operations |
| | SiC diodes | CCM/interleaved PFC | CoolSiC™ Schottky diode 650 V G6 and G5 | <ul style="list-style-type: none"> Low FOM $V_f * Q_G$ |
| | Control ICs | CCM PFC IC | ICE3PCS0xG | <ul style="list-style-type: none"> Ease of use |
| | IGBTs | CCM/interleaved PFC | TRENCHSTOP™ IGBT 650 V H5 TRENCHSTOP™ IGBT 650 V F5 | <ul style="list-style-type: none"> High PFC and low THD High efficiency in low inductance designs |

| Functional block | Product category | Topology | Product family | Benefits |
|------------------------|--|---|---|---|
| PFC | Gate driver ICs for high voltage MOSFETs | CCM/interleaved PFC TTF | EiceDRIVER™ 2EDi : (2EDF7275F 2EDF7175F) EiceDRIVER™ 1EDB*: (1EDB7275F 1EDB8275F) EiceDRIVER™ 1EDN-TDi: (1EDN8550B) | EiceDRIVER™ 1EDB*, 2EDi: <ul style="list-style-type: none"> Functional isolation up to 1500 V_{DC} channel-to-channel isolation Strong driving for increased switching speed Low part-to-part skew and low channel-to-channel mismatch for dead-time optimization EiceDRIVER™ 1EDN-TDi: <ul style="list-style-type: none"> Best used as low-side gate driver in combination with EiceDRIVER™ 1EDBx for half-bridge driving Best for high-power PFCs to reduce the gate drive loop using single-channel drivers |
| | Gate driver ICs for SiC MOSFETs | CMM totem pole | EiceDRIVER™ 2EDi, 1EDB*: (2EDF9275F, 1EDB9275F) | <ul style="list-style-type: none"> Up to 1500 V_{DC} channel-to-channel isolation 14 V UVLO version for SiC MOSFETs driving |
| | Gate driver ICs for high voltage GaN | CMM totem pole | EiceDRIVER™ 1EDi-GaN (1EDF5673F 1EDF5673K) | <ul style="list-style-type: none"> Functional isolation up to 1500 V_{DC} channel-to-channel isolation Robust driving against switching induced gate overshoots Reduced reverse conduction losses compared to bipolar driving |
| Main stage | High voltage MOSFETs | ITTF | 600 V CoolMOS™ C7/P7 | <ul style="list-style-type: none"> Fast switching speed for improved efficiency and thermals, low gate charge for enhanced light load efficiency and low power consumption at no load condition Optimized V_{GS} threshold for lower turn-off losses Rugged body diode which prevents device failure during hard commutation |
| | | LLC, half-bridge below 1 kW | 600 V CoolMOS™ P7/CFD7 | <ul style="list-style-type: none"> Low turn-off losses Low Q_{oss} Low Q_G |
| | | LLC, phase shift full-bridge below 1 kW | 600 V CoolMOS™ CFD7 650 V CoolMOS™ CFD2 | <ul style="list-style-type: none"> Fast and rugged body diode Optimized low Q_G and soft commutation behavior to reach highest efficiency Highest reliability for 650 V V_{DS} |
| | | ZVS PS FB; LLC, TTF | TRENCHSTOP™ IGBT 650 V F5 | <ul style="list-style-type: none"> Improved ruggedness and high efficiency in low inductance designs |
| | GaN e-mode HEMTs | LLC, ZVS phase shift full-bridge | CoolGaN™ 600 V | <ul style="list-style-type: none"> Enable the highest efficiency and highest power density |
| | Control ICs | HB LLC IC | ICE1HS01G-1 ICE2HS01G | <ul style="list-style-type: none"> High efficiency and low EMI |
| | Gate driver ICs for high voltage MOSFETs | LLC, ZVS phase shift full-bridge | EiceDRIVER™ 2EDi (2EDS8265H, 2EDS8165H) | <ul style="list-style-type: none"> Reinforced isolation up to 1000 RMS input-to-output working voltage Low part-to-part skew and low channel-to-channel mismatch for dead-time optimization |
| | Gate driver ICs for high voltage GaN | LLC, ZVS phase shift full-bridge | EiceDRIVER™ 1EDi-GaN (1EDS5663H) | <ul style="list-style-type: none"> Functional isolation up to 1500 V_{DC} channel-to-channel isolation Robust driving against switching induced gate overshoots Reduced reverse conduction losses compared to bipolar driving |
| | Gate driver ICs for high voltage SiC | LLC, ZVS phase shift full-bridge | EiceDRIVER™ 2EDi (2EDS9265H) | <ul style="list-style-type: none"> Reinforced isolation up to 1000 RMS input-to-output working voltage 14 V UVLO version for SiC MOSFETs driving |
| | Synchronous rectification | HB LLC and centertap | 40 V OptiMOS™ | <ul style="list-style-type: none"> High efficiency over whole load range, layout tolerance |
| | | | 40 V StrongIRFET™ | <ul style="list-style-type: none"> High robustness and ruggedness |
| | | ITTF | 60 V OptiMOS™ | <ul style="list-style-type: none"> High efficiency, low thermals, low V_{DS} overshoot |
| | | | 60 V StrongIRFET™ | <ul style="list-style-type: none"> High robustness and ruggedness |
| | | ZVS PS FB and center-tap | 80 V OptiMOS™ | <ul style="list-style-type: none"> High efficiency over whole load range, low V_{DS} overshoot and oscillations |
| | | | 80 V StrongIRFET™ | <ul style="list-style-type: none"> High robustness and ruggedness |
| | High voltage MOSFETs | - | 600 V CoolMOS™ S7 | <ul style="list-style-type: none"> Eliminated or reduced heat sink in solid state design Increased energy efficiency |
| Auxiliary power supply | Gate driver ICs for low voltage MOSFETs | Standard synchronous rectification | EiceDRIVER™ 2EDF7275K 2EDS7235K 2EDL811x | EiceDRIVER™ 2EDF72x5K <ul style="list-style-type: none"> Functional isolation up to 650 V_{DC} channel-to-channel isolation Compact solution available in LGA-13 5x5 mm package EiceDRIVER™ 2EDL811x <ul style="list-style-type: none"> Level-shift half-bridge gate driver up to 120 V isolation |
| | | Full-bridge synchronous rectification | EiceDRIVER™ 1EDN751x 2EDNx | <ul style="list-style-type: none"> Low side gate drivers 4 V and 8 V UVLO output supply UVLO versions for logic level and normal level OptiMOS™ driving |
| Auxiliary power supply | Control ICs | QR/FF flyback CoolSET™ | 800 V – ICE2QRxx80(Z)(G) ICE3xRxx80J(Z)(G) 700 V ICE5QRxx70A(Z)(G) 800 V ICE5QRxx80A(Z)(G) | <ul style="list-style-type: none"> Low standby power, high efficiency and robustness An integrated 700 V/800 V superjunction power MOSFET with avalanche capability standby power at Burst mode entry/exit to optimiz different low load conditions |
| Housekeeping | Microcontrollers | - | XMC1xxx | <ul style="list-style-type: none"> Flexibility, HR PWM, digital communication ARM® based standard MCU family and wide family |
| Conversion | Microcontrollers | - | XMC4xxx | <ul style="list-style-type: none"> Flexibility, HR PWM and digital communication |



Industrial SMPS

Industrial SMPS powers a wide range of devices from industrial automation robots to medical equipment and vending machines. With the expansion of the Internet of things and the adoption of Industry 4.0, the demand for industrial SMPS is on the rise.

The requirement to fit various usages, often in harsh environments, with many different mission profiles and together with the intrinsic availability needs of industrial and medical devices, makes product reliability one of the main concerns for industrial SMPS makers. There is also continuous trend towards higher power density that requires good thermal management at system level.

Infineon's CoolMOS™ 7 family and CoolSiC™ Schottky diode G6 boast superior quality, unparalleled energy efficiency and optimal price performance, are tailored to meet the high requirements of this market. The large product portfolio enables customers to meet all industrial SMPS power classes and fit well into the most used topologies. Infineon CoolGaN™ HV HEMTs and CoolSiC™ MOSFETs 650 V pace the next step towards max efficiency and max power density.

| Power Class | Topology PFC | Topology main stage | Product family | Benefits |
|--|--|----------------------------|---|--|
| <75 W | – | Flyback (quasi- resonant) | 700 V CoolMOS™ P7 800 V CoolMOS™ P7 | <ul style="list-style-type: none"> › Robustness › Price performance |
| 75-300 W | DCM PFC standard | Flyback (quasi- resonant) | 700 V CoolMOS™ P7 800 V CoolMOS™ P7 | <ul style="list-style-type: none"> › Energy efficiency › Outstanding portfolio granularity › Ease of use › Best EMI behavior |
| | | LLC | 600 V CoolMOS™ P7 | |
| 300-500 W | CCM PFC standard | Double forward | 650 V/600 V CoolMOS™ C7 650 V/600 V CoolMOS™ CFD7 600 V CoolMOS™ P7 CoolSiC™ Schottky diode 650 V | <ul style="list-style-type: none"> › Robustness › Ruggedness › Fast body diode with CFD7 › Lowest $R_{DS(on)}$ per package with C7 › Best efficiency with C7 › Best $Q_g \times V_f$ FOM with CoolSiC™ 650 V diode › Largest high-power portfolio › Enables higher efficiency › Highest efficiency and power density with CoolSiC™ and CoolGaN™ |
| | Active bridge rectification | | 600 V CoolMOS™ S7 | |
| >500 W | CCM PFC standard interleaved dual boost CCM totem pole | Half-bridge Full-bridge | 650 V/600 V CoolMOS™ C7 and G7 650 V/600 V CoolMOS™ CFD7 600 V CoolMOS™ P7 CoolSiC™ diode 650 V CoolSiC™ MOSFET 650 V | <ul style="list-style-type: none"> › Enables higher efficiency |
| | Active bridge rectification | | 600 V CoolMOS™ S7 | |
| Gate driver ICs for high voltage MOSFETs and SiC | CCM, DCM PFC Standard, interleaved, dual-boost | – | EiceDRIVER™ 2EDi: (2EDSxx65H, 2EDFxx75F) EiceDRIVER™ 1EDBx275F* | <ul style="list-style-type: none"> › Functional and reinforced isolation available › Low part-to-part skew and low channel-to-channel mismatch for dead-time optimization › 4 V, 8 V, 14 V output supply UVLO variants for HV MOSFETs and SiC |




Solar

Infineon provides a comprehensive portfolio to deliver the best efficiency, power density and reliability for solar applications. Infineon's leading edge technology like CoolMOS™ SJ MOSFET, HighSpeed 3 and TRENCHSTOP™ 5, CoolSiC™ Schottky diodes, CoolSiC™ MOSFETs, coreless transformer driver etc., combined with rich experience and the highest quality, ensured our number 1 position in solar applications. The newest add ARM® Cortex®-M4 based MCU enables easy and high efficiency design.

| | Optimizer 250-750 W | Single/dual/quadr microinverter 250-1200 W | Single phase multilevel inverter <10 kW | Single phase string inverter standard <10 kW |
|------------------------|--|--|--|--|
| MOSFETs | OptiMOS™ SuperSO8/DirectFET™ 75-150 V | OptiMOS™ SuperSO8 60-200 V CoolMOS™ D²PAK/TOLL /600-800 V | OptiMOS™ SuperSO8/D²PAK 150 V CoolMOS™ TO-247/D²PAK 600 V/650 V | CoolMOS™ TO-247-3/TO-247-4 600/650 V CoolSiC™ MOSFET TO-247-3/TO-247-4 650/1200 V |
| SiC diodes | | CoolSiC™ Schottky diodes DPAK 1200 V | CoolSiC™ Schottky diodes TO-247 600 V/1200 V D²PAK 650 V | CoolSiC™ Schottky diodes TO-220/TO-247 600 V/1200 V D²PAK 650 V |
| IGBTs | | | | TRENCHSTOP™ 5/TRENCHSTOP™ IGBT6 TO-247-3/TO-247-4 600/650/1200 V Easy 1B/2B |
| Gate driver ICs | | EiceDRIVER™ 2EDi Family | EiceDRIVER™ 2EDi product family (2EDSxx65H, 2EDFxx75F), EiceDRIVER™ 1EDBx275F* | |
| Schottky diode | | | | BA165 Schottky diode |
| Auxiliary power supply | | | | CoolSET™ 800 V |
| Microcontrollers | XMC1xxx ARM® Cortex®-M0 XMC45xx ARM® Cortex®-M4 | XMC1xxx ARM® Cortex®-M0 XMC45xx ARM® Cortex®-M4 | XMC1xxx ARM® Cortex®-M0 XMC45xx ARM® Cortex®-M4 | XMC1xxx ARM® Cortex®-M0 XMC45xx ARM® Cortex®-M4 |

Infineon leading products for complete solar system




www.infineon.com/solar

* Coming soon




Microinverter




| Functional block | Product technology | Voltage class [V _{DS} max] | Package | Part number | R _{DS(on)} |
|--------------------|--|-------------------------------------|--------------------|---------------|---------------------|
| MPPT – boost stage | OptiMOS™ | 60 V | SuperSO8 | BSC028N06NS | 2.8 mΩ |
| | | 80 V | | BSC026N08NS5 | 2.6 mΩ |
| | | 120 V | | BSC190N12NS3 | 19.0 mΩ |
| | | 150 V | | BSC093N15NS5 | 9.3 mΩ |
| | | | | BSC160N15NS5 | 16.0 mΩ |
| Inverter stage | CoolMOS™ | 600 V | TO-Leadless | IPT60R102G7 | 102.0 mΩ |
| | | | D ² PAK | IPB60R145CDF7 | 145.0 mΩ |
| | | | TO247 | IPW60R145CFD7 | 145.0 mΩ |
| | | 650 V | D ² PAK | IPB65R150CFD | 150.0 mΩ |
| | | 650 V | TO247 | IPW65R150CFD | 150.0 mΩ |
| | CoolSiC™ Schottky diode | 1200 V | DPAK | IDM02G120C5 | 2.0 A |
| | | | | IDM05G120C5 | 5.0 A |
| | | | | IDM08G120C5 | 8.0 A |
| Gate driver ICs | EiceDRIVER™ 2EDi Family (2EDF7175F and 2EDF7275F) , EiceDRIVER™ 1ED Compact, | | | | |
| Microcontroller | XMC1000, XMC4000 | | | | |

Single-phase string inverter

H4 topology



H6 topology



| Inverter | Functional block | Product category | Product technology | Package | Part number |
|--------------|--------------------|-----------------------------|-----------------------|-------------|----------------------------|
| Single-phase | MPPT – boost stage | Si MOSFET | 600 V CoolMOST™ P7 | TO247-3 | IPW60R037P7 |
| | | | | TO247-4 | IPZA60R037P7 |
| | | SIC MOSFET | CoolSiC™ MOSFET 650 V | TO247-4 | IMZA65R026M1H |
| | | | | TO247-4 | IMZA65R046M1H |
| | | IGBT | TRENCHSTOP™ 5 650 V | TO247-3 | IKW40N65H5 |
| | Inverter | Diode | CoolSiC™ diode 650 V | TO247 | IDW20G65C5 |
| | | Si MOSFET | 650 V CoolMOST™ C7 | TO247-3 | IPW65R65C7 |
| | | | 600 V CoolMOST™ S7 | TO-Leadless | IPT60R022S7 IPT60R040S7 |
| | | | 600 V CoolMOST™ CFD7 | TO247-3 | IPW60R018CFD7 |
| | | SIC MOSFET | CoolSiC™ MOSFET 650 V | TO247-3 | IPW60R031CFD7 |
| | | | | TO247-4 | IMZA65R026M1H |
| | | IGBT | 600 V HighSpeed 3 | TO247-4 | IMZA65R048M1H |
| | | | | TO247-3 | IKW40N60H3 |
| | | TRENCHSTOP™ 5 IGBT 650 V H5 | TO247-3 | IKW40N65H5 | |

Gate driver ICs for string inverter

| Power device | Driving method | Voltage class | Part number |
|-----------------------|----------------------------------|---------------|---|
| IGBT/SiC MOSFET | Single channel | 1200 V | EiceDRIVER™ 1ED Compact EiceDRIVER™ Enhanced 1ED020112-F2/ 2ED020112-F2 |
| IGBT/SiC MOSFET | Half-bridge & high- and low-side | 1200 V | EiceDRIVER™ Enhanced 2ED020112-F2/FI |
| HV MOSFETs/SiC MOSFET | Half-bridge & high- and low-side | 1200 V | EiceDRIVER™ 2EDi product family (2EDSxx65H, 2EDFxx75F), EiceDRIVER™ 1EDBx275F* |

CoolSET™ for string inverter

| Voltage class | Part number |
|---------------|--------------|
| 800 V | ICE3AR2280JZ |
| 650 V | ICE3BR1765JZ |

Microcontrollers for string inverter

| Topology | Package | Voltage class | Technology |
|------------------------|--------------------------|---------------|-----------------------------|
| Microcontroller | All | All | XMC1000 |
| Microcontroller supply | Linear voltage regulator | Up to 20 V | IFX1763, IFX54441, IFX54211 |
| Microcontroller | All | All | XMC4000 |

For Infineon's extensive module portfolio for string and central inverters, visit:

www.infineon.com/solar

www.infineon.com/igbtmodules1200v

* Coming soon



TV power supply

A growing number of TV manufacturers are using external adapters to deliver DC power to a TV, in order to achieve low thermal dissipation and a slim design. Infineon introduced two products based on digital power technology, designed to meet challenging efficiency and standby power requirements for the IoT-enabled TVs (both embedded PSU and adapter). Thanks to digital power, our customers can reduce the number of TV power supplies by adapting the digital IC parameters to different TVs and screen models by flexible parameter setting. Infineon recently introduced the digital based flyback controllers, ideal to implement in low power adapters for TVs and monitors. With the digital soft switching, the adapter power density can be improved significantly.

The new 600 V CoolMOS™ P7 has been developed to cover a broad spectrum of different applications where excellent performance and perfect ease of use are required. The rugged body diode is suitable for PFC, boost, and two transistor forward, as well as in resonant topologies such as LLC. For higher on-state resistance ($R_{DS(on)}$) classes, the new feature of an integrated ESD diode helps improve manufacturing quality, and at the same time, enables high efficiency in various topologies. Infineon developed specifically for TV power supplies a family of packages, characterized by short lead, SOT-223 mold stopper and wide creepage distance, which enables our customers to attain cost effectiveness and reliable manufacturing.

600 V CoolMOS™ P7 offers:

- › Competitive price positioning
- › Significant efficiency gains up to 1.8% at high but also at low line
- › Lower superjunction device temperature enabling reduced thermals on application level




700 V CoolMOS™ P7 offers:

- › Best price/performance ratio
- › Possibility to switch to higher $R_{DS(on)}$ classes due to temperature dependency of the $R_{DS(on)}$ and the lower switching losses even with higher integrated gate resistor
- › Increased efficiency compared to competitor device



| Functional block | Product category | Topology | Product family | Benefits |
|------------------------------|----------------------|------------------------|--|--|
| Main stage/PFC combo non-AUX | High voltage MOSFETs | DCM PFC, HB LLC | 600 V/700 V CoolMOS™ P7 | <ul style="list-style-type: none"> › Fast-switching speed for improved efficiency › Low gate charge for enhanced light load efficiency and low power consumption at no load condition › Optimized V_{GS} threshold for lower turn-off losses › Rugged body diode for HB LLC application |
| | | | 500 V/600 V CoolMOS™ CE | <ul style="list-style-type: none"> › Easy control of switching behavior even in non-optimized layout › Lower switching losses in comparison with its predecessor › Rugged body diode which prevents device failure during hard commutation |
| | Control ICs | IDP2308 | PFC-LLC non-AUX digital IC for TV embedded PSU | <ul style="list-style-type: none"> › Low BOM count/system cost due to high integration › Low standby power › High system reliability › Shorter development cycles and higher design and production flexibility |
| | | IDP2303A | PFC-LLC non-AUX digital IC for TV adapter | <ul style="list-style-type: none"> › Low BOM count/system cost due to high integration › Low standby power › Small form factor designs › High system reliability |
| PFC | Boost diodes | DCM PFC | 650 V Rapid diode | › Low conduction losses |
| | | CCM PFC | CoolSiC™ Schottky diode 650 V G5 | › Very low reverse recovery losses |
| | Control ICs | CCM PFC ICs | ICE3PCS0xG | › High PFC and low THD |
| Main stage | Control ICs | HB LLC ICs | ICE1HS01G-1/ICE2HS01G | › High efficiency and low EMI |
| Auxiliary power supply | Control ICs | QR/FF flyback CoolSET™ | 700 V/800 V – ICE5QRxx70/80A(Z)(G) | › Low standby power, high efficiency and robustness |
| Flyback | Control ICs | Digital ZVS flyback | IDP2105 | <ul style="list-style-type: none"> › Forced resonant ZVS control reduces the switching loss › Multilevel protection enables the robust design › Flexible firmware provides more differentiation for OEMs |
| | High voltage MOSFETs | Flyback | 700 V CoolMOS™ P7 | <ul style="list-style-type: none"> › Optimized for flyback topologies › Best price competitive CoolMOS™ SJ MOSFET family › Lower switching losses versus standard MOSFET › Controlled dV/dt and dI/dt for better EMI |

www.infineon.com/tvpower



Adapter and charger power supply

Manufacturers of slimmer and lighter adapters require cost effective MOSFETs in small packages that feature good electromagnetic interference (EMI) and excellent thermal performance, enabling high efficiency and low standby power. Infineon offers a wide range of products specifically designed for adapters including high voltage SJ MOSFETs and control ICs for PFC and PWM stages, as well as low voltage MOSFETs for synchronous rectification. Especially versatile is the CoolMOS™ P7 family which combines high efficiency and optimized cost with ease of use. Packages – characterized by having a short lead, IPAK Short Lead with ISO-Standoff and wide creepage – enable cost-effective and reliable manufacturing specifically for adapters. High power density at low manufacturing cost can be achieved using Infineon's SOT-223 cost-effective package which enables SMT manufacturing, while maintaining very good thermal performances. For synchronous rectification, Infineon's OptiMOS™ series offer extremely low on-state resistance and low capacitances. New control ICs support topologies such as quasi-resonant flyback and forced frequency resonant flyback (zero voltage switching) operation, ideal to implement high power density adapters and well supporting USB-PD requirements.

600 V CoolMOS™ P7

- › Most balanced technology of all CoolMOS™ families
- › Integrated Zener diode
- › Highest efficiency
- › Excellent ease of use and commutation ruggedness
- › Competitive price
- › Outstanding portfolio granularity



700 V/800 V/950 V CoolMOS™ P7

- › Price competitiveness compared to similar competitor technologies
- › Supports increased switching frequency to reduce magnetics
- › Integrated Zener diode
- › Best fit for target applications in terms of
 - Thermals and efficiency
 - Ease of use level
 - Fulfilling common EMI criteria



600 V CoolGa™

- › Outstanding performance
- › Highest power density > 20 W/in³




600 V CoolMOS™ PFD7

- › Minimizing switching losses
- › BOM cost reduction and easy manufacturing
- › Robustness and reliability
 - Integrated Zener Diode
 - Up to 2 kV ESD protection



| Functional block | Product category | Topology | Product family | Benefits |
|---------------------------|---|---------------------------|-------------------------------------|---|
| Flyback converter | High voltage MOSFETs and HEMTs | Flyback (ACF, FFR, etc.) | 600 V/700 V/800 V/950 V CoolMOS™ P7 | <ul style="list-style-type: none"> › Fast-switching speed for improved efficiency and thermals › Reduced gate charge for enhanced light load efficiency › Optimized gate-to-source voltage (V_{GS}) threshold for lower turn-off losses |
| | | | CoolGa™ 600 V e-mode HEMTs | <ul style="list-style-type: none"> › Highest efficiency › Highest power density |
| | | | 600 V CoolMOS™ PFD7 | <ul style="list-style-type: none"> › Optimized switching › Fast body diode › Integrated Zener diode |
| | Low voltage MOSFETs | Synchronous rectification | OptiMOS™ PD | <ul style="list-style-type: none"> › Low conduction losses and reduced overshoot › Logic level can support low voltage gate drive to achieve high efficiency |
| PFC | High voltage MOSFETs, HEMTs, and diodes | QR flyback IC | ICE2QS03G, ICE5QSAG | › High efficiency and low standby power |
| | | FFR flyback IC | XDPS21071 | › High power density and digital control |
| | Boost diode | DCM PFC | 600/700/800/950 V CoolMOS™ P7 | <ul style="list-style-type: none"> › Fast-switching speed for improved efficiency › Reduced gate charge for enhanced light load efficiency › Optimized gate-to-source voltage (V_{GS}) threshold for lower turn-off losses |
| | | DCM/CCM PFC | CoolGa™ 600 V e-mode HEMTs | <ul style="list-style-type: none"> › Highest efficiency contribution via less parasitic parameter › Space saving with SMD smaller package |
| Main stage | High voltage MOSFETs and HEMTs | HB LLC | 650 V Rapid 1 diodes | › Low conduction losses |
| | | | TDA4863G, IRS2505LTRPBF | <ul style="list-style-type: none"> › Simple external circuitry › High power factor and low THD |
| | Low voltage MOSFETs | Synchronous rectification | 600 V CoolMOS™ P7 | <ul style="list-style-type: none"> › Fast-switching speed for improved efficiency and thermals › Reduced gate charge for enhanced light load efficiency › Optimized gate-to-source voltage (V_{GS}) threshold for lower turn-off losses |
| | | | 600 V CoolMOS™ PFD7S | <ul style="list-style-type: none"> › Highest efficiency › Highest power density |
| Synchronous rectification | Low voltage MOSFETs | Synchronous rectification | OptiMOS™ PD | <ul style="list-style-type: none"> › Low conduction losses, reduced overshoot › Logic level switching |
| | Control ICs | Synchronous rectification | IR1161LTRPBF | <ul style="list-style-type: none"> › High efficiency › Simple external circuitry |

www.infineon.com/adapter



LED lighting

Our focus at Infineon lies on supplying tailored products for LED drivers, LED tubes, LED controls and LED strips. Our portfolio of high-quality, energy-efficient products and solutions comprises LED driver ICs, MOSFETs and microcontrollers suited for LED drivers as well as sensors and ICs for secure communication. Lighting applications create high demands on power supply designs in terms of efficiency, thermal management, surge protection, electromagnetic interference and cost. Our CoolMOS™ products offer a significant reduction of conduction, switching and driving losses and enable high power density and efficiency for superior power conversion systems. In particular, the latest state-of-the-art generation of high-voltage power MOSFETs contributes to making LED drivers more efficient, more compact, lighter and cooler than ever before.

800 V/950 V CoolMOS™ P7



- › Outstanding performance in terms of efficiency, thermals and ease of use
- › Enabling higher power density designs, BOM savings, and lower assembly cost
- › Easy to drive and to design in
- › Better production yield by reducing ESD related failures

CoolMOS™ P7 in SOT-223



- › Combining best-fit performant and ease of use superjunction technology with a cost-effective package solution
- › SOT-223 as drop-in replacement for DPAK
- › Enabling space savings and improved form factors in designs with low power dissipation

600 V CoolMOS™ P7



- › Suitable for hard/soft switching due to outstanding commutation ruggedness
- › Significant reduction of switching and conduction losses
- › Optimized balance between efficiency and ease of use

LED drivers

| Functional block | Product type | IC product family | MOSFET technology | Voltage class |
|---------------------------|--|--|----------------------------|---------------------------------|
| PFC stage | PFC | IRS2505 | CoolMOS™ P7 | 600/700/800/950 V ¹⁾ |
| Main stage | PFC + LCC (constant current) PFC + LLC (constant current) | ICL5102 ²⁾ | CoolMOS™ P7 (up to 600 mΩ) | 600 V |
| | | | CoolMOS™ CE (above 600 mΩ) | 600 V |
| | | ICL5102HV | CoolMOS™ P7 | 950 V |
| | | | CoolMOS™ C3 | 900 V |
| | PFC + flyback (dual stage) | XDPL8220 ³⁾ /XDPL8221 ²⁾ | CoolMOS™ P7 | 700/800/950 V |
| | PFC/flyback (single-stage constant current) | XDPL8105/XDPL8210 | CoolMOS™ P7 | 800/950 V |
| | PFC/flyback (single-stage constant voltage) | XDPL8218 | CoolMOS™ P7 | 800/950 V |
| Buck/linear solutions | Main buck | IRS2982 | CoolMOS™ P7 | 600/700 V |
| | Secondary buck (single-channel) | ILD6150/ILD8150 | Integrated | 60/80 V |
| | Secondary buck (multichannel) | XMC1300/XMC1400 ¹⁾ | OptiMOS™ | 100/150/200/250/300 V |
| | Secondary linear | BCR601 | OptiMOS™ | 75/100 V |
| Synchronous rectification | Synchronous rectification controller | IR1161/IR11688 | OptiMOS™ | 100/150/200 V |
| Dimming | 0-10 V dimming interface IC | CDM10V | - | - |
| | | CDM10VD | - | - |
| Hardware based security | OPTIGA™ | OPTIGA™ Trust | - | - |
| MCU | XMC™ microcontroller | XMC1100 | - | - |
| Sensors | XENSIV™ radar sensor IC | BGT24LTR11 | - | - |

1) 700 V, 800 V and 950 V CoolMOS™ P7 are optimized for PFC and flyback topologies. 600 V CoolMOS™ P7 is suitable for hard as well as soft switching topologies (flyback, PFC and LLC)

2) PFC and resonant combo controllers

3) PFC and flyback combo controllers

Linear/switch mode LED driver ICs

| Functional block | Product type | IC product family | MOSFET technology | Voltage class |
|---------------------------|--------------|-------------------|--|-----------------------|
| Linear LED driver IC | Linear | BCR400 series | Integrated (extra transistor for BCR450) | - |
| | | BCR602 | External N-channel MOSFET | 75/100 V |
| Switch mode LED driver IC | Buck | ILD6000 series | Integrated | - |
| | | XMC1300/XMC1400* | OptiMOS™ | 100/150/200/250/300 V |

www.infineon.com/lighting

* including communication



Audio power supply

For consumer audio SMPS solutions Infineon's 600 V, 700 V and 800 V CoolMOS™ P7 SJ MOSFETs are the ideal switch allowing for lower switching noise, voltage ripple, and a proper switching frequency to not produce additional audio noise. Higher efficiency and less thermals allow for smaller form factors and thus for lower cost and easier integration into speakers and sound systems.

Class D audio amplifiers offer 0 percent distortion and 100 percent efficiency. What decreases the actual number depends on how close the PWM is to an ideal waveform shape and how much power loss is in the device. The zero reverse recovery charge in the body diode and very small, linear input and output capacitances from Infineon CoolGaN™ 400 V technology allow switching waveforms to be close to an ideal switch device and thus is perfectly suitable for professional audio solutions.

| 600 V/700 V/800 V CoolMOS™ P7 | CoolGaN™ benefits in Class D amplifier |
|---|--|
| <ul style="list-style-type: none"> › Allows to reduce the number of total components while maintaining performance › Increased efficiency › Allows smaller form factors › Reduced noise | <ul style="list-style-type: none"> › Efficient: best FOM of 400 V power devices › Very low noise: zero reverse recovery charge enables quiet hard switching › Small and linear C_{oss} narrows dead time window for better THD › Easy-to-use: compatible with class D audio control ICs |

Audio power supply portfolio

| Functional block | Product category | Product family | Benefits |
|---------------------------|-----------------------------------|---|---|
| Main power supply | High voltage MOSFET | 600/700/800 V CoolMOS™ P7 | › Enables increased system level efficiency and compactness |
| Auxiliary power supply | Control IC with integrated MOSFET | PWM FF CoolSET™ 5 th generation: › ICE5xRxxxxAG › ICE5xRxxxxBZS | › Adjustable line input OVP (only SMD) › Adjustable OLP › Adjustable burst mode entry/exit level › Ability to disable burst mode operation › CCM/DCM › 100kHz and 125kHz |
| | Control IC | ICE5ASAG ICE5GSAG | |
| Synchronous rectification | Low voltage MOSFET | OptiMOS™ 5 80 V › BSC0xxN08NS5 › BSZxxxN08NS5 › IPP020N08N5 › IPB017N08N5 | › Fine-tuned for synchronous rectification applications reaching higher efficiency than the best competitor devices in the market over the whole load range |
| | | OptiMOS™ 5 60 V › BSC070xLS › BSZ070xLS | |
| | | OptiMOS™ 80 V › BSZ0602LS | |
| | | OptiMOS™ 5 100 V › IPA050N10NM5S | |

CoolGaN™ 400 V e-mode HEMT product offering for class D amplifiers

| | CoolGaN 400 V e-mode HEMTs | Recommended discrete audio amplifier driver IC |
|-------------------|----------------------------|--|
| Package | HSOF-8-3 (TO-leadless) | IRS209575PBF |
| P_{max} | Up to 200 W | |
| $R_{DS(on) max.}$ | 70 mΩ | |
| Part number | IGT40R070D1 E8220 | |




PC power supply

The PC power market is divided into high-end gaming PC and better cost-performance sectors to achieve a better price performance goal for desktop SMPS. The PC OEMs are implementing the desktop SMPS by removing the AUX power block, to save the cost of having a flyback circuit.

There is an increased efficiency requirements in the PC power application that leads to high efficient devices. Infineon CoolMOS™ 7 is tailored to meet the light load efficiency requirement, which remains a trend in the PC industry. With higher efficiency, a better thermal performance is ensured.

CoolMOS™ 7 comes with improved form factor through the use of smaller packages, which enables slimmer designs. Particularly our CoolMOS™ P7 allows customers to achieve the best price/performance.



| Functional block | Product category | Topology | Technology | Benefits |
|---------------------------|-----------------------|---------------------|-----------------------------------|--|
| PFC/Main stage | High voltage MOSFETs | CrCM/DCM PFC | 600 V CoolMOS™ P7 | > Best thermal performance > Rugged body diode > ESD enhancement for production line > Wide $R_{DS(on)}$ portfolio including both THD and SMD packages |
| | | | 600 V CoolMOS™ P6 | > Fast-switching speed for improved efficiency and thermals > Low gate charge for enhanced light-load efficiency and low power consumption at no load condition > Optimized V_{GS} threshold for low turn-off losses |
| | | | 500 V CoolMOS™ CE | > Optimized cost/performance > Lower transition losses versus standard MOSFET |
| | Boost diodes | DCM PFC | 650 V Rapid 1 | > Low conduction losses |
| | | CCM PFC | 650 V Rapid 2 | > Low reverse recovery losses and PFC switch turn-on losses |
| | | | CoolSiC™ diode 650 V G6 | > Very low reverse recovery losses |
| | Control ICs | CCM PFC ICs | ICE3PCS0xG | > High PFC and low THD |
| Main stage | Control ICs | HB LLC ICs | 650 V – ICE1HS01G-1/ ICE2HS01G | > High efficiency and low EMI |
| Synchronous rectification | Medium voltage diodes | HB LLC + center-tap | OptiMOS™ 40 V | > Optimized cost/performance and low thermals |
| | | | OptiMOS™ 60 V | > Layout tolerance and low thermals |




Smart meter

In today's technologically advanced world the demand for electrical energy is going up, as the traditional mechanical energy-based systems now depend on electrical power. An increasing trend can be seen in active monitoring and in dynamic pricing of electricity. A typical energy meter measures the amount of electrical energy consumed in kilowatt-hours (kWh) and can be mainly categorized into single phase and three phase types of smart meter. Existing and future energy meters should limit the self-consumption to 4 VA (~1.2 W) for single-phase or 8 VA (~2.4 W) for three-phasing energy meters. There is a tendency of moving from the traditional techniques of powering the meter to switch-mode-power-supply-based powering of the modern smart-grid-enabled smart energy meter.

Among the key characteristics of the smart meter SMPS are a wide input voltage ($60 V_{AC}$ to $580 V_{AC}$) and a quite low output voltage (12 V, 5 V, 3.3 V), as well as relatively low level of the output power (3-15 W). Among the requirements for the smart meter SMPS are low cost and low component count.

Infineon's latest CoolMOS™ P7 family, specifically 700 V/800 V/950 V CoolMOS™ P7, fulfills these requirements and satisfies comparatively high input voltage. The CoolMOS™ P7 technology brings the benefits of increased efficiency, low switching losses, high quality and reliability, and best-in-class thermal performance, being the right fit for the application.




| Functional block | Product category | Product family | Benefits |
|--|--------------------------|---|---|
| Flyback | High voltage MOSFETs | 800/950 V CoolMOS™ P7 | <ul style="list-style-type: none"> › Best-in-class performance › Highest efficiency › Outstanding thermal behavior |
| Cascode flyback | | 700/800/950 V CoolMOS™ P7 | <ul style="list-style-type: none"> › Best-in-class performance › Highest efficiency › Outstanding thermal behavior |
| Controller ICs for flyback and cascode flyback topologies | AC-DC PWM controller ICs | PWM-FF (fixed frequency) PWM-QR (Quasi resonant) | <ul style="list-style-type: none"> › High reliability › High efficiency |



Major home appliances

Based on industry-leading technology and manufacturing expertise, Infineon's line of innovative components for household appliances meets and exceeds even the most rigorous requirements for reliability and quality. The following block diagram example of an air conditioning system, together with the product selection table, provides effective recommendation for engineers selecting the right component for each power management stage inside major home appliances. The latest 600 V CoolMOS™ PFD7 series sets a new benchmark in 600 V super junction (SJ) technologies dedicated for ultrahigh power density designs as well as low power motor drives. It combines best-in-class performance with state-of-the-art ease-of-use, crystalized from Infineon's over 20 years' pioneering superjunction technology innovation and experience.



| Functional block | Topology | Voltage class | Technology/product family | Selection/benefit |
|--------------------------------------|---|---------------|--|---|
| PFC AC-DC | IGBT – PFC CCM (high frequency – SC) | 600 V | HighSpeed 3 | Recommendation |
| | IGBT – PFC CCM (low frequency – SC) | 600 V | TRENCHSTOP™ Performance | Recommendation |
| | IGBT – PFC CCM (cost competitive – no SC) | 650 V | TRENCHSTOP™ 5 – H5 | Recommendation |
| | IGBT – PFC CCM (low losses - SC) | 650 V | TRENCHSTOP™ IGBT6 | Recommendation |
| | IGBT – PFC | 600 V | TRENCHSTOP™ Advanced Isolation | Recommendation |
| | IGBT – PFC (cost competitive - no SC) | 650 V | TRENCHSTOP™ 5 WR5 | Recommendation |
| | MOSFET – PFC CCM | 600 V | CoolMOS™ P7 | Reference |
| | Diode – PFC CCM | 650 V | Rapid 1 and Rapid 2 diodes | Recommendation |
| | Controller – PFC CCM | – | ICE2PCS0xG, ICE3PCS0xG | Recommendation |
| | IPM – PFC CCM | 650 V | CIPOS™ Mini PFC interleaved IPM series, CIPOS™ PFC integrated IPM series | Recommendation |
| | Low-side gate driver IC-PFC | 25 V | Single low-side driver 1ED44176N01F Dual low-side driver IRS4427S Single low-side driver IRS44273L | OCP, fault and enable function in DSO-8 Rugged and reliable in DSO-8 Rugged and reliable in SOT23-5 |
| DC-AC | IGBT – B6-VSI | 650 V | TRENCHSTOP™ IGBT6 | Efficiency |
| | IGBT – B6-VSI | 600 V | RC-Drives Fast | Recommendation |
| | MOSFET - B6-VSI | 600 V | CoolMOS™PFD7 | Cost/performance |
| | IPM – B6-VSI | 600 V | CIPOS™ Mini | Recommendation |
| | Half-bridge gate driver IC | 650 V | 2ED2304S06F | SOI with integrated bootstrap diode |
| | Half-bridge gate driver ICs | 600 V | 2EDL05I06PF, 2EDL23I06PJ, 2ED28073J | Integrated bootstrap diode/FET |
| | Three-phase gate driver ICs | 600 V | 6EDL04I06PT, IR2136S, 6ED003L06-F2 | OCP, fault and enable function |
| AUX | Flyback fixed frequency | 700 V | CoolSET™ F5 | Recommendation |
| Microcontroller/ motor control IC | 32-bit ARM® Cortex®-M4 | - | XMC4100/XMC4200 | Recommendation |
| | iMOTION™ | - | IRMCxx motor control IC (incl. motion control algorithm) | Recommendation |
| Microcontroller supply | Linear voltage regulator | Up to 20 V | IFX1763, IFX54441, IFX54211, IFX3008 | Efficiency |
| Communication | CAN transceiver | - | IFX1050, IFX1051, IFX1040 | Robustness |
| Position sensing | Angle sensor | - | TLE5009, TLI5012B | Recommendation |
| | Hall switch | - | TLI496x | Recommendation |

CoolMOS™ SJ MOSFET package innovations for industrial applications

Space-saving and high performance packages



Innovative top-side cooled SMD solution for high power applications

Top-side cooled Double DPAK (DDPAK)

This is the first top-side cooled surface mount device (SMD) package addressing high power SMPS applications such as PC power, solar, server and telecom. SMD-based SMPS designs support fast switching and help to reduce the parasitic inductance associated with long leaded packages such as the common TO-220 package. In today's SMD-based designs, the output power is restricted by the thermal limit of the PCB material because the heat must be dissipated through the board. Thanks to the top-side cooling concept of DDPAK, the thermal decoupling of board and semiconductor is possible, enabling higher power density or improved system lifetime.



For highest efficiency and controllability in high power SMPS markets

TO-247 4-pin with asymmetric leads

The TO-247 4-pin package with asymmetric leads is an optimized version of the standard TO-247 4-pin and enables highest efficiency and controllability in the high power SMPS market. The fourth pin acts as a Kelvin source. The main current of the switch is placed outside of the gate loop and the feedback is eliminated. This leads to less switching losses, especially at high currents. Secondly, the EMI will be reduced due to cleaner waveforms. In addition, the asymmetric leads further improve the ease of use in the design-in process. Compared to the standard TO-247 4-pin the distance between the critical pins has been increased to enable simplified wave soldering and reduced board yield loss.



Enabling significant space savings

ThinPAK 8x8

With very small footprint of only 64 mm² (vs. 150 mm² for the D²PAK) and a very low profile with only 1 mm height (vs. 4.4 mm for the D²PAK) the ThinPAK 8x8 leadless SMD package for high voltage MOSFETs is a first choice to decrease system size in power-density driven designs. Low parasitic inductance and a separate 4-pin Kelvin source connection offer best efficiency and ease of use. The package is RoHS compliant with halogen-free mold compound.



Optimized for high power applications

TO-Leadless

Combined with the latest CoolMOS™ C7 Gold (G7) technology, the TO-leadless (TOLL) package is Infineon's flagship SMD package for high power/high current SMD solutions. Compared to D2PAK 7-pin, TO-leadless shows a 30 percent reduction in footprint, yet offers improved thermal performance. This and the 50 percent height reduction result in a significant advantage whenever highest power density is demanded. Equipped with 4-pin Kelvin source connection and low parasitic inductances the package offers best efficiency and ease of use. The package is MSL1 compliant and reflow solderable.

www.infineon.com/coolmos-latest-packages

CoolMOS™ SJ MOSFET package innovations for consumer applications

Addressing today's consumer needs



Cost-effective drop-in replacement for DPAK

SOT-223

The SOT-223 package without middle pin is a cost-effective alternative to DPAK, addressing the need for cost reductions in price sensitive applications. It offers a smaller footprint, while still being pin-to-pin compatible with DPAK, thus, allowing a drop-in replacement for DPAK and second sourcing. Moreover, SOT-223 achieves comparable thermal performance to DPAK and enables customers to achieve improved form factors or space savings in designs with low power dissipation.



Solution for higher assembly yield in charger applications

IPAK Short Lead with ISO Standoff

ThinPAK 5x6 reduces the PCB area by 52 percent and height by 54 percent when compared to the DPAK package which is widely used in chargers and adapters. ThinPAK 5x6 is the right device to replace DPAK and meet the market demands of slimmer and smaller designs. Also ThinPAK 5x6 enables a reduced charger and adapter case hot spot temperature by increasing the space between the MOSFET and the charger and adapter case.



Solution for height reduction in adapters and chargers

TO-220 FullPAK Narrow Lead

Infineon's TO-220 FullPAK Narrow Lead addresses customer needs with regards to height reduction requirements in adapter and charger applications. By offering an optimized standoff width and height and improved creepage distance, the package can be fully inserted into the PCB without any production concerns and, therefore, is especially suitable for slim and semi-slim adapter solutions.



Improved creepage distance for open frame power supplies

TO-220 FullPAK Wide Creepage

This package solution has an increased creepage distance between the pins to 4.25 mm compared to 2.54 mm of a TO-220 FullPAK package. It targets open frame power supplies such as TV sets and PC power, where dust can enter the case through air vents. Dust particles can reduce the effective creepage between pins over time, which may lead to high voltage arcing. The package meets the requirements of open frame power supplies without any additional measures. Thus, it reduces system cost by offering an alternative to frequently used approaches to increase creepage distance.

CoolMOS™ portfolio

950 V CoolMOS™ P7 **ACTIVE & PREFERRED**

| R _{DS(on)} [mΩ] | TO-220 | TO-220 FullPAK | SOT-223 | TO-251 Long lead | TO-252 (DPAK) | TO-220 Wide creepage | ThinPAK 8x8 | D²PAK |
|-----------------------------|--------|-------------------|-------------|---------------------|------------------|-------------------------|-------------|-------|
| 450 | | IPA95R450P7 | | IPU95R450P7 | IPD95R450P7 | | | |
| 750 | | IPA95R750P7 | | IPU95R750P7 | IPD95R750P7 | | | |
| 1200 | | IPA95R1K2P7 | IPN95R1K2P7 | IPU95R1K2P7 | IPD95R1K2P7 | | | |
| 2000 | | | IPN95R2K0P7 | IPU95R2K0P7 | IPD95R2K0P7 | | | |
| 3700 | | | IPN95R3K7P7 | IPU95R3K7P7 | | | | |

900 V CoolMOS™ C3 **ACTIVE**

| R _{DS(on)} [mΩ] | TO-220 | TO-262 (I²PAK) | TO-263 (D²PAK) | TO-220 FullPAK | TO-247 | TO-252 (DPAK) |
|-----------------------------|-------------|-------------------|-------------------|----------------|-------------|------------------|
| 120 | | | | | IPW90R120C3 | |
| 340 | IPP90R340C3 | IPJ90R340C3 | IPB90R340C3 | IPA90R340C3 | IPW90R340C3 | |
| 500 | | IPJ90R500C3 | | IPA90R500C3 | IPW90R500C3 | |
| 800 | IPP90R800C3 | | | IPA90R800C3 | | |
| 1000 | IPP90R1K0C3 | | | IPA90R1K0C3 | | |
| 1200 | IPP90R1K2C3 | IPJ90R1K2C3 | | IPA90R1K2C3 | | IPD90R1K2C3 |

800 V CoolMOS™ P7 **ACTIVE & PREFERRED**

| R _{DS(on)} [mΩ] | TO-220 | TO-220 FullPAK | TO-247 | TO-252 (DPAK) | TO-251 (IPAK) | TO-251 (IPAK Short Lead) | SOT-223 | TO-220 FullPAK narrow lead | ThinPAK 5x6* |
|-----------------------------|-------------|----------------|-------------|------------------|------------------|-----------------------------|-------------|-------------------------------|---------------|
| 280 | IPP80R280P7 | IPA80R280P7 | IPW80R280P7 | IPD80R280P7 | | | | IPAN80R280P7 | |
| 360 | IPP80R360P7 | IPA80R360P7 | IPW80R360P7 | IPD80R360P7 | | | | IPAN80R360P7 | |
| 450 | IPP80R450P7 | IPA80R450P7 | | IPD80R450P7 | | | | IPAN80R450P7 | |
| 600 | IPP80R600P7 | IPA80R600P7 | | IPD80R600P7 | IPU80R600P7 | IPS80R600P7 | IPN80R600P7 | | IPLK80R600P7* |
| 750 | IPP80R750P7 | IPA80R750P7 | | IPD80R750P7 | IPU80R750P7 | IPS80R750P7 | IPN80R750P7 | | IPLK80R750P7* |
| 900 | IPP80R900P7 | IPA80R900P7 | | IPD80R900P7 | IPU80R900P7 | IPS80R900P7 | IPN80R900P7 | | IPLK80R900P7* |
| 1200 | IPP80R1K2P7 | IPA80R1K2P7 | | IPD80R1K2P7 | IPU80R1K2P7 | IPS80R1K2P7 | IPN80R1K2P7 | | IPLK80R1K2P7* |
| 1400 | IPP80R1K4P7 | IPA80R1K4P7 | | IPD80R1K4P7 | IPU80R1K4P7 | IPS80R1K4P7 | IPN80R1K4P7 | | IPLK80R1K4P7* |
| 2000 | | | | IPD80R2K0P7 | IPU80R2K0P7 | IPS80R2K0P7 | IPN80R2K0P7 | | IPLK80R2K0P7* |
| 2400 | | | | IPD80R2K4P7 | IPU80R2K4P7 | IPS80R2K4P7 | IPN80R2K4P7 | | |
| 3300 | | | | IPD80R3K3P7 | IPU80R3K3P7 | | IPN80R3K3P7 | | |
| 4500 | | | | IPD80R4K5P7 | IPU80R4K5P7 | | IPN80R4K5P7 | | |

www.infineon.com/coolmos
www.infineon.com/c3

www.infineon.com/800v-p7
www.infineon.com/950v-p7

*Coming soon

800 V CoolMOS™ CE **ACTIVE**

| $R_{DS(on)}$ [mΩ] | TO-220 | TO-220 FullPAK | TO-247 | TO-252 (DPAK) | TO-251 (IPAK) | TO-251 (IPAK Short Lead) |
|----------------------|--------|----------------|--------|------------------|------------------|-----------------------------|
| 310 | | IPA80R310CE | | | | |
| 460 | | IPA80R460CE | | | | |
| 650 | | IPA80R650CE | | | | |
| 1000 | | IPA80R1K0CE | | IPD80R1K0CE | IPU80R1K0CE | |
| 1400 | | IPA80R1K4CE | | IPD80R1K4CE | | |
| 2800 | | | | IPD80R2K8CE | | |

800 V CoolMOS™ C3 **ACTIVE**

| $R_{DS(on)}$ [mΩ] | TO-220 | TO-262 (I ² PAK) | TO-263 (D ² PAK) | TO-220 FullPAK | TO-247 | TO-252 (DPAK) |
|----------------------|------------|--------------------------------|--------------------------------|----------------|------------|------------------|
| 85 | | | | | SPW55N80C3 | |
| 290 | SPP17N80C3 | | SPB17N80C3 | SPA17N80C3 | SPW17N80C3 | |
| 450 | SPP11N80C3 | | | SPA11N80C3 | SPW11N80C3 | |
| 650 | SPP08N80C3 | | | SPA08N80C3 | | |
| 900 | SPP06N80C3 | | | SPA06N80C3 | | SPD06N80C3 |
| 1300 | SPP04N80C3 | | | SPA04N80C3 | | SPD04N80C3 |
| 2700 | | | | SPA02N80C3 | | SPD02N80C3 |

700 V CoolMOS™ P7 **ACTIVE & PREFERRED**

| $R_{DS(on)}$ [mΩ] | TO-220 | TO-262 (I ² PAK) | TO-251 (IPAK Short Lead) | TO-220 FullPAK | ThinPAK 5x6 | TO-252 (DPAK) | TO-220 FullPAK narrow lead | TO-251 (IPAK Short Lead w/ ISO Standoff) | SOT-223 |
|----------------------|--------|--------------------------------|-----------------------------|----------------|--------------|------------------|-------------------------------|--|--------------|
| 360 | | | IPS70R360P7S | IPA70R360P7S | | IPD70R360P7S | IPAN70R360P7S | IPSA70R360P7S | IPN70R360P7S |
| 450 | | | | IPA70R450P7S | | | IPAN70R450P7S | IPSA70R450P7S | IPN70R450P7S |
| 600 | | | IPS70R600P7S | IPA70R600P7S | IPLK70R600P7 | IPD70R600P7S | IPAN70R600P7S | IPSA70R600P7S | IPN70R600P7S |
| 750 | | | | IPA70R750P7S | IPLK70R750P7 | | IPAN70R750P7S | IPSA70R750P7S | IPN70R750P7S |
| 900 | | | IPS70R900P7S | IPA70R900P7S | IPLK70R900P7 | IPD70R900P7S | IPAN70R900P7S | IPSA70R900P7S | IPN70R900P7S |
| 1200 | | | | | IPLK70R1K2P7 | | | IPSA70R1K2P7S | IPN70R1K2P7S |
| 1400 | | | IPS70R1K4P7S | | IPLK70R1K4P7 | IPD70R1K4P7S | | IPSA70R1K4P7S | IPN70R1K4P7S |
| 2000 | | | | | IPLK70R2K0P7 | | | IPSA70R2K0P7S | IPN70R2K0P7S |

700 V CoolMOS™ CE **ACTIVE**

| $R_{DS(on)}$ [mΩ] | TO-220 | TO-220 FullPAK Wide Creepage | TO-262 (I ² PAK) | TO-251 (IPAK Short Lead with ISO Standoff) | TO-252 (DPAK) | TO-251 (IPAK) | TO-251 (IPAK Short Lead) | SOT-223 |
|----------------------|--------|---------------------------------|--------------------------------|--|------------------|------------------|-----------------------------|-------------|
| 600 | | IPAW70R600CE | | IPSA70R600CE | IPD70R600CE | | | |
| 950 | | IPAW70R950CE | IP170R950CE | IPSA70R950CE | IPD70R950CE | | IPS70R950CE | |
| 1000 | | | | | | | | IPN70R1K0CE |
| 1400 | | | | IPSA70R1K4CE | IPD70R1K4CE | | IPS70R1K4CE | |
| 1500 | | | | | | | | IPN70R1K5CE |
| 2000 | | | | IPSA70R2K0CE | IPD70R2K0CE | | IPS70R2K0CE | |
| 2100 | | | | | | | | IPN70R2K1CE |


650 V CoolMOS™ C7 Gold (G-series) ACTIVE & PREFERRED

| $R_{DS(on)}$ [mΩ] | TO-220 | TO-Leadless (TOLL) | TO-263 (D ² PAK) | TO-220 FullPAK | TO-247 | TO-252 (DPAK) |
|----------------------|--------|-----------------------|--------------------------------|-------------------|--------|------------------|
| 33 | | IPT65R033G7 | | | | |
| 105 | | IPT65R105G7 | | | | |
| 195 | | IPT65R195G7 | | | | |


650 V CoolMOS™ C7 ACTIVE & PREFERRED

| $R_{DS(on)}$ [mΩ] | TO-220 | TO-263 (D ² PAK) | TO-220 FullPAK | TO-247 | TO-247 4-pin | TO-252 (DPAK) | ThinPAK 8x8 |
|----------------------|-------------|--------------------------------|----------------|-------------|--------------|------------------|-------------|
| 19 | | | | IPW65R019C7 | IPZ65R019C7 | | |
| 45 | IPP65R045C7 | IPB65R045C7 | IPA65R045C7 | IPW65R045C7 | IPZ65R045C7 | | |
| 65 | IPP65R065C7 | IPB65R065C7 | IPA65R065C7 | IPW65R065C7 | IPZ65R065C7 | | |
| 70 | | | | | | | IPL65R070C7 |
| 95 | IPP65R095C7 | IPB65R095C7 | IPA65R095C7 | IPW65R095C7 | IPZ65R095C7 | | |
| 99 | | | | | | | IPL65R099C7 |
| 125 | IPP65R125C7 | IPB65R125C7 | IPA65R125C7 | IPW65R125C7 | | | |
| 130 | | | | | | | IPL65R130C7 |
| 190 | IPP65R190C7 | IPB65R190C7 | IPA65R190C7 | IPW65R190C7 | | IPD65R190C7 | |
| 195 | | | | | | | IPL65R195C7 |
| 225 | IPP65R225C7 | IPB65R225C7 | IPA65R225C7 | | | IPD65R225C7 | |
| 230 | | | | | | | IPL65R230C7 |


650 V CoolMOS™ CE ACTIVE

| $R_{DS(on)}$ [mΩ] | TO-220 | TO-220 FullPAK | TO-247 | TO-252 (DPAK) | TO-251 (IPAK) | TO-251 (IPAK Short Lead) | SOT-223 | TO-220 FullPAK Narrow Lead |
|----------------------|--------|----------------|--------|------------------|------------------|-----------------------------|-------------|-------------------------------|
| 400 | | IPA65R400CE | | IPD65R400CE | | IPS65R400CE | | |
| 650 | | IPA65R650CE | | IPD65R650CE | | IPS65R650CE | | IPAN65R650CE |
| 1000 | | IPA65R1K0CE | | IPD65R1K0CE | | IPS65R1K0CE | | |
| 1500 | | IPA65R1K5CE | | IPD65R1K5CE | | | IPN65R1K5CE | |


650 V CoolMOS™ CFD2 ACTIVE

| $R_{DS(on)}$ [mΩ] | TO-220 | TO-262 (I ² PAK) | TO-263 (D ² PAK) | TO-220 FullPAK | TO-247 | TO-252 (DPAK) | ThinPAK 8x8 |
|----------------------|--------------|--------------------------------|--------------------------------|----------------|--------------|------------------|--------------|
| 41 | | | | | IPW65R041CFD | | |
| 80 | | | | | IPW65R080CFD | | |
| 110 | IPP65R110CFD | | IPB65R110CFD | IPA65R110CFD | IPW65R110CFD | | |
| 150 | IPP65R150CFD | | IPB65R150CFD | IPA65R150CFD | IPW65R150CFD | | |
| 165 | | | | | | | IPL65R165CFD |
| 190 | IPP65R190CFD | IPI65R190CFD | IPB65R190CFD | IPA65R190CFD | IPW65R190CFD | | |
| 210 | | | | | | | IPL65R210CFD |
| 310 | IPP65R310CFD | | IPB65R310CFD | IPA65R310CFD | | | |
| 340 | | | | | | | IPL65R340CFD |
| 420 | IPP65R420CFD | | | IPA65R420CFD | IPW65R420CFD | IPD65R420CFD | |
| 660 | | | | IPA65R660CFD | | IPD65R660CFD | |
| 950 | | | | | | IPD65R950CFD | |
| 1400 | | | | | | IPD65R1K4CFD | |

www.infineon.com/coolmos
www.infineon.com/g7
www.infineon.com/c7
www.infineon.com/cfd2
www.infineon.com/ce

600 V CoolMOS™ S7 **ACTIVE & PREFERRED**

| R _{DS(on)} [mΩ] | TO -220 | TO-Leadless (TOLL) |
|-----------------------------|-------------|-----------------------|
| 22 | IPP60R022S7 | IPT60R022S7 |
| 40 | | IPT60R040S7 |
| 65 | | IPT60R065S7 |

600 V CoolMOS™ P7 **ACTIVE & PREFERRED**

Industrial grade



| R _{DS(on)} [mΩ] | TO -220 | TO-220 FullPAK | TO-247 | TO-247 4-pin asymmetric leads | TO-252 (DPAK) | TO-220 FullPAK Wide Creepage | ThinPAK 8x8 | D ² PAK |
|-----------------------------|-------------|----------------|-------------|----------------------------------|------------------|---------------------------------|-------------|--------------------|
| 24 | | | IPW60R024P7 | IPZA60R024P7 | | | | |
| 37 | | | IPW60R037P7 | IPZA60R037P7 | | | | |
| 45 | | | IPW60R045P7 | IPZA60R045P7 | | | | IPB60R045P7 |
| 60 | IPP60R060P7 | IPA60R060P7 | IPW60R060P7 | IPZA60R060P7 | | | | IPB60R060P7 |
| 65 | | | | | | | IPL60R065P7 | |
| 80 | IPP60R080P7 | IPA60R080P7 | IPW60R080P7 | IPZA60R080P7 | | | IPL60R085P7 | IPB60R080P7 |
| 99 | IPP60R099P7 | IPA60R099P7 | IPW60R099P7 | IPZA60R099P7 | | | | IPB60R099P7 |
| 105 | | | | | | | IPL60R105P7 | |
| 120 | IPP60R120P7 | IPA60R120P7 | IPW60R120P7 | IPZA60R120P7 | | | | IPB60R120P7 |
| 125 | | | | | | | IPL60R125P7 | |
| 160 | IPP60R160P7 | IPA60R160P7 | | | | | | |
| 180 | IPP60R180P7 | IPA60R180P7 | IPW60R180P7 | IPZA60R180P7 | IPD60R180P7 | | | IPB60R180P7 |
| 185 | | | | | | | IPL60R185P7 | |
| 280 | IPP60R280P7 | IPA60R280P7 | | | IPD60R280P7 | | | IPB60R280P7 |
| 285 | | | | | | | IPL60R285P7 | |
| 360 | IPP60R360P7 | IPA60R360P7 | | | IPD60R360P7 | | | IPB60R360P7 |
| 365 | | | | | | | IPL60R365P7 | |
| 600 | IPP60R600P7 | IPA60R600P7 | | | IPD60R600P7 | | | |

600 V CoolMOS™ P7 **ACTIVE & PREFERRED**

Standard grade



| R _{DS(on)} [mΩ] | TO -220 | TO-220 FullPAK | TO-220 FullPAK Narrow lead | TO-247 4-pin | TO-252 (DPAK) | TO-220 FullPAK Wide Creepage | ThinPAK 8x8 | SOT-223 |
|-----------------------------|---------|----------------|-------------------------------|--------------|------------------|---------------------------------|-------------|--------------|
| 180 | | IPA60R180P7S | IPAN60R180P7S | | IPD60R180P7S | IPAW60R180P7S | | |
| 280 | | IPA60R280P7S | IPAN60R280P7S | | IPD60R280P7S | IPAW60R280P7S | | |
| 360 | | IPA60R360P7S | IPAN60R360P7S | | IPD60R360P7S | IPAW60R360P7S | | IPN60R360P7S |
| 600 | | IPA60R600P7S | IPAN60R600P7S | | IPD60R600P7S | IPAW60R600P7S | | IPN60R600P7S |

600 V CoolMOS™ CFD7 **ACTIVE & PREFERRED**

| R _{DS(on)} [mΩ] | TO-220 | TO-263 (D ² PAK) | TO-220 FullPAK | TO-247 | TO-252 (DPAK) | ThinPAK 8x8 | DDPAK | TO-Leadless (TOLL) |
|-----------------------------|---------------|--------------------------------|----------------|---------------|------------------|---------------|-----------------|-----------------------|
| 18 | | | | IPW60R018CFD7 | | | | |
| 24 | | | | IPW60R024CFD7 | | | | |
| 31/35 | | | | IPW60R31CFD7 | | | | IPT60R035CFD7* |
| 40/45 | | IPB60R040CFD7 | | IPW60R40CFD7 | | | IPDD60R045CFD7* | IPT60R045CFD7* |
| 55 | | IPB60R055CFD7 | | IPW60R55CFD7 | | | IPDD60R055CFD7* | IPT60R055CFD7* |
| 60 | | | | | | IPL60R060CFD7 | | |
| 70 | IPP60R70CFD7 | IPB60R70CFD7 | | IPW60R70CFD7 | | | | |
| 75 | | | | | | | | |
| 90/95 | IPP60R90CFD7 | IPB60R90CFD7 | | IPW60R90CFD7 | | IPL60R75CFD7 | IPDD60R075CFD7* | IPT60R075CFD7* |
| 105/115 | IPP60R105CFD7 | IPB60R105CFD7 | | IPW60R105CFD7 | | IPL60R095CFD7 | IPDD60R090CFD7* | IPT60R090CFD7* |
| 125/140 | IPP60R125CFD7 | IPB60R125CFD7 | IPA60R125CFD7 | IPW60R125CFD7 | | IPL60R115CFD7 | IPDD60R105CFD7* | IPT60R105CFD7* |
| 145/160 | IPP60R145CFD7 | IPB60R145CFD7 | IPA60R145CFD7 | IPW60R145CFD7 | IPD60R145CFD7 | IPL60R140CFD7 | IPDD60R125CFD7* | IPT60R125CFD7* |
| 170 | IPP60R170CFD7 | IPB60R170CFD7 | IPA60R170CFD7 | IPW60R170CFD7 | IPD60R170CFD7 | IPL60R160CFD7 | IPDD60R145CFD7* | IPT60R145CFD7* |
| 185 | | | | | | IPL60R185CFD7 | | |
| 210/225 | IPP60R210CFD7 | IPB60R210CFD7 | IPA60R210CFD7 | | IPD60R210CFD7 | IPL60R225CFD7 | | |
| 280 | IPP60R280CFD7 | IPB60R280CFD7 | IPA60R280CFD7 | | IPD60R280CFD7 | | | |
| 360 | IPP60R360CFD7 | IPB60R360CFD7 | IPA60R360CFD7 | | IPD60R360CFD7 | | | |

www.infineon.com/coolmoswww.infineon.com/g7www.infineon.com/600v-p7

*Coming soon


600 V CoolMOS™ C7 Gold (G-series) **ACTIVE & PREFERRED**

| R _{DS(on)} [mΩ] | TO-220 | TO-Leadless (TOLL) | TO-220 FullPAK | TO-247 | TO-247 4-pin | Double DPAK | ThinPAK 8x8 |
|-----------------------------|--------|-----------------------|----------------|--------|--------------|--------------|-------------|
| 28 | | IPT60R028G7 | | | | | |
| 50 | | IPT60R050G7 | | | | IPDD60R050G7 | |
| 80 | | IPT60R080G7 | | | | IPDD60R080G7 | |
| 102 | | IPT60R102G7 | | | | IPDD60R102G7 | |
| 125 | | IPT60R125G7 | | | | IPDD60R125G7 | |
| 150 | | IPT60R150G7 | | | | IPDD60R150G7 | |
| 190 | | | | | | IPDD60R190G7 | |


600 V CoolMOS™ C7 **ACTIVE & PREFERRED**

| R _{DS(on)} [mΩ] | TO-220 | TO-263 (D ² PAK) | TO-220 FullPAK | TO-247 | TO-247 4-pin | TO-252 (DPAK) | ThinPAK 8x8 |
|-----------------------------|-------------|--------------------------------|----------------|-------------|--------------|------------------|-------------|
| 17 | | | | IPW60R017C7 | IPZ60R017C7 | | |
| 40 | IPP60R040C7 | IPB60R040C7 | | IPW60R040C7 | IPZ60R040C7 | | |
| 60 | IPP60R060C7 | IPB60R060C7 | IPA60R060C7 | IPW60R060C7 | IPZ60R060C7 | | |
| 65 | | | | | | | IPL60R065C7 |
| 99 | IPP60R099C7 | IPB60R099C7 | IPA60R099C7 | IPW60R099C7 | IPZ60R099C7 | | |
| 104 | | | | | | | IPL60R104C7 |
| 120 | IPP60R120C7 | IPB60R120C7 | IPA60R120C7 | IPW60R120C7 | | | |
| 125 | | | | | | | IPL60R125C7 |
| 180 | IPP60R180C7 | IPB60R180C7 | IPA60R180C7 | IPW60R180C7 | | IPD60R180C7 | |
| 185 | | | | | | | IPL60R185C7 |


600 V CoolMOS™ P6 **ACTIVE**

| R _{DS(on)} [mΩ] | TO-220 | TO-220 FullPAK | TO-247 | TO-247 4-pin | TO-252 (DPAK) | ThinPAK 5x6 | ThinPAK 8x8 |
|-----------------------------|-------------|----------------|-------------|--------------|------------------|--------------|-------------|
| 41 | | | IPW60R041P6 | | | | |
| 70 | | | IPW60R070P6 | IPZ60R070P6 | | | |
| 99 | IPP60R099P6 | IPA60R099P6 | IPW60R099P6 | IPZ60R099P6 | | | |
| 125 | IPP60R125P6 | IPA60R125P6 | IPW60R125P6 | | | | |
| 160 | IPP60R160P6 | IPA60R160P6 | IPW60R160P6 | | | | |
| 180 | | | | | | | IPL60R180P6 |
| 190 | IPP60R190P6 | IPA60R190P6 | IPW60R190P6 | | | | |
| 210 | | | | | | | IPL60R210P6 |
| 230 | | IPA60R230P6 | | | | | |
| 255 | | | | | | | |
| 280 | IPP60R280P6 | IPA60R280P6 | IPW60R280P6 | | | | |
| 330/360 | | | | | | IPL60R360P6S | |
| 380 | | IPA60R380P6 | | | IPD60R380P6 | | |
| 600 | | IPA60R600P6 | | | IPD60R600P6 | | |
| 650 | | | | | | IPL60R650P6S | |

www.infineon.com/coolmos
www.infineon.com/c7
www.infineon.com/p6

600 V CoolMOS™ PFD7 **ACTIVE & PREFERRED**

| R _{DS(on)} [mΩ] | TO-220 FullPAK Narrow Leads | TO-251 (IPAK Short Lead) | TO-252 (DPAK) | SOT-223 | ThinPAK 5x6 |
|-----------------------------|--------------------------------|-----------------------------|------------------|----------------|----------------|
| 125 | IPAN60R125PFD7S | | | | |
| 210 | IPAN60R210PFD7S | IPS60R210PFD7S | IPD60R210PFD7S | | |
| 280 | IPAN60R280PFD7S | IPS60R280PFD7S | IPD60R280PFD7S | | |
| 360 | IPAN60R360PFD7S | IPS60R360PFD7S | IPD60R360PFD7S | IPN60R360PFD7S | IPLK60R360PFD7 |
| 600 | | IPS60R600PFD7S | IPD60R600PFD7S | IPN60R600PFD7S | IPLK60R600PFD7 |
| 1000 | | IPS60R1K0PFD7S | IPD60R1K0PFD7S | IPN60R1K0PFD7S | IPLK60R1K0PFD7 |
| 1500 | | | IPD60R1K5PFD7S | IPN60R1K5PFD7S | IPLK60R1K5PFD7 |
| 2000 | | | IPD60R2K0PFD7S | IPN60R2K0PFD7S | |

600 V CoolMOS™ CE **ACTIVE**

| R _{DS(on)} [mΩ] | TO-220 FullPAK | TO-220 FullPAK Wide Creepage | TO-247 | TO-252 (DPAK) | TO-251 (IPAK) | TO-251 (IPAK Short Lead) | SOT-223 | TO-220 FullPAK Narrow Lead |
|-----------------------------|----------------|---------------------------------|--------|------------------|------------------|-----------------------------|-------------|-------------------------------|
| 190 | | IPAW60R190CE | | | | | | |
| 280 | | IPAW60R280CE | | | | | | |
| 380 | | IPAW60R380CE | | | | | | |
| 400 | IPA60R400CE | | | IPD60R400CE | | IPS60R400CE | | |
| 460 | IPA60R460CE | | | IPD60R460CE | | IPS60R460CE | | |
| 600 | | IPAW60R600CE | | | | | | |
| 650 | IPA60R650CE | | | IPD60R650CE | | IPS60R650CE | | IPAN60R650CE |
| 800 | | | | IPD60R800CE | | IPS60R800CE | | IPAN60R800CE |
| 1000 | IPA60R1K0CE | | | IPD60R1K0CE | IPU60R1K0CE | IPS60R1K0CE | IPN60R1K0CE | |
| 1500 | IPA60R1K5CE | | | IPD60R1K5CE | IPU60R1K5CE | IPS60R1K5CE | IPN60R1K5CE | |
| 2100 | | | | IPD60R2K1CE | IPU60R2K1CE | IPS60R2K1CE | IPN60R2K1CE | |
| 3400 | | | | IPD60R3K4CE | | IPS60R3K4CE | IPN60R3K4CE | |

500 V CoolMOS™ CE **ACTIVE & PREFERRED**


| R _{DS(on)} [mΩ] | TO-220 | TO-220 FullPAK | TO-247 | TO-252 (DPAK) | TO-251 (IPAK) | TO-251 (IPAK Short Lead) | SOT-223 | TO-220 FullPAK Narrow Lead |
|-----------------------------|-------------|----------------|--------|------------------|------------------|-----------------------------|-------------|-------------------------------|
| 190 | IPP50R190CE | IPA50R190CE | | | | | | |
| 280 | IPP50R280CE | IPA50R280CE | | IPD50R280CE | | | | |
| 380 | IPP50R380CE | IPA50R380CE | | IPD50R380CE | | | | |
| 500 | | IPA50R500CE | | IPD50R500CE | | | | IPAN50R500CE |
| 650 | | | | IPD50R650CE | | | IPN50R650CE | |
| 800 | | IPA50R800CE | | IPD50R800CE | | | IPN50R800CE | |
| 950 | | IPA50R950CE | | IPD50R950CE | | | IPN50R950CE | |
| 1400 | | | | IPD50R1K4CE | | | IPN50R1K4CE | |
| 2000 | | | | IPD50R2K0CE | | | IPN50R2K0CE | |
| 3000 | | | | IPD50R3K0CE | | | IPN50R3K0CE | |

www.infineon.com/coolmos

www.infineon.com/ce

www.infineon.com/500v-ce

CoolMOS™ SJ MOSFET automotive portfolio

800 V CoolMOS™ C3A **ACTIVE & PREFERRED**

| $R_{DS(on)}$ @ $T_j = 25^\circ\text{C}$ $V_{GS} = 10\text{ V}$ [mΩ] | TO-247 | TO-252 | TO-263 |
|---|--------------|--------------|--------------|
| 290 | IPW80R290C3A | | IPB80R290C3A |
| 2700 | | IPD80R2K7C3A | |

650 V CoolMOS™ CFDA **ACTIVE & PREFERRED**

| $R_{DS(on)}$ @ $T_j = 25^\circ\text{C}$ $V_{GS} = 10\text{ V}$ [mΩ] | TO-220 | TO-247 | TO-252 | TO-263 |
|---|---------------|---------------|---------------|---------------|
| 48 | | IPW65R048CFDA | | |
| 80 | | IPW65R080CFDA | | |
| 110 | IPP65R110CFDA | IPW65R110CFDA | | IPB65R110CFDA |
| 150 | IPP65R150CFDA | IPW65R150CFDA | | IPB65R150CFDA |
| 190 | IPP65R190CFDA | IPW65R190CFDA | | IPB65R190CFDA |
| 310 | IPP65R310CFDA | | | IPB65R310CFDA |
| 420 | | | IPD65R420CFDA | |
| 660 | | | IPD65R660CFDA | IPB65R660CFDA |

www.infineon.com/coolmos

www.infineon.com/coolmos-automotive


www.infineon.com/cfda

www.infineon.com/cfd7a

650 V CoolMOS™ CFD7A **ACTIVE & PREFERRED**

| $R_{DS(on)}$ @ $T_J = 25^\circ\text{C}$ $V_{GS} = 10\text{ V}$ [mΩ] | TO-220 | TO-247 | TO-247 Short lead | TO-263-3 D ² PAK 3-pin | TO-263-7 D ² PAK 7-pin |
|---|-----------------|-----------------|----------------------|--------------------------------------|--------------------------------------|
| 22 | | IPW65R022CFD7A* | IPWS65R022CFD7A* | | |
| 35 | | IPW65R035CFD7A | IPWS65R035CFD7A* | | |
| 50 | IPP65R050CFD7A | IPW65R050CFD7A | IPWS65R050CFD7A* | IPB65R050CFD7A | IPBE65R050CFD7A |
| 75 | | IPW65R075CFD7A | IPWS65R075CFD7A* | | IPBE65R075CFD7A |
| 99 | IPP65R099CFD7A | IPW65R099CFD7A | | IPB65R099CFD7A | IPBE65R099CFD7A |
| 115 | IPP65R115CFD7A | IPW65R115CFD7A | | IPB65R115CFD7A | IPBE65R115CFD7A |
| 145 | | IPW65R145CFD7A* | | | IPBE65R145CFD7A* |
| 190 | IPP65R190CFD7A* | IPW65R190CFD7A* | | IPB65R190CFD7A* | IPBE65R190CFD7A* |
| 230 | | | | IPB65R230CFD7A | IPBE65R230CFD7A |

* Coming soon

600 V CoolMOS™ CPA **ACTIVE**

| $R_{DS(on)}$ @ $T_J = 25^\circ\text{C}$ $V_{GS} = 10\text{ V}$ [mΩ] | TO-220 | TO-247 | TO-262 | TO-263 |
|---|--------------|--------------|--------------|--------------|
| 45 | | IPW60R045CPA | | |
| 75 | | IPW60R075CPA | | |
| 99 | IPP60R099CPA | IPW60R099CPA | IPI60R099CPA | IPB60R099CPA |
| 199 | | | | IPB60R199CPA |
| 299 | | | | IPB60R299CPA |

CoolSiC™ portfolio

CoolSiC™ MOSFET Gen1 **ACTIVE & PREFERRED**

| $R_{DS(on)}$ max. [mΩ] | $R_{DS(on)}$ typ. [mΩ] | TO-247 4-pin | TO-247 |
|---------------------------|---------------------------|---------------|--------------|
| 34 | 27 | IMZA65R027M1H | IMW65R027M1H |
| 64 | 48 | IMZA65R048M1H | IMW65R048M1H |
| 94 | 72 | IMZA65R072M1H | IMW65R072M1H |
| 142 | 107 | IMZA65R107M1H | IMW65R107M1H |

CoolSiC™ Schottky diodes 650 V G6 **ACTIVE & PREFERRED**

| I_F [A] | TO-220 R2L | TO-247 Dual Die | TO-247 | Double DPAK | D ² PAK R2L | ThinPAK 8x8 |
|--------------|------------|--------------------|--------|-------------|------------------------|-------------|
| 4 | IDH04G65C6 | | | IDDD04G65C6 | | |
| 6 | IDH06G65C6 | | | IDDD06G65C6 | | |
| 8 | IDH08G65C6 | | | IDDD08G65C6 | | |
| 10 | IDH10G65C6 | | | IDDD10G65C6 | | |
| 12 | IDH12G65C6 | | | IDDD12G65C6 | | |
| 16 | IDH16G65C6 | | | IDDD16G65C6 | | |
| 20 | IDH20G65C6 | | | IDDD20G65C6 | | |

CoolSiC™ Schottky diodes 650 V G5 **ACTIVE**

| I_F [A] | TO-220 R2L | TO-247 Dual Die | TO-247 | D ² PAK R2L | ThinPAK 8x8 |
|--------------|------------|--------------------|------------|------------------------|-------------|
| 2 | IDH02G65C5 | | | IDK02G65C5 | IDL02G65C5 |
| 3 | IDH03G65C5 | | | IDK03G65C5 | |
| 4 | IDH04G65C5 | | | IDK04G65C5 | IDL04G65C5 |
| 5 | IDH05G65C5 | | | IDK05G65C5 | |
| 6 | IDH06G65C5 | | | IDK06G65C5 | IDL06G65C5 |
| 8 | IDH08G65C5 | | | IDK08G65C5 | IDL08G65C5 |
| 9 | IDH09G65C5 | | | IDK09G65C5 | |
| 10 | IDH10G65C5 | | IDW10G65C5 | IDK10G65C5 | IDL10G65C5 |
| 12 | IDH12G65C5 | | IDW12G65C5 | IDK12G65C5 | IDL12G65C5 |
| 16 | IDH16G65C5 | | IDW16G65C5 | | |
| 20 | IDH20G65C5 | IDW20G65C5B | IDW20G65C5 | | |
| 24 | | IDW24G65C5B | | | |
| 30/32 | | IDW32G65C5B | IDW30G65C5 | | |
| 40 | | IDW40G65C5B | IDW40G65C5 | | |

CoolSiC™ Schottky diodes 650 V G3 **ACTIVE**

| I_F [A] | TO-220 R2L | TO-247 Dual Die | TO-247 | DPAK R2L | D ² PAK | ThinPAK 8x8 |
|--------------|------------|--------------------|--------|------------|--------------------|-------------|
| 3 | IDH03SG60C | | | IDD03SG60C | | |
| 4 | IDH04SG60C | | | IDD04SG60C | | |
| 5 | IDH05SG60C | | | IDD05SG60C | | |
| 6 | IDH06SG60C | | | IDD06SG60C | | |
| 8 | IDH08SG60C | | | IDD08SG60C | | |
| 9 | IDH09SG60C | | | IDD09SG60C | | |
| 10 | IDH10SG60C | | | IDD10SG60C | | |
| 12 | IDH12SG60C | | | IDD12SG60C | | |

CoolGaN™ portfolio

CoolGaN™ 400 V e-mode



| | |
|----------------------|--------------------|
| $R_{DS(on)}$ [mΩ] | HSOF-8-3 (TOLL) |
| P_{max} | Up to 200 W |
| $R_{DS(on)}$ max. | 70 Ω |
| Typical part number | IGT40R070D1 E8220 |







600 V CoolGaN™ **






| $R_{DS(on)}$ max. | DSO-20-85 Bottom-side cooling | DSO-20-87 Top-side cooling | HSOF-8-3 (TO-leadless) | LSON-8-1 DFN8x8 |
|-------------------|----------------------------------|-------------------------------|---------------------------|--------------------|
| 42 | IGO60R042D1** | IGOT60R042D1** | IGT60R042D1** | |
| 70 | IGO60R070D1 | IGOT60R070D1 | IGT60R070D1 | IGLD60R070D1 |
| 190 | | | IGT60R190D1S* | IGLD60R190D1 |

EiceDRIVER™ portfolio



1EDN EiceDRIVER™ portfolio

| Package | | UVLO | Orderable part number | Pinout |
|---|-------------|------|-----------------------|---|
|  | SOT-23 6pin | 4 V | 1EDN7511BXUSA1 |  |
| | | 8 V | 1EDN8511BXUSA1 | |
|  | SOT-23 5pin | 4 V | 1EDN7512BXTSA1 |  |
|  | WSO 6pin | 4 V | 1EDN7512GXTMA1 |  |

2EDN EiceDRIVER™ portfolio

| Package | | UVLO | Inputs | Orderable part number | Industry standard pinout configuration |
|---|------------|------|----------|-----------------------|--|
|  | DSO 8pin | 4 V | Direct | 2EDN7524FXTMA1 |  |
| | | | Inverted | 2EDN7523FXTMA1 | |
| | | 8 V | Direct | 2EDN7424FXTMA1 | |
| | | | Inverted | 2EDN8523FXTMA1 | |
|  | TSSOP 8pin | 4 V | Direct | 2EDN7524RXUMA1 | |
| | | | Inverted | 2EDN7523RXUMA1 | |
| | | 8 V | Direct | 2EDN7424RXUMA1 | |
| | | | Inverted | 2EDN8523RXUMA1 | |
| | WSO 8pin | 4 V | Direct | 2EDN7524GXTMA1 | |
| | | | Inverted | 2EDN7523GXTMA1 | |

1EDN7550 and 1EDN8550 EiceDRIVER™ with truly differential inputs (TDI) portfolio

| Package | | UVLO | Ground shift robustness | | Product name | Industry standard pinout configuration |
|---|-------------|------|-------------------------|--------|--------------|---|
| | | | dynamic | static | | |
|  | SOT-23 6pin | 4 V | ± 150 V | ± 70 V | 1EDN7550B |  |
| | | 8 V | ± 150 V | ± 70 V | 1EDN8550B | |

2EDS8xx5H and 2EDF72x5x EiceDRIVER™ (2EDi) portfolio

| Package | UVLO | Isolation (input to output) | Output Current (source sink) | Orderable part number |
|---------------------|------|---|------------------------------|-----------------------|
| 16-pin DSO 150-mil | 4 V | 1.5 kV _{peak} | 4 A/8 A | 2EDF7275FXUMA1 |
| 16-pin DSO 300-mil | 8 V | V _{IO TM} = 6 kV _{peak} (VDE 0884-11) | 4 A/8 A | 2EDS8255HXUMA1 |
| | | V _{IO TM} = 6 kV _{peak} (VDE 0884-10) | 4 A/8 A | 2EDS8265HXUMA1 |
| | | V _{IO TM} = 6 kV _{peak} (VDE 0884-11) | 1 A/2 A | 2EDS8155HXUMA1 |
| | | V _{IO TM} = 6 kV _{peak} (VDE 0884-10) | 1 A/2 A | 2EDS8165HXUMA1 |
| 13-pin LGA (5x5 mm) | 4 V | 1.5 kV _{peak} | 4 A/8 A | 2EDF7275KXUMA1 |
| | | | 4 A/8 A | 2EDF7235KXUMA1 |

www.infineon.com/1edn
www.infineon.com/2edn

www.infineon.com/2edi
www.infineon.com/TDI

GaN EiceDRIVER™ family product portfolio

| Product | Package | Input to output isolation | | | | Propagation delay accuracy | Typ. high level (sourcing) output resistance | Typ. low level (sinking) output resistance | Orderable part number |
|-----------|---------------------|---------------------------|--|---------------------------------|-------------------|----------------------------|--|--|-----------------------|
| | | Isolation class | Rating | Surge testing | Certification | | | | |
| 1EDF5673K | LGA, 13-pin 5x5 mm | functional | $V_{IO} = 1.5 \text{ kV}_{DC}$ | n.a. | n.a. | -6 ns/+7 ns | 0.85 Ω | 0.35 Ω | 1EDF5673KXUMA1 |
| 1EDF5673F | DSO, 16-pin 150 mil | functional | $V_{IO} = 1.5 \text{ kV}_{DC}$ | n.a. | n.a. | -6 ns/+7 ns | 0.85 Ω | 0.35 Ω | 1EDF5673FXUMA1 |
| 1EDS5663H | DSO, 16-pin 300 mil | reinforced | $V_{IOTM} = 8 \text{ kV}_{pk}$ $V_{ISO} = 5.7 \text{ kV}_{rms}$ | $V_{ISOM} > 10 \text{ kV}_{pk}$ | VDE0884-10 UL1577 | -6 ns/+7 ns | 0.85 Ω | 0.35 Ω | 1EDS5663HXUMA1 |

650 V SiC MOSFET EiceDRIVER™ family product portfolio

| Product | Package | Input to output isolation | Output current (source sink) | V_{ISO} | UVLO | Orderable part number |
|------------|--------------------|---------------------------|------------------------------|--------------|------|-----------------------|
| 1EDB7275F* | DSO, 8-pin 150 mil | 3000 V_{RMS} (UL1577) | 4 A/8 A | 3 kV_{rms} | 4 V | 1EDB7275FXUMA1 |
| 1EDB8275F* | DSO, 8-pin 150 mil | 3000 V_{RMS} (UL1577) | 4 A/8 A | 3 kV_{rms} | 8 V | 1EDB8275FXUMA1 |
| 1EDB9275F* | DSO, 8-pin 150 mil | 3000 V_{RMS} (UL1577) | 4 A/8 A | 3 kV_{rms} | 14 V | 1EDB9275FXUMA1 |

Where to buy

Infineon distribution partners and sales offices:

www.infineon.com/WhereToBuy

Service hotline

Infineon offers its toll-free 0800/4001 service hotline as one central number, available 24/7 in English, Mandarin and German.

- › Germany 0800 951 951 951 (German/English)
- › China, mainland 4001 200 951 (Mandarin/English)
- › India 000 800 4402 951 (English)
- › USA 1-866 951 9519 (English/German)
- › Other countries 00* 800 951 951 951 (English/German)
- › Direct access +49 89 234-0 (interconnection fee, German/English)

* Please note: Some countries may require you to dial a code other than "00" to access this international number.
Please visit www.infineon.com/service for your country!



Mobile product catalog

Mobile app for iOS and Android.

www.infineon.com

Published by
Infineon Technologies Austria AG
9500 Villach, Austria

© 2020 Infineon Technologies AG.
All Rights Reserved.

Please note!

THIS DOCUMENT IS FOR INFORMATION PURPOSES ONLY AND ANY INFORMATION GIVEN HEREIN SHALL IN NO EVENT BE REGARDED AS A WARRANTY, GUARANTEE OR DESCRIPTION OF ANY FUNCTIONALITY, CONDITIONS AND/OR QUALITY OF OUR PRODUCTS OR ANY SUITABILITY FOR A PARTICULAR PURPOSE. WITH REGARD TO THE TECHNICAL SPECIFICATIONS OF OUR PRODUCTS, WE KINDLY ASK YOU TO REFER TO THE RELEVANT PRODUCT DATA SHEETS PROVIDED BY US. OUR CUSTOMERS AND THEIR TECHNICAL DEPARTMENTS ARE REQUIRED TO EVALUATE THE SUITABILITY OF OUR PRODUCTS FOR THE INTENDED APPLICATION.

WE RESERVE THE RIGHT TO CHANGE THIS DOCUMENT AND/OR THE INFORMATION GIVEN HEREIN AT ANY TIME.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[2EDS8155HXUMA1](#) [2EDS8255HXUMA1](#)