

## Target Applications


- Wireless charging
- Adapter
- Telecom

## Benefits

- Higher power density designs
- Higher switching frequency
- Uses OptiMOS™5 Chip
- Reduced parts count wherever 5V supplies are available
- Driven directly from microcontrollers (slow switching)
- System cost reductions

Typical values (unless otherwise specified)

| $V_{DS}$     | $V_{GS}$  | $R_{DS(on)}$ (max.) |
|--------------|-----------|---------------------|
| 60V min.     | ± 20V max | 17mΩ @ 10V          |
| $Q_{g\ tot}$ | $Q_{gd}$  | $V_{gs(th)}$        |
| 5.3nC        | 2.1nC     | 1.7V                |



| G    | D     | S      |
|------|-------|--------|
| Gate | Drain | Source |

| Base part number | Package Type   | Standard Pack |          | Orderable Part Number |
|------------------|----------------|---------------|----------|-----------------------|
|                  |                | Form          | Quantity |                       |
| IRL60HS118       | PQFN 2mm x 2mm | Tape and Reel | 4000     | IRL60HS118            |





Figure 1 Typical On-Resistance vs. Gate Voltage

Figure 2 Typical On-Resistance vs. Drain Current

**Table of Contents**

**Target Applications .....1**

**Benefits .....1**

**Ordering Table .....1**

**Table of Contents .....2**

**1 Parameters .....3**

**2 Maximum ratings, Thermal, and Avalanche characteristics .....4**

**3 Electrical characteristics .....5**

**4 Electrical characteristic diagrams .....6**

**Package Information .....12**

**Qualification Information .....14**

**Revision History .....15**

# 1 Parameters

**Table1 Key performance parameters**

| <b>Parameter</b>               | <b>Values</b> | <b>Units</b> |
|--------------------------------|---------------|--------------|
| $V_{DS}$                       | 60            | V            |
| $R_{DS(on) \max}$              | 17            | m $\Omega$   |
| $I_D @ T_C = 25^\circ\text{C}$ | 18.5          | A            |
| $I_D @ T_A = 25^\circ\text{C}$ | 10            | A            |

## 2 Maximum ratings and thermal characteristics

**Table 2 Maximum ratings (at  $T_J = 25^\circ\text{C}$ , unless otherwise specified)**

| Parameter   | Symbol         | Conditions  | Values       | Unit             |
|---|----------------|---|--------------|------------------|
| Continuous Drain Current (Silicon Limited) ⑥ ⑦  | $I_D$          | $T_{C(\text{Bottom})} = 25^\circ\text{C}, V_{GS} @ 10\text{V}$  | 18.5         | A                |
| Continuous Drain Current (Silicon Limited) ⑥  | $I_D$          | $T_{C(\text{Bottom})} = 100^\circ\text{C}, V_{GS} @ 10\text{V}$ | 13           |                  |
| Continuous Drain Current (Silicon Limited) ⑦<br>(Source Bonding Technologies Limited) | $I_D$          | $T_{C(\text{Bottom})} = 25^\circ\text{C}, V_{GS} @ 10\text{V}$  | 17           |                  |
| Continuous Drain Current (Silicon Limited) ⑤  | $I_D$          | $T_A = 25^\circ\text{C}, V_{GS} @ 10\text{V}$                   | 10           |                  |
| Pulsed Drain Current ①  | $I_{DM}$       | $T_{C(\text{Bottom})} = 25^\circ\text{C}$                       | 56           | W                |
| Maximum Power Dissipation   | $P_D$          | $T_{C(\text{Bottom})} = 25^\circ\text{C}$                       | 11.5         |                  |
| Maximum Power Dissipation   | $P_D$          | $T_{C(\text{Bottom})} = 100^\circ\text{C}$                      | 5.8          |                  |
| Maximum Power Dissipation   | $P_D$          | $T_A = 25^\circ\text{C}$  | 2.5          | V                |
| Gate-to-Source Voltage  | $V_{GS}$       | -   | $\pm 20$     | $^\circ\text{C}$ |
| Peak Soldering Temperature  | $T_P$          | -   | 270          |                  |
| Operating Junction and<br>Storage Temperature Range                                   | $T_J, T_{STG}$ | -   | -55 to + 175 |                  |

**Table 3 Thermal characteristics**

| Parameter                   | Symbol                        | Conditions | Min. | Typ. | Max. | Unit                      |
|-----------------------------|-------------------------------|------------|------|------|------|---------------------------|
| Junction-to-Case (Bottom) ④ | $R_{\theta JC}$               | -          | -    | -    | 13   | $^\circ\text{C}/\text{W}$ |
| Junction-to-Case (Top) ④    | $R_{\theta JC}$               | -          | -    | -    | 90   |                           |
| Junction-to-Ambient ⑤       | $R_{\theta JA}$               | -          | -    | -    | 60   |                           |
| Junction-to-Ambient ⑤       | $R_{\theta JA} (<10\text{s})$ | -          | -    | -    | 42   |                           |

**Table 4 Avalanche characteristics**

| Parameter                       | Symbol   | Values | Unit |
|---------------------------------|----------|--------|------|
| Single Pulse Avalanche Energy ② | $E_{AS}$ | 22     | mJ   |
| Avalanche Current ②             | $I_{AR}$ | 11     | A    |

**Notes:**

- ① Repetitive rating; pulse width limited by max. junction temperature.
- ② Starting  $T_J = 25^\circ\text{C}$ ,  $L = 0.36\text{mH}$ ,  $R_G = 50\Omega$ ,  $I_{AS} = 11\text{A}$ .
- ③ Pulse width  $\leq 400\mu\text{s}$ ; duty cycle  $\leq 2\%$ .
- ④  $R_\theta$  is measured at  $T_J$  of approximately  $90^\circ\text{C}$ .
- ⑤ When mounted on a 1 inch square PCB (FR-4). Please refer to AN-994 for more details.
- ⑥ Calculated continuous current based on maximum allowable junction temperature.
- ⑦ Current is limited to 17A by source bonding technology.

### 3 Electrical characteristics


**Table 5 Static characteristics**

| Parameter                                | Symbol                          | Conditions                       | Values |      |      | Unit  |
|--|---------------------------------|----------------------------------|--------|------|------|-------|
|  |                                 |                                  | Min.   | Typ. | Max. |       |
| Drain-to-Source Breakdown Voltage        | $V_{(BR)DSS}$                   | $V_{GS} = 0V, I_D = 250\mu A$    | 60     | -    | -    | V     |
| Breakdown Voltage Temp. Coefficient      | $\Delta V_{(BR)DSS}/\Delta T_J$ | Reference to 25°C, $I_D = 1mA$   | -      | 28   | -    | mV/°C |
| Static Drain-to-Source On-Resistance     | $R_{DS(on)}$                    | $V_{GS} = 10V, I_D = 11A$ ③      | -      | 13.3 | 17   | mΩ    |
|  |                                 | $V_{GS} = 4.5V, I_D = 5.5A$ ③    | -      | 18.3 | 23.5 |       |
| Gate Threshold Voltage                   | $V_{GS(th)}$                    | $V_{DS} = V_{GS}, I_D = 10\mu A$ | 1.1    | 1.7  | 2.3  | V     |
| Gate Threshold Voltage Temp. Coefficient | $\Delta V_{GS(th)}/\Delta T_J$  |                                  | -      | -6.8 | -    | mV°/C |
| Drain-to-Source Leakage Current          | $I_{DSS}$                       | $V_{DS} = 48V, V_{GS} = 0V$      | -      | -    | 1.0  | μA    |
| Gate-to-Source Forward Leakage           | $I_{GSS}$                       | $V_{GS} = 20V$                   | -      | -    | 100  | nA    |
|  | $I_{GSS}$                       | $V_{GS} = -20V$                  | -      | -    | 100  |       |
| Gate Resistance                          | $R_G$                           | -                                | -      | 1.2  | -    | Ω     |

**Table 6 Dynamic characteristics**

| Parameter                            | Symbol       | Conditions  | Values |      |      | Unit |
|--------------------------------------|--------------|---|--------|------|------|------|
|                                      |              |   | Min.   | Typ. | Max. |      |
| Forward Trans conductance            | gfs          | $V_{DS} = 10V, I_D = 11A$                                     | 17     | -    | -    | S    |
| Total Gate Charge                    | $Q_g$        | $I_D = 11A$<br>$V_{DS} = 30V$<br>$V_{GS} = 4.5V$<br>See Fig.8 | -      | 5.3  | 8.0  | nC   |
| Pre-Vth Gate-to-Source Charge        | $Q_{gs1}$    |   | -      | 1.5  | -    |      |
| Post-Vth Gate-to-Source Charge       | $Q_{gs2}$    |   | -      | 0.6  | -    |      |
| Gate-to-Drain Charge                 | $Q_{gd}$     |   | -      | 2.1  | -    |      |
| Gate Charge Overdrive                | $Q_{godr}$   |   | -      | 1.1  | -    |      |
| Switch Charge ( $Q_{gs2} + Q_{gd}$ ) | $Q_{sw}$     |   | -      | 2.7  | -    |      |
| Output Charge                        | $Q_{oss}$    | $V_{DS} = 30V, V_{GS} = 0V$                                   | -      | 11   | -    | nC   |
| Turn-On Delay Time                   | $t_{d(on)}$  | $V_{DD} = 30V$  | -      | 8.4  | -    | ns   |
| Rise Time                            | $t_r$        | $I_D = 11A$   | -      | 21   | -    |      |
| Turn-Off Delay Time                  | $t_{d(off)}$ | $R_G = 2.7\Omega$   | -      | 9.0  | -    |      |
| Fall Time                            | $t_f$        | $V_{GS} = 4.5V$ ③   | -      | 5.0  | -    |      |
| Input Capacitance                    | $C_{iss}$    | $V_{GS} = 0V$   | -      | 660  | -    | pF   |
| Output Capacitance                   | $C_{oss}$    | $V_{DS} = 25V$  | -      | 180  | -    |      |
| Reverse Transfer Capacitance         | $C_{rss}$    | $f = 1.0MHz$  | -      | 14   | -    |      |
| Output Capacitance                   | $C_{oss}$    | $V_{GS} = 0V, V_{DS} = 1.0V, f = 1.0MHz$                      | -      | 550  | -    |      |
| Output Capacitance                   | $C_{oss}$    | $V_{GS} = 0V, V_{DS} = 80V, f = 1.0MHz$                       | -      | 110  | -    |      |

**Table 7 Reverse Diode**

| Parameter                                  | Symbol   | Conditions  | Values |      |      | Unit |
|--|----------|---|--------|------|------|------|
|  |          |   | Min.   | Typ. | Max. |      |
| Continuous Source Current (Body Diode) ⑥ ⑦ | $I_S$    | MOSFET symbol showing the integral reverse p-n junction diode.  | -      | -    | 17   | A    |
| Pulsed Source Current (Body Diode) ①       | $I_{SM}$ |   | -      | -    | 56   |      |
| Diode Forward Voltage                      | $V_{SD}$ | $T_J = 25^\circ C, I_S = 11A, V_{GS} = 0V$ ③  | -      | -    | 1.2  | V    |
| Reverse Recovery Time                      | $t_{rr}$ | $T_J = 25^\circ C, I_F = 11A, V_{DD} = 30V$   | -      | 21   | -    | ns   |
| Reverse Recovery Charge                    | $Q_{rr}$ | $di/dt = 100A/\mu s$  | -      | 12   | -    | nC   |

### 4 Electrical characteristic diagrams





Figure 3 Typical Output Characteristics

Figure 4 Typical Output Characteristics





Figure 5 Typical Transfer Characteristics

Figure 6 Normalized On-Resistance vs. Temperature




Figure 7 Typical Capacitance vs. Drain-to-Source Voltage




Figure 8 Typical Gate Charge vs. Gate-to-Source Voltage




Figure 9 Typical Source-Drain Diode Forward Voltage




Figure 10 Maximum Safe Operating Area




Figure 11 Maximum Drain Current vs. Case Temperature

Figure 12 Typical Threshold Voltage vs. Junction Temperature




Figure 13 Maximum Avalanche Energy vs. Drain Current






Figure 14 Typical Avalanche Current vs. Pulse Width




Figure 15 Maximum Effective Transient Thermal Impedance, Junction-to-Case




Figure 16 Peak Diode Recovery  $dv/dt$  Test Circuit for N-Channel Power MOSFETs






Figure 17a Gate Charge Test Circuit

Figure 17b Gate Charge Waveform



**Figure 18a Unclamped Inductive Test Circuit**

**Figure 18b Unclamped Inductive Waveforms**




**Figure 19a Switching Time Test Circuit**

**Figure 19b Switching Time Waveforms**

## 5 Package Information

### PQFN 2 x 2 Outline Package Details




NOTES :

1. DIMENSION AND TOLERANCING CONFORM TO ASME Y14.5M-1994.
2. CONTROLLING DIMENSIONS : MILLIMETER
3. DIMENSION b APPLIES TO METALLIZED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.30 mm. FROM TERMINAL TIP.

For more information on board mounting, including footprint and stencil recommendation, please refer to application note AN-1136: <http://www.infineon.com/technical-info/appnotes/an-1136.pdf>

For more information on package inspection techniques, please refer to application note AN-1154: <http://www.infineon.com/technical-info/appnotes/an-1154.pdf>

### PQFN 2 x 2 Part Marking



Note: For the most current drawing please refer to website at : [www.irf.com/package/](http://www.irf.com/package/)

# IRL60HS118

## Package Information

### PQFN 2 x 2 Tape and Reel





TABLE 1: REEL DETAILS

| TAPE WIDTH | T        | W1                                   | W2       | W3                   | PART NO |
|------------|----------|--------------------------------------|----------|----------------------|---------|
| 8 MM       | 3 ± 0.50 | 8.4 <sup>+1.5</sup> <sub>-0.0</sub>  | 14.4 Max | 7.90 Min<br>10.9 Max | 91586-1 |
| 12 MM      | 5 ± 0.50 | 12.4 <sup>+2.0</sup> <sub>-0.0</sub> | 18.4 Max | 11.9 Min<br>15.4 Max | 91586-2 |

Note: Surface resistivity is  $\geq 1 \times 10^5$  but  $< 1 \times 10^{12}$  ohm/sq.



NOTE: The Surface Resistivity is  $10^4 - 10^8$  OHM/SQ

Note: For the most current drawing please refer to website at : [www.irf.com/package/](http://www.irf.com/package/)

## 6 Qualification Information

**Qualification Information**

|                                   |                                     |                                 |
|-----------------------------------|-------------------------------------|---------------------------------|
| <b>Qualification Level</b>        | Industrial<br>(per JEDEC JESD47F) † |                                 |
| <b>Moisture Sensitivity Level</b> | PQFN 2 mm x 2 mm                    | MSL1<br>(per JEDEC J-STD-020D)† |
| <b>RoHS Compliant</b>             | Yes                                 |                                 |

† Applicable version of JEDEC standard at the time of product release.

## Revision History

### Major changes since the last revision

| Page or Reference | Revision | Date       | Description of changes  |
|-------------------|----------|------------|---|
| All pages         | 1.0      | 2016-09-16 | <ul style="list-style-type: none"> <li>First release data sheet as Provisional.</li> </ul>  |
| All pages         | 1.1      | 2016-10-17 | <ul style="list-style-type: none"> <li>Added Switch Time test data.</li> <li>Datasheet released as Provisional.</li> </ul>  |
| All page          | 2.0      | 2017-03-29 | <ul style="list-style-type: none"> <li>Parts tested as Unique datasheet with revised current and all other tests</li> <li>Updated datasheet in new Infineon Template .</li> </ul> |
| All page          | 2.1      | 2018-05-08 | <ul style="list-style-type: none"> <li>Corrected typo on part marking from “60HS118” to “S118” to matched actual marking on the devices –page12.</li> </ul>                       |
| All page          | 2.2      | 2019-12-13 | <ul style="list-style-type: none"> <li>Features-Corrected from “IR MOSFET /OptiMOS™5” to “OptiMOS™5” to in line with the technology positioning of product –page 1.</li> </ul>    |

## Trademarks of Infineon Technologies AG

$\mu$ HVIC™,  $\mu$ IPM™,  $\mu$ PFC™, AU-ConvertIR™, AURIX™, C166™, CanPAK™, CIPOST™, CIPURSE™, CoolDP™, CoolGaN™, COOLiR™, CoolMOS™, CoolSET™, CoolSiC™, DAVE™, DI-POL™, DirectFET™, DrBlade™, EasyPIM™, EconoBRIDGE™, EconoDUAL™, EconoPACK™, EconoPIM™, EiceDRIVER™, eupec™, FCOS™, GaNpowIR™, HEXFET™, HITFET™, HybridPACK™, iMOTION™, IRAM™, ISOFACE™, IsoPACK™, LEDrivIR™, LITIX™, MIPAQ™, ModSTACK™, my-d™, NovalithIC™, OPTIGA™, OptiMOS™, ORIGA™, PowIRaudio™, PowIRstage™, PrimePACK™, PrimeSTACK™, PROFET™, PRO-SIL™, RASIC™, REAL3™, SmartLEWIS™, SOLID FLASH™, SPOC™, StrongIRFET™, SupIRBuck™, TEMPFET™, TRENCHSTOP™, TriCore™, UHVIC™, XHP™, XMC™

Trademarks updated November 2015

## Other Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

## IMPORTANT NOTICE

**Edition 2015-05-06**  
**Published by**  
**Infineon Technologies AG**  
**81726 Munich, Germany**

**© 2016 Infineon Technologies AG.**  
**All Rights Reserved.**

**Do you have a question about this document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

## Document reference

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

## WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[IRL60HS118](#)