MOSFET

StrongIRFET™



V_{DSS}	300V
$R_{DS(on)}$ typ.	33mΩ
max	40mΩ
I_D	50A

TO-247AC
IRF300P227

Applications

- UPS and Inverter applications
- Half-bridge and full-bridge topologies
- Resonant mode power supplies
- DC/DC and AC/DC converters
- OR-ing and redundant power switches
- Brushed and BLDC Motor drive applications
- Battery powered circuits

Benefits

- Improved Gate, Avalanche and Dynamic dv/dt Ruggedness
- Fully Characterized Capacitance and Avalanche SOA
- Enhanced body diode dv/dt and di/dt Capability
- Pb-Free ; RoHS Compliant ; Halogen-Free

G	D	S
Gate	Drain	Source

Halogen-Free RoHS

Base part number	Package Type	Standard Pack		Orderable Part Number
		Form	Quantity	
IRF300P227	TO-247AC	Tube	25	IRF300P227



Figure 1 Typical On-Resistance vs. Gate Voltage



Figure 2 Maximum Drain Current vs. Case Temperature

Table of Contents

1 Parameters

Table1 Key performance parameters

Parameter	Values	Units
V_{DS}	300	V
$R_{DS(on)\ max}$	40	mΩ
I_D	50	A

2 Maximum ratings and thermal characteristics

Table 2 Maximum ratings (at T_J=25°C, unless otherwise specified)

Parameter	Symbol	Conditions	Values	Unit
Continuous Drain Current	I_D	T_C = 25°C, V_{GS} @ 10V	50	A
Continuous Drain Current	I_D	T_C = 100°C, V_{GS} @ 10V	35	
Pulsed Drain Current ①	I_{DM}	T_C = 25°C	189	
Maximum Power Dissipation	P_D	T_C = 25°C	313	W
Linear Derating Factor		T_C = 25°C	2.1	W/°C
Peak Diode Recovery ③	dv/dt	T_J = 175°C, I_S = 20A, V_{DS} = 150V	6.0	V/ns
Gate-to-Source Voltage	V_{GS}	-	± 20	V
Operating Junction and Storage Temperature Range	T_J T_{STG}	-	-55 to + 175	°C
Soldering Temperature, for 10 seconds (1.6mm from case)	-	-	300	
Mounting Torque, 6-32 or M3 Screw	-	-	10 lbf·in (1.1 N·m)	-

Table 3 Thermal characteristics

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Junction-to-Case ⑦	$R_{\theta JC}$	T_J approximately 90°C	-	-	0.48	°C/W
Case-to-Sink, Flat Greased Surface	$R_{\theta CS}$	-	-	0.24	-	
Junction-to-Ambient	$R_{\theta JA}$	-	-	-	40	

Table 4 Avalanche characteristics

Parameter	Symbol	Values	Unit
Single Pulse Avalanche Energy ②	$E_{AS\ (Thermally\ limited)}$	455	mJ
Single Pulse Avalanche Energy Tested Value ⑧	$E_{AS\ (tested)}$	451	
Avalanche Current ①	I_{AR}	See Fig 16, 17, 23a, 23b	A
Repetitive Avalanche Energy ①	E_{AR}		mJ

Notes:

① Repetitive rating; pulse width limited by max. junction temperature.

② Limited by T_{Jmax}, starting T_J = 25°C, L = 1mH, R_G = 50Ω, I_{AS} = 30A, V_{GS} =10V.

③ I_{SD} ≤20A, di/dt ≤1000A/µs, V_{DD} ≤ $V_{(BR)DSS}$, T_J ≤175°C.

④ Pulse width ≤400µs; duty cycle ≤2%.

⑤ C_{oss} eff. (TR) is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

⑥ C_{oss} eff. (ER) is a fixed capacitance that gives the same energy as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

⑦ R_θ is measured at T_J approximately 90°C.

⑧ This value determined from sample failure population, starting T_J = 25°C, L= 1mH, R_G = 50Ω, I_{AS} = 30A, V_{GS} =10V.

3 Electrical characteristics

Table 5 Static characteristics

Parameter	Symbol	Conditions	Values			Unit
			Min.	Typ.	Max.	
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0V, I_D = 1mA	300	-	-	V
Breakdown Voltage Temp. Coefficient	$\Delta V_{(BR)DSS}/\Delta T_J$	Reference to 25°C, I_D = 1.0mA ①	-	0.12	-	V/°C
Static Drain-to-Source On-Resistance	$R_{DS(on)}$	V_{GS} = 10V, I_D = 30A	-	33	40	mΩ
Gate Threshold Voltage	$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = 270µA	2.0	-	4.0	V
Drain-to-Source Leakage Current	I_{DSS}	V_{DS} = 240V, V_{GS} =0V	-	-	10	µA
		V_{DS} = 240V,V_{GS} = 0V,T_J =125°C	-	-	300	
Gate-to-Source Forward Leakage	I_{GSS}	V_{GS} = 20V	-	-	100	nA
Gate Resistance	R_G		-	2.7	-	Ω

Table 6 Dynamic characteristics

Parameter	Symbol	Conditions	Values			Unit
			Min.	Typ.	Max.	
Forward Trans conductance	gfs	V_{DS} = 50V, I_D =30A	62	-	-	S
Total Gate Charge	Q_g	I_D = 30A V_{DS} = 150V V_{GS} = 10V	-	71	107	nC
Gate-to-Source Charge	Q_{gs}		-	28	-	
Gate-to-Drain Charge	Q_{gd}		-	13	-	
Total Gate Charge Sync. (Qg– Qgd)	Q_{sync}		-	58	-	
Turn-On Delay Time	$t_{d(on)}$	V_{DD} = 150V I_D = 30A R_G = 2.7Ω V_{GS} = 10V	-	16	-	ns
Rise Time	t_r		-	43	-	
Turn-Off Delay Time	$t_{d(off)}$		-	51	-	
Fall Time	t_f		-	28	-	
Input Capacitance	C_{iss}	V_{GS} = 0V V_{DS} = 50V f = 1.0MHz, See Fig.7	-	4893	-	pF
Output Capacitance	C_{oss}		-	425	-	
Reverse Transfer Capacitance	C_{rss}		-	6.6	-	
Effective Output Capacitance (Energy Related)	$C_{oss\ eff.(ER)}$	V_{GS} = 0V, V_{DS} = 0V to 240V ⑥	-	282	-	
Output Capacitance (Time Related)	$C_{oss\ eff.(TR)}$	V_{GS} = 0V, V_{DS} = 0V to 240V ⑤	-	485	-	

Table 7 Reverse Diode

Parameter	Symbol	Conditions	Values			Unit
			Min.	Typ.	Max.	
Continuous Source Current (Body Diode)	I_S	MOSFET symbol showing the integral reverse p-n junction diode. 	-	-	50	A
Pulsed Source Current (Body Diode) ①	I_{SM}		-	-	189	
Diode Forward Voltage	V_{SD}	T_J = 25°C, I_S = 30A,V_{GS} = 0V ④	-	-	1.2	V
Reverse Recovery Time	t_{rr}	T_J = 25°C	-	140	-	ns
		T_J = 125°C	-	199	-	
Reverse Recovery Charge	Q_{rr}	T_J = 25°C	-	313	-	nC
		T_J = 125°C	-	811	-	
Reverse Recovery Current	I_{RRM}	T_J = 25°C	-	3.1	-	A
		T_J = 125°C	-	5.5	-	

V_{DD} = 150V
I_F = 30A,
di/dt = 100A/µs ④

4 Electrical characteristic diagrams



Figure 3 Typical Output Characteristics



Figure 4 Typical Output Characteristics



Figure 5 Typical Transfer Characteristics



Figure 6 Normalized On-Resistance vs. Temperature

Electrical characteristic diagrams



Figure 7 Typical Capacitance vs. Drain-to-Source Voltage

Figure 8 Typical Gate Charge vs. Gate-to-Source Voltage



Figure 9 Typical Source-Drain Diode Forward Voltage



Figure 10 Maximum Safe Operating Area



Figure 11 Drain-to-Source Breakdown Voltage



Figure 12 Typical Coss Stored Energy

Electrical characteristic diagrams



Figure 13 **Typical On-Resistance vs. Drain Current**

Figure 14 **Threshold Voltage vs. Temperature**



Figure 15 **Maximum Effective Transient Thermal Impedance, Junction-to-Case**



Figure 16 Avalanche Current vs. Pulse Width



Figure 17 Maximum Avalanche Energy vs. Temperature

Notes on Repetitive Avalanche Curves , Figures 16, 17:
(For further info, see AN-1005 at www.infineon.com)

1.Avalanche failures assumption:
Purely a thermal phenomenon and failure occurs at a temperature far in excess of T_{jmax}. This is validated for every part type.

2. Safe operation in Avalanche is allowed as long asT_{jmax} is not exceeded.

3. Equation below based on circuit and waveforms shown in Figures 23a, 23b.

4. $P_{D\ (ave)}$ = Average power dissipation per single avalanche pulse.

5. BV = Rated breakdown voltage (1.3 factor accounts for voltage increase during avalanche).

6. I_{av} = Allowable avalanche current.

7. DT = Allowable rise in junction temperature, not to exceed T_{jmax} (assumed as 25°C in Figure 15, 16).

t_{av} = Average time in avalanche.

D = Duty cycle in avalanche = tav ·f

$Z_{thJC}(D, t_{av})$ = Transient thermal resistance, see Figures 14)

$$PD\ (ave) = 1/2\ (1.3 \cdot BV \cdot I_{av}) = \Delta T / Z_{thJC}$$

$$I_{av} = 2\Delta T / [1.3 \cdot BV \cdot Z_{th}]$$

$$E_{AS\ (AR)} = P_{D\ (ave)} \cdot t_{av}$$



Figure 18 Typical Recovery Current vs. dif/dt



Figure 19 Typical Recovery Current vs. dif/dt



Figure 20 Typical Stored Charge vs. dif/dt



Figure 21 Typical Stored Charge vs. dif/dt



Figure 22 Peak Diode Recovery dv/dt Test Circuit for N-Channel HEXFET™ Power MOSFETs



Figure 23a Unclamped Inductive Test Circuit



Figure 23b Unclamped Inductive Waveforms



Figure 24a Switching Time Test Circuit



Figure 24b Switching Time Waveforms



Figure 25a Gate Charge Test Circuit



Figure 25b Gate Charge Waveform

5 Package Information

TO-247AC Package Outline (Dimensions are shown in millimeters (inches))



NOTES:

1. DIMENSIONING AND TOLERANCING AS PER ASME Y14.5M 1994.
2. DIMENSIONS ARE SHOWN IN INCHES.
3. CONTOUR OF SLOT OPTIONAL.
4. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED .005" (0.127) PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
5. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS D1 & E1.
6. LEAD FINISH UNCONTROLLED IN L1.
7. øP TO HAVE A MAXIMUM DRAFT ANGLE OF 1.5 ° TO THE TOP OF THE PART WITH A MAXIMUM HOLE DIAMETER OF .154 INCH.
8. OUTLINE CONFORMS TO JEDEC OUTLINE TO-247AC .

SYMBOL	DIMENSIONS				NOTES
	INCHES		MILLIMETERS		
	MIN.	MAX.	MIN.	MAX.	
A	.183	.209	4.65	5.31	
A1	.087	.102	2.21	2.59	
A2	.059	.098	1.50	2.49	
b	.039	.055	0.99	1.40	
b1	.039	.053	0.99	1.35	
b2	.065	.094	1.65	2.39	
b3	.065	.092	1.65	2.34	
b4	.102	.135	2.59	3.43	
b5	.102	.133	2.59	3.38	
c	.015	.035	0.38	0.89	
c1	.015	.033	0.38	0.84	
D	.776	.815	19.71	20.70	4
D1	.515	–	13.08	–	5
D2	.020	.053	0.51	1.35	
E	.602	.625	15.29	15.87	4
E1	.530	–	13.46	–	
E2	.178	.216	4.52	5.49	
e	.215 BSC		5.46 BSC		
øk	.010		0.25		
L	.559	.634	14.20	16.10	
L1	.146	.169	3.71	4.29	
øP	.140	.144	3.56	3.66	
øP1	–	.291	–	7.39	
Q	.209	.224	5.31	5.69	
S	.217 BSC		5.51 BSC		

LEAD ASSIGNMENTS

HEXFET

1.– GATE
2.– DRAIN
3.– SOURCE
4.– DRAIN

IGBTs, CoPACK

1.– GATE
2.– COLLECTOR
3.– EMITTER
4.– COLLECTOR

DIODES

1.– ANODE/OPEN
2.– CATHODE
3.– ANODE

TO-247AC Part Marking Information

EXAMPLE: THIS IS AN IRFPE30
WITH ASSEMBLY
LOT CODE 5657
ASSEMBLED ON WW 35, 2001
IN THE ASSEMBLY LINE "H"

Note: "P" in assembly line position
indicates "Lead-Free"



TO-247AC package is not recommended for Surface Mount Application.

6 Qualification Information

Qualification Information

Qualification Level	Industrial (per JEDEC JESD47F) †	
Moisture Sensitivity Level	TO-247AC	N/A
RoHS Compliant	Yes	

† Applicable version of JEDEC standard at the time of product release.

Revision History

Major changes since the last revision

Page or Reference	Revision	Date	Description of changes
All pages	1.0	2017-02-27	• First release data sheet.
All pages	1.1	2017-07-20	• Updated @ 25c =20A on Avalanche Current vs. Pulse Width fig 16 on page10 • Added DV/DT = 6V/ns, Di/Dt = 1000A/us, Tjmax = 175C, VDS = 150V, Id = 20A on page 4 • Added I_{RRM} = 5.5A @ 125c on page 5.
All pages	2.0	2017-11-14	• First release final datasheet.
All pages	2.1	2020-01-07	• Update from “IR MOSFT/StrongIRFET™” to “StrongIRFET™” -all pages • Update Package picture –page1

Edition 2015-05-06
Published by
Infineon Technologies AG
81726 Munich, Germany

Do you have a question about this document?
Email: erratum@infineon.com

Document reference

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics (“Beschaffenheitsgarantie”) .

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer’s compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer’s products and any use of the product of Infineon Technologies in customer’s applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer’s technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office **(www.infineon.com).**

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies’ products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Infineon:
IRF300P227